# Technical Data Hydraulic crawler crane

# **Basic machine with undercarriage**



## **Dimensions**

#### mm

Α	Width of superstructure	3000
A <sub>1</sub>	Width of superstructure with walk way	3440
С	Height of basic machine	3450
D	Tail reach	4530
	Tail swing radius	4560
D <sub>1</sub>	Tail reach A-frame	5090
F	Distance between rear end of crawler and	
-	outside of counterweight	1590
G	Overall length of superstructure with	
ŭ	lowered A-frame	11860
	Ground alconomy of hears fact simpl	1000
н	Ground clearance of boom foot pivot	1920
	Ground clearance of superstructure	1370
$\mathbf{L}$	Wheel base (centre idler to centre tumbler)	4850
$\mathbf{L}_{1}$	Distance from centre of rotation to	
	centre of tumbler	2425
м	Length of crawlers	5890
Р	Height of crawlers	1260
Q	Ground clearance of crawler	<b>400</b>
R	Distance from edge of horizontal boom foot	
	to crawler	3820
S	Ground clearance of horizontal boom foot	1320
т	Length of superstructure	7280

#### mm

X Distance from centre of rota	tion to end of cab 2750
N Width of track shoes	700 800 900 1000
W <sub>1</sub> Track width retracted	2600 2600 2600 2600
W Track width extended	3900 3900 3900 3900
<b>B</b> Crawler width extended	4600 4700 4800 4900

HS 853 HD

B<sub>1</sub> Crawler width retracted 3300 3400 3500 3600

# **Operating Weight and Ground Pressure**

The operating weight includes the basic unit with B7 crawler tracks, 2 main winches 25 t and 11 m boom, consisting of A-frame, boom foot (5.5 m), boom head (5.5 m) and 22 t counterweight + 2 t add. counterweight. All systems are ready.

		with 700 mm flat track shoes	78.4 t – 1.08 kg/cm <sup>2</sup>
Length of crawlers	<b>5890</b>	with 800 mm flat track shoes	79.3 t – 0.96 kg/cm <sup>2</sup>
Height of crawlers	1260	with 900 mm flat track shoes	80.2 t – 0.86 kg/cm <sup>2</sup>
Ground clearance of crawler	<b>400</b>	with 1000 mm flat track shoes	81.2 t – 0.79 kg/cm <sup>2</sup>
Distance from edge of horizontal boom foot		with 700 mm 3-web shoes	76.4 t – 1.05 kg/cm <sup>2</sup>
to crawler	3820	with 800 mm 3-web shoes	76.8 t – 0.93 kg/cm <sup>2</sup>
Ground clearance of horizontal boom foot	1320	with 900 mm 3-web shoes	77.5 t – 0.83 kg/cm <sup>2</sup>
Length of superstructure	7280	with 1000 mm 3-web shoes	78.1 t – 0.75 kg/cm <sup>2</sup>





# **Basic machine**

with HD undercarriage, without counterweight, L 6 cylinder Liebherr diesel engine, 2 x 25 t winches A–frame, boom foot section with boom back stops and pulley block with equalizer

3-web shoes	mm	700	800	900	1000
Width	mm	3300	3400	3500	3600
Weight	t	47.7	48.4	<b>49.0</b>	<b>49.6</b>
L Length	mm	11860	11860	11860	11860
H Height	mm	3450	3450	3450	3450

eight	Basic	<b>Additional</b>		
mm	1240	1040		
kg	22000	2000		
mm	3000	1070		
mm	1430	250		
	mm kg mm	mm 1240 kg 22000 mm 3000		

## **Pulley block with equalizer**

Width	mm	<b>490</b>
Weight	kg	300
L Length	mm	1010
H Height	mm	660

## **A**-frame

Width	mm	530
Weight	kg	790
L Length	mm	4830
H Height	mm	1210

	Basic
mm	1400
kg	1280
mm	5680
mm	1340
	kg mm

Tubular b	oom extension	3 m	6 m	9 m
Width	mm	1400	1400	1400
Weight*	kg	420	670	930
L Length	mm	3140	6140	9140
H Height	mm	1220	1220	1220

Boom head	1	Crane	Dragline		
Width	mm	1400	1400		
Weight*	kg	1600	1550		
L Length	mm	6070	6160		
H Height	mm	1940	2030		

\*) including stay ropes

# **Transport dimensions and weights**

# Engine

Water cooled, in-line 6 cylinder Liebherr diesel engine, turbocharged with intercooler, model D 926 TI-E, power rating according to ISO 9249, 220 kW (300 hp) at 1800 rpm. **Ontion**:

Water cooled, V 8 cylinder Liebherr diesel engine, turbo charged with intercooler, model D 9408 TI-E, power rating according to ISO 9249, 400 kW (544 hp) at 1900 rpm. The automatic limiting load control adapts perfectly the power of the main users to the present engine speed. The temperature and engine speed controlled cooling system saves energy and reduces the noise emission.

Fuel Tank: 800 l capacity with continuous level indicator and reserve warning.

# **Hydraulic System**

The main pumps are operated by a distributor gearbox. Axial piston displacement pumps work in closed and open circuits supplying oil only when needed (flow control on demand). To minimize peak pressure an automatically working pressure cut off is integrated. This spares pumps

and saves energy. Winch 1 and 2: Axial piston displacement pumps (swash plate design) with 324 l/min. each. Crawlers: Axial piston displacement pumps (swash plate

design) with 2 x 296 l/min

Swing gear: Axial piston displacement pump (swash plate design) with 296 l/min.

Boom hoist: Axial piston displacement pump (swash plate design) with 296 l/min.

Max. working pressure: 350 bar.

Hydraulic oil tank capacity: 650 l

The hydraulic oil is cleaned through electronically controlled pressure and return filters.

Possible contamination is signalled in the cabin. The use of synthetic environmentally friendly oils is possible. Ready made hydraulic retrofit kits are available to

customize requirements e.g. powering casing oscillators, auger drills etc.

# Winches

which options:					
Line pull (nom. load)	120 kN	160 kN	200 kN	250 kN	
<b>Rope diameter :</b>	<b>24 mm</b>	<b>26 mm</b>	<b>30 mm</b>	<b>34 mm</b>	
Drum diameter :	525 mm	550 mm	630 mm	<b>750 mm</b>	
Rope speed m/min	0–136	0-114	0–92	0-72	
Rope capacity					

46.5 m 46.5 m **1st laver** 45 m 48.3m The winches are outstanding in their compact design and easy assembly.

Propulsion is via a planetary gearbox in oil bath. Load support by the hydraulic system; additional safety factor provided by a spring loaded, multi-disc holding brake. Clutch and braking functions on the freefall system are provided by a compact designed, low wear and maintenance free multi-disc brake. The dragline and hoist winches use pressure controlled, variable flow hydraulic motors. This system features sensors that automatically adjust oil flow to provide max. winch speed depending on load.

Working with 2 rope clamshell, the oil motors distribute the load to both winches providing speed compensation, even when working in different rope layers. **Option:** 

Crane winch 80 kN (8 t) - without clutch, but with multi-disc holding brake.

#### 5))) **Noise emission**

Special sound proofing results in a very low noise pressure level of 76 dB (A) at 16 m radius.

# 🖄 Equipment

Lattice boom of tubular construction up to 65 m. universal boom head with interchangeable rope pulleys. Modular designed equipment for operation as crane, dragline or clamshell

For dragline operation, a rotating fairlead is fitted into the boom foot. This minimizes rope angle to drum, which results in lower rope wear. Jibs and fly jibs of different lengths are available on request.

# ↔ Swing Drive

Consists of single row ballbearing with external teeth for lower tooth flank pressure, fixed axial piston hydraulic motor, spring loaded and hydraulically released multi-disc holding brake, planetary gearbox and pinion. Free swing with hydraulic moment control reduces wear to a minimum, because rotation moment is sustained through the hydraulic system by the diesel engine.

A multi-disc holding brake acts automatically at zero swing motion.

Swing speed from 0 – 4.7 rpm continuously variable, selector for 3 speed ranges to increase swing precision.



The track width of the undercarriage is changed hydraulically

Propulsion through axial piston motor, hydraulically released spring loaded multi-disc brake, maintenance free crawler tracks, hydraulic chain tensioning device. Flat or 3 - web track shoes. Drive speed 0 - 1.4 km/h. **Option:** 

2 speed hydraulic motor for higher travel speed.

# Control

The control system - developed and manufactured by Liebherr - is designed to withstand extreme temperature and the many heavy-duty construction tasks for which this crane has been designed. Complete machine operating data are displayed on a high resolution monitor screen. To ensure clarity of the information on display, different levels of data are shown in en-larged lettering and symbols. Control and monitoring of the sensors are also handled by this high technology system. Error indications are automatically displayed on the monitor in English. The crane is equipped with proportional control for all movements, which can be carried out simultaneously.

A special "Interlock" control system is also optionally available. It is designed for power lifting of the dragline bucket without using the grab winch brake.

An additional option is also the so-called "Redundant" control system, which allows restricted operation of the machine in the event of a failure on the electronic base control or its sensors.

On request, Liebherr also offers special custom designed control systems for free fall winches.

The crane is operated with 2 multi-directional joysticks, right for winch I and boom hoist drive, left for winch II and slewing gear. Crawler control is actuated with the two central foot pedals. Additionally, hand levers can be attached to the pedals. **Options:** 

Both main winches with double-T levers

- **Special demolition control system**
- **MDE: Machine data recording**
- **PDE: Process data recording**

# **Boom hoist drive**

Twin drum with internally located planetary gearbox, axial piston hydraulic motor and hydraulically released spring loaded multi-disc brake.

Max. line pull 2x 50 kN. Rope diameter: 18 mm Max. line speed: 45 m/min. Counterweight lifting with boom hoist. Two speed boom hoist option

# **Technical Description**

## 24 t counterweight



## **Scope of delivery:**

- Basic machine with corresponding track shoes
- Second swing drive with free swing
- A-frame
- Boom foot 5.5 m
- Boom extension 3 m tubular steel
  Boom extension 6 m tubular steel
- Boom extension 9 m tubular steel
- Boom head 5.5 m
- Boom head with interchangeable pulleys
- Main winches according to specification
- Drag rope should be 2 mm below nominal diameter
- Corresponding fair lead
- Corresponding ropes optional
- Dragline bucket optional

Capacitie	Capacities in metric tons for boom lengths from 14 m to 29 m Counterweight 24 t																	
	14 m				17 m		20 m			23 m		26 m			29 m			
	С	J		С	J		С	J		С	J		С	J		С	J	
α°	m	m	t	m	m	t	m	m	t	m	m	t	m	m	t	m	m	t
45	12.0	11.3	17.4	14.1	13.4	14.0	16.2	15.5	11.6	18.3	17.6	8.2	20.5	19.7	8.2	22.6	21.9	7.1
40	12.8	10.4	16.0	15.1	12.3	12.9	17.4	14.3	10.6	19.6	16.2	7.5	21.9	18.1	7.5	24.2	20.0	6.4
35	13.5	9.5	15.0	15.9	11.2	12.0	18.4	12.9	9.8	20.8	14.6	6.9	23.3	16.4	6.9	25.7	18.1	5.8
30	14.1	8.5	14.1	16.7	10.0	11.3	19.3	11.5	9.2	21.9	13.0	6.4	24.5	14.5	<b>6.4</b>	27.0	16.0	5.4
25	14.6	7.5	13.3	17.3	8.7	10.5	20.0	10.0	8.6	22.7	11.3	5.9	25.4	12.5	5.9	28.2	13.8	5.0

Max. capacities in metric tons do not exceed 75 % of tipping load

# Dragline equipment

## 24 t counterweight



## **Scope of delivery:**

- Basic machine with corresponding track shoes
- A-frame
- Boom foot (5.5 m)
- Boom extension 3 m tubular steel
- Boom extension 6 m tubular steel
- Boom extension 9 m tubular steel
- Boom head 5.5 m
- Boom head with interchangeable pulleys
- Stay ropes according to boom length
- Main winches according to specification
- Tagline winch
- Corresponding ropes optional
- Clamshell optional
- Hoist limit switch
- Load moment limitation
- 4-rope clamshell on request

- Working diagram C = Radius / dumping radius
- J = Height of boom head sheave
- centre above ground level
- K = Length of clamshell (depending on type and capacity of bucket)

Capacities in metric tons for boom lengths from 14 m to 29 m: Counterweight 24 t																		
	14 m			17 m			20 m			23 m			26 m					
	С	J		С	J		С	J		С	J		С	J		С	J	
α°	m	m	t	m	m	t	m	m	t	m	m	t	m	m	t	m	m	t
65	8.1	13.9	26.3	9.4	16.6	21.5	10.7	19.3	18.0	11.9	22.1	15.4	13.2	24.8	13.3	14.5	27.5	11.7
60	9.2	13.4	22.2	10.7	16.0	18.0	12.2	18.6	15.0	13.7	21.2	12.8	15.2	23.8	11.0	16.7	<b>26.4</b>	9.6
55	10.2	12.7	19.3	11.9	15.2	15.6	13.6	17.7	13.0	15.3	20.1	11.0	17.0	22.6	9.4	18.8	25.0	8.1
50	11.1	12.0	17.1	13.0	14.3	13.8	15.0	16.6	11.4	16.9	18.9	9.6	18.8	21.2	8.2	20.8	23.5	7.1
45	12.0	11.3	15.5	14.1	13.4	12.5	16.2	15.5	10.3	18.3	17.6	8.6	20.5	19.7	7.3	22.6	21.9	6.3
40	12.8	10.4	14.3	15.0	12.3	11.4	17.4	14.3	9.4	19.6	16.2	7.9	21.9	18.1	6.6	24.2	20.0	5.7
35	13.5	9.5	13.3	15.9	11.2	10.6	18.4	12.9	8.7	20.8	14.6	7.3	23.3	16.4	6.1	25.7	18.1	5.2
30	14.0	8.5	12.6	16.7	10.0	10.0	19.3	11.5	8.2	21.9	13.0	6.8	24.5	14.5	5.7	27.0	16.0	4.8
25	14.6	7.5	11.8	17.3	8.7	9.4	20.0	10.0	7.6	22.7	11.3	6.3	25.4	12.5	5.3	28.2	13.8	4.4

Max. capacities in metric tons do not exceed 66.7 % of tipping load.

Load diagram restricted by safety factors of standard ropes:

Winches	120 kN	160 kN	200 kN	250 kN
Rope diameter	<b>24 mm</b>	<b>26 mm</b>	<b>30 mm</b>	<b>34 mm</b>
Calc. breaking load	524 kN	613 kN	820 kN	1051 kN
1-rope clamshell	<b>9.5 t</b>	11.1 t	14.8 t	19.0 t
2–rope clamshell	14.4 t	16.8 t	22.5 t	28.9 t

# **Clamshell equipment**

# 24 t Counterweight



### **Scope of delivery:**

Basic machine with corresponding track shoes

- A-frame
- Pulley block
- Boom foot 5.5 m
- Boom extension 3 m tubular steel
- Boom extension 6 m tubular steel
- Boom extension 9 m tubular steel
- Boom head 5.5 m with interchangeable pulleys
- Stay ropes according to boom length
- Main winches according to specification
- Hoisting limit switch
- Load moment limitation
- Corresponding hook block optional

### **Remarks**:

- 1. The lifting capacities are valid for wide track.
- 2. The lifting capacities stated do not exceed 75 % of the tipping load.
- 3. The lifting capacities are indicated in metric tons with unlimited swing (360 degrees).
- 4. The weight of the lifting device must be deducted to arrive at the net lifting capacity.
- 5. Working radii are measured from centre of swing.
- 6. Crane standing on firm, horizontal ground.
- 7. Indicated values on load chart are affected by off-lead operation, wind speeds, load under slew and stop/go movements.
- 8. The max. lifting capacity of the crane may be reduced dependent on the admissible rope safety regulations of each country.

# **Crane configuration**

Capacities in metric tons for boom lengths from 11 m to 65 m: Counterweight 24 t																			
Boom length	11m	14m	17m	<b>20</b> m	23m	26m	<b>29</b> m	32m	35m	38m	<b>41m</b>	<b>44</b> m	<b>47</b> m	<b>50</b> m	53m	56m	<b>59m</b>	62m	65m
Radius in (m)	t	t	t	t	t	t	t	t	t	t	t	t	t	t	t	t	t	t	t
3.5	80.0																		
4.0	80.0	78.6																	
4.5	74.0	73.9	73.7																
5.0	61.9	61.9	61.9	61.9															
5.5	52.8	52.8	52.8	52.7	52.7	52.7													
6.0	46.0	46.0	45.9	45.9	45.9	45.8	45.8												
6.5	40.7	40.6	40.6	40.6	40.5	40.5	40.4	40.4											
7.0	36.4	36.4	36.4	36.3	36.3	36.2	36.2	36.1	36.0										
7.5	30.1	32.9	32.9	32.9	32.8	32.7	32.7	32.6	32.5	32.5									
8.0	25.6	30.1	30.0	30.0	29.9	29.8	29.8	29.7	29.6	29.6	29.5	27.3							
9.0	22.2	25.5	25.5	25.4	25.4	25.3	25.2	25.1	25.1	25.0	24.9	24.8	22.8	19.9					
10.0	19.5	22.1	22.1	22.0	22.0	21.9	21.8	21.7	21.6	21.6	21.5	21.4	21.3	19.2	16.7	14.9			
11.0		19.5	19.5	19.4	19.3	19.2	19.2	19.1	19.0	18.9	18.8	18.7	18.6	18.5	16.1	14.4	12.0	10.2	8.8
12.0		17.4	17.3	17.3	17.2	17.1	17.0	16.9	16.9	<b>16.8</b>	16.7	16.6	16.5	16.4	15.5	13.8	11.5	9.7	8.3
13.0		15.6	15.6	15.5	15.5	15.4	15.3	15.2	15.1	15.0	14.9	14.8	14.7	14.7	14.6	13.3	10.9	9.2	7.8
14.0		14.2	14.2	14.1	14.0	13.9	13.9	13.8	13.7	13.6	13.5	13.4	13.3	13.2	13.1	12.9	10.3	8.7	7.3
15.0			12.9	12.9	12.8	12.7	12.6	12.5	12.4	12.4	12.3	12.2	12.1	12.0	11.9	11.8	9.8	8.2	6.9
16.0			11.9	11.8	11.7	11.7	11.6	11.5	11.4	11.3	11.2	11.1	11.0	10.9	10.8	10.7	9.4	7.7	6.5
17.0			11.0	10.9	10.8	10.8	10.7	10.6	10.5	10.4	10.3	10.2	10.1	10.0	9.9	9.8	8.9	7.3	6.1
18.0				10.1	10.0	10.0	9.9	9.8	9.7	9.6	9.5	9.4	9.3	9.2	9.1	9.0	8.4	6.9	5.8
19.0				9.4	9.3	9.3	9.2	9.1	9.0	8.9	8.8	8.7	8.6	8.5	8.4	8.3	8.0	6.5	5.4
20.0				8.8	8.7	8.6	8.6	8.5	8.4	8.3	8.2	8.1	8.0	7.9	7.8	7.6	7.5	6.2	5.1
22.0					7.7	7.6	7.5	7.4	7.3	7.2	7.1	7.0	6.9	6.8	6.7	6.6	6.5	5.6	4.5
24.0						6.7	6.6	6.5	6.4	6.3	6.2	6.1	6.0	5.9	5.8	5.7	5.6	5.0	4.0
26.0						6.0	5.9	5.8	5.7	5.6	5.5	5.4	5.3	5.2	5.1	5.0	4.9	4.5	3.6
28.0							5.3	5.2	5.1	5.0	4.9	4.8	4.7	4.6	4.5	4.4	4.2	4.1	3.1
30.0								4.6	4.6	4.5	4.3	4.2	4.1	4.0	3.9	3.8	3.7	3.6	2.8
32.0									4.1	4.0	3.9	3.8	3.7	3.6	3.5	3.4	3.3	3.1	2.5
34.0									3.7	3.6	3.5	3.4	3.3	3.2	3.1	3.0	2.8	2.7	2.1
36.0										3.2	3.1	3.0	2.9	2.8	2.7	2.6	2.5	2.4	1.8
38.0										2.9	2.8	2.7	2.6	2.5	2.4	2.3	2.2	2.1	1.5
40.0											2.5	2.4	2.3	2.2	2.1	2.0	1.9	1.8	1.3
42.0													2.1	2.0	1.9	1.8	1.6	1.5	1.1
44.0													1.8	1.7	1.6	1.5	1.4	1.3	0.8
46.0													1.6	1.5	1.4	1.3	1.2	1.1	
48.0														1.3	1.2	1.1	1.0		

Up to 59 m of boom length self erection is possible. The necessary hoistrope reeving arrangement has to be provided according to the load diagram in the cabin.

Optimal boom configuration for boom lengths between 11 m to 65 m:																				
	Length		Number of boom extensions																	
Boom foot	5.5 m	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
Boom extension	3.0 m		1			1			1			1			1			1		
Boom extension	6.0 m			1			1			1			1			1			1	
Boom extension	9.0 m				1	1	1	2	2	2	3	3	3	4	4	4	5	5	5	6
Boom head	5.5 m	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
<b>Boom length in meters</b>		11	14	17	20	23	26	29	32	35	38	41	44	47	50	53	56	59	62	65

# Load diagram for crane configuration



# **Casing oscillator**

Winch options	2 x 20 t	2 x 25 t	Free fa loaded
Line pull 2 x	400 kN	500 kN	Simult
Line speed 1st layer (m/min)	0–92	0-72	Hydra q = 2 x
Drilling diameter	2000 mm	2000 mm	P = 300 Mecha
Chisel weight	12 t	16 t	undero
Max. capacity with boom posit longitudinal direction of under		(option Hoistin	
at 7.5 m radius.	37.8 t	37.8 t	oscilla

Free fall winches with maintenance free, spring loaded multi disc brake working in an oil bath. Simultaneous working of both winches is assured through our hydraulic system. Hydraulic supply for casing oscillator q = 2 x 296 l/min. P = 300 bar max. Mechanical connection casing oscillator on undercarriage. Automatic operation for one and two rope grabs. (optional) Hoisting speed will have priority over the casing oscillator while main winches are activated.

LIEBHERR-WERK NENZING GMBH,

P.O. Box 10, A–6710 Nenzing / Austria / Europe Telephone (0043) 5525 – 606 – 473, Telefax (0043) 5525 – 606 – 499 Email: info@lwn.liebherr.com