
Below zero, zero problem.


FrostProtect guarantees flawless operation, even in ambient temperatures as low as -15°C .

LIEBHERR


Freezers

LIEBHERR

Frost
Protect



Frost
Protect




When below zero is a big plus: FrostProtect.

No room for a freezer in the kitchen
or other heated areas in your home?

We have some great news: With
FrostProtect, all components are
designed for temperatures as low
as $-15\text{ }^{\circ}\text{C}$. If the ambient temperature
falls below $0\text{ }^{\circ}\text{C}$, our freezers continue
working just as efficiently, saving just
as much energy and your frozen food
is just as well protected.

So you can put them in unheated
rooms like a garden shed or garage
and have more room for more
important things.



**New: FrostProtect now in
NoFrost models with
BluPerformance technology**

All of the refrigeration technology is in the appliance base.
So appliances with BluPerformance with the same outer
dimensions have a much greater usable volume. Meaning
you have noticeably more space for your food. And we were
able to further improve energy efficiency thanks to improved
ventilation and extraction in the base.

No
Frost

Convenience of never having to defrost.

Smart
Frost

Much less frequent defrosting.

Stop
Frost

Less frequent defrosting and easier opening
of the chest lid thanks to no vacuum.

Freezers

No Frost

← 60 →

BLU
Performance

BluRoX



FNC 5277
Peak



Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

277 l

185.5 / 59.7 / 67.5

Fig. front page



FNSdd 5257
Prime



Total volume¹

Exterior dimensions in cm (H/W/D)

277 l

185.5 / 59.7 / 67.5

Side walls: Silver / door: Stainless steel w / SmartSteel



FND 525i
Prime



Total volume¹

Exterior dimensions in cm (H/W/D)

277 l

185.5 / 59.7 / 67.5



FNB 5056
Prime



Total volume¹

Exterior dimensions in cm (H/W/D)

238 l

165.5 / 59.7 / 65.5

Available Q2 2023



FND 5056
Prime



Total volume¹

Exterior dimensions in cm (H/W/D)

238 l

165.5 / 59.7 / 67.5



FND 4655
Prime



Total volume¹

Exterior dimensions in cm (H/W/D)

199 l

145.5 / 59.7 / 67.5



FND 4254
Prime



Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

160 l

125.5 / 59.7 / 67.5



FNE 5227
Plus



Total volume¹

Exterior dimensions in cm (H/W/D)

277 l

185.5 / 59.7 / 67.5



FNE 5026
Plus



Total volume¹

Exterior dimensions in cm (H/W/D)

238 l

165.5 / 59.7 / 67.5



FNE 4625
Plus



Total volume¹

Exterior dimensions in cm (H/W/D)

199 l

145.5 / 59.7 / 67.5



FNF 4204
Pure



Total volume¹

Exterior dimensions in cm (H/W/D)

160 l

125.5 / 59.7 / 67.5

Freezers

No Frost

← 70 →

BLU
Performance



FNC 7277
Peak



Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

363 l

185.5 / 69.7 / 76.0



FNC 7227
Plus



Total volume¹

Exterior dimensions in cm (H/W/D)

363 l

185.5 / 69.7 / 76.0



FNC 7277

Table-height freezers

Smart Frost



GP 1486
Premium



Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

102 l

85.1 / 60.2 / 62.8



GPesf 1476
Premium



Total volume¹

Exterior dimensions in cm (H/W/D)

102 l

85.1 / 60.2 / 61.0

Side walls: Silver / door: Stainless steel w / SmartSteel



GP 1476
Premium



Total volume¹

Exterior dimensions in cm (H/W/D)

102 l

85.1 / 60.2 / 62.8



GP 1376
Premium



Total volume¹

Exterior dimensions in cm (H/W/D)

102 l

85.1 / 55.3 / 62.4



Gsl 1223
Comfort



Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

97 l

85.1 / 55.3 / 62.4

Side walls: Silver
door: Silver



G 1223
Comfort



Total volume¹

Exterior dimensions in cm (H/W/D)

97 l

85.1 / 55.3 / 62.4



GP 1213
Comfort



Total volume¹

Exterior dimensions in cm (H/W/D)

97 l

85.1 / 55.3 / 62.4



GX 823
Comfort



Total volume¹

Exterior dimensions in cm (H/W/D)

68 l

63.1 / 55.3 / 62.4

Chest freezers

Stop Frost



Cff 2500
Pure



Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

497 l

82.5 / 167.5 / 70.2



Cff 2080
Pure



Total volume¹

Exterior dimensions in cm (H/W/D)

353 l

82.5 / 125.5 / 70.2



Cff 1870
Pure



Total volume¹

Exterior dimensions in cm (H/W/D)

281 l

82.5 / 104.5 / 70.2

¹ In accordance with regulation EU 2019/2016, we indicate the total volume to the nearest integer (rounded off).
The term "volume" refers to the term "capacity", which is used in the current Regulation.

You can find the entire range of efficiency ratings on the reverse side. According to (EU) 2017/1369 6a.

For complete model descriptions, visit home.liebherr.com



BluRoX



The future is circular.

The newly developed BluRoX technology from Liebherr is going to change the market for refrigerators and freezers sustainably. Instead of polyurethane foam, we use a much more effective form of cold insulation: a vacuum. Finely ground lava stone, known as perlite, stabilises the vacuumed components.

The first freezer using vacuum perlite technology in the door and built for the circular economy of re-use has already been certified with the “B” efficiency rating. And with every new BluRoX appliance we design, we will set new standards in terms of energy efficiency and capacity – and humanity and the environment will be the winners.




To learn more about this exciting technology and the many advantages of BluRoX, visit:
home.liebherr.com/blurox



FNb 5056
Available from the
2nd quarter of 2023



The current energy labels for electrical appliances



1. QR code to identify the product in the EU database EPREL (European Product Registry for Energy Labelling).
2. The model identifier for manual identification of the product in the EU database EPREL, using the article number for example.
3. The new efficiency scale from “A” to “G”. However, “G” is only intended for wine cabinets.
4. The total volume* of all freezer compartments.
5. The sum of the volume* of all cold-storage and refrigerator compartments.
6. The noise level is now classified into classes “A” to “D”.

* The term “volume” is defined in current regulation EU 2019/2016.

home.liebherr.com

Subject to technical changes, errors and deviations in image and text. Deviations in colour due to media used. For latest available data, see home.liebherr.com. Printed in Germany by WPP Offsetdruck GmbH 7901 672-00/02.23 EN/GB

