

EU declaration of conformity regarding energy consumption according to (EU) 2019/2019

Energy Label (EU) 2019/2016

Applied standard EN 62552:2020

## Product Information Sheet

|                               |   |
|-------------------------------|---|
| Supplier's name or trade mark | LIEBHERR  |
| Supplier's address            | Liebherr-Hausgeräte GmbH<br>Memminger Straße 77-79<br>88416 Ochsenhausen<br>Germany |
| Model identifier              | CBNbsa 575i_997212651   |

### Electrical data

| Parameter     | Value   | Parameter      | Value |
|---------------|---------|----------------|-------|
| Voltage (V ~) | 220-240 | Frequency (Hz) | 50-60 |

### Type of refrigerating appliance

|                        |    |                               |              |
|------------------------|----|-------------------------------|--------------|
| Low-noise appliance    | no | Design type                   | freestanding |
| Wine storage appliance | no | Other refrigerating appliance | yes          |

### General product parameters

|   |        |   |  |     |
|---|--------|---|--|-----|
| Overall dimensions (millimetre)   | Height | 2015  | Total volume (dm <sup>3</sup> or l)                  | 362 |
|   | Width  | 597   |  |     |
|   | Depth  | 675   |  |     |
| EEl   | 41     | Energy efficiency class   | A  |     |
| Airborne acoustical noise emissions (dB(A) re 1 pW)                                 | 33     | Airborne acoustical noise emission class  | B  |     |
| Annual energy consumption (kWh/a)   | 116    | Climate class   | extended temperate, temperate, subtropical, tropical |     |
| Minimum ambient temperature (°C), for which the refrigerating appliance is suitable | 10     | Maximum ambient temperature (°C), for which the refrigerating appliance is suitable | 43   |     |
| Winter setting  | no     |   |  |     |

**Compartment Parameters**

| Compartment type      |     | Compartment Volume (dm <sup>3</sup> or l) | Recommended temperature setting for optimised food storage (°C) | Freezing capacity (kg/24 h) | Defrosting type (auto-defrost = A, manual defrost = M) |
|-----------------------|-----|---|---|-----------------------------|--|
| Pantry                | no  | -   | -   | -                           | -  |
| Wine storage          | no  | -   | -   | -                           | -  |
| Cellar                | no  | -   | -   | -                           | -  |
| Fresh food            | yes | 159.9                                     | 5   | -                           | A  |
| Chill                 | yes | 99.2                                      | 0   | -                           | A  |
| 0-star or ice- making | no  | -   | -   | -                           | -  |
| 1-star                | no  | -   | -   | -                           | -  |
| 2-star                | no  | -   | -   | -                           | -  |
| 3-star                | no  | -   | -   | -                           | -  |
| 4-star                | no  | -   | -   | -                           | -  |
| 2-star section        | no  | -   | -   | -                           | -  |

**Variable temperature compartment**

|            |       |     |    |   |
|------------|-------|-----|----|---|
| Fresh food | 103.1 | 5   | -  | A |
| 4-star     |       | -18 | 10 |   |

**For 4-star compartments**

|                      |     |
|----------------------|-----|
| Fast freeze facility | yes |
|----------------------|-----|

**For wine storage appliances**

|                                 |   |
|---------------------------------|---|
| Number of standard wine bottles | 0 |
|---------------------------------|---|

**Light source parameters**

| Light Source | Lighting technology used | Energy efficiency class |
|--------------|--------------------------|-------------------------|
| 1            | LED                      | G                       |
| 2            | LED                      | G                       |
| 3            | LED                      | G                       |

**Additional information**

Minimum duration of the guarantee offered by the manufacturer: 24 month

Additional information: -

Weblink to the manufacturer's website, where the information in point 4(a) Annex of Commission Regulation (EU) 2019/2019 is found: <https://home.liebherr.com/>

The energy consumption was confirmed by measurements according to EN 62552:2020.