
Freestanding Under Counters 2024

Your first choice for efficiency and quality in small spaces.

LIEBHERR

Refrigeration and Freezing



Offer crisp freshness with smart features, as standard.

Reversible Door

Touch Control

Super Cool

Door Stop

Fridges

Freezers

Reversible Door

Smart Frost

Touch Control

LED

Super Frost

Vario Space



Rc 1400 ○ Pure

Fc 1404 ○ Pure



Many things change over time, but one thing you can always rely on is German engineering. Since 1954, Liebherr has consistently adhered to the highest aspirations and standards established by its founder, Hans Liebherr.

To this day, the family-owned company remains dedicated to quality in even the smallest details and maintains a tireless pursuit of perfection. Liebherr products undergo rigorous testing before delivery, and the company has developed a range of products to suit every lifestyle.

Space-Saving Design without Compromise

Welcome to a new generation of Under Counter appliances, where innovation meets elegance. Liebherr's latest generation of fridges and freezers are specifically designed to fit perfectly into any kitchen space.

Unmatched Variety:

With the largest range of Under Counter units available, including 12 freezer models and 18 fridge models, there's a perfect fit for every pantry, storage area, or small kitchen.

Sophisticated Technology:

Our advanced cooling and freezing systems keep food fresher for longer, enhancing convenience and quality.

Compact Excellence:

Space-saving designs that don't compromise on performance, providing maximum freshness in a minimal footprint.

Explore how Liebherr's new Under Counter appliances can elevate any kitchen with innovative solutions tailored to modern living.

Design meets functionality

Liebherr's fridges and freezers seamlessly blend cutting-edge technology with elegant design, ensuring kitchens not only look great but also perform at their best. Experience the convenience of effortless door opening, the peace of mind that comes with SmartDevice connectivity, and the satisfaction of maintaining optimal freshness and energy efficiency.



Stainless Steel/Silver

White

Available in two colours with two door handle options, our models can be tailored to personal taste and kitchen décor. Whether mixing and matching or opting for a coordinated look, the perfect balance of style and functionality is achieved. For a cohesive and optimal display, it is recommended to coordinate colour, handle type, and SmartDevice functionality.

Liebherr offers innovative solutions that enhance daily life, providing reliability, convenience, and elegance in every detail.



Slimline Handle



Recessed Handle

Fridges



TouchControl

A gentle finger tap can set the Liebherr to 3, 5, 7 or 9°C with TouchControl. So simple – and efficient, as the sleek button is integrated into the interior, creating more space for fresh goods.



EasyFresh

Experience market-freshness at home with EasyFresh-Safe. Its airtight closure raises humidity, preserving unpackaged fruits and vegetables for extended periods.



DoorStop

Stay fresh and odour-free with the retractable DoorStop. Prevents odours by keeping the door open when not in use, saving time and energy.



SuperCool

Maintain optimum temperature, even after adding sun-warmed groceries. Activate SuperCool to cool new items quickly, then it automatically turns off within 12 hours.



LED side lighting

The LED side lighting illuminates the interior from the side – providing a clear view of food throughout. Another highlight: the LEDs are positioned in front of the glass shelves, so that even a full fridge is well lit.



Adjustable inner door shelves

The height-adjustable inner door shelves can be repositioned at any time, providing flexible and secure storage for various containers and foodstuffs.

Freezers



TouchControl

A gentle tap of a finger and smart features are activated, like SuperFrost or other hidden functions, without even opening the freezer's door. So simple – and also energy-efficient, that is TouchControl.



VarioSpace

All NoFrost and SmartFrost freezers feature removable drawers and glass shelves, creating VarioSpace for quickly accommodating larger frozen items.



SuperFrost

To freeze fresh food while preserving vitamins, activate SuperFrost. It boosts the freezer's cooling capacity to maintain a constant temperature with new items. SuperFrost saves energy by automatically deactivating after 65 hours if not turned off manually.



FrostProtect

All Under Counter freezers can also be used in unheated rooms at ambient temperatures down to -15°C.



SmartFrost

SmartFrost technology reduces frost build-up, minimising the need to defrost and lowering electricity consumption. Additionally, the smooth interior walls are easy to clean.



NoFrost

Say goodbye to frost and ice in your freezer. Saves energy, time, and money by preventing ice buildup and eliminating the need for defrosting.

Under Counter Fridges

Discover Liebherr's Pure and Plus series of under counter fridges, energy-efficient models crafted to enhance any kitchen.

This range offers advanced feature options such as SmartDevice technology for precise temperature control and SuperCool for rapid cooling, ensuring food freshness. Available in widths 60, 55 and 50cm and a variety of colours, Liebherr fridges offer flexibility to suit various kitchen needs.

Enjoy convenient features like TouchControl and DoorStop, with additional options that complement any kitchen setup, including matching freezers if required.



60cm Fridges



Rsdci 1620
Plus

| | |
|--|-------------------------------------|
| Energy efficiency class: | C ¹ |
| Energy consumption year / 24 hrs: | 59 / 0.161 kWh |
| Total volume ² : | 141 l |
| Noise output / noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door / side walls: | SmartSteel / silver |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 |

- Easy Fresh
- Super Cool
- Super Silent
- Touch Display
- Touch Control
- Door Stop
- Smart Device



Rsdci 1621
Plus

| | |
|--|---|
| Energy efficiency class: | C ¹ |
| Energy consumption year / 24 hrs: | 95 / 0.260 kWh |
| Total volume ² : | 125 l |
| Volume: | Fridge: 109.2 l / Freezer compartment: 17 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door / side walls: | SmartSteel / silver |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 |

- Easy Fresh
- Smart Frost
- Super Cool
- Super Silent
- Touch Display
- Touch Control
- Smart Device



Rci 1620
Plus

| | |
|--|-------------------------------------|
| Energy efficiency class: | C ¹ |
| Energy consumption year / 24 hrs: | 59 / 0.161 kWh |
| Total volume ² : | 141 l |
| Noise output / noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 |

- Easy Fresh
- Super Cool
- Super Silent
- Touch Display
- Touch Control
- Door Stop
- Smart Device



Rdi 1621
Plus

| | |
|--|---|
| Energy efficiency class: | D ¹ |
| Energy consumption year / 24 hrs: | 116 / 0.317 kWh |
| Total volume ² : | 125 l |
| Volume: | Fridge: 109.2 l / Freezer compartment: 17 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 |

- Easy Fresh
- Smart Frost
- Super Cool
- Super Silent
- Touch Display
- Touch Control
- Smart Device



Rdi 1620
Plus

| | |
|--|-------------------------------------|
| Energy efficiency class: | D ¹ |
| Energy consumption year / 24 hrs: | 73 / 0.200 kWh |
| Total volume ² : | 141 l |
| Noise output / noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 |

- Easy Fresh
- Super Cool
- Super Silent
- Touch Display
- Touch Control
- Door Stop
- Smart Device



Rci 1621
Plus

| | |
|--|---|
| Energy efficiency class: | C ¹ |
| Energy consumption year / 24 hrs: | 95 / 0.260 kWh |
| Total volume ² : | 125 l |
| Volume: | Fridge: 109.2 l / Freezer compartment: 17 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 |

- Easy Fresh
- Smart Frost
- Super Cool
- Super Silent
- Touch Display
- Touch Control
- Smart Device

55cm Fridges

Perfectly pairs with Fc 1404 or FNe 1404



Rc 1400
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | C |
| Energy consumption year / 24 hrs: | 58 / 0.158 kWh¹ |
| Total volume ² : | 125 l |
| Noise output / noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7¹ |

- Super Cool
- LED
- Touch Control
- Door Stop



Re 1401
Pure

| | |
|--|--|
| Energy efficiency class: | E |
| Energy consumption year / 24 hrs: | 142 / 0.389 kWh¹ |
| Total volume ² : | 111 l |
| Volume: | Fridge: 96.9 l / Freezer compartment: 15 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7¹ |

- Smart Frost
- Super Cool
- Touch Display
- Touch Control



Rc 1401
Pure

| | |
|--|--|
| Energy efficiency class: | C |
| Energy consumption year / 24 hrs: | 91 / 0.249 kWh¹ |
| Total volume ² : | 111 l |
| Volume: | Fridge: 96.9 l / Freezer compartment: 15 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7¹ |

- Smart Frost
- Super Cool
- Super Silent
- Touch Display
- Touch Control



Re 1400
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | E |
| Energy consumption year / 24 hrs: | 90 / 0.246 kWh¹ |
| Total volume ² : | 125 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7¹ |

- Super Cool
- Super Silent
- Touch Display
- Touch Control

Perfectly pairs with Fd 1404



Rd 1400
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | D |
| Energy consumption year / 24 hrs: | 72 / 0.197 kWh¹ |
| Total volume ² : | 125 l |
| Noise output / noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7¹ |

- Super Cool
- Super Silent
- Touch Display
- Touch Control
- Door Stop



Rd 1401
Pure

| | |
|--|--|
| Energy efficiency class: | D |
| Energy consumption year / 24 hrs: | 114 / 0.312 kWh¹ |
| Total volume ² : | 111 l |
| Volume: | Fridge: 96.9 l / Freezer compartment: 15 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7¹ |

- Smart Frost
- Super Cool
- Super Silent
- Touch Display
- Touch Control



Rd 1400N
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | D |
| Energy consumption year / 24 hrs: | 72 / 0.197 kWh¹ |
| Total volume ² : | 125 l |
| Noise output / noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7¹ |

- Super Cool
- Super Silent
- Touch Display
- Touch Control
- Door Stop



50cm Fridges



← 50 →

Rd 1200
Pure

| | |
|--|-----------------------------|
| Energy efficiency class: | |
| Energy consumption year / 24 hrs: | 71 / 0.194 kWh ¹ |
| Total volume ² : | 110 l |
| Noise output / noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 50 / 60.7 ¹ |



← 50 →

Rsve 1201
Pure

| | |
|--|--|
| Energy efficiency class: | |
| Energy consumption year / 24 hrs: | 138 / 0.378 kWh ¹ |
| Total volume ² : | 98 l |
| Volume: | Fridge: 85.2 l / Freezer compartment: 13 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | silver / silver |
| Exterior dimensions in cm (h / w / d): | 85 / 50 / 60.7 ¹ |



← 50 →

Re 1200
Pure


| | |
|--|-----------------------------|
| Energy efficiency class: | |
| Energy consumption year / 24 hrs: | 88 / 0.241 kWh ¹ |
| Total volume ² : | 110 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 50 / 60.7 ¹ |



← 50 →

Rd 1201
Pure

| | |
|--|--|
| Energy efficiency class: | |
| Energy consumption year / 24 hrs: | 110 / 0.301 kWh ¹ |
| Total volume ² : | 98 l |
| Volume: | Fridge: 85.2 l / Freezer compartment: 13 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 50 / 60.7 ¹ |



Touch Control



← 50 →

Re 1201
Pure

| | |
|--|--|
| Energy efficiency class: | |
| Energy consumption year / 24 hrs: | 138 / 0.378 kWh ¹ |
| Total volume ² : | 98 l |
| Volume: | Fridge: 85.2 l / Freezer compartment: 13 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 50 / 60.7 ¹ |



Practical accessories for every need



Butter dish



Bottle shelf



FlexCube



HNGRYnsite

The Bottle Shelf is included with orders of Plus fridges. Additional accessories can be found and ordered via our webshop.

Under Counter Freezers

Explore Liebherr's under counter freezers in 60cm and 55cm sizes from our Pure and Plus series.

Standard features include TouchControl, LED lighting, SuperFrost, and VarioSpace for flexible storage. SmartFrost is available on various models.

Choose premium features tailored to meet your specific needs, such as NoFrost technology, SmartDevice connectivity, and enhanced energy efficiency.

Pair with our under counter fridges for a coordinated kitchen setup.



60cm Freezers

Perfectly pairs with Rsdci 1620



FNsddi 1624
Plus

| | |
|--|-------------------------------------|
| Energy efficiency class: | D ¹ |
| Energy consumption year / 24 hrs: | 148 / 0.405 kWh ¹ |
| Total volume ² : | 92 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | SmartSteel / silver |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 ¹ |

- No Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect
- Smart Device

Perfectly pairs with Rdi 1620



FNdi 1624
Plus

| | |
|--|-------------------------------------|
| Energy efficiency class: | D ¹ |
| Energy consumption year / 24 hrs: | 148 / 0.405 kWh ¹ |
| Total volume ² : | 92 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 ¹ |

- No Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect
- Smart Device

Perfectly pairs with Rci 1620



Fci 1624
Plus

| | |
|--|-------------------------------------|
| Energy efficiency class: | C ¹ |
| Energy consumption year / 24 hrs: | 110 / 0.301 kWh ¹ |
| Total volume ² : | 107 l |
| Noise output / noise class: | 36 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 ¹ |

- Smart Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect
- Smart Device

Perfectly pairs with Rdi 1620





Fdi 1624
Plus

| | |
|--|-------------------------------------|
| Energy efficiency class: | D ¹ |
| Energy consumption year / 24 hrs: | 137 / 0.375 kWh ¹ |
| Total volume ² : | 107 l |
| Noise output / noise class: | 36 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 60 / 60.7 ¹ |


- Smart Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect
- Smart Device



 home.liebherr.com/getsmart



You can download the SmartDevice app here:



55cm Freezers

Perfectly pairs with Re 1400



← 55 →

FNe 1404
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | E ¹ |
| Energy consumption year / 24 hrs: | 185 / 0.506 kWh |
| Total volume ² : | 92 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7 |

- No Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect

Perfectly pairs with Rc 1400



← 55 →

Fc 1404
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | C ¹ |
| Energy consumption year / 24 hrs: | 110 / 0.301 kWh |
| Total volume ² : | 107 l |
| Noise output / noise class: | 36 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7 |

- Smart Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect



← 55 →

Fsvsve 1404
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | E ¹ |
| Energy consumption year / 24 hrs: | 172 / 0.471 kWh |
| Total volume ² : | 107 l |
| Noise output / noise class: | 39 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | silver / silver |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7 |

- Smart Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect

Perfectly pairs with Re 1400



← 55 →

Fe 1404
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | E ¹ |
| Energy consumption year / 24 hrs: | 172 / 0.471 kWh |
| Total volume ² : | 107 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7 |

- Smart Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect

Perfectly pairs with Rd 1400



← 55 →

Fd 1404
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | D ¹ |
| Energy consumption year / 24 hrs: | 137 / 0.375 kWh |
| Total volume ² : | 107 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7 |

- Smart Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect

Perfectly pairs with Rd 1400N



← 55 →

Fe 1414
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | E ¹ |
| Energy consumption year / 24 hrs: | 172 / 0.471 kWh |
| Total volume ² : | 107 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7 |

- Smart Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect



← 55 →

Fc 1404N
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | C ¹ |
| Energy consumption year / 24 hrs: | 110 / 0.301 kWh |
| Total volume ² : | 107 l |
| Noise output / noise class: | 36 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7 |

- Smart Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect

Perfectly pairs with Rd 1400N



← 55 →

FNe 1404N
Pure

| | |
|--|-----------------------------------|
| Energy efficiency class: | E ¹ |
| Energy consumption year / 24 hrs: | 185 / 0.506 kWh |
| Total volume ² : | 92 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10°C to +43°C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white / white |
| Exterior dimensions in cm (h / w / d): | 85 / 55 / 60.7 |

- No Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect

