

Hydroseilbagger HS-Serie

DE

| | HS 8040.1 | HS 8070.1 | HS 8100.2 | HS 8130.1 | HS 8200 | HS 8300.2 |
|-----------------------------|--|--|--|---|--|--|
| Traglast | | | | | | |
| Max. Traglast | 40 t | 70 t | 100 t | 130 t | 200 t | 293 t |
| Transport | | | | | | |
| Min. Transportgewicht | 41 t | 35 t | 40 t | 51 t | 47 t | 72.2 t |
| Min. Transportbreite | 3000 mm | 3000 mm | 3500 mm | 3500 mm | 3500 mm | 3990 mm |
| Motor | | | | | | |
| Modell | Liebherr D 944 A7-05 | Liebherr D 936 A7-05 | Liebherr D 966 A7-05 | Liebherr D 9508 A7-04 | Liebherr D 9512 A7-05 | Liebherr D 9512 A7 |
| Leistung bei 1700 U/min | 230 kW / 313 PS | 320 kW / 435 PS | 450 kW / 612 PS | 565 kW / 768 PS | 750 kW / 1020 PS | 750 kW / 1020 PS |
| Winden | | | | | | |
| Winden (2x) | 12 t | 20 t | 30 t | 35 t | 35 t | 50 / 70 t |
| Seildurchmesser | 22 mm | 30 mm | 34 mm | 36 mm | 36 mm | 46 / 50 mm |
| Ausleger | | | | | | |
| für Hebezeugeinsatz | 41 m | 50 m | 59 m | 53 m | 68 m | 68 m |
| für Baggerbetrieb | 26 m | 32 m | 32 m | 38 m | 50 m | 56 m |
| für Schürfkübeleinsatz | 26 m | 29 m | 32 m | 35 m | 50 m | 50 m |
| Einsatzarten | | | | | | |
| Schürfkübel | ● | ● | ● | ● | ● | ● |
| Greifer | ● | ● | ● | ● | ● | ● |
| Rüttler | ○ | ● | ● | ● | ● | ● |
| Verrohrungsmaschine | ● | ● | ● | ● | ● | ● |
| Schlitzwandgreifer | ○ | ● | ○ | ● | ● | ○ |
| Fräse | - | - | ○ | ● | ○ | - |
| Hängemäkler | ○ | ○ | ● | ● | ● | ● |
| Dynamische Bodenverdichtung | ○ | ● | ● | ● | ● | ● |
| Hebezeugeinsatz | ● | ● | ● | ● | ● | ● |
| Magnet | ○ | ● | ● | ○ | ○ | ○ |
| Barge | ● | ● | ● | ● | ● | ● |
| Andwendungen | | | | | | |
| Schürfkübel | | | | | | |
| Max. Tiefe | 13 m | 14 m | 15 m | 17 m | 22 m | 25 m |
| Max. Inhalt | 1.9 m ³ / 2.5 yd ³ | 3.8 m ³ / 5 yd ³ | 4.6 m ³ / 6 yd ³ | 5.4 m ³ / 7.1 yd ³ | 7.6 m ³ / 10 yd ³ | 10.8 m ³ / 14.1 yd ³ |
| Zweischalengreifer | | | | | | |
| Max. Inhalt | 3 m ³ / 3.9 yd ³ bis 10 m | 6 m ³ / 7.8 yd ³ bis 10 m | 7 m ³ / 9.2 yd ³ bis 12 m | 8 m ³ / 10.5 yd ³ bis 14 m | 14 m ³ / 18.3 yd ³ bis 20 m | 20 m ³ / 26 yd ³ bis 26 m |

- ja
- auf Anfrage
- nein



Bitte kontaktieren Sie uns.

Liebherr-Werk Nenzing GmbH · Dr. Hans Liebherr Str. 1 · 6710 Nenzing, Austria
Phone +43 50809 41-473 · crawler.crane@liebherr.com · www.liebherr.com
facebook.com/LiebherrConstruction