

Hydroseilbagger HS-Serie

DE

	HS 8040.1	HS 8070.1	HS 8100.1	HS 8130.1	HS 8200	HS 8300.2
Traglast						
Max. Traglast	40 t	70 t	100 t	130 t	200 t	293 t
Transport						
Min. Transportgewicht	41 t	35 t	40 t	51 t	47 t	72.2 t
Min. Transportbreite	3000 mm	3000 mm	3500 mm	3500 mm	3500 mm	3990 mm
Motor						
Modell	Liebherr D 944 A7-05	Liebherr D 936 A7-05	Liebherr D 946 A7-05	Liebherr D 9508 A7-04	Liebherr D 9512 A7-05	Liebherr D 9512 A7
Leistung bei 1700 U/min	230 kW / 313 PS	320 kW / 435 PS	390 kW / 530 PS	565 kW / 768 PS	750 kW / 1020 PS	750 kW / 1020 PS
Winden						
Winden (2x)	12 t	20 t	27.5 t	35 t	35 t	50 / 70 t
Seildurchmesser	22 mm	30 mm	34 mm	36 mm	36 mm	46 / 50 mm
Ausleger						
für Hebezeugeinsatz	41 m	50 m	59 m	53 m	68 m	68 m
für Baggerbetrieb	26 m	32 m	32 m	38 m	50 m	56 m
für Schürfkübeleinsatz	26 m	29 m	29 m	35 m	50 m	50 m
Einsatzarten						
Schürfkübel	●	●	●	●	●	●
Greifer	●	●	●	●	●	●
Rüttler	○	●	●	●	●	●
Verrohrungsmaschine	●	●	●	●	●	●
Schlitzwandgreifer	○	●	○	●	●	○
Fräse	-	-	○	●	○	-
Hängemäkler	○	○	●	●	●	●
Dynamische Bodenverdichtung	○	●	●	●	●	●
Hebezeugeinsatz	●	●	●	●	●	●
Magnet	○	●	●	○	○	○
Barge	●	●	●	●	●	●
Andwendungen						
Schürfkübel						
Max. Tiefe	13 m	14 m	15 m	17 m	22 m	25 m
Max. Inhalt	1.9 m ³ / 2.5 yd ³	3.8 m ³ / 5 yd ³	4.6 m ³ / 6 yd ³	5.4 m ³ / 7.1 yd ³	7.6 m ³ / 10 yd ³	10.8 m ³ / 14.1 yd ³
Zweischalengreifer						
Max. Inhalt	3 m ³ / 3.9 yd ³ bis 10 m	6 m ³ / 7.8 yd ³ bis 10 m	7 m ³ / 9.2 yd ³ bis 12 m	8 m ³ / 10.5 yd ³ bis 14 m	14 m ³ / 18.3 yd ³ bis 20 m	20 m ³ / 26 yd ³ bis 26 m

- ja
- auf Anfrage
- nein



Bitte kontaktieren Sie uns.

Liebherr-Werk Nenzing GmbH · Dr. Hans Liebherr Str. 1 · 6710 Nenzing, Austria
Phone +43 50809 41-473 · crawler.crane@liebherr.com · www.liebherr.com
facebook.com/LiebherrConstruction