

Pelles à câbles

Gamme HS

FR

	HS 8040.1	HS 8070.1	HS 8100.2	HS 8130.1	HS 8200	HS 8300.2
Levage						
Capacité de levage max.	40 t	70 t	100 t	130 t	200 t	293 t
Transport						
Poids de transport min.	41 t	35 t	40 t	51 t	47 t	72.2 t
Largeur de transport min.	3000 mm	3000 mm	3500 mm	3500 mm	3500 mm	3990 mm
Moteur						
Modèle	Liebherr D 944 A7-05	Liebherr D 936 A7-05	Liebherr D 966 A7-05	Liebherr D 9508 A7-04	Liebherr D 9512 A7-05	Liebherr D 9512 A7
Puissance à 1700 t/mn	230 kW / 313 ch	320 kW / 435 ch	450 kW / 612 ch	565 kW / 768 ch	750 kW / 1020 ch	750 kW / 1020 ch
Treux principaux						
Treux principaux (2x)	12 t	20 t	30 t	35 t	35 t	50 / 70 t
Diamètre de câble	22 mm	30 mm	34 mm	36 mm	36 mm	46 / 50 mm
Flèche principale						
en utilisation levage	41 m	50 m	59 m	53 m	68 m	68 m
en utilisation pelle	26 m	32 m	32 m	38 m	50 m	56 m
en utilisation dragline	26 m	29 m	32 m	35 m	50 m	50 m
Modes d'opération						
Dragline	●	●	●	●	●	●
Grappin	●	●	●	●	●	●
Vibreux	○	●	●	●	●	●
Louvoyeuse	●	●	●	●	●	●
Benne à parois moulées	○	●	○	●	●	○
Hydrofraise	-	-	○	●	○	-
Machine de battage	○	○	●	●	●	●
Compactage dyn. du sol	○	●	●	●	●	●
Grue	●	●	●	●	●	●
Aimant	○	●	●	○	○	○
Ponton	●	●	●	●	●	●
Utilisation						
Dragline						
Profondeur max.	13 m	14 m	15 m	17 m	22 m	25 m
Capacité max.	1.9 m ³ / 2.5 yd ³	3.8 m ³ / 5 yd ³	4.6 m ³ / 6 yd ³	5.4 m ³ / 7.1 yd ³	7.6 m ³ / 10 yd ³	10.8 m ³ / 14.1 yd ³
Benne						
Capacité max.	3 m ³ / 3.9 yd ³ à 10 m	6 m ³ / 7.8 yd ³ à 10 m	7 m ³ / 9.2 yd ³ à 12 m	8 m ³ / 10.5 yd ³ à 14 m	14 m ³ / 18.3 yd ³ à 20 m	20 m ³ / 26 yd ³ à 26 m

- oui
- sur demande
- non



Contactez-nous.

Liebherr-Werk Nenzing GmbH · Dr. Hans Liebherr Str. 1 · 6710 Nenzing, Austria
Phone +43 50809 41-473 · crawler.crane@liebherr.com · www.liebherr.com
facebook.com/LiebherrConstruction