HC 2090G

Fully Integrated Appliances



Refrigeration and Freezing





home.liebherr.com

	HC 2090G		
Energy consumption (kWh / y)	580		
Estimated Yearly Energy Cost* in US \$	81		
Sound rating** dB(A)	39		
Total refrigerator capacity cu.ft. (l)	13.5(382)		
BioFresh compartment cu.ft. (l)	-		
Freezer capacity cu.ft. (l)	6.0(170)		
Electronic control	MagicEye with digital temp.		
	display, touch electronic		
Defrost type	Automatic		
Interior light	LED Light column/ LED ceiling		
Number of shelves	3		
Number of door racks	6		
Number of drawers	3		
Number of freezer drawers	2		
Refrigerator Temperature range °F (°C)	+36°F to +43°F (+2°C to +6°C)		
Freezer Temperature range °F (°C)	+7°F to -17°F (-14°C to -27°C)		
Water filter	yes		
Ice maker	Fixed with water connection		
Ice cube output lbs. (kg.)	3.1(1.4)		
Ice cube stock lbs. (kg.)	6(2.7)		
Door hinges	right		
Product dimensions			
in inch (H / W / D)	79 13/16" / 35 7/8" / 24 1/16"		
in cm (H / W / D)	202.7/91/61.5		
Cut out dimensions			
in inch (H / W / D)	80"-815/8" / 361/16" / 25"		
in cm (H / W / D)	203.2-207.2/91.5/63.5		
Net weight lbs. (kg)	372.6(169)		
Voltage V / Hz	115/60		

* Energy Cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 14 cents per KWh.



Accessories	
Water Filter	9880980/7440002
Stainless Steel Round Handles	9900327
Brushed Aluminimum Square Handles	9900329
Door Stopper 90*	9096699
Stainless Steel Panels Freezer	9900323
Stainless Steel Panels Refrigerator 8	0 " 9900333
Stainless Steel Panels Refrigerator 84	4" 9904386

Features



Lengthen the shelf life and preserve the flavor of your foods with a dual refrigeration system that creates ideal conditions in both the refrigerator and freezer.



Liebherr's automatic IceMaker produces perfect ice cubes and keeps a constant supply on hand for every occasion.




Store food securely within reach thanks to fully extendable pull-out drawers. The SoftTelescopic system provides convenient and reliable self-retraction with soft closing.


** Noise output - according to EN 60704-3

Diagrams

Product Dimensions



Panel Dimensions



The height of this panel cannot be reduced for higher toe kicks as it will reveal structural elements of the appliance. Instead, install appliance on a platform and adjust the opening height to accommodate.


Cabinet opening A	Refrigerator door panel B	Cabinet opening A	Refrigerator door panel B
80"	45-1/2" (1156 mm)	80"	45-5/8" (1159 mm)
84"	49-1/4" (1251 mm)	84"	49-3/4" (1264 mm)

Minimum panel thickness is 5/8" (16 mm).

Maximum panel thickness is 3/4" (20 mm).

Maximum weight of the refrigerator panel is 60 lbs (27 kg).

Maximum weight of each freezer panel is 26.5 lbs (12 kg).



Ventilation Requirements



The appliance do not require ventilation considerations in the cabinetry. The required airflow is directed through the toe kick base. It is important to use the provided cover grille for the ventilation opening. This opening must not be covered.

 ${\it Subject to modification. For up-to-date information, visit home.liebherr.com.}$

Specifications are for planning purposes only. For more detailed information, refer to installation instructions or Design Guide.