
Ready, steady, lift!

2024

Full range
Programme intégral















LIEBHERR
















Mobile and crawler cranes


































LTM®-Mobile and truck cranes















Grues mobiles routière et tout terrain


















											
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	load charts
LTM 1030-2.1	40 10	209 280	53	4 x 4 x 4	-	30 - 98	28 - 49	144	130	12,100	
LTM 1040-2.1	45 9	209 280	53	4 x 4 x 4	-	34 - 115	31	144	125	14,330	















											
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	load charts
LTM 1050-3.1	60 10	270 367	53	6 x 4 x 6 6 x 6 x 6	-	37 - 125	5 - 52	177	145	19,800	
LTM 1055-3.2	65 9	270 367	53	6 x 4 x 6 6 x 6 x 6	-	33 - 131	8 - 52	184	155	26,450	
LTM 1060-3.1	70 7	270 367	53	6 x 4 x 6 6 x 6 x 6	-	34 - 157	8 - 52	207	155	28,200	















											
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	load charts
LTM 1070-4.2	80 8	330 449	53	8 x 4 x 8 8 x 6 x 8	-	36 - 164	10 - 52	215	155	32,000	
LTM 1090-4.2	110 9	330 449	53	8 x 6 x 8	-	31 - 197	7 - 52	249	204	49,600	
LTM 1120-4.1	135 10	330 449	53	8 x 6 x 8	-	40 - 217	10 - 85	308	210	68,300	

											
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	load charts
LTM 1100-5.3	110 10	400 544	53	10 x 6 x 10 10 x 8 x 10	-	43 - 203	7 - 53	249	210	49,600	
LTM 1110-5.2	125 9	400 544	53	10 x 6 x 10 10 x 8 x 10	-	38 - 197	10 - 108	299	215	63,900	
LTM 1150-5.3	175 10	400 544	53	10 x 6 x 10 10 x 8 x 10	-	40 - 217	10 - 85	302	236	99,200	
LTM 1160-5.2	190 10	400 544	53	10 x 6 x 10 10 x 8 x 10	-	43 - 203	10 - 131	325	256	119,000	

											
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	load charts
LTM 1230-5.1	275 10	400 544	53	10 x 6 x 10 10 x 8 x 10	-	41 - 246	11 - 141	364	282	158,700	
LTM 1250-5.1	300 9	400 544	53	10 x 6 x 10 10 x 8 x 10	-	43 - 197	13 - 164	345	315	194,000	


											
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	load charts
LTM 1300-6.2	360 10	455 619	53	12 x 6 x 12 12 x 8 x 12	-	48 - 256	18 - 230	374	308	211,600	
LTM 1300-6.3	360 10	455 619	53	12 x 6 x 12 12 x 8 x 12	-	48 - 295	13 - 141	394	308	194,000	
LTM 1300-6.4	360 10	455 619	53	12 x 6 x 12 12 x 8 x 12	-	48 - 295	13 - 141	394	308	194,000	
LTM 1350-6.1	400 10	455 619	53	12 x 6 x 12 12 x 8 x 12	180 245	49 - 230	20 - 256	439	310	308,600	
LTM 1400-6.1	450 10	455 619	53	12 x 6 x 12 12 x 8 x 12	-	49 - 230	23 - 264	394	315	308,600	
















											
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	load charts
LTM 1450-8.1	550 10	505 686	53	16 x 8 x 16	-	53 - 279	23 - 276	433	335	295,400	
LTM 1650-8.1	770 9	505 686	53	16 x 8 x 16	-	55 - 263	20 - 299	499	370	385,800	

											
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	load charts
LTM 1750-9.1	900 10	505 686	53	18 x 8 x 18	300 408	53 - 171	20 - 299	505	380	449,700	
LTM 11200-9.1	1500 8	505 686	50	18 x 8 x 18	300 408	60 - 328	21 - 413	617	446	445,300	

LTC®-Compact mobile cranes


Grues compactes















	 class		 mph								
	t (us) ft	kW h.p.	max	Standard Option	min - max	min - max	max	max	max lb	load charts	
LTC 1050-3.1 Telematik	50 10	243 326	-	6 x 4 x 6 6 x 6 x 6	27 - 118	5 - 43	157	130	14,330		
Rope pull technology Technique de traction de câble	50 10	243 326	-	6 x 4 x 6 6 x 6 x 6	27 - 102	5 - 43	141	125	14,330		
LTC 1050-3.1 	50 10	243 326	72	6 x 4 x 6 6 x 6 x 6	27 - 118	5 - 43	157	130	14,330		

LTF®-Truck mounted telescopic cranes


Grues télescopiques sur porteur châssis cabine















	 class		 mph								
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	load charts
LTF 1045-4.1	55 9	Depending on truck chassis Dépendant du châssis porteur			129 175	35 - 115	31	144	138	19,800	
LTF 1060-4.1	70 9	Depending on truck chassis Dépendant du châssis porteur			129 175	33 - 131	31 - 52	184	157	22,500	

LG®-Lattice boom mobile crane


Grue à flèche en treillis
















	 class		 mph									
	t (us) ft	kW h.p.	max	Standard Option	kW h.p.	min - max	min - max	max	max	max lb	max lb	load charts
LG 1750	850 22.7	505 686	50	16 x 8 x 16	455 619	69 - 459	92 - 344	633	445	551,150	881,850	
LG 1800-1.0	880 29	505 686	53	18 x 8 x 18	455 619	118 - 590	59 - 334	669	512	595,300	881,850	

LRT®-Rough terrain cranes


Grues rough-terrain


















	 class		 mph							
	t (us) ft	kW h.p.	max	Standard Option	min - max	min - max	max	max	max lb	load charts
LRT 1090-2.1	100 8	201 270	15.5	4 x 4 x 4	39 - 154	6.5 - 62	215	165	28,700	
LRT 1100-2.1	110 8	201 270	15.5	4 x 4 x 4	41 - 164	6.5 - 62	226	177	33,100	
LRT 1130-2.1	140 10	188 252	12.5	4 x 4 x 4	38 - 197	9.5 - 85	279	217	45,450	

LTR®-Telescopic crawler cranes


Grues télescopiques sur chenilles



	 class		 mph							
	t (us) ft	kW h.p.	max	min - max	min - max	min - max	max	max lb	max lb	load charts
LTR 1040	50 10	129 175	1.9	33 - 131	8 - 52	179	125	12,300	0	
LTR 1060	65 7	129 175	1.9	33 - 131	8 - 52	179	160	34,400	22,050	
LTR 1100	110 9	129 175	1.7	38 - 171	10 - 108	272	195	70,540	33,100	
LTR 1150	170 10	218 296	1.4	37 - 171	10 - 108	272	249	90,400	48,500	
LTR 1220	250 10	230 312	1.18	44 - 197	11 - 141	331	289	154,350	44,100	

LR®-Crawler track cranes

Grues sur chenilles



	t (us) ft	kW h.p. 308 (us)	max	max	max	max	max lb	max lb	max lb	load charts
LR 1100.1**	110 9	230 308 (us)	46 - 203	36 - 66	195	171	71,200	42,300	-	
LR 1110**	127 10	230 308 (us)	46 - 233	74 - 219	347	224	74,957	38,581	-	
LR 1130.1** ¹⁾	151 12	230 308 (us)	55 - 262	74 - 257	415	256	115,302	44,092	-	
LR 1160.1** ¹⁾	200 16	230 308 (us)	65 - 287	65 - 272	443	275	137,348	44,092	-	
LR 1200.1** ¹⁾	242 13	230 308 (us)	65 - 292	65 - 312	485	338	181,440	79,366	-	
LR 1250.1** ¹⁾	275 13	230 308 (us)	65 - 282	65 - 312	485	319	181,440	79,366	-	
LR 1300.1 SX**	331 14	390 523 (us)	65 - 361	65 - 370	644	469	272,000	125,663	264,500	
LR 1400 SX**	441 16	450 603 (us)	66 - 312	66 - 370	566	407	330,693	114,640	-	
LR 1500	550 25	350 476	118 - 433	59 - 275	538	472	374,800	88,200	617,300	
LR 1700-1.0	770 28	400 544	79 - 541	39 - 315	643	525	507,000	198,400	826,750	
LR 1700-1.0W	770 28	400 544	79 - 541	39 - 315	650	525	507,000	143,300	826,750	
LR 1800-1.0	880 29	455 619	118 - 590	59 - 334	663	498	507,000	198,400	882,000	
LR 11000	1200 36	505 686	59 - 551	59 - 374	722	603	551,250	198,450	992,100	
LR 11350	1500 39	660 898	98 - 492	39 - 276	722	538	749,600	66,140	1,322,775	
LR 12500-1.0	2750 33	800 1088	197 - 532	59 - 354	656	591	705,500	220,460	3,086,470	
LR 13000	3300 39	1000 1360	197 - 473	59 - 413	774	656	1,653,500	330,700	3,306,950	

** Liebherr-Werk Nenzing GmbH
¹⁾ available as battery powered version - disponible en version alimentée par batterie



MyLiebherr

Our MyLiebherr portal is the easy way for you to access Liebherr's digital service world.
Take advantage of extensive basic and additional services for your mobile and crawler cranes.

Avec notre portail MyLiebherr, accédez facilement à l'univers numérique du service de Liebherr.
Bénéficiez dès maintenant d'un service global et de prestations complémentaires pour vos grues mobiles et sur chenilles.



One portal, all services

MyLiebherr



Planning

Crane Finder



Operations

Performance



Planning

Crane Planner 2.0



Operations

Documents



Maintenance

Spare Parts Catalogue



Planning

LICCON Work Planner



Training

Digital Crane Operator



Maintenance

Parts Shop

Proposition 65



WARNING: This product can expose you to chemicals, including exhaust emissions, including lead and lead compounds, which are known to the State of California to cause cancer, birth defects or other reproductive harm.
For more information see: www.P65warnings.ca.gov/diesel

Subject to modification · Sous réserve de modifications

Liebherr-Werk Ehingen GmbH · Postfach 1361 · 89582 Ehingen, Germany
Phone +49 73 91 5 02-0 · www.liebherr.com

MyLiebherr



Printed in Germany (1)
lwe-full-range-us05-2024