
Freshness to the fullest

Discover our freestanding and
fully-integrated appliances.

LIEBHERR

Refrigeration and freezing







Contents

Liebherr Group	4
Quality	6
Freshness technology	8
Comfort & flexibility	10
Design	12
Performance in balance	14
Accessories	16
Freestanding appliances	18
Fully integrated appliances	36
Wine cabinets	60
Liebherr Barrique	74
Design and lifestyle	86

Global success: The Liebherr Group.

Liebherr is a third-generation, family-owned company founded in 1949 by Hans Liebherr with his ground-breaking invention of the world's first mobile tower crane.

With over 70 years of success, Liebherr is known as a pioneer in high-quality, breakthrough innovations and countless cutting-edge technologies in numerous industries. One of the world's largest manufacturers of construction machinery, Liebherr has expanded its broadly diversified portfolio to 13 product segments including earthmoving, deep foundation machines, mobile and crawler cranes, tower cranes, concrete technology, material handling technology, mining, maritime cranes, aerospace and transportation systems, gear technology and automation systems, components, hotel, and refrigeration and freezing. The company currently employs about 48,000 people in more than 140 companies in over 50 countries worldwide.



Mobile cranes



Aerospace



Earthmoving



Crawler cranes



Refrigeration and freezing



Liebherr-Hausgeräte GmbH, Germany

**Liebherr-Hausgeräte –
Specialists in refrigeration and freezing.**

Liebherr-Hausgeräte covers the full range of refrigeration and freezing for domestic and commercial use. Headquartered in Germany, Liebherr-Hausgeräte has an impressive range of more than 3,000 products in its portfolio.


Before we think about fridges, we think about you.

Fridges are supposed to cool. But what else should modern appliances be capable of today? How can they better meet customer needs? How can their design be more efficient, intuitive and modern?

We think about all these questions every day, because for us a fridge is not just an appliance. Instead, it should be a partner who supports us where it can ... who thinks in harmony with us, takes on tasks and makes work easier. In order to achieve this, we are constantly developing our appliances. Because the smarter and more helpful they are, the more time you have for all the other important things in life.

Achieving the highest quality is our standard.

We have been manufacturing high-quality fridges and freezers and selling them around the world since 1954. Yet at heart we are still a family business and have our roots firmly based in Germany. We continue to develop our products here. German engineering – from an enduring connection with our founder and in the knowledge that engineering expertise has been pooled here for generations.



Built to last.

You can experience our quality standards in the smallest of details. For example, before a door hinge is approved by us, it must pass through at least 100,000 opening cycles. This corresponds to a usage period of more than 15 years. We also test all other functional parts to ensure that they can last just as long. We have leveling bars to ensure that your fully integrated appliance works perfectly over this long period and stands firmly in place, even when the wood in the kitchen unit settles. They harmoniously compensate for any unevenness between the floor and the appliance, so that the fridge door always closes tightly. It may sound simple, but this is crucial for avoiding condensation and increased energy consumption.

And if, contrary to expectations, a small detail no longer meets your requirements, you or your expert service partner can usually correct it quickly, because all of our appliances are extremely easy to repair. We keep all essential spare parts in stock for well over 10 years. This saves you money for minor repairs or the purchase of a new appliance – and it is also sustainable.

We don't just say it. We also guarantee it.

During production, we take a very close look at all of our fridge components and test them far more thoroughly and more often than required by law – right up until the packaging stage. Only then may our appliances take a little rest. All our production sites are certified according to international ISO 9001 standard for quality and ISO 14001 standard for environmental management. Therefore it is wholly natural for us to guarantee you that for at least two years our products will be free of material and manufacturing defects and are particularly easy to install.

One thing is certain in any case: Your Liebherr will be reliable companion for a very long time.



Taste that stands the test of time: Freshness is a question of technology.

Storing groceries in ideal climatic conditions not only ensures extra-long freshness and storage time, it also makes a substantial contribution to avoiding food waste. With our appliances this is possible – thanks to the perfect combination of integrated freshness technologies.

DuoCooling. No drying out.

Our basic technology in all fridge-freezers is called DuoCooling. Thanks to two completely separate refrigeration circuits, it ensures that there is no exchange of air between the fridge and freezer compartments. The food neither dries out nor are odours transferred – so that only the Camembert smells and tastes like Camembert.

EasyFresh. Ideal for fruit and vegetables.

The freshness guarantee in your Liebherr fridge. Unpacked fruit and vegetables feel right at home here. At the same temperature as in the fridge compartment and air-tight, lettuce, for example, remains crisp and fresh even after 10 days.

BioFresh. Our all-rounder.

With our patented BioFresh technology, food is stored at a much cooler temperature than in the rest of the appliance. At temperatures just over 0 °C and with perfect humidity, BioFresh offers the ideal storage conditions. The air-tight Fruit & Vegetable safe is the ideal environment for fresh produce. Meat, fish and dairy products are in good hands in the Meat & Dairy safe.

BioFresh Professional. Refrigerate like the professionals.

A special innovation can be found in the BioFresh Professional and the brand new HydroBreeze feature. Every time the door is opened and after every 90 minutes, a fresh, cold mist is produced, covering fruits and vegetables like a balm to ensure crisp freshness and giving them a nice wow effect.

Fresh. Sustainable. Healthy.

The storage climate: We could write so much about it. To put it briefly, there are three main reasons that motivate us to keep perfecting it. First: An ideal climate contributes to keeping your food fresh for longer. You can enjoy it fresh for longer. Second: This prevents unnecessary food waste and means you have to go shopping less frequently. Three: Optimal storage helps to protect vitamins and nutrients. And this contributes to a healthy diet.



HydroBreeze – the cold fresh mist.

We found inspiration for the HydroBreeze in Salinas Valley in California. Due to the proximity to the cool Pacific Ocean, in the summer a fine humid mist covers the valley and the fields. This prevents the vegetables grown here from drying out.

**Hydro
Breeze**



Comfort and flexibility



Fits exactly to your needs.

Fridges and freezers are used daily. They have long been an essential part of our lives. And they should be as simple to use and convenient for you as possible. That's why we develop fridges and freezers that impress with their ease of use and flexibility – from the first door opening to the smallest features – to perfectly adapt to your needs.

As flexible as your life.

The features of our new appliances give you more freedom: The divisible glass shelf creates space for tall containers and carafes. Do you like things to be well organised? With the VarioBox and the VarioSafe you can store smaller objects neatly in the door or interior – always exactly at the height you like.



How about a cold drink? The glass shelf above the BioFresh safe transforms into a bottle shelf in the blink of an eye. The freezer compartment also ensures that you are well prepared with one of our new appliances: VarioSpace creates space for the largest turkey or the highest ice cream cake. Speaking of cake: For all those who love baking, our fridges and fridge-freezers offer enough space for a full baking tray.

Full of food. And convenience.

To ensure that all your food is always perfectly accessible, our appliances have telescopic rails in the fridge and freezer compartments which enable the drawers to slide back and forth with ease. And even once you have found all the ingredients, there is still further convenience. Thanks to the SoftSystem. This means that our doors always close gently and quietly, even if the force applied is a little too strong.



Timeless and elegant. Design for every kitchen.

Liebherr appliances are designed to inspire awe and integrate seamlessly into your kitchen. Multiple size configurations, installation options, and choice of stainless steel or personalized finishes allow for perfect integration into your dream kitchen.

Design meets functionality.

Puristic and timeless on the one hand. Elegant and exclusive on the other. The Liebherr design language blends design and functionality. The high quality glass and stainless steel components are impressive. The precise craftsmanship, an eye for detail, and the harmonious combination of materials, shapes and colours create an aesthetically pleasing end product.





Our LEDs provide a pleasant, bright light tone that makes your food look even more appetizing. As they have a very low heat generation, everything stays cool and fresh.



Just a fan? Not at all: the high glossy fan with ambient lighting ensures almost uniform temperature distribution and also includes the FreshAir activated charcoal filter. Functionality at its best.



Perfectly balanced: a powerful, complete package.

A good fridge is a real all-rounder: In addition to low power consumption and low noise levels, it should also offer plenty of space for food and have power reserves for when they are needed. For this reason we don't pay attention to just one factor, instead we have all usage situations in mind at once. The result: our appliances offer a balanced, perfectly coordinated complete package of energy efficiency, volume, noise level and cooling performance. So all good things come in fours for us.



Efficiency

Liebherr appliances occupy top positions in efficiency rankings. In this way, they protect the precious resources of our environment and, thanks to low electricity costs, your wallet too.

Volume

We have the perfect appliance for all family sizes, lifestyles and niche heights. From extra-large drawers to the smallest details, we make sure that no liter of volume goes to waste. For example, through space-saving lighting solutions recessed into the housing.

Noise level

Kitchen and living spaces are merging more and more in modern home design concepts. This underlines the importance of particularly quiet fridges. Our product range therefore offers a wide selection of extremely quiet appliances. Some even achieve the ultra-quiet level of 29 dB.

Refrigeration

Intelligent sensor technology constantly adapts the cooling performance to the current use – our appliances are very energy-efficient and economical in everyday use. At the same time, they offer considerable power reserves. For example, to cool a larger amount of food after the weekly shop and they are especially good for spontaneous visits. Drinks can be brought to a pleasant drinking temperature extremely quickly at the touch of a button.



Sustainability inside.

With a Liebherr, you are not only doing something good for your food, but also for the environment. Because we are constantly working on reducing the consumption and electricity costs of the appliances even further – while maintaining their excellent performance.

For example, we test all functional parts for a service life of 15 years. And just in case, we guarantee a long availability of spare parts. This means that you can enjoy a Liebherr for many years – and at the same time take care of your ecological footprint: because a long service life significantly reduces the consumption of energy and resources.



Accessories



Flexible accessories for your appliance.

Discover the versatility of the Liebherr range of accessories for your fridge – and make your daily life a little bit easier.



Organisational systems

Set up your fridge how you want it: In addition to the VarioSafe and the VarioBoxes, we also offer optimal organisation with the variable egg tray and the FlexSystem. Thanks to our bottle shelves and the clip labelling system for your wine inventory, you can also keep track of your beverages.



Useful help of all kinds

From the handy butter dish to the easy-fill ice cube tray, from the freezer tray to the Vario energy-saving panel, our range of accessories offers plenty of smart solutions for serving food and keeping it fresh.



Perfect installation – perfect appearance


Connecting sets, stainless steel frames and fronts with matching handles or drawers for accessories: the product range features many accessories that can help integrate a built-in appliance in the kitchen in an individual and visually perfect fashion.

Subject to availability. Please check with your local dealer for accessories available in your region.

Freestanding appliances







BioFresh 0°C



fresh-Safe

Bio
Fresh

BioFresh-Safe

Unique features.



IceMaker

Are there any ice cubes left? An IceMaker means you never have to ask. With the IceMaker with fixed water connection, the water comes directly from the tap. The MaxIce function allows you to produce up to 1.5 kg of ice cubes a day. The ice cube separator helps to divide the drawer into any size you want – for example, ice cubes on the left, ice cream on the right – or just for ice cubes.



SoftSystem

From breakfast to a midnight snack – a fridge needs to be open and closed on many occasions. And your Liebherr makes this a lot of fun. With the SoftSystem, your fridge door closes softly and safely, and in a way which is pleasantly quiet and light. Bottles stored in the inside door remain securely in place – nothing rattles or wobbles.



BioFresh

BioFresh provides the perfect climate for long-lasting food storage. When stored at just over 0°C and at the ideal humidity level, fruit, vegetables, meat and fish all retain their nutritious vitamins for longer.



SmartSteel

A specially treated stainless steel finish that significantly reduces the visibility of fingerprints, making it very easy to clean. Maintain this beautiful surface simply by wiping it with a soft, damp cloth.



Touch-Display

The elegant MagicEye control system with the innovative, user-friendly Touch-electronic feature ensures that the temperature in the fridge compartment and freezer compartment is kept to the selected temperature. All the functions can be simply and conveniently operated at the touch of a finger.



PowerCooling system

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



**Bio
Fresh
Plus**

**No
Frost**

**Ice
Maker**

Wine

**Soft
System**

**Soft-
Telescopic**

**Smart
Steel**

SBSes 8486

Masterpiece in Innovative Freshness Technology.

Timelessly elegant with a full stainless steel body, our award-winning BluPerformance SBSes 8486 Side-by-Side Fridge-Freezer with six different climate zones boasts an array of innovative solutions.

The dual-zone wine compartment allows you to store two different types of wine at their respective desired temperatures, ranging from +5°C to +20°C. The NoFrost freezer with automatic IceMaker provides professional freezing technology for long-term freshness while a spacious refrigerator provides an extended shelf life for fresh groceries.

The BioFresh-Plus compartment includes a versatile Fish & Seafood safe and offers an adjustable temperature range of 0°C and -2°C to provide even more storage flexibility for a wide array of meat and produce.

Technical data see page 92.





Bio
Fresh
Plus

No
Frost


Ice
Maker

Soft
System

Soft-
Telescopic

Smart
Steel

SBSes 8484



The big, cool combination.

The SBSes 8484 Fridge-Freezer from the energy efficient BluPerformance series combines ample fridge storage with perfect cooling performance for long-lasting freshness.

This side-by-side appliance can be precisely controlled via its intuitive touch & swipe temperature display. With its Fish & Seafood safe and adjustable temperature range between 0 °C and -2 °C, the BioFresh-Plus compartment provides perfect freshness for all types of food. And thanks to the innovative NoFrost technology, this appliance never has to be defrosted.

Its stunning SmartSteel exterior in combination with high-quality materials and exquisite workmanship make this model the highlight of your kitchen.

Also available in SBSes 8474 with BioFresh technology.

Technical data see page 93-94.



Bio
Fresh
Plus

No
Frost

Ice
Maker

Soft
System

Soft-
Telescopic

Smart
Steel

SBSes 8683

It doesn't get any fresher.

Fall in love with the BluPerformance SBSes 8683, Liebherr's range of energy-efficient fridge-freezers. Its stainless steel body and BioFresh-Plus technology strike the perfect balance between timeless beauty and keeping food fresh.

The right temperature and ideal humidity conditions are essential for the optimum storage of fruits, vegetables, dairy, and meat. With an adjustable temperature range between 0 °C and -2 °C, BioFresh-Plus ensures that your groceries retain their delicious freshness and nutrients for much longer. Keep your seafood in the versatile Fish & Seafood safe to preserve the delicate flavours for an extended period of time!

As with all Liebherr's freestanding models, you can choose to flush this appliance with your kitchen cabinetry for a clean, seamless look.

Technical data see page 95.



**Bio
Fresh**

**No
Frost**

**Ice
Maker**

**Soft
System**

**Soft-
Telescopic**

**Smart
Steel**

SBSbs 8673

An optical highlight in BlackSteel.

Elevate your living space with the SBSbs 8673 BlackSteel masterpiece. The black transverse-polished finish lends a premium appeal and exceptional textural depth to the fridge-freezer to give this striking model a luxurious, exclusive appearance.

Get your daily dose of freshness with Liebherr's patented BioFresh technology which allows each drawer to be adjusted individually to provide the ideal humidity for different types of food. Our IceMaker ensures that you stay refreshed in the heat.

This energy-efficient BluPerformance model is also available in stainless steel as SBSes 8673.

Technical data see page 96-97.






No
Frost

Smart
Steel

SBSef 7242



A spacious refrigerator and freezer all in one.

The SBSef 7242 Side-by-Side Fridge-Freezer brings together high-quality components and meticulous workmanship to guarantee food freshness and user-friendliness.

The freezer offers up to eight drawers to give an extra-large capacity for freezing your food. The transparent fruit and vegetable drawers in the refrigerator provide a clear view of the stored food and slide out effortlessly on the roller system.

The stainless doors with special SmartSteel coating makes this appliance easier to clean.

Technical data see page 98.



CNPef 4516

Practicality and elegance for your kitchen.

The CNPef 4516 Bottom-mount Freezer is the practical and elegant solution for small footprint installations such as studio apartments.

Thanks to VarioSpace, the drawers and safety glass shelves can be removed to conveniently create extra storage space for larger frozen goods.

Independent temperature control of the fridge and freezer compartments is facilitated by DuoCooling, two separately adjustable cooling circuits to prevent air exchange between the two compartments. This eliminates odour transfers and prevents food from drying out.

For larger households, double your food storage capacity by installing two units together.

Technical data see page 99.

No
Frost

Duo
Cooling

Smart
Steel

Vario
Space



Smart
Steel

Duo
Cooling

No
Frost

Bio
Cool

CNef 4315



Energy efficiency at its best.

The CNeF 4315 Bottom-mount Freezer is the perfect solution for galley kitchens or small families. The most compact model from Liebherr's BluPerformance range, it ensures maximum energy efficiency while providing more space for your food.

Its BioCool drawer allows you to regulate its humidity level within so that fresh fruits and vegetables can be stored up to twice as long. The door exterior is coated with SmartSteel, a specially treated stainless steel surface that significantly reduces the visibility of fingerprints, making it very easy to clean so that your fridge always looks good as new.

Technical data see page 99.

Fully integrated appliances






For a clear overview.
Even before you
open the fridge.

○ Pure ◇ Plus △ Peak

Which appliance is right for me?
A customer question that is not always
easy to answer. That's why we have made
it even simpler for you choose what's
right for you by dividing our product range
into easy to understand series.

○ Pure series

The Pure series is our basic class. Simple, clear and perfectly equipped for all essential needs. The Pure series has been reduced to the essentials. But full to the brim with the highest level of Liebherr quality.



◇ Plus series

The Plus series builds on our Pure series and has many impressive additional details. Above all, plus means a plus in comfort. The appliances not only provide first-class refrigerating and freezing, they are also just that little bit smarter. They help make much of the handling a little easier.

△ Peak series

The Peak series sits at the top of our series. Here the best is combined with the best. There is no compromise. Innovative Liebherr technology meets high-end design and comfort solutions that are simply first in its class. Appliances in this series are for those who want everything.





BioFresh Professional 0°C



Bio
Fresh
Professional

BioFresh 0°C



Unique features.



PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



Touch & Swipe Display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your refrigerator intuitively and with ease. Simply select functions such as SuperCool on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? Well, it then shows you the actual temperature.



Meat & Dairy safe

Want that tender veal fillet or fresh milk to stay fresh for as long as possible? Sure! In the Meat & Dairy safe, temperature is close to 0°C – ideal storage conditions for even the most delicate of foods. And best of all, everything is perfectly adjusted in the factory for immediate use.



IceMaker

Are there any ice cubes left? An IceMaker means you never have to ask. With the IceMaker with fixed water connection, the water comes directly from the tap. The MaxIce function allows you to produce up to 1.5 kg of ice cubes a day. The ice cube separator helps to divide the drawer into any size you want – for example, ice cubes on the left, ice cream on the right – or just for ice cubes.



SuperSilent

Shhh – listen carefully. Your Liebherr is so quiet that you have to strain your ears to hear it. How is this achieved? All refrigeration components such as compressors, valves, fans and evaporators are optimised and perfectly adapted to one another. This means you only hear what you want to hear in your kitchen.



ICNh 5173 | ICBNh 5173

See food in a new light.

Our most premium range of new Fully Integrated appliances: Meet the ICNh 5173 and ICBNh 5173 from the Peak series.

One highlight exclusive to the ICBNh 5173 is the brand new HydroBreeze which produces a fresh, cold mist that coats fruits and vegetables to ensure their crisp freshness. In the Meat & Dairy safe, temperature is close to 0°C – ideal storage conditions for even the most delicate of foods.

The ICNh 5173 Fridge-Freezer with EasyFresh drawers offers plenty of space for your favourite food and ingredients.

Both models in this combination are equipped with a high-resolution Touch & Swipe display. Their exquisite interior craftsmanship of glass and stainless steel illuminated by our new LightTower makes every peek inside a visual experience.

Technical data see page 100.

Bio
Fresh
Professional

Easy
Fresh

Duo
Cooling

No
Frost

Super
Silent

Soft
System

Glass &
Steel
Interior

Light
Tower

LED

Ice
Maker

Touch &
Swipe-
Display

Built-in luxury.

ICNh 5123 and ICNh 5133: Plus series models from our new Fully Integrated selection.

These models, that can also be installed as Side-by-Side, offer plenty of storage space with EasyFresh drawers that allow different humidity modes for a wide array of fresh groceries. NoFrost technology ensures a permanently frost-free freezer compartment.

Thanks to Liebherr's door-on-door technology, our fully integrated appliances fit perfectly into spacious kitchens and integrate seamlessly into your existing cabinetry.

Being SuperSilent models due to the special design and low-noise components, this combination is extremely quiet. Thanks to our SoftSystem the appliance doors always close gently even when fully loaded.

Technical data see page 101.

- Easy Fresh
- Duo Cooling
- No Frost
- Super Silent
- Soft System
- LED
- Ice Maker
Water tank
- Touch-Display



ICNh 5123 | ICNh 5133

There's room for freshness everywhere.

The sophisticated ICNh 5103 fits seamlessly into your kitchen: Elegant, slim, full of innovative features.

In the EasyFresh safe, you can store fresh fruits and vegetables in the best possible way. With its airtight seal, no moisture can escape and groceries stays as fresh and appetising as at the market stand.

Thanks to DuoCooling technology, this built-in fridge-freezer has two completely separate cooling circuits. This prevents any air exchange between the refrigerator and freezer compartments, keeping your food from drying out and eliminating odour transfers. Want to keep your homemade pizza or cake fresh? The ICNh 5103 even has room for a whole baking tray!

Technical data see page 102.

Easy
Fresh

Duo
Cooling

No
Frost

Super
Silent

LED

Touch-
Display





SIGN 3576 | SIKB 3550

The best sides of your kitchen.

Seamlessly tucked away behind your cabinetry, the SIGN 3576 and SIKB 3550 side-by-side combination is your kitchen's best kept secret.

Enjoy ultimate freshness with SIKB 3550 Fridge! Liebherr's patented BioFresh technology keeps meat, fish, and dairy fresh in the DrySafe drawer while high humidity in the Fruit & Vegetable-Safe efficiently retains natural moisture in unpackaged fruits and vegetables. With our practical FlexSystem and flexible bottle racks, you can get things organised while maximising interior space.

The SIGN 3576 NoFrost Freezer comes with eight generous FrostSafe drawers on telescopic rails that can be easily removed for added flexibility. And thanks to the built-in IceMaker you will always be able to have cold drinks on hand for every occasion. SoftSystem facilitates the gentle closing of both appliance doors even when the fridge door shelves are fully-loaded.

Technical data see page 103.

Bio
Fresh

No
Frost

Soft
System

Soft-
Telescopic

LED

Power
Cooling

Ice
Maker

Vario
Space



Bio
Fresh


No
Frost

Duo
Cooling

Ice
Maker

Soft
System

ECBN 6256



Fresh on the inside, sleek on the outside.

Behold the ECBN 6256 Fridge-Freezer with its magnificent French doors. Highlighted by BioFresh technology to provide targeted humidity for specific foods, this is your answer to style and freshness.

Our innovative DuoCooling system eliminates any odour transfers between the fridge and freezer compartments, while the plumb-in IceMaker provides an ample supply of perfect ice cubes.

Opt for our stainless steel panels and handles for that extra touch of elegance!

Technical data see page 104.

The spacious freshness centre.

Seamlessly integrated with your custom kitchen cabinetry via the door-on-door system, the 91 cm wide built-in ECBN 6156 Fridge-Freezer is a real eye-catcher.

The generous fridge space and adjacently arranged BioFresh compartments coupled with two NoFrost freezer drawers on telescopic rails offer optimum storage for all types of food. The plumbed-in IceMaker automatically keeps you topped up with the finest quality ice cubes so that you are prepared for every occasion.

Opt for our stainless steel panels and handles for that extra touch of elegance!

Technical data see page 104.

Bio
Fresh

No
Frost

Duo
Cooling

Ice
Maker





Bio
Fresh

No
Frost

Duo
Cooling

Ice
Maker

ECBN 5066

More space for fresh ideas.

At 76 cm wide, the built-in ECBN 5066 Fridge-Freezer is a slimmer version of the ECBN 6156 model. Features a special satin-finish on the LED light cover to create an appealing and sophisticated interior ambience.

Two BioFresh drawers allows you to organise different types of foods through targeted humidity. The DrySafe is perfect for meat, fish, and dairy products while the HydroSafe keeps fresh fruits and vegetables crisp and fresh for longer. Our plumbed-in IceMaker automatically keeps you topped up with ice to keep you cool in the heat.

Opt for our stainless steel panels and handles for that extra touch of elegance!

Technical data see page 105.



The smooth operator.

A unique pull-out model, the SUIKo 1550 Undercounter Fridge serves as a great option for kitchen islands.

Mounted on soft telescopic rails to enhance user-friendliness and convenience, it comes with a practical bottle shelf and removable fruit and vegetable drawer. The large drawer can also be divided into two equal-sized compartments, with further storage space underneath.

SuperCool function quickly reduces temperature which is perfect for rapidly cooling down freshly stored food. The innovative LED light and special satin finish of the light cover produces a pleasant lighting atmosphere.

Technical data see page 106.



Convenience at your fingertips.

Our space-saving undercounter appliances are the practical choice for compact living spaces. The SUIK 1510 Undercounter Fridge is great for fresh produce with height-adjustable glass shelves to ensure maximise storage flexibility.

The perfect companion for this undercounter fridge is the SUIG 1514 Undercounter Freezer with SmartFrost technology, allowing food to freeze faster and reducing ice build-up to make defrosting simpler and quicker.

Both models are equipped with innovative SoftSystem technology which ensures that the appliance door closes gently and automatically from an opening angle of approximately 30°. No ventilation grill is needed in your worktop as airflow enters and exits from the front of both undercounter models.

Technical data see page 107.

Soft
System

Smart
Frost







Wine cabinets





On/Off Ventilation Light

5.8°C
16

Zone
Up
Down
Alarm

Unique features.



LED lighting

The LED lighting in the individual wine compartments can be dimmed to give a pleasing ambient light inside the appliance. All Vinidor appliances are equipped with this innovative, no-heat LED lighting concept. The LED lighting can also be adjusted to operate continuously or in conjunction with door openings.



Insulated glass door

Liebherr wine cabinets come with insulated glass doors with special UV protection. The double-glazed construction means that most of the damaging UV radiation is reflected away. In addition, LED lighting guarantees perfect illumination of the wine cabinet interior without risk of UV exposure.



FreshAir activated charcoal filter

Environmental odours can have an wine stored for longer periods. Fresh air is supplied to Liebherr wine cabinets through the easily replaceable FreshAir activated charcoalfilter to ensure optimal air quality.



Handcrafted beechwood shelves

Our natural, handcrafted, and untreated beechwood shelves release no chemical aromas into the environment that could adversely influence the flavour of wine. In addition, wooden shelves contribute to the reduction of vibrations which allows wine to develop in peace.



Touch electronic control system

Our touch electronic control system is easy to navigate and enables tailored storage options. Temperature can be set between +5°C and +20°C based on your preference. In our multi-temperature models, each wine safe can be controlled independently, allowing different types of wine to be stored in one wine cabinet.



Compressor

Specially developed compressors installed in the wine cabinets from Liebherr ensure that the wines are stored in a particularly low vibration environment.




LED

Wine

Soft System

Telescopic Rails

WTes 5872



Created for true wine connoisseurs.

The WTes 5872 Multi-temperature Wine Cabinet satisfies your thirst for the smartest, most elegant ways to store wine. It adds sophisticated flair to entertainment areas while providing ideal conditions for wine to mature successfully. With three adjustable temperature zones, you can simultaneously store red wine, white wine, and champagne all at their optimum serving temperature between +5 °C and +20 °C.

An insulated glass door protects wines from damaging UV radiation while the presentation shelves allow the perfect display of your finest collection. Specially developed compressors provide a low vibration environment and telescopic rails help shelves to slide out gently without causing sudden movements that could damage your wine. An activated charcoal filter provides a permanent supply of odourless, fresh air.

Impress your guests with what is a true wine storage unit. Also available in two temperature zones as WTes 5972.

Technical data see page 108.



Wine

LED

WKT 6451

Quality wines deserve quality storage.

The WKt 6451 Wine Cabinet offers similar conditions to an underground wine cellar. Its solid door means that chances of condensation are reduced, making it easier to maintain in a tropical climate.

The handcrafted, untreated beechwood shelves release no chemical aromas into the environment that could adversely influence the flavour of wine. In addition, wooden shelves contribute to the reduction of vibrations which allows wine to develop in peace.

With the capacity to hold up to 312 Bordeaux bottles (0.75 litres), this jumbo model is one of the largest wine cabinets in the market – the perfect choice for serious wine collectors with a huge range of wine bottles to mature.

Technical data see page 109.



LED

Wine

Soft System

Telescopic Rails

EWtdf 3553

Savour the difference with a Liebherr.

Like a shaken bottle of champagne, the EWTdf 3553 dual-zone wine cellar is absolutely exploding and overflowing with innovative features.

Its touchscreen controls are integrated into the insulation layer between the temperature zones, allowing you to set two different temperatures within the unit and simultaneously store red and white wines, each at its optimum drinking temperature. An insulated glass door protects your favourite collection from UV exposure while handcrafted beechwood shelves on telescopic rails reduces vibrations, allowing wines to develop in peace.

Seamlessly fit this built-in model into your customised kitchen décor or turn it into a stainless steel masterpiece with our selection of accessories.

Technical data see page 110.



reddot award 2018
winner



LED

Wine

Telescopic
Rails

UWTes 1672 | UWKes 1752

A cabinet full of treasures.

The UWKes 1752 Undercounter Wine Cabinet is ideal for storing wines for extended periods, allowing them to mature to perfection. Its LED lighting ensures uniform illumination of the interior without any damages caused by UV light.

If you like reds, whites, as well as champagne, pair the UWKes 1752 with our dual-temperature zone model UWTeS 1672. Now enjoy your favourite bottles all stored at their desired temperatures between +5 °C to +20 °C!

Technical data see page 111.





LED

Wine

Telescopic
Rails

WKEes 553

Classic and sleek, fits anywhere.

Take advantage of the design flexibility of Liebherr's fully integrated WKEes 553 Wine Cabinet – Place this sleek, modular model anywhere in your home and proudly display your best wine collection at eye level.

Temperature is adjustable from +5 °C to +20 °C and the LED ceiling light is dimmable to cast a cool glow across the room. The insulated glass door with UV protection and activated charcoal filter protects your wine from light and odour. This compact unit holds up to 18 Bordeaux bottles in an ideal storage environment.

Technical data see page 110.





LIEMER

120L

Liebherr Barrique





Unique features.



LED lighting

The tinted glass door provides not only a perfect UV protection, but also an optimum glance at wine. The integrated LED lighting ensures a pleasant illumination of the complete interior.



Precision electronics

The precise electronic control system is equipped with a digital temperature display. The door and temperature alarm alerts of any irregularities, e.g. when the door is left open. The integrated lock on the front panel prevents unwanted access to the stored bottles.



Handcrafted beechwood shelves

Our natural, handcrafted, and untreated beechwood shelves release no chemical aromas into the environment that could adversely influence the flavour of wine. In addition, wooden shelves contribute to the reduction of vibrations which allows wine to develop in peace.



Presentation shelf

The presentation shelf, equipped with wooden angles, is ideal for presenting wine and storing open bottles safely. Up to 6 bottles can be set upright on the flexible shelf. In addition further bottles can be stored lying down either behind or at the side.



Optimum humidity

Liebherr wine cabinets guarantee an optimum humidity and this ensured the corks are supple in place whilst still allowing the wine to breathe in its maturing process.



Activated charcoal filter

The easy replaceable active charcoal filter purifies the incoming air to obtain an optimum odour-free interior.




LIEBHERR

LED

Wine

WKb 4612



Perfect display for all your favourites.

With the capacity to hold 195 Bordeaux bottles, the spacious Liebherr Barrique WKb 4612 Wine Cabinet is ideal for the long-term storage and maturation of wines.

Constant temperature can be set as desired between +5 °C to +20 °C via the intuitive control system with digital temperature display.

Thanks to its coated glass door, wines will always be well-protected from UV radiation. Efficient LED lighting ensures that the interior is illuminated evenly and pleasantly, allowing you to proudly showcase your prized collection.

Also available in a shorter height as WKb 4112 with the capacity to store 168 Bordeaux bottles.

Technical data see page 112-113.

Wine storage sophistication for your home.


The WKb 4611 Wine Cabinet mimics the conditions of an underground wine cellar where its solid door creates a dark, undisturbed environment with zero exposure to UV light and heat fluctuations – perfect for maturing wines.

When humidity level falls below 50%, natural corks begin to shrink, causing oxygen to enter the bottle and damage stored wines. With a humidity range between 50% – 80%, Liebherr wine cabinets guarantee the ideal conditions to preserve the suppleness of wine corks which in turn prevents oxidation.

Your wines are always stored safely on our untreated beech wood shelves while an activated charcoal filter provides optimal air quality.

Technical data see page 112.






WKb 4611



LED

Wine

WKgb 4113



The storage choice for wine aficionados.

The Liebherr Barrique WKgb 4113 Wine Cabinet features an insulated full-glass, black door that provides protection from UV radiation and preserves the quality of wine.

Temperature can be adjusted between +5°C to +20°C and is ideal for the long-term storage of fine wines – be it for maturing or storage. Our integrated activated carbon filter absorbs odours from the ambient air and prevents the taste of fine wines from being impaired.

With its elegantly designed recessed handle, this wine cabinet looks perfect in any home or restaurant.

Technical data see page 113.

Superb conditions for fine wines.

Our most compact model from the Liebherr Barrique series, the WKb 1712 Wine Cabinet can store up to 60 Bordeaux bottles. Wines are stored optimally on three untreated, height-adjustable beech wood shelves.

Wines are well protected from UV radiation thanks to a tinted insulated glass door while the activated charcoal filter provides optimum air quality and is easy to replace.

Energy-efficient LED lighting ensures even and pleasant illumination so that your favourite bottles are seen in the best light.

Technical data see page 114.







Design and lifestyle





LIEBHERR

GrandCru



Light



Up



Down

18°C



On/Off



Ventilation



Alarm

CIOCCOLATO FONDENTE
BITTER CHOCOLATE
EXTRA 70%
CHUAO
MEDEI
LIBRERIA

MOLIBDA
24 Napoli

MEDEI
LIBRERIA

MEDEI
LIBRERIA

Unique features.



LED lighting in humidor

Liebherr's ZKes 453 has LED lighting with dimmer function incorporated in the glass door. As the LEDs emit virtually no heat, the cigars can be exposed to the light for long periods of time without damage.



LED lighting in wine cabinet

For ideal presentation of your best wine, the WKes 653 features LED lighting with dimmer function and separate switch. As the LEDs emit minimal heat and no UV radiation, wine can be showcased bathed in light for lengthy periods without compromising its quality.



Fine cedar wood

Our ZKes 453 humidor features two presentation boxes and two wooden shelves crafted from Spanish cedar wood. The presentation boxes are perfect for storing loose cigars.



Wall mount option

Both the WKes 653 wine cabinet and ZKes 453 humidor can be wall-mounted as an attractive eye-catcher with convenient access for serving.



Ideal humidity

The integrated water tray can accommodate one liter of distilled water for ideal humidity. Sensors regulate precise humidity level selected. The display informs when water needs to be replenished.



Touch electronic control system

The perfect wine storage temperature is +8°C to +12°C. White wine should ideally be stored below +10°C and red wine at up to +18°C. Our electronic control system allows temperature to be set to the exact degree required between +5°C to +20°C.



LED

Wine

Smart
Steel

Cigar

WKes 653 | ZKes 453

The perfect indulgence.

The ZKes 453 Humidor offers the perfect micro-climate for storing beloved cigars through fully-customisable humidity settings. Natural, handmade cigars are both delicate and sensitive, requiring a balanced mix of temperature and humidity to achieve the optimum flavour. The compartments in our humidor are crafted from Spanish cedar wood which allows its aroma to enhance the unique flavour of refined cigars.

For the perfect indulgence, pair the humidor with our WKes 653 Wine Cabinet. It has a compact footprint yet manages to hold up to 12 Bordeaux bottles. LED lighting and dimmer function ensures perfect illumination for your selection of coveted wines.

Coated with a beautiful SmartSteel surface, both units are easy to clean and maintain. Opt to wall-mount this stunning pair to give it the attention it deserves.

Technical data see page 115.



Freestanding



←121→



SBSes 8486 PremiumPlus



Energy consumption (kWh/y)	405
Max. No. of Bordeaux bottles (0.75l) *	48
Refrigerator capacity litre	366
BioFresh comp. litre	132
Wine comp. litre	153
Freezer capacity litre	126
Number of shelves / Number of door racks	10 / 5
Number of BioFresh drawers	3 with LED lighting
Number of freezer drawers	5 with LED lighting
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	stainless steel with SmartSteel / stainless steel with SmartSteel
Refrigerator temperature range °C	+2 °C to +9 °C
Freezer temperature range °C	-14 °C to -26 °C
Wine temperature range °C	+5 °C to +20 °C
Temperature alarm / Defrost type	visual and acoustic / automatic
Interior light	LED ceiling lighting with dimmer function
Door alarm	visual and acoustic
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	1.2
SoftSystem	yes
Door hinges	left / right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Net weight kg / Voltage V/Hz	159 / 220 - 240 / 50 / 60



Installation Diagram







SBSes 8484
PremiumPlus



Energy consumption (kWh/y)	398
Refrigerator capacity litre	538
BioFresh comp. litre	304
Freezer capacity litre	126
Number of shelves	8
Number of door racks	5
Number of freezer drawers	5 with LED lighting
Number of BioFresh drawers	5 with LED lighting
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	stainless steel with SmartSteel / stainless steel with SmartSteel
Refrigerator temperature range °C	+2 °C to +9 °C
Freezer temperature range °C	-14 °C to -26 °C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting with dimmer function
Door alarm	visual and acoustic
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	1.2
SoftSystem	yes
Door hinges	left / right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Net weight kg	163.6
Voltage V/Hz	220 - 240/50/60



Installation Diagram



Freestanding





SBSes 8474
Premium



Energy consumption (kWh/y)	398
Refrigerator capacity litre	539
BioFresh comp. litre	305
Freezer capacity litre	126
Number of shelves	8
Number of door racks	5
Number of freezer drawers	5 with LED lighting
Number of BioFresh drawers	5 with LED lighting
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	stainless steel with SmartSteel / stainless steel with SmartSteel
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-14°C to -26°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting with dimmer function
Door alarm	visual and acoustic
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	1.2
SoftSystem	yes
Door hinges	left / right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Net weight kg	163.6
Voltage V/Hz	220 - 240/50/60



Installation Diagram






SBSes 8683
PremiumPlus



Energy consumption (kWh/y)	405
Refrigerator capacity litre	366
BioFresh comp. litre	132
Freezer capacity litre	262
Number of shelves	6
Number of door racks	5
Number of BioFresh drawers	3 with LED lighting
Number of freezer drawers	9
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	stainless steel with SmartSteel / stainless steel with SmartSteel
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-14°C to -28°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED interior lighting / LED ceiling lighting with dimmer function
Door alarm	visual and acoustic
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	0.8
SoftSystem	yes
Door hinges	left / right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Net weight kg	164
Voltage V/Hz	220 - 240/50/60



Installation Diagram



Freestanding





SBSbs 8673
Premium



Energy consumption (kWh/y)	405
Refrigerator capacity litre	367
BioFresh comp. litre	133
Freezer capacity litre	262
Number of shelves	6
Number of door racks	5
Number of BioFresh drawers	3 with LED lighting
Number of freezer drawers	9
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	BlackSteel with SmartSteel / BlackSteel with SmartSteel
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-14°C to -28°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED interior lighting
Door alarm	visual and acoustic
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	0.8
SoftSystem	yes
Door hinges	left / right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Net weight kg	164.5
Voltage V/Hz	220 - 240/50/60



Installation Diagram







SBSes 8673
Premium



Energy consumption (kWh/y)	405
Refrigerator capacity litre	367
BioFresh comp. litre	133
Freezer capacity litre	262
Number of shelves	6
Number of door racks	5
Number of BioFresh drawers	3 with LED lighting
Number of freezer drawers	9
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	stainless steel with SmartSteel / stainless steel with SmartSteel
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-14°C to -28°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED interior lighting
Door alarm	visual and acoustic
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	0.8
SoftSystem	yes
Door hinges	left / right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Net weight kg	164
Voltage V/Hz	220 - 240/50/60



Installation Diagram



Freestanding




SBSef 7242
Comfort

Energy consumption (kWh/y)	589
Refrigerator capacity litre	381
Freezer capacity litre	253
Number of shelves	7
Number of door racks	5
Number of fruit and vegetable drawers	2
Number of freezer drawers	8
Electronic control	MagicEye with digital temp. display, touch electronic
Door /side walls	stainless steel with SmartSteel / silver
Refrigerator temperature range °C	+1 °C to +9 °C
Freezer temperature range °C	-14 °C to -26 °C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting
Door alarm	acoustic
Door hinges	left / right
Product dimensions (H/W/D) cm	185.2/121/62.3
Net weight kg	151.5
Voltage V/Hz	220 - 240/50/60



Installation Diagram





CNPef 4516
Comfort

Energy consumption (kWh/y)	360
Refrigerator capacity litre	331
Freezer capacity litre	82
Number of shelves	5
Number of door racks	4
Number of freezer drawers	2
Number of fruit and vegetable drawers	2 with LED lighting
Electronic control	MagicEye with LCD temp. display, touch electronic
Door / side walls	stainless steel with SmartSteel / silver
Refrigerator temperature range °C	+2°C to +7°C
Freezer temperature range °C	-14°C to -27°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting
Door alarm	acoustic
Door hinges	right, reversible
Product dimensions (H/W/D) cm	185.9 / 74.7 / 63
Net weight kg	95
Voltage V/Hz	220 - 240/50




CNef 4315
Comfort




Energy consumption (kWh/y)	202
Refrigerator capacity litre	220
Freezer capacity litre	101
Number of shelves	4
Number of door racks	3
Number of freezer drawers	3
Number of BioCool drawers	1
Electronic control	2.4" TFT-monochrome temp. display, touch electronic
Door / side walls	stainless steel with SmartSteel / silver
Refrigerator temperature range °C	+1°C to +9°C
Freezer temperature range °C	-14°C to -26°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting
Door alarm	visual and acoustic
Door hinges	right, reversible
Product dimensions (H/W/D) cm	185 / 60 / 66.5
Net weight kg	74.8
Voltage V/Hz	220 - 240/50/60



Installation Diagram



Installation Diagram



Fully Integrated



ICBNh 5173

Peak

Energy consumption (kWh/y)	181
Refrigerator capacity litre	172
BioFresh comp. litre	69
Freezer capacity litre	67
Number of shelves	4
Number of door racks	2
Number of freezer drawers	3
Number of BioFresh drawers	2 with LED lighting
Electronic control	2.4" TFT-colour display, Touch & Swipe
Refrigerator temperature range °C	+3 °C to +9 °C
Freezer temperature range °C	-15 °C to -26 °C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED light panel on both sides
Door alarm	visual and acoustic
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	1.2
SoftSystem	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	177 / 55.9 / 54.6
Cut out dimensions (H/W/D) cm	177.2-178.8 / 56-57 / 55
Net weight kg	78
Voltage V/Hz	220 - 240/50-60




ICNh 5173

Peak


Energy consumption (kWh/y)	176
Refrigerator capacity litre	174
Freezer capacity litre	69
Number of shelves	6
Number of door racks	3
Number of freezer drawers	3 with LED lighting
Number of EasyFresh drawers	1
Electronic control	2.4" TFT-colour display, Touch & Swipe
Refrigerator temperature range °C	+2 °C to +9 °C
Freezer temperature range °C	-15 °C to -26 °C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED light panel on both sides
Door alarm	visual and acoustic
SoftSystem	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	177 / 55.9 / 54.6
Cut out dimensions (H/W/D) cm	177.2-178.8 / 56-57 / 55
Net weight kg	66
Voltage V/Hz	220 - 240/50/60



Installation Diagram



* Recommended: 560 mm



* Recommended: 560 mm



ICNh 5133
Plus




ICNh 5123
Plus

Energy consumption (kWh/y)	182
Refrigerator capacity litre	182
Freezer capacity litre	67
Number of shelves	6
Number of door racks	3
Number of freezer drawers	3
Number of EasyFresh drawers	1
Electronic control	LCD display monochrome, touch electronic
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-15°C to -26°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting
Door alarm	visual and acoustic
IceMaker	watertank
Ice cube output kg/24h	1.2
SoftSystem	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	177 / 55.9 / 54.6
Cut out dimensions (H/W/D) cm	177.2-178.8 / 56-57 / 55
Net weight kg	66
Voltage V/Hz	220 - 240/50-60

Energy consumption (kWh/y)	176
Refrigerator capacity litre	182
Freezer capacity litre	69
Number of shelves	6
Number of door racks	3
Number of freezer drawers	3
Number of EasyFresh drawers	1
Electronic control	LCD display monochrome, touch electronic
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-15°C to -26°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting
Door alarm	visual and acoustic
SoftSystem	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	177 / 55.9 / 54.6
Cut out dimensions (H/W/D) cm	177.2-178.8 / 56-57 / 55
Net weight kg	66
Voltage V/Hz	220 - 240/50-60




Installation Diagram



* Recommended: 560 mm

Installation Diagram



* Recommended: 560 mm

Fully Integrated



↑
178
↓


ICNh 5103

Pure

Energy consumption (kWh/y)	250
Refrigerator capacity litre	182
Freezer capacity litre	69
Number of shelves	4
Number of door racks	3
Number of freezer drawers	3
Number of EasyFresh drawers	1
Electronic control	LCD display monochrome, touch electronic
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-15°C to -26°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting
Door alarm	visual and acoustic
Door hinges	right, reversible
Product dimensions (H/W/D) cm	177 / 55.9 / 54.6
Cut out dimensions (H/W/D) cm	177.2-178.8 / 56-57 / 55
Net weight kg	62.2
Voltage V/Hz	220 - 240/50-60



Installation Diagram



* Recommended: 560 mm



SIGN 3576
Premium




SIKB 3550
Premium

Energy consumption (kWh/y)	331
Freezer capacity litre	207
Number of freezer drawers	9
Electronic control	MagicEye with LCD temp. display, touch electronic
Freezer temperature range °C	-15 °C to -28 °C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED interior lighting
Door alarm	acoustic
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	0.8
SoftSystem	yes
Door hinges	left, reversible
Product dimensions (H/W/D) cm	177-178.6 / 55.9 / 54.4
Cut out dimensions (H/W/D) cm	177.2-178.8 / 56-57 / 55
Net weight kg	73.9
Voltage V/Hz	220 - 240/50

Energy consumption (kWh/y)	149
Refrigerator capacity litre	308
BioFresh comp. litre	92
Number of shelves	8
Number of door racks	5
Number of BioFresh drawers	3 with LED lighting
Electronic control	MagicEye with LCD temp. display, touch electronic
Refrigerator temperature range °C	+3 °C to +9 °C
Defrost type	automatic
Interior light	LED light column on both sides
Door alarm	acoustic
SoftSystem	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	177-178.6 / 55.9 / 54.4
Cut out dimensions (H/W/D) cm	177.2-178.8 / 56-57 / 55
Net weight kg	75
Voltage V/Hz	220 - 240/50

- No Frost
- LED
- Ice Maker
- Soft System
- Telescopic Rails
- Vario Space
- Super Frost


Installation Diagram



* Recommended: 560 mm

- Bio Fresh
- Soft System
- Soft-Telescopic Rails
- Super Cool

Installation Diagram



* Recommended: 560 mm

Fully Integrated



← 91 → 203

ECBN 6256
PremiumPlus

Energy consumption (kWh/y)	487
Refrigerator capacity litre	357
BioFresh comp. litre	68
Freezer capacity litre	114
Number of shelves / Number of door racks	4 / 6
Number of freezer drawers	2 with LED lighting
Number of BioFresh drawers	2 with LED lighting
Electronic control	MagicEye with digital temp. display, touch electronic
Refrigerator temperature range °C	+3°C to +9°C
Freezer temperature range °C	-14°C to -28°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED light column on both sides and LED ceiling lighting
Door alarm	acoustic
Water filter	yes
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	1.3
SoftSystem	yes
Door hinges	left / right
Product dimensions (H/W/D) cm	202.7 / 91 / 61
Cut out dimensions (H/W/D) cm	203.2-207.2 / 91.5 / 63.5
Net weight kg	161
Voltage V/Hz	220 - 240/50




← 91 → 203

ECBN 6156
PremiumPlus


Energy consumption (kWh/y)	496
Refrigerator capacity litre	364
BioFresh comp. litre	69
Freezer capacity litre	116
Number of shelves	4
Number of door racks	6
Number of freezer drawers	2 with LED lighting
Number of BioFresh drawers	2 with LED lighting
Electronic control	MagicEye with digital temp. display, touch electronic
Refrigerator temperature range °C	+3°C to +9°C
Freezer temperature range °C	-14°C to -28°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED light column on both sides and LED ceiling lighting
Door alarm	acoustic
Water filter	yes
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	1.3
Door hinges	right
Product dimensions (H/W/D) cm	202.7 / 91 / 61
Cut out dimensions (H/W/D) cm	203.2-207.2 / 91.5 / 63.5
Net weight kg	164
Voltage V/Hz	220 - 240/50



Installation Diagram



Installation Diagram






ECBN 5066
PremiumPlus

Energy consumption (kWh/y)	304
Refrigerator capacity litre	276
BioFresh comp. litre	57
Freezer capacity litre	103
Number of shelves	4
Number of door racks	3
Number of freezer drawers	2 with LED lighting
Number of BioFresh drawers	2 with LED lighting
Electronic control	MagicEye with digital temp. display, touch electronic
Refrigerator temperature range °C	+3°C to +9°C
Freezer temperature range °C	-14°C to -28°C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED light column on both sides
Door alarm	acoustic
Water filter	yes
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	1.0
Door hinges	right, reversible
Product dimensions (H/W/D) cm	202.4 / 75.7 / 61
Cut out dimensions (H/W/D) cm	203.2-207.2 / 76.2 / 63.5
Net weight kg	147
Voltage V/Hz	220 - 240/50



Installation Diagram



Undercounter



Side
by
Side

↑
82-88
↓


SUIKo 1550 Premium

Energy consumption (kWh/y)	158
Refrigerator capacity litre	124
Number of shelves	2
Number of fruit and vegetable drawers	1
Electronic control	MagicEye with LCD temp. display, key electronic
Refrigerator temperature range °C	+2 °C to +9 °C
Defrost type	automatic
Interior light	LED ceiling lighting
Door alarm	visual and acoustic
Door type	steel
Door hinges	pullout
Product dimensions (H/W/D) cm	82-88 / 59.7 / 55
Cut out dimensions (H/W/D) cm	82-88 / 60 / 55
Net weight kg	41.5
Voltage V/Hz	220 - 240/50

Soft-
Telescopic
Rails

Super
Cool

Installation Diagram





SUIG 1514
Comfort

Energy consumption (kWh/y)	168
Freezer capacity litre	95
Number of freezer drawers	3
Electronic control	MagicEye with LCD temp. display, key electronic
Freezer temperature range °C	-14 °C to -26 °C
Defrost type	manual
Door alarm	visual and acoustic
Door type	steel
SoftSystem	yes
Door hinges	left, reversible
Product dimensions (H/W/D) cm	82-88 / 59.7 / 55
Cut out dimensions (H/W/D) cm	82-88 / 60 / 55
Net weight kg	38.2
Voltage V/Hz	220 - 240/50




SUIK 1510
Comfort

Energy consumption (kWh/y)	147
Refrigerator capacity litre	136
Number of shelves	4
Number of door racks	2
Number of fruit and vegetable drawers	1
Electronic control	MagicEye with LCD temp. display, key electronic
Refrigerator temperature range °C	+2 °C to +9 °C
Defrost type	automatic
Interior light	LED interior lighting
Door alarm	visual and acoustic
Door type	steel
SoftSystem	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	82-88 / 59.7 / 55
Cut out dimensions (H/W/D) cm	82-88 / 60 / 55
Net weight kg	34.5
Voltage V/Hz	220 - 240/50/60


Smart Frost Soft System Vario Space

Installation Diagram



Soft System Super Cool

Installation Diagram



Wine Cabinets



WTes 5872
Vinidor

Energy consumption (kWh/y)	245
Total capacity litre	511
Max. No. of Bordeaux bottles (0.75l) *	178
Total no. of storage shelves (incl. bottom compartment)	13
Shelves on telescopic rails	10
Shelf material	beech wood shelves
Presentation shelf	1
Electronic control	LCD temp. display for 3 wine zones, touch electronic
Temperature range °C	+5°C to +20°C
Temperature zones	3
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	glass door with stainless steel frame
Integrated lock	yes
SoftSystem	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	192 / 70 / 74.2
Net weight kg	137
Voltage V/Hz	220 - 240/50




WTes 5972
Vinidor


Energy consumption (kWh/y)	248
Total capacity litre	526
Max. No. of Bordeaux bottles (0.75l) *	211
Total no. of storage shelves (incl. bottom compartment)	10
Shelves on telescopic rails	8
Shelf material	beech wood shelves
Presentation shelf	1
Electronic control	LCD temp. display for both wine zones, touch electronic
Temperature range °C	+5°C to +20°C
Temperature zones	2
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	glass door with stainless steel frame
Integrated lock	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	192 / 70 / 74.2
Net weight kg	125
Voltage V/Hz	220 - 240/50



Installation Diagram



Installation Diagram



*These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).




WKt 6451
GrandCru


Energy consumption (kWh/y)	143
Total capacity litre	625
Max. No. of Bordeaux bottles (0.75l) *	312
Total no. of storage shelves (incl. bottom compartment)	7
Shelf material	beech wood shelves
Electronic control	MagicEye with digital temp. display, key electronic
Temperature range °C	+5°C to +20°C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED interior lighting
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	full door, terra
Integrated lock	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	193 / 74.7 / 75.9
Net weight kg	87
Voltage V/Hz	220 - 240/50



Installation Diagram



* The specified number of bottles (=maximum capacity) is only possible with this arrangement of the height-adjustable shelves.



Wine Cabinets



reddot award 2018 winner

178

EWTdf 3553

Vinidor

Energy consumption (kWh/y)	162
Total capacity litre	256
Max. No. of Bordeaux bottles (0.75l) *	80
Total no. of storage shelves (incl. bottom compartment)	10
Shelves on telescopic rails	8
Shelf material	beech wood shelves
Presentation shelf	1
Electronic control	LCD temp. display for both wine zones, touch electronic
Temperature range °C	+5°C to +20°C
Temperature zones	2
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	panel ready or stainless steel panel as accessory
SoftSystem	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	177 / 55.7 / 55.3
Cut out dimensions (H/W/D) cm	177.2-178 / 56-57 / 55
Net weight kg	91
Voltage V/Hz	220 - 240/50



45


WKEes 553

GrandCru


Energy consumption (kWh/y)	130
Total capacity litre	47
Max. No. of Bordeaux bottles (0.75l) *	18
Total no. of storage shelves (incl. bottom compartment)	3
Shelves on telescopic rails	2
Shelf material	beech wood shelves
Electronic control	LCD temp. display, touch electronic
Temperature range °C	+5°C to +20°C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Activated Charcoal filter	yes
Door type	glass door with stainless steel frame
Door hinges	right, reversible
Product dimensions (H/W/D) cm	44.1 / 55.7 / 52.2
Cut out dimensions (H/W/D) cm	45 / 56 / 55
Net weight kg	30
Voltage V/Hz	220 - 240/50



Installation Diagram



Installation Diagram





82-87

UWTes 1672

Vinidor



82-87

UWKes 1752


GrandCru

Energy consumption (kWh/y)	190
Total capacity litre	94
Max. No. of Bordeaux bottles (0.75l) *	34
Total no. of storage shelves (incl. bottom compartment)	5
Shelves on telescopic rails	3
Shelf material	beech wood shelves
Electronic control	MagicEye with digital temp. display for both wine zones, key electronic
Temperature range °C	+5°C to +20°C
Temperature zones	2
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	glass door with stainless steel frame
Integrated lock	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	81.8 / 59.7 / 57.7
Cut out dimensions (H/W/D) cm	82-87 / 60 / 58
Net weight kg	49
Voltage V/Hz	220 - 240/50


Energy consumption (kWh/y)	145
Total capacity litre	112
Max. No. of Bordeaux bottles (0.75l) *	46
Total no. of storage shelves (incl. bottom compartment)	4
Shelves on telescopic rails	3
Shelf material	beech wood shelves
Electronic control	MagicEye with digital temp. display, key electronic
Temperature range °C	+5°C to +20°C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	glass door with stainless steel frame
Integrated lock	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	81.8 / 59.7 / 57.7
Cut out dimensions (H/W/D) cm	82-87 / 60-61 / 58
Net weight kg	44
Voltage V/Hz	220 - 240/50



Installation Diagram



Installation Diagram



Liebherr Barrique Wine Cabinets



← 66 →

WKb 4612

Liebherr Barrique

Energy consumption (kWh/y)	204
Total capacity litre	336
Max. No. of Bordeaux bottles (0.75l) *	195
Total no. of storage shelves (incl. bottom compartment)	7
Shelf material	beech wood shelves
Presentation shelf	1
Electronic control	MagicEye with digital temp. display, key electronic
Temperature range °C	+5°C to +20°C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED interior lighting
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	Insulated glazed door, black frame
Integrated lock	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	184.2 / 65.7 / 66.3
Net weight kg	86
Voltage V/Hz	220 - 240/50



← 66 →


WKb 4611

Liebherr Barrique


Energy consumption (kWh/y)	175
Total capacity litre	336
Max. No. of Bordeaux bottles (0.75l) *	195
Total no. of storage shelves (incl. bottom compartment)	7
Shelf material	beech wood shelves
Electronic control	MagicEye with digital temp. display, key electronic
Temperature range °C	+5°C to +20°C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	light bulb
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	full door with handle, black
Integrated lock	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	184.2 / 65.7 / 66.3
Net weight kg	68.5
Voltage V/Hz	220 - 240/50



Installation Diagram



Installation Diagram





WKgb 4113
Liebherr Barrique

Energy consumption (kWh/y)	178
Total capacity litre	293
Max. No. of Bordeaux bottles (0.75l) *	168
Total no. of storage shelves (incl. bottom compartment)	6
Shelf material	beech wood shelves
Presentation shelf	1
Electronic control	MagicEye with digital temp. display, key electronic
Temperature range °C	+5 °C to +20 °C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	Full glass door with heating function
Integrated lock	yes
Door hinges	right
Product dimensions (H/W/D) cm	164.5 / 65.7 / 66.3
Net weight kg	78
Voltage V/Hz	220 - 240/50




WKb 4112
Liebherr Barrique


Energy consumption (kWh/y)	178
Total capacity litre	293
Max. No. of Bordeaux bottles (0.75l) *	168
Total no. of storage shelves (incl. bottom compartment)	6
Shelf material	beech wood shelves
Presentation shelf	1
Electronic control	MagicEye with digital temp. display, key electronic
Temperature range °C	+5 °C to +20 °C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED interior lighting
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	Insulated glazed door, black frame
Integrated lock	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	164.5 / 65.7 / 66.3
Net weight kg	78
Voltage V/Hz	220 - 240/50



Installation Diagram



Installation Diagram



Liebherr Barrique Wine Cabinets




WKb 1712

Liebherr Barrique

Energy consumption (kWh/y)	149
Total capacity litre	121
Max. No. of Bordeaux bottles (0.75l) *	60
Total no. of storage shelves (incl. bottom compartment)	3
Shelf material	beech wood shelves
Electronic control	MagicEye with digital temp. display, key electronic
Temperature range °C	+5°C to +20°C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED interior lighting
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	glass door with handle, frame black
Integrated lock	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	85 / 65.7 / 66.3
Net weight kg	45
Voltage V/Hz	220 - 240/50



Installation Diagram






WKes 653
GrandCru

Energy consumption (kWh/y)	75
Total capacity litre	38
Max. No. of Bordeaux bottles (0.75l) *	12
Total no. of storage shelves (incl. bottom compartment)	3
Shelf material	beech wood shelves
Electronic control	LCD temp. display, touch electronic
Temperature range °C	+5 °C to +20 °C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Activated Charcoal filter	yes
Door type	glass door with stainless steel frame and SmartSteel
Integrated lock	yes
Door hinges	right
Product dimensions (H/W/D) cm	61.2 / 42.5 / 47.8
Net weight kg	28
Voltage V/Hz	220 - 240/50



Installation Diagram




ZKes 453
Humidor

Energy consumption (kWh/y)	162
Total capacity litre	39
Total no. of storage shelves (incl. bottom compartment)	2
Shelf material	Spanish cedar wood shelves
Electronic control	LCD temp. display, touch electronic
Temperature range °C	+16 °C to +20 °C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Activated Charcoal filter	yes
Door type	glass door with stainless steel frame and SmartSteel
Integrated lock	yes
Door hinges	right
Product dimensions (H/W/D) cm	61.2 / 42.5 / 47.8
Net weight kg	30
Voltage V/Hz	220 - 240/50



Installation Diagram





Liebherr Appliances Flagship Store
70 Tras Street, Singapore 079009

E-mail: appliances.lsi@liebherr.com | Tel: 6226 2549 | Online Shop: home.liebherr.sg/shop



Visit our social media channels at
socialmedia.home.liebherr.com

home.liebherr.com

Products and their details are staged for advertising purposes. Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss. (080622)

Subject to modification. Current data see home.liebherr.com.
Printed in Singapore 2022.