

Static inverter

World class standalone
Power Electronics
tailored to market needs

LIEBHERR

Aerospace



Comprehensive power conversion range

- 28 VDC, 120 VAC 60 Hz single phase
- 28 VDC, 115 VAC 400 Hz single phase



Applications

- Linefit, retrofit or upgrade
- TSO / ETSO certification

Key features

- Wide band gap semi-conductor technology
- Fanless technology/passive cooling expertise
 - Reliability 200k OH
 - Lightweight
 - Noiseless
- Digital control and communication (CAN bus)
 - Smart monitoring and protection capability
- Discrete inputs/outputs
- Internal monitoring and protection
- Health management/predictive maintenance capabilities
- USB power plugs supply output in option

Liebherr-Aerospace & Transportation SAS

408, avenue des Etats Unis · B.P. 52010 · 31016 Toulouse Cedex 2, France
+33 5 61 35 2828 · www.liebherr.com · E-Mail: info.aer@liebherr.com