
Freshness without compromise

Discover our all-round worry-free appliances that set new standards in terms of freshness technology, efficiency and design.

LIEBHERR

Refrigeration and freezing





Cools. Saves. Impresses.

Fridges and freezers operate all day every day, which is why we have always worked on reducing energy consumption and noise. And our work has paid off, because we now offer the most energy-efficient and quietest appliances on the market.

In addition, we offer many well thought-out freshness technologies to suit all storage requirements, and help you keep food fresh for longer and avoid food waste due to premature spoiling. The design itself is also innovative. Many models now also feature black stainless steel inside – the elegant BlackSteel interior gives your purchases a truly eye-catching appearance.

This preview gives just a few highlights. With Liebherr, you know that you are getting a state-of-the-art appliance – whether in freshness technology, efficiency or design. This leaves you to concentrate on fully enjoying the contents. But first, please enjoy this brochure and discover even more innovations.



**10-year
Liebherr
warranty**

Increased sustainability through long product life and outstanding energy efficiency.



A
A-rated energy efficiency

Our freestanding fridge-freezers with energy efficiency class A are equipped with the best possible buying arguments: outstanding energy efficiency, clever freshness technologies, and long-lasting Liebherr quality. And that comes with a 10-year warranty. That's how to convince you sustainably. (See all models on page 42.)

Contents

6	History	26	VarioTemp
8	Sustainability	27	Convenience and flexibility – freezing
10	Use phase	29	Design awards
12	Freshness technologies	30	Wine fridges
16	Energy efficiency	37	Brief overview: Freestanding appliances Fully integrated appliances Wine fridges
18	Design	52	Accessories
20	SmartDevice	53	Description of series
21	AutoDoor	54	Description of key equipment details
22	OpenStage		
23	Comfort and ergonomics when cooling		
24	Water and ice		



The full range of Liebherr freestanding and fully integrated appliances can be found in a brief overview from page 39 or on our website, which also includes Liebherr specialist dealers: home.liebherr.com

Innovation comes in many forms.

No matter what space or requirements you have, Liebherr is always the right choice. Whether you're looking for a chest freezer or a fridge. Whether you're looking for a huge side-by-side fridge-freezer, a freestanding or fully integrated appliance, or even a small under-worktop appliances. You will always benefit from our innovative strength and attention to detail. All for our goal: long-lasting freshness for your food.



Fridges



Fridge-freezers



Side-by-Side combinations



Freezers



Under counter and under-worktop appliances



Wine fridges

German engineering – then as now

We have been manufacturing refrigerators and freezers of the highest quality and selling them worldwide since 1954. However, at heart we are still a family business with our roots firmly established in Germany. This is where we continue to develop our long-lasting products. German engineering – born out of an enduring connection with our founder and in the knowledge that engineering expertise has been built up here for generations.



“My life has strengthened my belief that, with a firm resolve to do a good job and fulfil the customers’ various wishes to the best of your ability, it is possible to achieve goals that at first seem almost unattainable. Don’t be discouraged by setbacks, and you can move mountains if you believe in yourself.”

Dr.-Ing. e. h. Hans Liebherr (1915–1993)




The L 319 was Liebherr’s “mobile showcase” in the 1960s. Until 1968, the specially converted bus travelled around West Germany promoting the latest refrigerators and freezers from Upper Swabia.



SFNbdd 5227 | SRBdd 5220 ◊ Plus series



Our first appliances came off the production line in Ochsenhausen back in 1954. And this is exactly where our main factory is still located today.



Quality that will remain quality in 15 years.

Our aspiration to deliver quality is reflected even in the smallest details. Before we approve a door hinge, for example, it must undergo at least 100,000 opening cycles. And just like the door hinge, we test every other functional part extensively and intensively. All with one purpose in mind: ensuring that our appliances have a useful life of at least 15 years.



Our path to the future

One thing unites all our product innovations: they all present a path towards greater sustainability. Taking responsibility is one of our core values. That's why we have a decades-long tradition of research and development into eco-friendly products. During this work, we always have the entire product lifecycle in mind.



*** EcoVadis Gold**
We treat the issue of corporate responsibility holistically and at all stages of the product life cycle. Our efforts have been awarded gold award for 2023 by EcoVadis, the world's leading Corporate Social Responsibility ratings agency. We are proud to be among the top 3 percent of companies assessed by EcoVadis.

Recycling / disposal

We are aiming for a sustainable circular economy and actively design our products to maximise the re-use of the materials in them by making them easy to separate.

Materials

We want to minimise the environmental impact of our business activities and make recyclable products by using more renewable and recycled materials in our appliances and by reducing the variety of materials we use. In doing so, we look at the entire product.



Use phase

We reduce our environmental impact by continuing to offer first-class, energy-efficient products that are highly durable and easy to repair – supported by proactive customer service. We also offer you products and solutions that help you to reduce food waste. Find out more about this on the next pages.

Production

We aim for environmentally conscious production by lowering the energy consumption of our plants and increasing the use of renewable energy sources. By using water responsibly, minimising waste and avoiding pollution, we reduce our environmental impact by considering factors above and beyond CO₂ emissions.*



Save food with Liebherr

Around the world, every year around 931 million tonnes of food are thrown away¹. For an average household, this works out at approximately 113 kg annually².

113 kilograms²

The amount of discarded food breaks down roughly into the following groups²:



50% fresh fruit and vegetables



4% dairy products



5% meat and fish



7% cooked and ready-made food

Food does not just have personal and financial value, it also has environmental value.

Food production is responsible for³



of all global greenhouse emissions and



of freshwater consumption.

¹ UNEP Food Waste Index Report (2021)

² German Federal Environmental Agency (2021).



For a two-person household in Germany

³ Our World in Data (2022)



With our innovative freshness technologies and digital solutions, we can help you to reduce the amount of food you waste in very simple ways.

Alongside the ideal temperature, optimum humidity is crucial for perfect food storage. At Liebherr, we have developed innovative freshness technologies and improve them year after year for this very purpose. This way, food still tastes genuinely fresh even after several days, and loses none of its vitamins and nutrients. For each type of fresh food, we have just the right freshness technology:



DuoCooling



With our SmartDevice app, the appliance can be easily operated via smartphone or tablet. For example, settings can be changed from anywhere without having to open the appliance. This way, no cold air is lost, and that not only saves energy, but helps to prevent food waste.

Freshness technologies

Easy Fresh

+10 days

+8 days

+3 days

+10 days

The specified comparisons in days are relative to the normal fridge compartment.

Freshness technologies

Bio Fresh

+11 days

+12 days

+40 days

+48 days

+40 days

Fruit & Vegetable safe



EasyFresh – ideal for fruit and vegetables

Unpackaged fruit and vegetables feel right at home here. When stored at the same temperature as the fridge compartment and sealed airtight in the safe, lettuce, for example, is still crisp and fresh after seven days.



BioFresh – our all-rounder

The reliable BioFresh technology stores groceries at a temperature just above 0°C, much cooler than in the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable safe. Meat, fish and dairy products benefit from ideal conditions in the Meat & Dairy safe.



BioFresh Professional with HydroBreeze – refrigerate like a pro

A cold mist covers fruit and vegetables like a protective balm, ensuring crisp freshness and improving structure – the special wow effect for fruit and vegetables in the BioFresh Professional Safe.



BioFresh Professional with Fish & Seafood safe – like freshly caught fish from the market.

Particularly delicate foods like fish and seafood are best stored at icy temperatures and at low humidity. The constant temperature of -2°C in the Fish & Seafood safe is therefore ideal to keep items tasting fresh for longer.



DuoCooling – no drying out

Our basic technology in all fridge-freezers. The two completely separate cooling circuits ensure that there is no exchange of air between the fridge and freezer compartments. The food neither dries out nor spreads odour.



NoFrost – No more defrosting

The automatic defrosting function guarantees that frozen foods remain fresh. There is no longer a need to store frozen food temporarily during a manual defrost. The constant optimal freezing remains the same without interruptions.




The specified comparisons in days are relative to the normal fridge compartment.

Meat & Dairy safe



Maximum efficiency with Liebherr

Because they run 24 hours a day, the biggest environmental impact of fridges and freezers is the energy they consume while in use. They account for about a fifth of the electricity used by an average household.¹



Our appliances are real all-rounders. Besides the low power consumption of our entire product range, they also offer impressively low noise levels, plenty of space for food and intelligent sensor systems for the best refrigeration.

Energy consumption

Our appliances take top spots in the efficiency rankings or even outperform the highest efficiency class. This means they protect our precious environmental resources as well as your wallet.

Cooling volume

From the extra-large drawers down to the tiniest details, we make sure that not a litre of cooling volume is wasted, despite maximum energy efficiency.

Noise level

Kitchens are increasingly becoming part of our living space. That's why we not only aim for maximum energy efficiency, but also appliances that are noticeably quieter.

Refrigeration

Our appliances' intelligent sensor systems constantly adapt the refrigeration to current use – making them efficient and economical in everyday use, but fully up to the job when the weekly shopping arrives.

¹ German Federal Environmental Agency (2021). For an average household in Germany.

Another 10 percent more economical* than appliances in the highest energy efficiency class A: This means that our freestanding fridge-freezer has exceeded even Liebherr's own standards.

This ultra-efficient fridge-freezer in elegant BlackSteel is one of the most energy-efficient ever. The features leave nothing to be desired: The BioFresh safes ensure that food stays fresh for longer and EasyTwist Ice guarantees perfectly chilled drinks. Plus, the appliance is super quiet at just 29 dB(A).

* Compared to the threshold for maximum energy efficiency class A according to Regulation (EU) 2019/2016 (as of July 2023).

← 60 →



Ultra Efficient A -10%

Ultra Silent

29 db(A)

CBNbsa10 575i ◉ Prime series



Find out more at home.liebherr.com/bettertomorrow

10-year Liebherr warranty
Increased sustainability through long product life and outstanding energy efficiency.
A-rated energy efficiency

Our freestanding fridge-freezers with energy efficiency class A are equipped with the best possible buying arguments: outstanding energy efficiency, clever freshness technologies, and long-lasting Liebherr quality. And that comes with a 10-year warranty. That's how to convince you sustainably. (See all models on page 42.)

Make a statement.



CBNbsd 578i Δ Peak series

Attractive both inside and out:

Our appliances with a BlackSteel interior fit in but also stand out. The finest black stainless steel interior and exterior gives all BlackSteel freestanding appliances from the Peak and Prime series as well as selected Peak fully integrated appliances an exclusive and eye-catching look for you to enjoy every time you open the door.



Recessed grip

This handle does not extend into the room. The elegant recess blends in with your kitchen's sleek, handle-free design.



Handle with opening mechanism

The door handle adapts gently to your hand movement and is thus even easier to open.



Perfect fit

With InteriorFit, our freestanding appliances fit into the kitchen and save space – they do not require any lateral ventilation gap from the walls or adjacent furniture. Only the fridge door itself projects into your kitchen. Everything else is invisible.



Black Steel Interior


IRBbsci 5170 Δ Peak series



Always well connected

All our appliances are either factory-equipped with a network connection module or can be retrofitted with the SmartDeviceBox.

This way, you will benefit from the many possibilities of our SmartDevice app and from connecting all fridges or freezers in your existing smart home environment. Important status and alarm notifications are sent directly to your smartphone, for example notification of an open fridge door via the door alarm. But our SmartDevice app has even more to offer: As well as simple management and remote control of your appliances, the app also helps you with tips and tricks for your Liebherr. The perfect accessories for each appliance, access to instruction manuals and much more can also be found here.



home.liebherr.com/getsmart

You can download the SmartDevice app here:



One less task for you.

Our AutoDoor feature rounds off the handle-less kitchen perfectly, as the Liebherr appliances open automatically in response to a knocking signal, via the SmartDevice app or voice command.

Plus, the door does more than just open automatically, it makes things easier for you in every way by adjusting the settings to suit your needs. The opening angle and how long the door stays open for before it closes automatically closes can be individually selected. Anybody who still prefers to open and close our fully integrated appliances by hand is still of course free to do so.



Find out more about our automatic door on selected models at home.liebherr.com/autodoor

Freshness with zoom function


Our ergonomic drawers are very easy to use. They are particularly easy to reach, ensuring maximum visibility.



Our fully integrated refrigerator with OpenStage drawers can also be finished with a BlackSteel interior for an even higher-quality finish with greater contrast.

Transform your kitchen into a market stall

Inspired by display cabinets in fine delicatessens, the award-winning OpenStage drawers showcase all your groceries at a glance. All the contents of the fridge are presented with maximum clarity and are within easy reach ergonomically. We are setting new standards for ease of use and design. In the lower area, three additional BioFresh safes offer you the perfect climate for storing fruit and vegetables as well as meat, fish and dairy products.




reddot winner 2021

IRBPdi 5170 Δ Peak series



One drinks space. Two configurations.

The practical pull-out shelf provided on telescopic rails in the IRDe 51 is equipped with two removable bottle baskets for easy transport. However, a whole beverage crate can also be stored here if you need space for more drinks.



All clearly arranged

Our VarioSafe does not only create order for small food items, but is also height adjustable. Simply place VarioSafe in the fridge compartment that suits you best.



Spacious compartments combined


The GlassLine shelves in our under-counter models UIK o models retract gently using a self-closing mechanism. And the LiftUp-Box at the bottom of the UIKo 1560 slides upwards when it is pulled out for easy removal.



UIKo 1560

Specially designed for cool drinks

With Liebherr, your guests will never go without a perfectly cooled drink. This is thanks to the integrated cold water source and a never-ending supply of ice. The easy way to have constant refreshment.



Enough ice for even the largest party: the IceTower

The IceTower in our freezers sets new standards by combining two large compartments – the automatic IceMaker for up to 8 kg of ice cubes and another spacious compartment – large enough to store a few family-sized pizzas upright, for example. And because we wanted even more convenience, both sections glide on a pull-out shelf with telescopic rails. We have even thrown in an ice shovel, so your hands can stay warm while you handle so many chilled goods.



It's raining ice cubes: the IceMaker

Each day the IceMaker produces up to 130 ice cubes, which automatically drop into two drawers. When MaxIce is activated, it is even possible to speed up the production of ice cubes if more guests than expected arrive. The IceMaker is connected to the fresh water pipe. If no plumbed-in connection is available, there is also a model with a water tank in the fridge compartment.



Ice-cold water on tap with no heavy lifting

With the InfinitySpring, we bring a crystal clear, cold water source right into the heart of your kitchen, so you can always stay hydrated. This makes lugging of heavy crates and water in plastic bottles a thing of the past. This relieves the strain on your back and on our environment. Simple and sustainable.



Ice in an instant: EasyTwist Ice

Quickly rustle up a supply of ice cubes – without a plumbed-in connection. Simply fill the tank with water, let it freeze and then release the ice cubes with a twist. EasyTwist Ice is easy to clean, and is installed in most of the freestanding appliances of our Pure series. Alternatively, it can also easily be added as an accessory.



CBNsda 575i ◊ Prime series

No more defrosting thanks to NoFrost



No Frost

The NoFrost automatic defrosting function guarantees that frozen foods remain fresh.

There is no longer a need to store frozen food temporarily during a manual defrost, as the food is frozen with cooled re-circulated air and the air humidity is also diverted. This keeps the freezer compartment ice-free at all times, and food is no longer covered in frost. The constant optimal freezing remains the same without any interruptions.

Convenience and flexibility – freezing



Easy Open

Open the door multiple times with ease: EasyOpen

Have you experienced this problem? Once you've put your shopping away in the freezer, you notice that you've left something on the side and you have to pull hard to open the door again. This does not happen with a Liebherr: EasyOpen means the door can be opened multiple times in succession, conveniently and easily.



Refrigerator compartment (-2°C to +9°C)



Cellar compartment (+14°C)




Freezer compartment (-18°C)

VarioTemp

Versatile freshness with a freezer compartment that can also be a fridge.

With VarioTemp, the freezer compartment can also be converted to a cooling zone, or to a storage compartment at cellar temperature.

The details shown depend on the model.



When below zero is a big plus

No room for a freezer in the kitchen or other heated areas in your home? We have some great news: with FrostProtect, all components are designed for temperatures as low as -15°C, no matter what groceries you are storing. If the ambient temperature falls below 0°C, our freezers continue working just as efficiently, saving just as much energy and keeping your frozen food just as well protected. This means that you can put them in unheated spaces like a garden shed or garage, giving you more room for more important things.



Frost Protect



Perfect freshness for a vegetable rich diet:

This Liebherr with two fruit and vegetable safes guarantees plenty of space and ideal conditions for keeping vegetables fresh and tasty. The clever FlexSystem in each BioFresh drawer keeps everything tidy and easy to find. Perfect freshness for a vegetable rich diet.



CBNsfcc 57vi ◊ Plus series

**Outstanding design.
Award winning.**

Our appliances have impressed the most prestigious design juries to win major awards such as the German Design Award, the iF Award and the Red Dot Award. The purist Liebherr look and impressive details create a stylish backdrop for your food.




SFNstd 529i | SRBstc 529i ◊ Peak series



CBNsdb 775i ◊ Prime series

Plus-size freshness

Ideal for large families who do a big weekly shop: Our biggest-ever BioFresh safe in our freestanding fridge-freezers provides plenty of space and ideal conditions for keeping fruit, vegetables, meat, fish and dairy products fresh. And in energy efficiency class B, it offers the perfect combination of plentiful space and low energy costs.




Treasuring true taste.

Discover our wine fridges – and find out how you can not only store and temper your collection under the perfect conditions, but preserve the very essence of the wine.



Top-quality engineering for maximum enjoyment

The optimal storage of wine hinges on five essential conditions. To ensure these are met, Liebherr has developed innovative technical solutions.





WPbli 5231 GrandCru Selection

1
Zone

Our wine storage fridges replicate the conditions of a wine cellar. A constant temperature is maintained throughout the interior of these appliances. This can be adjusted to between +5°C and +20°C, as required. Wine storage fridges are specially designed to hold a large number of bottles for storing and maturing, but they can also keep a larger stock of wine at drinking temperature.



Humidity regulation

With HumiditySelect, the humidity of GrandCru models can be adjusted in two stages: dehumidify or humidify. GrandCru Selection models are equipped with Humidity-Control. This function allows the humidity to be set as required within the range of 50% to 80% RH*. If the value falls below 50% RH, the appliance indicates this.



LightColumn, one-sided

For a perfect view of your wine: the LED LightColumn runs from the top to the bottom of your glass door appliance. It evenly illuminates the interior of your GrandCru Selection wine storage fridge. A special highlight is the dimmable presentation light for attractively showing off your wine collection even when the door is closed.



Neck-to-neck storage for maximum bottle capacity

Maximum capacity. A Liebherr wine storage fridge also makes it easier to organise a growing wine collection. To take full advantage of its capacity, the interior has been designed so that your wine bottles can be stored neck-to-neck on the wooden shelves. This means there is plenty of room even for ever-increasing wine collections. So feel free to keep collecting.



FreshAir activated charcoal filter


To ensure that your wine can mature in air of the best quality, all Liebherr wine storage fridges have an activated charcoal filter that reliably protects wine from all odours. This means your wine will retain its pure bouquet. To make sure that it stays that way, your Liebherr reminds you every six months to change the filter, which you can easily do yourself.

* At temperatures in home environments. In the case of very dry/cold environments, e.g. basement rooms, we recommend the customised water tray from our accessories range to support the system.



SommelierBoard

An absolute highlight in our new wine tempering fridges. There's room to show off everything you need for decanting. The high-quality shelf made of natural beechwood comes with a stainless-steel bottle presenter, a wooden box for decanting utensils and a space for tempering wine glasses for that extra-special enjoyment.



LightTower

Now also in our new wine tempering fridges: Lights on both sides create a unique ambience and a perfect view of the wines. Another special highlight is the dimmable presentation light, which skilfully shows off the wines – even when the door is closed.



Recessed vertical grip

All models in the Vinidor Selection series have a recessed vertical grip all the way down so that they can be opened ergonomically and comfortably from any position. Models with the optically discreet grip blend particularly harmoniously into handle-free kitchens and living-dining areas.



FlexFit wooden racks

Wine bottles of almost any size and shape are safely stored here: the removable wooden bars can be individually positioned in the frame.



More information on wine storage and our wine fridges, including detailed model descriptions, can be found in our special wine brochure available from a Liebherr specialist dealer or at home.liebherr.com/wine



WPgbi 7483 Vinidor Selection

2
Zones

With two or three separate temperature zones that can be set accurately to the degree between +5°C and +20°C, our wine tempering fridges offer maximum versatility of use. This means that red wines, white wines and champagnes can all be stored at the same time and at an ideal temperature in one single appliance with three temperature zones.

3
Zones

And for long-term storage of wines, appliances in the Vinidor Selection series have the StorageZone in the lower section. With their temperature zones of different sizes and temperature settings that offer complete flexibility, these appliances are perfect for each individual wine collection.

Refrigeration and freezing Brief overview



IRBPbsci 5170 Δ Peak series | EWTgb 3583 Vinidor | SIFNbsdi 5188 Δ Peak series




The full range of Liebherr freestanding and fully integrated appliances with detailed product descriptions can be found on our website, which also includes Liebherr specialist dealers, at home.liebherr.com



Freestanding appliances

SFNbsd 529i Δ Peak series | SRBbsc 529i Δ Peak series

The current EU energy label for electrical appliances



1. The QR code to identify the product in the EU database EPREL (European Product Registry for Energy Labelling).
2. The model identifier for manual identification of the product in the EU database EPREL, using the article number for example.
3. The new efficiency scale from A to G. However, "G" is only intended for wine fridges.
4. The total volume* of all freezer compartments.
5. The total volume* of all cold storage and refrigerator compartments.
6. The noise level is now classified into classes "A" to "D".

* The term "volume" is defined in the current Regulation (EU) 2019/2016.

Model overview – freestanding appliances



SFNstd 529i | SRBstc 529i



SFNsdd 526i | SRBsdd 526i



SFNsf 5247 | SRBsfc 5220

Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Fish & Seafood	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Smart Device	Smart Device ready
SFNstd 529i SRBstc 529i	D										
SFNsdd 526i SRBsdd 526i	D										
SFNsf 5247 SRBsfc 5220	D										

Side-by-Side fridge-freezers with BioFresh Professional / BioFresh

Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Fish & Seafood	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Smart Device	Smart Device ready
SFNbsd 529i Peak	D										
SRBbsc 529i Peak	C										
SFNstd 529i Peak	D										
SRBstc 529i Peak	C										
SFNsdd 526i Prime	D										
SRBsdd 526i Prime	D										
SFNsf 5247 Plus	D										
SRBsfc 5220 Plus	C										
SFNsf 5227 Plus	D										
SRBsfc 5220 Plus	C										



SCNsdc 525i | SCNsdc 525i



SFNsf 5227 | SRsfd 5220

Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Fish & Seafood	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Smart Device	Smart Device ready
SCNsdc 525i Prime	C										
SFNsf 5227 Plus	D										
SRsfd 5220 Plus	D										

Side-by-Side fridge-freezers with EasyFresh

Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Fish & Seafood	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Smart Device	Smart Device ready
SCNsdc 525i Prime	C										
SFNsf 5227 Plus	D										
SRsfd 5220 Plus	D										



CBNste 8872



CBNstc 778i



CNSfd 7723

Model / series

EEC



BLU Fridge-freezers with BioFresh Professional / BioFresh

Height	Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Easy Twist Ice	Smart Device	Smart Device ready
203	--91-- CBNste 8872 **	E										
202	--75-- CBNstc 778i Peak	C										
202	--60-- CBNbsd 578i Peak	D										
	CBNbsa10 575i Prime	A										
	CBNsda 575i Prime	A										
	CBNsdc 575i Prime	C										
	CBNa 572i Plus	A										
	CBNba 572i Plus	A										
	CBNsda 572i Plus	A										
	CBNsfc 572i Plus	C										
	CBNc 5723 Plus	C										
186	--60-- CBNc 5223 Plus	C										
	CBNba 5223 Plus	A										
	CBNsda 5223 Plus	A										
	CBNsfc 57vi Plus	C										
	CBNsfc 5223 Plus	C										

BLU Fridge-freezers with EasyFresh

Height	Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Easy Twist Ice	Smart Device	Smart Device ready
202	--75-- CNSfd 7723 Plus	D										
	CNd 7723 Plus	D										
202	--60-- CNSfc 574i Plus	C										
	CNc 5724 Plus	C										
	CNc 5703 Pure	C										
	CNd 5703 Pure	D										
	CNsfd 5703 Pure	D										
186	--60-- CNd 5204 Pure	D										
	CNc 5203 Pure	C										
	CNsfd 5203 Pure	D										
	CNd 5203 Pure	D										
166	--60-- CNc 5023 Plus	C										



All our freestanding fridge-freezers with energy efficiency class A* come with a 10-year warranty now.

More information at home.liebherr.com/bettertomorrow

** no BLUPerformance technology



CUefe 3331



CUe 2331



CTe 2131

Model / series

EEC



BLU Fridge-freezers

Height	Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Bio Fresh	Easy Fresh	Smart Frost	Soft System	Ice Maker	Easy Twist Ice	Smart Device	Smart Device ready
181	--55-- CUefe 3331	A										
	CUefe 3331	A										
	CUe 3331	A										
161	--55-- CUefe 2831	A										
	CUe 2831	A										
137	--55-- CUefe 2331	A										
	CUe 2331	A										
157	--55-- CTele 2931	A										
	CTe 2931	A										
140	--55-- CTele 2531	A										
	CTe 2531	A										
124	--55-- CTele 2131	A										
	CTe 2131	A										



RBbsb 525i



RBsdc 525i



RBc 5220

Model / series

EEC



BLU Fridges with BioFresh

Height	Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Bio Fresh	Easy Fresh	Smart Frost	Soft System	Ice Maker	Easy Twist Ice	Smart Device	Smart Device ready
186	--60-- RBbsb 525i Prime	B										
	RBsdc 525i Prime	C										
	RBc 525i Prime	C										
	RBsfc 5220 Plus	C										
	RBc 5220 Plus	C										
	RBsfd 5221 Plus	D										

* with 4* freezer compartment

You can find the full range of efficiency ratings on page 51. According to (EU) 2017/1369 6a. Detailed model descriptions can be found at home.liebherr.com



RDSfd 5220



RsfD 5000



Rd 4200

Model / series	EEC	Easy Fresh	Smart Frost	Soft System	Smart Device	Smart Device ready
----------------	-----	------------	-------------	-------------	--------------	--------------------

BLU Fridges with EasyFresh

Height	Model / series	EEC	Easy Fresh	Smart Frost	Soft System	Smart Device	Smart Device ready
186	--60-- RDSfd 5220 Plus	D	■				■
	RsfD 5220 Plus	D	■				■
	Rd 5220 Plus	D	■				■
166	--60-- RsfD 5000 Pure	D	■				■
	--60-- Rd 4200 Pure	D	■				■



Rsdci 1620



Rc 1401



Rd 1200

Model / series	EEC	Easy Fresh	Smart Frost	Door Stop	Smart Device	Outdoor
----------------	-----	------------	-------------	-----------	--------------	---------

Under counter refrigerators

Height	Model / series	EEC	Easy Fresh	Smart Frost	Door Stop	Smart Device	Outdoor	
85	--60-- Rsdci 1620 Plus	C	■		■	■		
	Rsdci 1621 Plus	C	■	■*		■		
	Rci 1620 Plus	C	■		■	■		
	Rci 1621 Plus	C	■	■*		■		
	Rdi 1620 Plus	D	■		■	■		
	Rdi 1621 Plus	D	■	■*		■		
85	--55-- Rc 1400 Pure	C			■			
	Rc 1401 Pure	C		■*				
	Rd 1400 Pure	D			■			
	Rd 1401 Pure	D		■*				
	Re 1400 Pure	E			■			
	Re 1401 Pure	E		■*				
85	--50-- Rd 1200 Pure	D			■			
	Rd 1201 Pure	D		■*				
	Re 1200 Pure	E			■			
	Re 1201 Pure	E		■*				
	68	--55-- Re 1000 Pure	E			■		

* with 4* freezer compartment



Fnc 727i



FNe 5006



FNe 4605

Model / series	EEC	No Frost	Telescopic Rails	Easy Open	Frost Protect	Easy Twist Ice	LED	Smart Device	Smart Device ready
----------------	-----	----------	------------------	-----------	---------------	----------------	-----	--------------	--------------------

BLU Freezers with NoFrost

Height	Model / series	EEC	No Frost	Telescopic Rails	Easy Open	Frost Protect	Easy Twist Ice	LED	Smart Device	Smart Device ready
186	--70-- Fnc 727i Peak	C	■	■	■	■	■	■	■	
186	--60-- FNd 525i Prime	D	■		■	■	■	■	■	
	FNd 522i Plus	D	■		■	■			■	
166	--60-- FNe 5207 Pure	E	■		■					■
	FNe 5006 Pure	E	■		■	■				■
146	--60-- FNe 4605 Pure	E	■		■	■				■
126	--60-- FNe 4204 Pure	E	■		■	■				■



FNsddi 1624



FNe 1404



Fe 1003

Model / series	EEC	No Frost	Smart Frost	Frost Protect	LED	Smart Device
----------------	-----	----------	-------------	---------------	-----	--------------

Under counter freezers

Height	Model / series	EEC	No Frost	Smart Frost	Frost Protect	LED	Smart Device
85	--60-- FNsddi 1624 Plus	D	■		■	■	■
	FNdi 1624 Plus	D	■		■	■	■
	Fci 1624 Plus	C		■	■	■	■
85	--55-- Fdi 1624 Plus	D		■	■	■	■
	FNe 1404 Pure	E	■		■	■	
	Fsve 1404 Pure	E		■	■	■	
85	Fe 1414 Pure	E		■	■	■	
	Fc 1404 Pure	C		■	■	■	
	Fe 1404 Pure	E		■	■	■	
	Fd 1404 Pure	D		■	■	■	
68	--55-- Fe 1003 Pure	E		■	■	■	

Fully integrated appliances

Side by Side

Your individual freshness centre

Combine your Liebherr fully integrated appliance with complete flexibility to suit your freshness needs. Many models can be vertically and/or horizontally combined to form an individual freshness centre, providing perfect solutions to all your storage needs.

Ask your Liebherr dealer or kitchen specialist about the Liebherr Side-by-Side concept.

SIFNAd 5188-617 Δ Peak series | IRBAc 5190 Δ Peak series



ECBNe 8872



ECBNe 8870



ECBNe 7870

Model / series	EEC	Bio Fresh	No Frost	Soft System	Ice Maker
Integrated fridge-freezers					
203 → 91.5 → ECBNe 8872	▶ E C A G	■	■	■	■
ECBNe 8870	▶ E C A G	■	■	■	■
ECBNe 8871	▶ E C A G	■	■	■	■
203 → 76.2 → ECBNe 7870	▶ E C A G	■	■	■	■
ECBNe 7871	▶ E C A G	■	■	■	■

SCAN

▮ Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

▮ For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.



ICBNbsci 5173



ICBNdi 5163



ICBbi 5152

Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Bio Fresh	Easy Fresh	No Frost	Smart Frost	Soft System	Ice Maker	Smart Device	Smart Device ready
----------------	-----	------------------------	--------------	-----------	------------	----------	-------------	-------------	-----------	--------------	--------------------

Integrated fridge-freezers with BioFresh Professional / BioFresh

178 → 56-57 → ICBNci 5183	Peak	▶ C A G	■	■		■		■	■	■	
ICBNbsci 5173	Peak	▶ C A G	■	■		■		■	■	■	
ICBNdi 5163	Prime	▶ D A G		■		■		■	■	■	
ICBNdi 5123	Plus	▶ D A G		■		■		■		■	
ICBbi 5152	Prime	▶ B A G		■			■	■		■	



ICBNbsci 5173



ICNci 5173



ICd 5103

Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Bio Fresh	Easy Fresh	No Frost	Smart Frost	Soft System	Ice Maker	Smart Device	Smart Device ready
----------------	-----	------------------------	--------------	-----------	------------	----------	-------------	-------------	-----------	--------------	--------------------

Integrated fridge-freezers with EasyFresh

178 → 56-57 → ICBnbsci 5173	Peak	▶ C A G			■	■		■	■	■	
ICNci 5173	Peak	▶ C A G			■	■		■	■	■	
ICNd 5133	Plus	▶ D A G			■	■		■	■*		■
ICNc 5103	Pure	▶ C A G			■	■					■
ICNSd 5103 **	Pure	▶ D A G			■	■					■
ICNe 5103	Pure	▶ E A G			■	■					■
ICd 5103	Pure	▶ D A G			■		■				■
ICe 5103	Pure	▶ E A G			■		■				■
ICSe 5103 **	Pure	▶ E A G			■		■				■

* with watertank

** with sliding door instead of door-on-door assembly

SCAN

Model overview – fully integrated appliances



IRBAC 5190-001



IRBPbsci 5170



IRBc 4520

Model / series	EEC	Bio Fresh Professional	Hydro Breeze	Fish & Seafood	Bio Fresh	Smart Frost	Soft System	Auto Door	Smart Device	Smart Device ready
----------------	-----	------------------------	--------------	----------------	-----------	-------------	-------------	-----------	--------------	--------------------

Integrated fridges with BioFresh Professional / BioFresh

Height	Series	Model	Feature	EEC	Bio Fresh Professional	Hydro Breeze	Fish & Seafood	Bio Fresh	Smart Frost	Soft System	Auto Door	Smart Device	Smart Device ready	
178	-56-57-	IRBAC 5190-001	Peak		■	■				■	■	■		
		IRBAC 5190-617	Peak		■	■				■	■	■		
140	-56-57-	IRBci 5171	Peak		■	■			■*	■		■		
		IRBbsci 5170	Peak		■	■				■		■		
		IRBdi 5170	Peak		■	■	■				■		■	
		IRBPbsci 5170	Peak					■			■		■	
		IRBci 5150	Prime					■			■		■	
		IRBd 5120	Plus					■			■			■
		IRBd 5121	Plus					■	■*		■			■
122	-56-57-	IRBc 4520	Plus					■		■			■	
		IRBc 4120	Plus					■		■			■	

* with 4* freezer compartment



IRDdi 5120



IRd 4520



IRd 4100

Model / series	EEC	Easy Fresh	Smart Frost	Soft System	Auto Door	Smart Device	Smart Device ready
----------------	-----	------------	-------------	-------------	-----------	--------------	--------------------

Integrated fridges with EasyFresh

Height	Series	Model	Feature	EEC	Easy Fresh	Smart Frost	Soft System	Auto Door	Smart Device	Smart Device ready
178	-56-57-	IRDdi 5120	Plus		■		■		■	
		IRd 5100	Pure		■					■
		IRd 5101	Pure		■	■*				■
140	-56-57-	IRd 4520	Plus		■		■			■
		IRd 4100	Pure		■					■

* with 4* freezer compartment

▮ Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

▮ For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.

Model overview – fully integrated appliances



SIFNAd 5188-001



SIFNdi 4155



IFNbi 3553

Model / series	EEC	No Frost	Smart Frost	Soft System	Ice Maker	Ice Tower	Auto Door	LED	Smart Device	Smart Device ready
----------------	-----	----------	-------------	-------------	-----------	-----------	-----------	-----	--------------	--------------------

Integrated freezers

Height	Series	Model	Feature	EEC	No Frost	Smart Frost	Soft System	Ice Maker	Ice Tower	Auto Door	LED	Smart Device	Smart Device ready	
178	-56-57-	SIFNAd 5188-001	Peak		■		■	■	■			■		
		SIFNAd 5188-617	Peak		■		■	■	■			■		
140	-56-57-	SIFNbsdi 5188	Peak		■		■	■	■			■		
		SIFNdi 5188	Peak		■		■	■	■			■		
		SIFNe 5128	Plus		■		■						■	
		SIFNSe 5128**	Plus		■								■	
		SIFNe 5108	Pure		■								■	
		SIFNdi 4556	Prime		■		■					■	■	
		SIFNdi 4155	Prime		■		■					■	■	
88	-56-57-	IFNci 3954	Prime		■		■					■		
		IFNci 3553	Prime		■		■					■		



UIKP 1550



UIKo 1560



SUIGN 1554

Model / series	EEC	Bio Fresh	No Frost	Smart Frost	Soft System	LiftUp Box
----------------	-----	-----------	----------	-------------	-------------	------------

Under-worktop fridges and freezer

Height	Series	Model	Feature	EEC	Bio Fresh	No Frost	Smart Frost	Soft System	LiftUp Box
82-88	-60-	UIKP 1550	Premium					■	
		UIKo 1560	Premium					■	■
		UIKo 1550	Premium					■	
		SUIGN 1554	Premium			■		■	

** with sliding door instead of door-on-door assembly

Wine appliances



WPgbi 7473 Vinidor Selection



WPgbi 7483



WPbsi 5252



WPsd 4652

Model / series	EEC	2 Zones	3 Zones	Glass Door	Humidity Control	Humidity Select	UV Protect	UV Protect Plus	Sommelier Board	Soft System	Smart Device	Smart Device ready	
----------------	-----	---------	---------	------------	------------------	-----------------	------------	-----------------	-----------------	-------------	--------------	--------------------	--

Freestanding wine tempering fridges

201	-70--	WPgbi 7483	Vinidor Selection			■	■	■**		■	■	■	145
		WPgbi 7473	Vinidor Selection			■	■	■**		■	■	■	182
		WPgbi 7472	Vinidor Selection		■		■	■**		■	■	■	204
185	-60--	WPgbi 5283	Vinidor Selection			■	■	■**		■	■	■	85
		WPgbi 5273	Vinidor Selection			■	■	■**		■	■	■	104
		WPgbi 5272	Vinidor Selection		■		■	■**		■	■	■	106
		WPbsi 5252	Vinidor		■		■		■		■	■	155
		WSbsi 5252	Vinidor		■			■		■	■	155	
		WPsd 5252	Vinidor		■		■				■	155	
165	-60--	WPbsi 5052	Vinidor		■		■		■	■		131	
145		WPsd 4652	Vinidor		■		■				■	107	
82	-60--	WTes 1672	Vinidor		■		■	■				34	

* Maximum capacity of Bordeaux bottles (0.75 l) based on: H: 300.5 mm, ø: 76.1 mm.
** In the StorageZone.

Model overview – Wine fridges



WSbli 7731



WPbli 5001



WSbli 4201

Model / series	EEC	1 Zone	Glass Door	Humidity Control	Humidity Select	UV Protect	UV Protect Plus	Smart Device	Smart Device ready	
----------------	-----	--------	------------	------------------	-----------------	------------	-----------------	--------------	--------------------	--

Freestanding wine storage fridges

204	-75--	WSbli 7731	GrandCru Selection		■		■			■	324
		WSbli 5231	GrandCru Selection		■		■			■	229
168	-60--	WPbli 5231	GrandCru Selection		■	■	■		■	■	229
		WSbli 5031	GrandCru Selection		■		■			■	196
		WPbli 5031	GrandCru Selection		■	■	■		■	■	196
		WSbli 5001	GrandCru		■		■			■	196
148	-60--	WPbli 5001	GrandCru		■	■		■		■	196
		WSbli 4601	GrandCru		■		■			■	166
128	-60--	WPbli 4601	GrandCru		■	■		■		■	166
		WSbli 4201	GrandCru		■		■			■	141
		WPbli 4201	GrandCru		■	■		■		■	141



WKes 653




ZKes 453

Model / series	EEC	1 Zone	Glass Door	Humidity Control	Humidity Select	UV Protect	Cigar	
----------------	-----	--------	------------	------------------	-----------------	------------	-------	--

Freestanding compact appliances

61	-43--	WKes 653	GrandCru		■		■		■	12
		ZKes 453	Humidor		■		■		■	



Bordeaux bottle size (0.75 l)
All specifications regarding bottle capacity refer to these dimensions.

You can find the full range of efficiency ratings on page 51. According to (EU) 2017/1369 6a. Detailed model descriptions can be found at home.liebherr.com



EWTgb 3583



EWTdf 2353



EWTgb 1683

Model / series	EEC	1 Zone	2 Zones	Glass Door	Humidity Select	UV Protect	Soft System	Tip Open	Bottle*
----------------	-----	--------	---------	------------	-----------------	------------	-------------	----------	---------

Integrated wine tempering fridges

178	-56-57-	EWTgb 3583	Vinidor			■	■	■	■	■	■	83
		EWTdf 3553	Vinidor			■	■	■	■	■	■	80
122	-56-57-	EWTgb 2383	Vinidor			■	■	■	■	■	■	51
		EWTdf 2353	Vinidor			■	■	■	■	■	■	48
88	-56-57-	EWTgb 1683	Vinidor			■	■	■	■	■	■	33
		EWTdf 1653	Vinidor			■	■	■	■	■	■	30



WKEgb 582



WKEgw 582

Integrated wine storage fridges

45	-56-57-	WKEgb 582	GrandCru			■	■	■	■	■	■	18
		WKEgw 582	GrandCru			■	■	■	■	■	■	18



UWTgb 1682



UWTes 1672



UWKes 1752

Under worktop wine fridges


82-87	-60-	UWTgb 1682	Vinidor			■	■	■	■	■	■	34
		UWTes 1672	Vinidor			■	■	■	■	■	■	34
		UWKes 1752	GrandCru			■	■	■	■	■	■	46

SCAN

Special requirements

Wine fridges must meet the same EU standards as refrigerators and freezers for storing food. However, the particular requirements for reliable wine storage and tempering demand a lot more in terms of performance. That's why most wine fridges on the market are in energy efficiency class G.

The current EU energy label* for wine fridges:





1. The QR code for identifying the product in the EU database EPREL (European Product Registry for Energy Labelling).
2. The model identifier for manual identification of the product in the EU database EPREL, using the article number for example.
3. The efficiency scale from A to G. "G" is intended only for wine fridges.
4. Maximum storage capacity.
5. The noise level is now classified into classes A to D.

Optimum energy efficiency

Liebherr puts a special focus on sustainability. Our wine fridges are among the most energy-efficient in their class. While most manufacturers offer models in class G, most of our wine fridges are already in energy efficiency classes F and E, and one of them is even in class D.

Distribution among efficiency classes in 2023:



* In accordance with Regulation (EU) 2019/2016

** Source: EPREL 2023

Practical accessories for every need

Discover the versatility of the Liebherr range of accessories and make your daily life that little bit easier.



VarioSafe and bottle shelf



FlexSystem



Bottle shelf



Ice cube tray with lid



FreshAir activated charcoal filter
Cleans the circulating air and quickly traps any unpleasant odours. The filter is easy to replace and ensures optimum air quality.



EasyTwist-Ice
Thanks to EasyTwist Ice, you can prepare a supply of ice cubes quickly and easily – without the need for a fixed water connection. Simply fill the tank with water, let it freeze and then release the finished ice cubes with a simple twist.



SmartDeviceBox
You can retrofit your Liebherr with a SmartDeviceBox to connect it to the internet. The SmartDeviceBox can be installed in just a few steps and instantly opens up the whole world of digital possibilities.

For a clear overview – even before you open the fridge

○ Pure ◇ Plus ◻ Prime △ Peak

Which appliance is right for me?
A question that is not always easy to answer when you are buying new appliances. That's why we have made it even easier to find your way around our range of products by dividing our fridges and freezers into four series.



You'll find our accessories online with your dream model in the Liebherr-Hausgeräte shop at home.liebherr.com/shop or from your Liebherr specialist dealer.

○ Pure series

The Pure series is our basic class: simple, clear and perfectly equipped to cover all essential requirements. Pure series appliances have been reduced to the basics, but are full to the brim with the highest Liebherr quality.



◇ Plus series

The Plus series builds on our Pure series and impresses with many additional details. Plus here particularly means a plus in convenience. These appliances are not only first-class in their refrigeration and freezing capabilities, they are also that little bit smarter. In this way, they help make lots of manual operations a little easier.

○ Prime series

The Prime series is all about class. It makes an unmistakable mark in terms of design and material. Above all, top quality materials are used inside the appliances, such as stainless steel. But special lighting solutions also make the appliances in this series particularly appealing.



△ Peak series

The Peak series is our top-of-the-range series. It combines the best with the best. There is no compromise. Innovative Liebherr technology is blended with exceptional high-end design and solutions for convenience in a class of its own. Appliances in this series are for those who want to have it all.

Freshness technologies

- Bio Fresh Professional** BioFresh Professional offers even more flexibility for your individual food-storage needs.
- Hydro Breeze** Cooling like a pro: Cold mist and a temperature in the Fruit & Vegetable safe of just over 0°C ensure a longer shelf life and create a fabulous visual effect.
- Fish & Seafood** The Fish & Seafood safe stores fish and seafood at the optimum temperature of -2°C, just as professionally as your fishmonger.
- Bio Fresh** At a temperature just above 0°C and an ideal humidity, fruits, vegetables, meat, fish and dairy products stay fresh for much longer than in the usual fridge compartment.
- Easy Fresh** The adjustable humidity prolongs the freshness of your fruits and vegetables.
- No Frost** Frost-free convenience
- Smart Frost** Far less frequent defrosting

Convenience and flexibility

- Soft System** Very soft door closing, even when fully loaded, automatically below an opening angle of 30°.
- LiftUp Box** With the LiftUp-Box, you can make the most of the storage space underneath the pull-out drawer. Once the drawer is pulled out, the LiftUp-Box slides upwards from the space in the bottom of the appliance, allowing convenient removal of food.
- Easy Open** With EasyOpen the freezer door can be opened multiple times in succession, conveniently and easily.
- Frost Protect** Our freezers are also able to run at low temperatures, meaning they can even be installed in unheated rooms with an ambient temperature as cold as -15°C (minimum temperature).
- Auto Door** Unique worldwide: AutoDoor allows easy and convenient opening and closing of the door via voice command, knocking signal and smartphone* – or simply by hand.

Water and ice

- Ice Maker** Automatic IceMaker for a plumbed-in connection
- Ice Maker Water tank** Automatic IceMaker with a water tank, if a plumbed-in connection is not available or not wanted.
- Easy Twist Ice** Conjure up ice cubes quickly and easily: Fill the tank with water, let it freeze and then release the finished ice cubes with a twist (freestanding appliances).

Wine

- 1 Zone** With a constant temperature throughout the interior, adjustable from +5°C to +20°C.
- 2 Zones** With two temperature zones, independently and precisely adjustable from +5°C to +20°C.
- 3 Zones** With three temperature zones, independently and precisely adjustable from +5°C to +20°C.
- Glass Door** Your entire wine collection at a glance: behind tinted UV safety glass.
- Humidity Control** The humidity can be actively regulated in 5% increments between 50% and 80%RH**.
- Humidity Select** The humidity can be adjusted in two levels: Standard or High.
- UV Protect Plus** Triple protection: A tinted glass door with two layers of vacuum-deposited metal provides highly efficient protection from sunlight.
- UV Protect** Double protection: A tinted glass door with one layer of vacuum-deposited metal provides efficient protection from sunlight.
- Sommelier Board** For effective presentation and decanting: Wooden shelf with stainless steel bottle display, wooden box for decanting utensils and space for tempering wine glasses.

Connectivity

- Smart Device** The integrated SmartDeviceBox enables you to control the appliance and make use of additional services via computers and mobile devices.
- Smart Device ready** The SmartDeviceBox can be retrofitted so that you can control the appliance and make use of additional services via computers and mobile devices. Available as an accessory.

Special product groups

- Outdoor** This Liebherr is ideal for use outdoors thanks to its rust- and weatherproof materials, robust construction and high-quality components.
- Wine** Perfect conditions for fine wines with unique storage and tempering features.
- Cigar** Innovative features and perfect climate for fine cigars.

Ultra-efficient models

- Ultra Efficient A -10%** Even more economical¹ than appliances in the highest energy efficiency class A – Liebherr is setting new standards in the industry.

* Can also be used via SmartDevice/Smart app. | ** For temperatures in home environments. In the case of very dry/cold environments, e.g. basement rooms, we recommend the customised water box from our accessories range to support the system. | *** Information regarding many more equipment variations and detailed model descriptions can be found at home.liebherr.com

¹ Compared to the threshold for maximum energy efficiency class A according to Regulation (EU) 2029/2016 (as of December 2023).

Bio Fresh

No Frost

Soft System

Ultra Efficient A -10%



Ultra Silent

29 db(A)

Easy Twist Ice

Smart Device



Subject to technical changes, errors and deviations in image and text. Deviations in colour are due to printing processes. For the latest available data, go to home.liebherr.com. Typodruck GmbH & Co. KG.

* Compared to the threshold for maximum energy efficiency class A according to R egulation (EU) 2019/2016 (as of July 2023).

CBNbsa10 575i ◊ Prime-Serie




10-year Liebherr warranty

Increased sustainability through long product life and outstanding energy efficiency.



A-rated energy efficiency



Witt A/S
Tlf. 70 25 23 23
info@witt.dk
www.witt.dk



Witt Sverige AB
Tel. 08-525 084 80
info@wittsverige.se
www.wittsverige.se



Witt Norge
Tlf. 32 82 99 40
info@witt.no
www.witt.no



Witt A/S Filial Finland
Puh. 093 157 9150
info@witt.fi
www.witt.fi