SCB5790IM

Freestanding / Semi Built-in



Refrigeration and Freezing





home.liebherr.com

Energy consumption (kWh / y)370Estimated Yearly Energy Cost in US \$52Sound rating dB(A)33Total refrigerator capacity cu.ft. (l)9 (256)BioFresh compartment cu.ft. (l)3.4 (96)Freezer capacity cu.ft. (l)3.7 (104)Electronic controlTouch & Swipe DisplayDefrost typeAutomaticInterior lightLightTowerNumber of shelves3* VarioSafeNumber of freezer drawers3Number of BioFresh drawers2Refrigerator Temperature range °F (°C)36° to 46°F (3 to 9°C)Freezer Temperature range °F (°C)5° to -15°F (-15° to -26°C)Water filter1Ice makerFixed water connectionIce cube output Ibs. (kg.)2.6 (1.2)Ice cube stock Ibs. (kg.)119 (5.4)Door hingesright, reversible Product dimensions 79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)203.2 / 60.9 / 60.9Net weight Ibs. (kg)374 (170)Voltage V / Hz115/60		SCB5790IM
Sound rating dB(A)33Total refrigerator capacity cu.ft. (l)9 (256)BioFresh compartment cu.ft. (l)3.4 (96)Freezer capacity cu.ft. (l)3.7 (104)Electronic controlTouch & Swipe DisplayDefrost typeAutomaticInterior lightLightTowerNumber of shelves3+ VarioSafeNumber of door racks2+ VarioBoxNumber of freezer drawers3Number of BioFresh drawers2Refrigerator Temperature range °F (°C)5° to 46°F (3 to 9°C)Freezer Temperature range °F (°C)5° to 15°F (-15° to -26°C)Water filter1Ice makerFixed water connectionIce cube output Ibs. (kg.)2.6 (1.2)Ice cube stock Ibs. (kg.)119 (5.4)Door hingesright, reversibleProduct dimensions79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)201.5 / 59.7 / 67.5Cut out dimensions80" / 24" / 24"in cm (H / W / D)80" / 24" / 24"in cm (H / W / D)80" / 24" / 24"hor (H / W / D)374 (170)	Energy consumption (kWh / y)	370
Total refrigerator capacity cu.ft. (I)9 (256)BioFresh compartment cu.ft. (I)3.4 (96)Freezer capacity cu.ft. (I)3.7 (104)Electronic controlTouch & Swipe DisplayDefrost typeAutomaticInterior lightLighTowerNumber of shelves3+ VarioSafeNumber of door racks2+ VarioBoxNumber of freezer drawers3Number of BioFresh drawers2Refrigerator Temperature range °F (°C)5° to 46° F (3 to 9°C)Freezer Temperature range °F (°C)5° to 15° F (-15° to -26°C)Water filter1Ice makerFixed water connectionIce cube output Ibs. (kg.)2.6 (1.2)Ice cube stock Ibs. (kg.)119 (5.4)Door hingesright, reversibleProduct dimensions79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)79 5/16" / 24" / 24"in cm (H / W / D)203.2 / 60.9 / 60.9Net weight Ibs. (kg)374 (170)	Estimated Yearly Energy Cost in US \$	52
BioFresh compartment cu.ft. (I)3.4 (96)Freezer capacity cu.ft. (I)3.7 (104)Electronic controlTouch & Swipe DisplayDefrost typeAutomaticInterior lightLightTowerNumber of shelves3+ VarioSafeNumber of door racks2+ VarioBoxNumber of freezer drawers3Number of BioFresh drawers2Refrigerator Temperature range °F (°C)36° to 46°F (3 to 9°C)Freezer Temperature range °F (°C)5° to -15°F (-15° to -26°C)Water filter1Ice makerFixed water connectionIce cube output Ibs. (kg.)1.9 (5.4)Door hingesright, reversibleProduct dimensions20.5 / 59.7 / 67.5Cut out dimensions80" / 24" / 24"in inch (H / W / D)203.2 / 60.9 / 60.9Net weight Ibs. (kg)374 (170)	Sound rating dB(A)	33
Freezer capacity cu.ft. (l)3.7 (104)Electronic controlTouch & Swipe DisplayDefrost typeAutomaticInterior lightLightTowerNumber of shelves3+ VarioSafeNumber of door racks2+ VarioBoxNumber of freezer drawers3Number of BioFresh drawers2Refrigerator Temperature range °F (°C)36° to 46°F (3 to 9°C)Freezer Temperature range °F (°C)5° to -15°F (-15° to -26°C)Water filter1Ice makerFixed water connectionIce cube output Ibs. (kg.)2.6 (1.2)Door hingesright, reversibleProduct dimensions79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)80" / 24" / 24"in cm (H / W / D)203.2 / 60.9 / 60.9Net weight Ibs. (kg)374 (170)	Total refrigerator capacity cu.ft. (l)	9 (256)
Electronic controlTouch & Swipe DisplayDefrost typeAutomaticInterior lightLightTowerNumber of shelves3+ VarioSafeNumber of door racks2+ VarioBoxNumber of freezer drawers3Number of BioFresh drawers2Refrigerator Temperature range °F (°C)36° to 46° F (3 to 9°C)Freezer Temperature range °F (°C)5° to -15° F (-15° to -26°C)Water filter1Ice makerFixed water connectionIce cube output Ibs. (kg.)2.6 (1.2)Door hingesright, reversibleProduct dimensionsright, reversiblein inch (H / W / D)79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)80" / 24" / 24"in cm (H / W / D)203.2 / 60.9 / 60.9Net weight Ibs. (kg)374 (170)	BioFresh compartment cu.ft. (l)	3.4 (96)
Interior lightAutomaticInterior lightLightTowerNumber of shelves3+ VarioSafeNumber of door racks2+ VarioBoxNumber of freezer drawers3Number of BioFresh drawers2Refrigerator Temperature range °F (°C)36° to 46°F (3 to 9°C)Freezer Temperature range °F (°C)5° to -15°F (-15° to -26°C)Water filter1Ice makerFixed water connectionIce cube output Ibs. (kg.)2.6 (1.2)Ice cube stock Ibs. (kg.)11.9 (5.4)Door hingesright, reversibleProduct dimensions79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)80" / 24" / 24"in cm (H / W / D)203.2 / 60.9 / 60.9Net weight Ibs. (kg)374 (170)	Freezer capacity cu.ft. (l)	3.7 (104)
Interior lightLightTowerNumber of shelves3+ VarioSafeNumber of shelves2+ VarioBoxNumber of freezer drawers3Number of BioFresh drawers2Refrigerator Temperature range °F (°C)36° to 46°F (3 to 9°C)Freezer Temperature range °F (°C)5° to -15°F (-15° to -26°C)Water filter1Ice makerFixed water connectionIce cube output Ibs. (kg.)2.6 (1.2)Ice cube stock Ibs. (kg.)11.9 (5.4)Door hingesright, reversibleProduct dimensions79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)79 5/16" / 23 1/2" / 26 9/16"in inch (H / W / D)80" / 24" / 24"in cm (H / W / D)203.2 / 60.9 / 60.9Net weight Ibs. (kg)374 (170)	Electronic control	Touch & Swipe Display
Number of shelves 3+ VarioSafe Number of door racks 2+ VarioBox Number of freezer drawers 3 Number of BioFresh drawers 2 Refrigerator Temperature range °F (°C) 36° to 46°F (3 to 9°C) Freezer Temperature range °F (°C) 5° to -15°F (-15° to -26°C) Water filter 1 Ice maker Fixed water connection Ice cube output Ibs. (kg.) 2.6 (1.2) Ice cube stock Ibs. (kg.) 119 (5.4) Door hinges right, reversible Product dimensions right, reversible in inch (H / W / D) 79 5/16" / 23 1/2" / 26 9/16" in ncm (H / W / D) 80" / 24" / 24" in ncm (H / W / D) 203.2 / 60.9 / 60.9 Net weight Ibs. (kg) 374 (170)	Defrost type	Automatic
Number of door racks 2+ VarioBox Number of freezer drawers 3 Number of BioFresh drawers 2 Refrigerator Temperature range °F (°C) 36° to 46°F (3 to 9°C) Freezer Temperature range °F (°C) 5° to -15°F (-15° to -26°C) Water filter 1 Ice maker Fixed water connection Ice cube output lbs. (kg.) 2.6 (1.2) Ice cube stock lbs. (kg.) 119 (5.4) Door hinges right, reversible Product dimensions right, reversible in inch (H / W / D) 79 5/16" / 23 1/2" / 26 9/16" in ncm (H / W / D) 80" / 24" / 24" in ncm (H / W / D) 203.2 / 60.9 / 60.9 Net weight lbs. (kg) 374 (170)	Interior light	LightTower
Number of freezer drawers 3 Number of BioFresh drawers 2 Refrigerator Temperature range °F (°C) 36° to 46°F (3 to 9°C) Freezer Temperature range °F (°C) 5° to -15°F (-15° to -26°C) Water filter 1 Ice maker Fixed water connection Ice cube output Ibs. (kg.) 2.6 (1.2) Ice cube stock Ibs. (kg.) 11.9 (5.4) Door hinges right, reversible Product dimensions	Number of shelves	3+ VarioSafe
Number of BioFresh drawers 2 Refrigerator Temperature range °F (°C) 36° to 46°F (3 to 9°C) Freezer Temperature range °F (°C) 5° to -15°F (-15° to -26°C) Water filter 1 Ice maker Fixed water connection Ice cube output Ibs. (kg.) 2.6 (1.2) Ice cube stock Ibs. (kg.) 119 (5.4) Door hinges right, reversible Product dimensions 201.5 / 59.7 / 67.5 Cut out dimensions 80" / 24" / 24" in inch (H / W / D) 203.2 / 60.9 / 60.9 Net weight Ibs. (kg) 374 (170)	Number of door racks	2+ VarioBox
Refrigerator Temperature range °F (°C) 36° to 46°F (3 to 9°C) Freezer Temperature range °F (°C) 5° to -15°F (-15° to -26°C) Water filter 1 Ice maker Fixed water connection Ice cube output Ibs. (kg.) 2.6 (1.2) Ice cube stock Ibs. (kg.) 119 (5.4) Door hinges right, reversible Product dimensions	Number of freezer drawers	3
Freezer Temperature range °F (°C) 5° to -15°F (-15° to -26°C) Water filter 1 Ice maker Fixed water connection Ice cube output lbs. (kg.) 2.6 (1.2) Ice cube stock lbs. (kg.) 119 (5.4) Door hinges right, reversible Product dimensions 79 5/16" / 23 1/2" / 26 9/16" in inch (H / W / D) 79 5/16" / 23 1/2" / 26 9/16" in inch (H / W / D) 201.5 / 59.7 / 67.5 Cut out dimensions in inch (H / W / D) in nch (H / W / D) 80" / 24" / 24" in cm (H / W / D) 203.2 / 60.9 / 60.9 Net weight lbs. (kg) 374 (170)	Number of BioFresh drawers	2
Water filter 1 Ice maker Fixed water connection Ice cube output Ibs. (kg.) 2.6 (1.2) Ice cube stock Ibs. (kg.) 11.9 (5.4) Door hinges right, reversible Product dimensions in inch (H / W / D) in cm (H / W / D) 79 5/16" / 23 1/2" / 26 9/16" in inch (H / W / D) 201.5 / 59.7 / 67.5 Cut out dimensions in inch (H / W / D) in inch (H / W / D) 80" / 24" / 24" in cm (H / W / D) 203.2 / 60.9 / 60.9 Net weight Ibs. (kg) 374 (170)	Refrigerator Temperature range °F (°C)	36° to 46°F (3 to 9°C)
Ice maker Fixed water connection Ice cube output lbs. (kg.) 2.6 (1.2) Ice cube stock lbs. (kg.) 119 (5.4) Door hinges right, reversible Product dimensions in inch (H / W / D) in cm (H / W / D) 79 5/16" / 23 1/2" / 26 9/16" in inch (H / W / D) 201.5 / 59.7 / 67.5 Cut out dimensions in inch (H / W / D) in inch (H / W / D) 80" / 24" / 24" in cm (H / W / D) 203.2 / 60.9 / 60.9 Net weight lbs. (kg) 374 (170)	Freezer Temperature range °F (°C)	5° to -15°F (-15° to -26°C)
Ice cube output lbs. (kg.) 2.6 (1.2) Ice cube stock lbs. (kg.) 11.9 (5.4) Door hinges right, reversible Product dimensions	Water filter	1
Ice cube stock lbs. (kg.) 11.9 (5.4) Door hinges right, reversible Product dimensions	Ice maker	Fixed water connection
Door hinges right, reversible Product dimensions	Ice cube output lbs. (kg.)	2.6 (1.2)
Product dimensions in inch (H / W / D) 79 5/16" / 23 1/2" / 26 9/16" in cm (H / W / D) 201.5 / 59.7 / 67.5 Cut out dimensions in inch (H / W / D) 80" / 24" / 24" in cm (H / W / D) 80" / 24" / 24" Net weight lbs. (kg) 374 (170)	Ice cube stock lbs. (kg.)	11.9 (5.4)
in inch (H / W / D) 79 5/16" / 23 1/2" / 26 9/16" in cm (H / W / D) 201.5 / 59.7 / 67.5 Cut out dimensions in inch (H / W / D) 80" / 24" / 24" in cm (H / W / D) 203.2 / 60.9 / 60.9 Net weight lbs. (kg) 374 (170)	Door hinges	right, reversible
in cm (H / W / D) 201.5 / 59.7 / 67.5 Cut out dimensions in inch (H / W / D) 80" / 24" / 24" in cm (H / W / D) 203.2 / 60.9 / 60.9 Net weight lbs. (kg) 374 (170)	Product dimensions	
Cut out dimensions in inch (H / W / D) 80" / 24" / 24" in cm (H / W / D) 203.2 / 60.9 / 60.9 Net weight lbs. (kg) 374 (170)	in inch (H / W / D)	79 5/16" / 23 1/2" / 26 9/16"
in inch (H / W / D) 80" / 24" / 24" in cm (H / W / D) 203.2 / 60.9 / 60.9 Net weight lbs. (kg) 374 (170)	in cm (H / W / D)	201.5 / 59.7 / 67.5
in cm (H / W / D) 203.2 / 60.9 / 60.9 Net weight lbs. (kg) 374 (170)	Cut out dimensions	
Net weight lbs. (kg) 374 (170)	in inch (H / W / D)	80" / 24" / 24"
	in cm (H / W / D)	203.2 / 60.9 / 60.9
Voltage V/Hz 115/60	Net weight lbs. (kg)	374 (170)
	Voltage V / Hz	115/60

This product can be paired SBS with SC5781

 * Energy Cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 14 cents per KWh.
** Noise output – according to EN 60704-3



Accessories	
FreshAir activated carbon filter	9882460
Side By Side kit	9905353
Top Ventilation grill for Side by Side Installation	9900368
Door opening limitation	9096414

Features





Vario

Temp

The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



Do you want to cool fruit and vegetables like professionals? The cold mist combined with a temperature in the safe of just over 32°F (0°C) gives food that extra boost for longer shelf life.



Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times.



Love fish? Your Liebherr keeps fish fresh! Stores fish and seafood at the optimum temperature of 28°F (-2°C); as professionally as your fishmonger. Adjust the size of the 28°F (-2°C) zone as much as you want.

Diagrams

Product Dimensions





Allow door swing clearance at locations next to a wall. If the appliance is installed with the hinges next to a wall, the distance between the appliance and the wall must be at least $1\frac{1}{2}$ " (40 mm). This is how far the handle protrudes when the door is open. The refrigerator door must open to a minimum of 90° to allow the crispers to open and the shelves to be removed. A 90° door limiter is available for this model.

Height can be increased by 3/8" (10mm) by turning the levelling feet at the front and the height adjustable rollers at the appliance rear.

Semi built-in look – Cutout Dimensions



The appliances can be used freestanding or semi built-in. If semi built-in, consider the minimum cabinet opening dimensions specified on this image.

The power cord exists the rear of the appliances (A) right side and has a length of 6.5 ft (2m). We suggest the electrical outlet not to be located behind the appliance, so it is easily accessible. This can be located on top of the niche like shown on the image.

Do not install the shut-off valve for the water supply behind the appliance, to allow access to shut off without having to pull out the appliance. The water line lead out position is according to graphic (B).

Ventilation Requirements



If the appliance is integrated in a fitted kitchen, the following ventilation requirements must be met: - The spacing fins on the back of the appliance are used to ensure sufficient ventilation. These must not lie in cavities or recesses in their final installation position. -Basically, the larger the ventilation gap, the more energy the appliance saves during operation. Do not restrict the air flow.

A cross-sectional air flow of at least 31 in2 (200cm2) per appliance at the airflow inlet (1) and at the airflow outlet (2). The top ventilation space can be directed in one of the following ways:

A. Directly over the appliance (2) with a gap between the ceiling of the unit and the cabinet

B. Above the cabinet and below the ceiling (3).

C. Through a vent installed in a soffit (4).

Be sure to consider the possibility of having to raise some of the leveling legs in order to level the appliance when installing. If you adjust the height of the appliance – it will effectively reduce air flow. Therefore leave yourself some room for adjustment. The appliance is designed to allow proper air flow when installed up against the wall.

Subject to modification. For up-to-date information, visit home.liebherr.com

Specifications are for planning purposes only. For more detailed information, refer to installation instructions or Design Guide.