

EN

CAL series

Offshore crane
technology

www.liebherr.com

LIEBHERR

Maritime cranes



Liebherr CAL series



Applications

Heavy lift construction & maintenance
Wind turbine installation & maintenance

Characteristics

Safe and reliable state-of-the-art Crane Around the Leg with slewing bearing technology, rope luffing system and twin, delta or lambda boom design.

Specifications

Overturning moment: 45,000 tm - 180,000 tm
Main hoist capacity: 1,200 t - 3,000 t
Boom length: up to 136 m


Customer benefits

Maintenance-friendly
Minimised total lifecycle costs
Guaranteed spare parts availability
Worldwide customer service station network

Authorities | rules | certificates

Liebherr works together with all relevant certification organisations worldwide and locally in a trustful manner. Please contact us for detailed information.

CAL series



Offshore crane customer references*

ADCO | ADNOC | ALTERA | APACHE APA CORP. | BP | BW OFFSHORE | CANADIAN COAST GUARD | CHEVRON | CHIWAN SEMBAWANG | CNOOC | COASTLINE | CONOCOPHILLIPS | OSCO | COSL | COTEMAR | DALIAN | DEEPOCEAN | DIAMOND | DOLPHIN | DRYDOCKS WORLD | DSME | ENI | EQUINOR | EQUINOX | ESSAR | EXXON MOBIL | FLOATTEL | FRIGSTAD | ENGIE | GSI | HESS | HGO INFRASEA | HOCHTIEF | HOOP LOBITH | CONOVUS | HYUNDAI | INPEX | JURONG | KEPPEL | LAMPRELL | LUKOIL | MAERSK | McDERMOTT | MODEC | NOBLE | NPCC | ODEBRECHT | ODFJELL | PAXOCEAN | PEMEX | PETROBRAS | PETROFAC | PETROSERV MARINE | POET | PROSAFE | REPSOL | ROSETTI MARINO | RWE | SAIPEM | SAMSUNG | SAUDI ARAMCO | SBM | SEADRAGON | SEADRILL | SEAJACKS | SEVAN SSP | SHELL | SMIT SAVVAGE | SUBSEA7 | SWIBER | TECHNIP | TIDEWATER | TOTAL | TRANSOCEAN | VALARIS | VAN OORD | VANTAGE | WINTERSHALL | WORKFOX | WORLEY | YANTAI RAFFLES | ZITON | extract only*