

Series


Pure series

The Pure series is our basic class: simple, clear and perfectly equipped to cover all essential requirements. Pure series appliances have been reduced to the basics, but are full to the brim with the highest Liebherr quality.




Plus series

The Plus series builds on our Pure series and has many impressive additional details. "Plus" here specifically signifies enhanced convenience. These kitchen appliances are not only first-class in their refrigeration and freezing capabilities but also smarter and more user-friendly. This means they simplify many manual tasks, making life a little easier.



Prime series

The Prime series is all about class. It makes a distinctive impression when it comes to design and material. For example, top-quality materials like stainless steel are used in the interiors of our freestanding appliances. Additionally, unique lighting solutions enhance the visual appeal of this series, making it truly stand out.



Peak series

The Peak series represents our top-of-the-line offering. Here, the best is combined with the best. There is no compromise. Innovative Liebherr technology is blended with exceptional high-end design and solutions for convenience. Appliances in this series are for anyone who wants to have it all.

Our promise to you: globally unmatched energy efficiency.

World first

178

Bio Fresh

Smart Frost

Soft System

Smart Device ready

A+ G

10-year manufacturer's guarantee

ICBa 5123 ♦ Plus series

Available from the second quarter of 2025.

The ICBa 5123 is the world's first fully integrated fridge-freezer in energy efficiency class A.

home.liebherr.com

Subject to modification. Current data see home.liebherr.com. Printed in UK.

Inspired by a passion for freshness.

Inspired by a passion for freshness.

Discover our all-round, worry-free appliances that set new standards in freshness technology, efficiency and design.

LIEBHERR

Refrigeration and freezing



Decide for yourself. Or choose them all.

With us, you only have to give up one thing: compromises. We aim to offer appliances that impress not only with their top-of-the-range, innovative freshness technologies but also their sustainable product lifecycle and German engineered quality—year after year, day after day.

We have continued to grow into 2025, literally as well as figuratively – with extra-high fully integrated appliances and more space for your food. We're also offering even greater flexibility than ever before, thanks to new under counter appliances available in two different height variants. Plus, a highlight for design enthusiasts: Our brand-new freestanding fridge-freezers with French doors now include MoodLight plus a convenient Water & Ice Centre directly on the outside of the appliance.

This is on top of the many invisible innovations that make our fridges and freezers the most energy-efficient and quietest appliances on the market.

You see: We have done everything we can to make your decision to opt for a Liebherr appliance as easy as possible. You will find a few more of these reasons on the following pages. Enjoy discovering more.

German engineering – then as now.

We have been manufacturing refrigerators and freezers of the highest quality and selling them worldwide since 1954. However, at heart, we are still a family business with our roots firmly established in Germany. This is where we continue to develop our long-lasting products.

German engineering – from an enduring connection with our founder and in the knowledge that engineering expertise has been pooled here for generations.



“My life has strengthened my belief that with a firm intention to do a good job and fulfil the customers’ various wishes to the best of your ability, it is possible to achieve goals that at first seem almost unattainable. Don’t be discouraged by setbacks, and belief in yourself can move mountains.”

Dr.-Ing. e. h. Hans Liebherr (1915–1993)



The L 319 was Liebherr’s “mobile showcase” in the 1960s. Until 1968, the specially converted bus travelled around West Germany promoting the latest refrigerators and freezers from Upper Swabia.



Our first appliances came off the production line in Ochsenhausen back in 1954. And this is exactly where our main factory is still located today.

Quality that will remain quality in 15 years.

Our aspiration to deliver quality is reflected even in the smallest details. Before we approve a door hinge, for example, it must undergo at least 100,000 opening cycles. And just like the door hinge, we test every other functional part extensively and intensively. All with one purpose in mind: ensuring that our appliances have a useful life of at least 15 years.



State-of-the-art laser technology is used to check the entire door surface as well as the precision of the Liebherr font – for quality down to the finest detail.



Our path to the future

One thing unites all our product innovations: They all present a path toward greater sustainability. Taking responsibility is one of our core values. That’s why we have a decades-long tradition of research and development into eco-friendly products, with the entire product lifecycle in mind.

People and sustainable business

Respect for human rights is of the utmost importance to us. We place great value on treating everyone equally and ensuring the health, safety and personal development of our employees. We also want to make a positive contribution to our communities.

Recycling

We are aiming for a sustainable circular economy in the long term and actively design our products to maximise the reuse of the materials within them by making them easy to separate.

What is more, we emphasise responsible and economical practices, including long-term financial planning and self-financing. Fairness toward other market participants, compliance with laws and internal standards and codes of conduct are an integral part of our approach.

Materials

We want to reduce the environmental impact of our business activities by preparing recyclable products, increasing the use of renewable and recycled materials in our appliances, and reducing the variety of materials we use. In doing so, we consider the entire product.



Use

We reduce our environmental impact by continuing to offer first-class, energy-efficient products that are extremely long-lasting and easy to repair – supported by forward-thinking customer service. We also offer products and solutions that help to reduce food waste. More on this on the following pages.

Production

We want to produce in an environmentally conscious manner by reducing the energy requirements of our plants and increasingly utilising renewable energy sources. By using water responsibly, minimising waste and avoiding pollution, we reduce our environmental impact above and beyond CO₂ emissions.*



Saving food with Liebherr

Around the world, every year around 1,052 million tonnes of food are thrown away. ¹ For an average household, this works out at around 113 kg annually.²



¹ UNEP Food Waste Index Report (2024)
² GfK (2021). For a two-person household in Germany
³ Our World in Data (2022)

113 Kilograms²

The amount of food waste can be roughly broken down into the following groups: ²



50 %
fresh fruit and
vegetables



4 %
dairy products



5 %
meat and fish



7 %
cooked and ready-
made food

Food has not only emotional and financial value, but also environmental value.

Food production is responsible for ³



of all global greenhouse emissions and



of freshwater consumption.



With our carefully considered freshness technologies and digital solutions, we help you to reduce food waste in very simple ways.

For perfect food storage, alongside the ideal temperature, optimal humidity is a decisive factor. At Liebherr, we have developed innovative freshness technologies and continue to improve them year after year. This way, food tastes genuinely fresh even after several days and retains all of its vitamins and nutrients. For each type of fresh food, we have just the right freshness technology:



DuoCooling

Freshness technologies

Easy
Fresh

+10 days

+8 days

+3 days

+10 days

The specified
comparisons
in days are
relative to the
regular fridge
compartment.

Freshness technologies

The specified
comparisons in
days are
relative to the
regular fridge
compartment.

+16 days

+90 days

+7 days

+8 days

Bio
Fresh

Meat & Dairy Safe



EasyFresh – ideal for fruit and vegetables

Unpackaged fruit and vegetables feel right at home here. When stored at the same temperature as the fridge compartment and sealed airtight in the safe, lettuce, for example, remains crisp and fresh even after seven days.



DuoCooling – no drying out

Our basic technology in our fridge-freezers. The two completely separate cooling circuits ensure that there is no exchange of air between the fridge and freezer compartments. The food stays fresh without drying out, and odours are not transferred.



NoFrost – No more defrosting

The automatic defrosting function guarantees that frozen food remains fresh. There is no longer a need to store frozen food temporarily during a manual defrost. The constant optimal freezing remains the same without any interruptions.



BioFresh – our all-rounder

The reliable BioFresh technology stores groceries at a temperature of just above 0°C, much cooler than the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable Safe. Meat, fish and dairy products benefit from ideal conditions in the Meat & Dairy Safe.



BioFresh Professional with HydroBreeze – refrigerate like a pro

A cold mist covers fruit and vegetables like a protective balm, ensuring crisp freshness and improving structure – the special wow effect for fruit and vegetables in the BioFresh Professional Safe.




BioFresh Professional with Fish & Seafood Safe – like freshly caught fish from the market.

Particularly delicate foods like fish and seafood are best stored in icy temperatures and at low humidity. The constant temperature of -2 °C in the Fish & Seafood Safe is therefore ideal to keep items tasting fresh for longer.

Maximum efficiency
with Liebherr

Because they run 24 hours a day, the biggest environmental impact of fridges and freezers is the energy they consume while in use. They account for about a fifth of the electricity used by an average household.¹



Our fridges are real all-rounders: In addition to the low power consumption across our entire product range, they also impress with a low noise level, plenty of space for food and intelligent sensor technology for optimum cooling power.

Energy consumption

Our appliances take top spots in the efficiency rankings or even outperform the highest efficiency class. This means they protect our precious environmental resources, as well as your wallet.

Cooling volume

From extra-large drawers down to the tiniest details, we ensure that not a litre of cooling volume is wasted, all while maintaining maximum energy efficiency.

Noise level

Kitchens are increasingly becoming part of our living areas. That's why we focus not only on maximum energy efficiency but also on 'audibly' quieter appliances.

Cooling power

Our appliances' intelligent sensor systems constantly adapt the cooling power to the current use – making them efficient and economical day to day, but fully up to the job when the weekly shopping arrives.

¹ German Federal Environmental Agency (2021). For an average household in Germany.

Another 30% more economical* than appliances in the highest energy efficiency class A: Our freestanding fridge sets new standards – even for us.

The ultra-efficient fridge is one of the most energy-saving models on the market. The features leave nothing to be desired: The BioFresh safes ensure that food stays fresh for longer and control at your finger tips, with Touch & Swipe display. The appliance is also super quiet at 34 dB(A).




For more, please visit home.liebherr.com

*Compared to the threshold of the highest energy efficiency class A as per Regulation (EU) 2019/2016 (as of July 2023).

Energy efficiency champions

Our promise: Globally unmatched energy efficiency.



ICBa 5123 ♦ Plus series
Available from the second quarter of 2025.

♦ Plus series



ICBa 5123
World first:
The first fully integrated fridge-freezer in energy efficiency class A.

Available from the second quarter of 2025

◊ Prime series



ICBn 5123
The first Liebherr fully integrated fridge-freezer with NoFrost in energy efficiency class B.

Available from the second quarter of 2025



IRBbi 5150
The first fully integrated fridge for a 178-cm recess with BioFresh in energy efficiency class B.



Freshness without compromise

Reliability and durability are not just buzzwords for us. Why? Because at Liebherr, every tiny detail must meet our demanding requirements. Every functional part is extensively and intensively tested. We don't stop until we are convinced that our fridges and freezers are of the highest quality.



*This guarantee is granted free of charge for all freestanding fridge-freezers in energy efficiency classes A, B, and C, extended to fully integrated fridges, freezers and fridge-freezers with energy efficiency classes of A and B. With our manufacturer's guarantee, you will not incur any costs for repair and service for 10 years.

For more information, registration and guarantee conditions, go to: home.liebherr.com/guarantee



To register and see the guarantee terms and conditions, go to home.liebherr.com/guarantee

10-year manufacturer's guarantee

Secure your 10-year manufacturer's guarantee:



Buy

Buy a qualifying appliance* from a Liebherr specialist dealer by 31/12/2025.



Register

Register your appliance within 12 months using our web form or SmartDevice app.



Enjoy

Enjoy 10 years of Liebherr manufacturer's guarantee and long-lasting freshness.



It's what's inside that counts.

At first glance, the new FNa 6635 looks like any other Liebherr freezer, but there is much more to it. Each component has been carefully selected to develop an appliance that not only offers optimal energy efficiency but also has the least impact on the environment.



FNa 6635 ♦ Plus series *

*This model is special order only

Made in Germany

Sustainable freezing revolutionised – with vacuum and volcanic rock.

Our vacuum perlite technology is an innovation that will transform refrigeration and freezing. Introducing BluRoX.



BluRoX

Made in Germany

Inner liner and insulating foam

Both the inner liner and the insulating foam contain recycled materials, as well as materials from organic sources. These help reduce the environmental impact while maintaining the same excellent insulation performance.

Product packaging

The environmental footprint of the packaging has also been reduced without compromising safety during transport.



Side panels and door

The door and side panels are made from 100% recycled steel, the production of which generates 80% less CO₂ emissions than the production of conventional steel.

Door seal

The TPE used for the door seal combines optimum functionality, durability and good recyclability.

Our pioneering BluRoX technology features perlite, finely ground volcanic rock, in vacuum insulation. This enables unmatched energy efficiency, as well as a significant increase in the freezing volume with the same exterior dimensions. Unlike conventional insulation methods, the unique and patented BluRoX technology provides optimal thermal conductivity, which significantly reduces energy consumption and sets new standards in sustainable cooling.



FNa 505i ◊ Prime series



The first hybrid model with BluRoX in the door as well as the first NoFrost freezer (165 cm) in energy efficiency class B.




To learn more about this exciting technology and the many advantages of BluRoX, visit: home.liebherr.com/blurox



For the highest demands

We are expanding our range of fully integrated fridge-freezers. Or, should we say, we're raising it. Our 194cm high XL fully integrated fridge-freezers fit seamlessly into high-quality kitchen designs and impress in every way: two BioFresh Safes, the highest energy efficiency in their class and a timeless, elegant design. Discover our new XL fully integrated appliances from the Pure, Plus and Prime series – perfect for everyone, even those with the most exacting demands.



Perfect freshness for a vegetable-rich diet



This Liebherr with two Fruit & Vegetable safes guarantees plenty of space and ideal conditions for keeping vegetables fresh and tasty. The clever FlexSystem in each BioFresh drawer keeps everything tidy and easy to find. Perfect freshness for a vegetable-rich diet.

Variable temperature space as required

With VarioTemp, there is flexibility for every situation. The freezer compartment can be adjusted to a fridge or cellar compartment, with a variable temperature between -2 °C and +14 °C.

As a result, you are always perfectly prepared, even for big parties. If necessary, the freezer compartment can be used as an additional cooling zone for appetisers or drinks. Or as a cellar compartment for groceries that are sensitive to cold, such as potatoes, onions and other similar items.

Your family has grown and you are running out of space in your fridge-freezer? Not a problem. VarioTemp allows you to use the freezer compartments as a fridge in your kitchen. If combined with a separate freezer, this means you have enough space to supply even a large family with fresh groceries.



Use as fridge compartment (between -2 °C and +9 °C)



Use as freezer compartment (-18 °C)



Use as cellar compartment (+14 °C)



The GlassLine pull-outs in our undercounter models close gently with a self-closing mechanism. The lower LiftUp-Box slides upwards when pulled out for easy removal.



One beverage store. Two options.


The practical pull-out shelf made of telescopic pull-outs in the IRDdi 5120 and with freezer compartment IRDdi 5121 is equipped with two removable bottle baskets for easy transport. It can also be loaded with a whole crate of beverages to quench your thirst.



IRDdi 5120 ♦ Plus series

Specially designed for cool drinks

With Liebherr, your guests will never go without a perfectly cooled drink. This is thanks to the integrated cold water source and a never-ending supply of ice. The easy way to have constant refreshment.



Water & Ice Centre

Direct access: the Water & Ice Centre

In the door of our new fridge-freezers with French doors (see also pages (32 - 33), the Water & Ice Centre provides plenty of cold water, ice cubes and crushed ice around the clock.



Ice Tower

Enough ice for even the largest party: the IceTower

The IceTower in our freezers sets new standards by combining two large compartments – the automatic IceMaker for up to 8 kg of ice cubes, and another spacious compartment large enough to store a few family-sized pizzas upright, for example. And because that was not convenient enough for us, both compartments glide in and out on a pull-out shelf with telescopic rails. We have even thrown in an ice shovel, so your hands can stay warm while you handle so many chilled goods.



Ice Maker

It's raining ice cubes: the IceMaker

Each day, the IceMaker produces up to 130 ice cubes, which automatically drop into two drawers. When MaxIce is activated, it is even possible to speed up the production of ice cubes if more guests than expected arrive. The IceMaker is connected to the fresh water pipe. If no plumbed-in connection is available, a model with a water tank in the fridge compartment is also available.



Water and ice

Infinity Spring

Ice-cold water on tap with no heavy lifting

With the InfinitySpring, we bring a crystal clear, cold water source right into the heart of your kitchen, so you can always stay hydrated. This makes lugging of heavy crates and water in plastic bottles a thing of the past, relieving the strain on your back and on our environment. Simple and sustainable.



Easy Twist Ice

Ice in an instant: EasyTwist-Ice

Quickly rustle up a supply of ice cubes – without a plumbed-in connection. Simply fill the tank with water, let it freeze and then release the ice cubes with a twist. EasyTwist-Ice is easy to clean and is installed in many of the freestanding appliances in our Plus series.



CBNsda 575i ◊ Prime series

No more defrosting thanks to NoFrost



The NoFrost automatic defrosting function guarantees that frozen foods remain fresh.

There is no longer a need to store frozen food temporarily during a manual defrost, as the food is frozen with cooled recirculated air and the air humidity is also diverted. This keeps the freezer compartment ice-free at all times, and food is no longer covered in frost. The constant optimal freezing remains the same without any interruptions.

Convenience and flexibility – freezing



Open the door multiple times with ease: EasyOpen

Have you experienced this problem? Once you've put your shopping away in the freezer, you notice that you've left something on the side and you have to pull hard to open the door again. This does not happen with a Liebherr: EasyOpen means the door can be opened multiple times in succession, conveniently and easily.



Fridge compartment
(-2 °C to +9 °C)



Cellar compartment
(+14 °C)



Freezer compartment
(-18 °C)

VarioTemp

Versatile freshness with a freezer compartment that can also be a fridge.

With VarioTemp, you can set the temperature of the freezer compartment in your fridge-freezer from -2 °C to +14 °C. This allows you to use this space as an extra cooling zone at parties or as a 'cellar compartment'. Don't need the freezer compartment? Switch it off independently of the fridge compartment and save energy and money.

When below zero is a big plus

No room for a freezer in the kitchen or other heated areas in your home? We have some great news: with FrostProtect, all components are designed for temperatures as low as -15 °C, no matter what groceries you are storing. If the ambient temperature falls below 0 °C, our freezers continue working just as efficiently, saving just as much energy and keeping your frozen food just as well protected. This means that you can put them in unheated spaces like a garden shed or garage, giving you more room for more important things.




Frost Protect



Always well connected

Almost all Liebherr appliances are either factory-equipped with a network connection module or can be retrofitted with the SmartDeviceBox.

This way, you will benefit from the many possibilities offered by our SmartDevice app and from connecting your fridges, freezers or wine fridges to your existing smart home environment. Important status and alarm notifications are sent directly to your smartphone, such as notification of an open fridge door via door alarm. Our SmartDevice app offers much more than that: In addition to simple management and remote control of your appliances, the app also helps you with tips and tricks for your Liebherr appliance. The right accessories for each appliance, access to instruction manuals and much more can also be found here.




One less task for you.


Our AutoDoor feature perfectly complements the handle-less kitchen, as the Liebherr appliances open automatically in response to a knock, via the SmartDevice app, or by voice command*.

Plus, the door does more than just open automatically, it makes things easier for you in every way by adjusting the settings to suit your needs. The opening angle and how long the door stays open before it closes automatically can be individually selected. Anybody who still prefers to open and close our fully integrated appliances by hand is, of course, free to do so.

* Voice command requires a smart speaker and Google Assistant or amazon Alexa



You can download the SmartDevice app here:



home.liebherr.com/getsmart



Find out more about our automatic door on selected models at:
home.liebherr.com/autodoor

Make a statement.



XRFbs 5295 Δ Peak series

Tasteful inside and out:

Our award-winning appliances with a BlackSteel interior fit in while also standing out. The finest black stainless steel, both inside and out, gives all BlackSteel freestanding appliances from the Peak and Prime series, as well as selected fully integrated Peak appliances, an exclusive and eye-catching look for you to enjoy every time you open the door.



Handle with opening mechanism

The door handle adapts gently to your hand movement, making it even easier to open.



Fits perfectly

With InteriorFit, our freestanding appliances fit into the kitchen in a space-saving way – they do not require any lateral ventilation distance from the walls or adjacent furniture. Only the fridge door is visible in your kitchen. Everything else is invisible.

Superb, even down to the smallest detail

How would we describe our new French-door appliances? Superb in the truest sense of the word. With maximum storage space for freshness and quality down to the finest detail, nothing is left to be desired.

Visually, the impressive fridge-freezers feature sophisticated design highlights and features, such as the MoodLight, the Water & Ice centre and the VarioTemp zone. Ample space for freshness behind the French doors – whether with EasyFresh, BioFresh or BioFresh Professional with HydroBreeze. Open the doors individually and easily thanks to our patented FlexDoorSystem. Plus, these combination appliances are available in two versions: as a French-door fridge compartment with two freezer drawers or with four French doors, one pair on the fridge and one on the freezer compartment. Suffice to say, superb is something of an understatement for these new French-door appliances.



MBbsdi 9024 ♦ Plus series
Available from the fourth quarter of 2025



FlexDoorSystem

Quiet opening and closing: With the patented FlexDoorSystem, the French doors can be opened and closed one at a time. The doors open easily, close securely and the 100% tight closure helps save energy.




Water & Ice Centre

The Water & Ice Centre supplies cold water, ice cubes and crushed ice 24 hours a day. Practical: The water volume of the water dispenser can be set individually for each desired container.



VarioTempZone

Maximum flexibility: The VarioTempZone can be set to the exact degree from -18 to -10 °C and from -2 to +5 °C, turning it into an extra cooling zone, if required.



Surface options

No matter which material you choose, one thing is certain: your appliance will draw the eye.

Designed for exquisite kitchens. Meeting the highest expectations.

The generous BioFresh Professional safes including HydroBreeze in the top safe, plenty of space in the NoFrost freezer compartment with IceMaker and a separate wine-tempering compartment make our new Side-by-Side fridge-freezers an elegant freshness hub for your kitchen. And thanks to InfinitySpring in the fridge compartment, there will always be cooled water ready for you.

SmartSteel



XRCst 5295 Δ Peak series

BlackSteel



XRCbs 5295 Δ Peak series

↑
185
↓

←121→

2
Zones

max. 44

No
Frost

Ice
Maker

Bio
Fresh
Professional

Hydro
Breeze

Infinity
Spring

Glass &
Steel
Interior

XRCbs 5295 Δ Peak series

No recess? How about a kitchen island.
There are installation options for every
situation.

They are easy to plan, simple to install and impressively equipped:
The new Liebherr under counter appliances are now available in
variants with a height of 82 to 88 cm
and with a height of 86 to 92 cm,
meaning that they fit perfectly under
any work surface.

With a wide range of models and the highest quality, thanks
to German engineering, these fridges and freezers allow
room for even more flexibility in kitchen design. Thanks to
many clever interior solutions, our compact fridges, freezers
and wine fridges are real space-saving wonders. We are
certain that the wide range of models and equipment
options will allow every customer to find exactly what they
are looking for.



Decor options
Decor panel-ready appliances can
be fitted with a kitchen front to
match the kitchen plan or (as a
Liebherr accessory) with a stainless
steel panel and separate handle
options. It can even be handle-free
with the TipOpen feature

82-88

2
Zones

UWgbi 3682 Vinidor Selection


No
Frost

SUFNd 365i Prime series

Easy
Fresh

URd 365i Prime series


82-88



+9 l
more cooling volume



86-92



Treasuring true taste.

Discover our wine fridges – and find out how you can not only store your collection under the perfect conditions, but preserve the very essence of the wine.



Qualities that surpass even those of a wine cellar.

They not only match wine cellars in terms of the five essentials of perfect storage but surpass them, thanks to our engineering expertise. We take care of every detail.





SommelierBoard

An absolute highlight in our Vinidor Selection Series. There's room to show off everything you need for decanting. The high-quality shelf made of natural beechwood comes with a stainless-steel bottle presenter, a wooden box for decanting utensils and a space for tempering wine glasses for that extra-special enjoyment.



LightTower

One of the most important design elements is lighting. In our Vinidor Selection models, the LightTower vertical lights on each side beautifully illuminate the wine collection. The lighting can be activated each time the door is opened, or remain on at all times when the dimmable presentation light is set.



Vertical recessed grip

All models in the Vinidor Selection series have a recessed vertical grip extending the entire length, allowing for ergonomic and comfortable opening from any position. Models with the optically discreet grip integrate harmoniously into handle-free kitchens and living-dining areas.



FlexFit wooden shelves

The removable slats of the FlexFit wooden shelves ensure they accommodate any bottle, even magnums. Plus, thanks to the individual placement of the slats in the frame, all bottles are stored safely.



More information on wine storage and our wine fridges, including detailed model descriptions, can be found in our special wine brochure available from a Liebherr specialist dealer or at: home.liebherr.com/wine



3 Zones

Sommelier Board

Light Tower

Flex Fit

Humidity Select

Soft System

Smart Device



2 Zones

3 Zones

WPgbi 5283 Vinidor Selection

With two or three separate temperature zones that can be set accurately to the degree between +5 °C and +20 °C, our wine tempering fridges offer maximum versatility of use. This means that red wines, white wines, and champagnes can all be stored at the same time and at an ideal temperature in one single appliance with three temperature zones. With their temperature zones of different sizes and temperature settings that offer complete flexibility, these appliances are perfect for each individual wine collection.



WPbli 5231 GrandCru Selection

1
Zone

Our wine storage fridges replicate the conditions of a wine cellar. A constant temperature is maintained throughout the interior of these appliances. This can be adjusted to between +5 °C and +20 °C, as required. Wine storage fridges are specially designed to hold a large number of bottles for storing and maturing, but they can also keep a larger stock of wine at drinking temperature.


To reduce printing requirements, only the key equipment details are mentioned. Detailed model descriptions can be found at home.liebherr.com

- 1
Zone
- Humidity
Control
- Light
Column
- UV
Protect
Plus
- Smart
Device



Humidity regulation

With HumiditySelect, the humidity of GrandCru models can be adjusted in two stages: dehumidify or humidify. GrandCru Selection models are equipped with HumidityControl, which allows the humidity to be set as required within the range of 50% to 80% RH*. If the value falls below 50% RH, the appliance indicates this.



LightColumn, one-sided

For a perfect view of your wine: The LED LightColumn runs from the top to the bottom of your glass-door appliance. It evenly illuminates the interior of your GrandCru Selection wine storage fridge. A special highlight is the dimmable presentation light for attractively showing off your wine collection even when the door is closed.



Neck-to-neck storage for maximum bottle capacity

A Liebherr wine storage fridge also makes it easier to organise a growing wine collection. To take full advantage of its capacity, the interior has been designed so that your wine bottles can be stored neck-to-neck on the wooden shelves. This means there is plenty of room even for ever-increasing wine collections. So feel free to keep collecting.



FreshAir activated charcoal filter

To ensure that your wine can mature in optimum air quality, all Liebherr wine storage fridges have an activated charcoal filter that reliably protects wine from all odours. This means your wine will keep its pure bouquet. To make sure that it stays that way, your Liebherr reminds you every six months to change the filter, which you can easily do yourself.

* For temperatures in the living environment. Such as very dry or cold cellars, we recommend supporting the system with the tailor-made water box from our range of accessories.

Refrigeration and freezing

Model overview



XRCsd 5255 ○ Prime series

Our complete Liebherr portfolio of freestanding and fully integrated appliances with detailed product descriptions can be found on our website, which also lists Liebherr specialist dealers – visit us at: home.liebherr.com

For a clear overview – before you even open the fridge

- Pure
- ◇ Plus
- ◻ Prime
- △ Peak

Which appliance is right for me? This question is not always easy to answer when you are buying a new appliance. That's why we have made it even easier for you to find your way around our range of products by dividing our fridges and freezers into four series.

Freestanding appliances



CBNste 8872



CBNste 8872



MBbsdi 9528



MBsddi 9028

Model / series	Energy rating	Bio Fresh Professional	Hydro Breeze	Bio Fresh	Easy Fresh	No Frost	Vario Temp Zone	Mood Light	Soft System	Water & Ice Centre	Ice Maker
----------------	---------------	------------------------	--------------	-----------	------------	----------	-----------------	------------	-------------	--------------------	-----------

French door fridge-freezers											
with 2 drawers	CBNste 8872*										
	MBsddi 9558** Prime										
	MBbsdi 9528** Plus										
	MBtsdi 9528** Plus										
with 4 doors	MBsddi 9524** Plus										
	MBsddi 9058** Prime										
	MBsddi 9028** Plus										
	MBbsdi 9024** Plus										
	MBsddi 9024** Plus										
	Msdd 9012** Pure										

LOB

Model overview – freestanding appliances



XRCst 5295



XRFbs 5295



XRCsd 5255

Model / series	Energy rating	Bio Fresh Professional	Hydro Breeze	No Frost	Soft System	Ice Maker	Smart Device	Wine
----------------	---------------	------------------------	--------------	----------	-------------	-----------	--------------	------

Side-by-Side fridge-freezers with BioFresh Professional / Wine

← 60 → ↑ 185	← 60 → ↑ 185	XRCbs 5295 Peak						
		SWNbsd 529i						
		SRBbsc 529i						
		XRCst 5295 Peak						
		SWNstd 529i						
		SRBstc 529i						

Model / series	Energy rating	Bio Fresh Professional	Hydro Breeze	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Smart Device	Smart Device ready
----------------	---------------	------------------------	--------------	-----------	------------	----------	-------------	-----------	--------------	--------------------

Side-by-Side fridge-freezers with BioFresh Professional / BioFresh

← 60 → ↑ 185	← 60 → ↑ 185	XRFbs 5295 Peak							
		SFNbsd 529i							
		SRBbsc 529i							
		XRFst 5295 Peak							
		SFNstd 529i							
		SRBstc 529i							
		XRCsd 5255 Prime							
		SBNsdd 526i							
		SRsdc 525i							
		XRFsf 5245 Plus							
		SFNsfd 5247							
		SRBsfc 5220							
		XRFsf 5225 Plus							
		SFNsfd 5227							
		SRBsfc 5220							

LOB

Key to appliance material:
_st SmartSteel
_sd SmartSteel door
_bs BlackSteel
_bd BlackSteel door
_ts TerraSteel
_sf SteelFinish



XCCsd 5250



XRFsf 5240



XRFbd 5220

Model / series	Energy rating							
----------------	---------------	--	--	--	--	--	--	--

Side-by-Side fridge-freezers with EasyFresh

← 60 → 185	← 60 → 185	XCCsd 5250 Prime							
		SCNsdc 525i		■	■	■	■	■	
		SCNsdc 525i		■	■	■	■	■	
		XRFsf 5240 Plus							
		SFNsfd 5247			■		■		■
		SRsfd 5220			■				■
		XRFbd 5220 Plus							
		SFNbdd 5227			■				■
		SRbdd 5220			■				■
		XRFsf 5220 Plus							
		SFNsfd 5227			■				■
		SRsfd 5220			■				■
		XRF 5220 Plus							
		SFNd 5227			■				■
		SRd 5220			■				■

Key to appliance material:

- _st SmartSteel
- _sd SmartSteel door
- _bs BlackSteel
- _bd BlackSteel door
- _ts TerraSteel
- _sf SteelFinish
- _ White



CBNstb 579i



CBNa 572i



CNSdd 776i

Model / series	Energy rating											
----------------	---------------	--	--	--	--	--	--	--	--	--	--	--















Fridge-freezers with BioFresh Professional / BioFresh

202	← 60 →	CBNstb 579i	Peak		■	■	■			■	■	■
		CBNsda 575i	Prime		■			■	■		■	■
		CBNbdc 573i	Plus		■			■				■
		CBNbda 572i	Plus		■			■			■	■
		CBNsda 572i	Plus		■			■			■	■
		CBNa 572i	Plus		■			■			■	■
		CBNsfc 57vi	Plus		■			■			■	■
		CBNc 5723	Plus		■			■			■	
186	← 60 →	CBNbda 5223	Plus		■			■			■	■
		CBNsda 5223	Plus		■			■			■	■
		CBNsfc 5223	Plus		■			■			■	■
		CBNc 5223	Plus		■			■			■	■

Fridge-freezers with EasyFresh

202	← 75 →	CNSdd 776i	Prime					■	■	■	■		■
		CNsfa 7723*	Plus		■			■	■				■
202	← 60 →	CNc 5724	Plus		■			■	■			■	■
		CNbda 5723	Plus		■			■	■			■	■
		CNsda 5723	Plus		■			■	■			■	■
		CNsfd 5704	Pure					■	■				■
		CNsfd 5703	Pure					■	■				■
		CNd 5703	Pure					■	■				■
186	← 60 →	CNsdb 5223	Plus		■			■	■			■	■
		CNsfd 5204	Pure					■	■				■
		CNd 5204	Pure					■	■				■
		CNsfd 5203	Pure					■	■				■
		CNd 5203	Pure					■	■				■


*Special order only

							
CUele 3331		CUele 2831		CUe 2331			
Model / series		Energy rating	Easy Fresh	Smart Frost	Soft System	Smart Device	Smart Device ready
Fridge-freezers							
181	↔ 55 ↔	CUele 3331					
161	↔ 55 ↔	CUele 2831					
		CUe 2831					
137	↔ 55 ↔	CUele 2331					
		CUe 2331					
157	↔ 55 ↔	CTele 2931					
		CTe 2931					
140	↔ 55 ↔	CTele 2531					
		CTe 2531					
124	↔ 55 ↔	CTele 2131					
		CTe 2131					

LGB

LGB

The current EU energy label for electrical appliances



1. The QR code to identify the product in the EU database EPREL (European Product Registry for Energy Labelling).
2. The model identifier for manual identification of the product in the EU database EPREL, using the article number for example.
3. The new efficiency scale from A to G. However, "G" is only intended for wine fridges.
4. The total volume* of all freezer compartments.
5. The total volume* of all cold storage and refrigerator compartments.
6. The noise level is now classified into classes "A" to "D".

* The term "volume" is defined in the current Regulation (EU) 2019/2016.
















						
RBsdc 525i		RBc 5220		RBa30 425i		
Model / series		Energy rating	Bio Fresh	Soft System	Smart Device	Smart Device ready
Fridges with BioFresh Professional / BioFresh						
186	↔ 60 ↔	RBsdc 525i Prime				
		RBc 5220 Plus				
126	↔ 60 ↔	RBa30 425i Prime				
						
Rd 5220		Rd 5000		Rd 4200		
Model / series		Energy rating	Easy Fresh	Smart Device ready		
Fridges with EasyFresh						
186	↔ 60 ↔	Rd 5220 Plus				
166	↔ 60 ↔	Rd 5000 Pure				
146	↔ 60 ↔	Rd 4600 Pure				
126	↔ 60 ↔	Rd 4200 Pure				

Key to appliance material:

- _st SmartSteel
- _sd SmartSteel door
- _bs BlackSteel
- _bd BlackSteel door
- _ts TerraSteel
- _sf SteelFinish
- _ White

You can find the full range of efficiency ratings on page 50. According to (EU) 2017/1369 6a.


















LGB

								
		Rsdci 1620		Re 1401		OKes 1750		
Model / series		Energy rating		Easy Fresh		Smart Frost		
				Door Stop		Smart Device		
				Outdoor				
Under counter refrigerators								
85	-- 60 --	Rsdci 1620	Plus		■		■	
		Rsdci 1621	Plus		■		■	
		Rdi 1620	Plus		■		■	
		Rdi 1621	Plus		■		■	
85	-- 55 --	Rd 1400	Pure				■	
		TK 14Vd00	Pure					
		Re 1400	Pure				■	
		Re 1401	Pure		■ *			
85	-- 50 --	Rd 1200	Pure				■	
		Rd 1201	Pure		■ *			
		Re 1200	Pure				■	
82	-- 60 --	OKes 1750						■
* with 4* freezer compartment								





































LGB

Key to appliance material:

- _st SmartSteel
- _sd SmartSteel door
- _bs BlackSteel
- _bd BlackSteel door
- _ts TerraSteel
- _sf SteelFinish
- _ White

										
		Fnc 7227	FNa 6625	FNb 505i						
Model / series		Energy rating	No Frost	Telescopic Rails	Easy Open	Frost Protect	Easy Twist Ice	LED	Smart Device	Smart Device ready
<div><div><div>BLU performance</div></div><div>Freezers with NoFrost</div></div>										
186	↔ 70 →	Fnc 7227	Plus							
146	↔ 70 →	FNa 6635 *	Plus							
		FNa 6625	Plus							
186	↔ 60 →	Fnc 527i	Peak							
		FNe 5207	Pure							
166	↔ 60 →	FNb 505i	Prime							
		FNd 5026	Plus							
146	↔ 60 →	FNb 465i	Prime							
		FNd 4625	Plus							
126	↔ 60 →	FNb 425i	Prime							
		FNd 4224	Plus							
		FNe 4204	Pure							
*Special order only										

LGB

									
FNSddi 1624		FNdi 1624		Fe 1404					
Model / series		Energy rating	No Frost	Smart Frost	Frost Protect	LED	Smart Device		
Under counter freezers									
85 ↑ ↓	↔ 60 ↔	FNSddi 1624	Plus						
		FNdi 1624	Plus						
		Fdi 1624	Plus						
85 ↑ ↓	↔ 55 ↔	TGN 14Ve04	Pure						
		Fd 1404	Pure						
		Fe 1404	Pure						



CFe 2500

Model / series		Energy rating	Stop Frost	Super Frost	Frost Protect	LED
Chest freezer						
83	↔ 168 ↔	CFe 2500 Pure				

Key to appliance material:

- _st SmartSteel
- _sd SmartSteel door
- _bs BlackSteel
- _bd BlackSteel door
- _ts TerraSteel
- _sf SteelFinish
- _ White

Side by Side

Fully integrated appliances

Your individual freshness centre

Combine your Liebherr fully integrated appliance with complete flexibility to suit your freshness needs. Many models can be vertically and / or horizontally combined to form an individual freshness centre, providing perfect solutions to all your storage needs.

Ask your Liebherr dealer or kitchen specialist about the Liebherr Side-by-Side concept.



IXRF 5175 Peak series



ECBNe 8872



ECBNe 8870



ECBNe 7870

Model / series		Energy rating	Bio Fresh	No Frost	Soft System	Ice Maker
Integrated fridge-freezers French door / Large door with BioFresh						
203	↔ 91,5 ↔	ECBNe 8872				
		ECBNe 8870				
		ECBNe 8871				
203	↔ 76,2 ↔	ECBNe 7870				
		ECBNe 7871				

Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.



ICBNci 5153



ICNb 5123

Model / series	Energy rating											
----------------	---------------	--	--	--	--	--	--	--	--	--	--	--

Integrated fridge-freezers with BioFresh Professional / BioFresh

ICBNdi 5163	Prime					■		■		■	■	
ICBNci 5153	Prime					■		■			■	
ICBNdi 5123	Plus					■		■			■	
ICBa 5123	Plus		■			■		■	■			■
ICBbi 5122	Plus		■			■		■	■		■	

Integrated fridge-freezers with EasyFresh

↑ 194 ↓	↔ 56-57 →	ICNSd 5603**	Pure						■	■				■
		ICNd 5603	Pure						■	■				■
↑ 178 ↓	↔ 56-57 →	SICNdi 5153	Prime						■	■		■		
		ICNb 5123	Plus		■				■	■		■		■
		ICNd 5123	Plus						■	■		■		■
		ICNc 5103	Pure						■	■				■
		ICNe 5103	Pure						■	■				■
		ICSe 5103**	Pure						■		■			■
		ICe 5103	Pure						■		■			■

LOB



IRBci 5180



IRBc 4520

Model / series	Energy rating								
----------------	---------------	--	--	--	--	--	--	--	--

Integrated fridges with BioFresh Professional / BioFresh

IRBbi 5150	Prime		■				■	■		■	
IRBd 5120	Plus						■	■			■
IRBSd 5120**	Plus						■				■
IRBc 4520	Plus						■	■			■
IRBSd 4120**	Plus						■				■

LOB



Model / series		Energy rating	Easy Fresh	Smart Frost	Soft System	Auto Door	Smart Device	Smart Device ready
Integrated fridges with EasyFresh								
178	~ 56-57 ~	IRDdi 5120	Plus		■		■	
		IRe 5100	Pure		■			■
		IRe 5101	Pure		■	■ *		■
140	~ 56-57 ~	IRd 4520	Plus		■		■	■
		IRe 4100	Pure		■			■
122	~ 56-57 ~	IRe 4101	Pure		■	■ *		■
		IRci 3950	Prime		■		■	
88	~ 56-57 ~	IRc 3920	Plus		■		■	■
		IRc 3921	Plus		■	■ *	■	■
		IRe 3900	Pure		■			■
		IRSe 3900**	Pure		■			■
		IRSe 3901**	Pure		■	■ *		■

* with 4* freezer compartment

** with sliding door instead of door-on-door assembly
For reasons of space, only the most important distinguishing features are mentioned. Detailed model descriptions can be found at [home.liebherr.com](#)



Model / series		Energy rating	10 years warranty	No Frost	Smart Frost	Soft System	Ice Maker	Ice Tower	Auto Door	LED	Smart Device	Smart Device ready
Integrated freezers												
140	~ 56-57 ~	SIFNdi 5188	Peak			■		■	■		■	■
		SIFNe 5128	Plus			■						■
		SIFNSe 5128**	Plus			■						■
		SIFNe 5108	Pure			■						■
		SIFNdi 4556	Prime			■					■	■
122	~ 56-57 ~	SIFNdi 4155	Prime			■					■	■
		SIFNci 3954	Prime			■					■	■
88	~ 56-57 ~	IFNd 3924	Plus			■						■
		IFd 3904	Pure				■					■
		IFSd 3904**	Pure				■					■
		IFNd 3503	Pure			■						■

You can find the full range of efficiency ratings on page 50. According to (EU) 2017/1369 6a.

URc 375i

URc 3700

URd 3600

Model / series

Energy
rating

Easy
Fresh

Smart
Frost

Soft
System

Smart
Device

Under counter fridges

URc 3700

Pure

URc 3701

Pure

URPd 365i

Prime

URd 365i

Prime

URd 3600

Pure

URd 3601

Pure

■*

■

■







■

■


■

■*
















* with 4* freezer compartment

						
SUFc 3703		SUFc 3703		SUFd 3603		
Model / series		Energy rating	No Frost	Smart Frost	LED	Smart Device
Under counter freezers						
82-88 ↑ ↓	SUFc 3703	Pure			■	
	SUFNd 365i	Prime		■		■
	SUFd 3603	Pure			■	

For reasons of space, only the most important distinguishing features are mentioned. Detailed model descriptions can be found at home.liebherr.com



Wine appliances

													
WPgbi 7483		WPbsi 5252		WPsd 4652									
Model / series		Energy rating	2 Zones	3 Zones	Glass Door	Humidity Select	UV Protect Plus	Sommelier Board	Soft System	Smart Device	Smart Device ready		
201 ↑ ↓	-- 70 --	WPgbi 7483	Vinidor Selection			■	■	■	■	■	■	■	149
		WPgbi 7473	Vinidor Selection			■	■	■	■	■	■	■	182
		WPgbi 7472	Vinidor Selection		■		■	■	■	■	■	■	204
185 ↑ ↓	-- 60 --	WPgbi 5283	Vinidor Selection			■	■	■	■	■	■	■	85
		WPgbi 5273	Vinidor Selection			■	■	■	■	■	■	■	104
		WPgbi 5272	Vinidor Selection		■		■	■	■	■	■	■	106
		WPbsi 5252	Vinidor		■		■	■	■	■	■	■	155
		WSbsi 5252	Vinidor		■		■	■	■	■	■	■	155
		WPsd 5252	Vinidor		■		■	■	■	■	■	■	155
165 ↑ ↓	-- 60 --	WPbsi 5052	Vinidor		■		■	■	■	■	■	131	
145 ↑ ↓	-- 60 --	WPsd 4652	Vinidor		■		■	■	■	■	■	107	


*Maximum capacity of Bordeaux bottles (0.75 l) based on: H: 300.5 mm, ø: 76.1 mm.
You can find the full range of efficiency ratings on page 50. According to (EU) 2017/1369 6a.



Model / series		Energy rating	1 Zone	Glass Door	Humidity Control	Humidity Select	UV Protect Plus	Smart Device	Smart Device ready	✎*
Freestanding wine storage fridges										
204 ↑ 188 ↓	↔ 75 →	WSbli 7731	GrandCru Selection		■		■		■	324
	↔ 60 →	WPbli 5231	GrandCru Selection		■	■	■	■	■	229
168 ↑ ↓		WSbli 5231	GrandCru Selection		■		■	■		229
	↔ 60 →	WSbli 5031	GrandCru Selection		■		■	■		196
		WPbli 5031	GrandCru Selection		■	■	■	■	■	196
		WSbl 5001	GrandCru		■		■		■	196
148 ↑ ↓		WPbl 5001	GrandCru		■	■	■		■	196
	↔ 60 →	WSbl 4601	GrandCru		■		■		■	166
128 ↑ ↓		WPbl 4601	GrandCru		■	■	■		■	166
	↔ 60 →	WSbl 4201	GrandCru		■		■		■	141
		WPbl 4201	GrandCru		■	■	■		■	141



Model / series		Energy rating	1 Zone	Glass Door	Humidity Control	Humidity Select	UV Protect	Cigar	✎*
Freestanding compact appliances									
61 ↑ ↓	↔ 43 →	WKes 653	GrandCru		■	■	■		12
		ZKes 453	Humidor		■		■	■	



Model / series		Energy rating	1 Zone	2 Zones	Glass Door	Humidity Select	UV Protect Plus	UV Protect	Soft System	Tip Open	✎*
Integrated wine tempering fridges											
EWTgb 3583	Vinidor			■	■	■		■	■	■	83
EWTgb 2383	Vinidor			■	■	■		■	■	■	51
EWTgb 1683	Vinidor			■	■	■		■	■	■	33



Integrated wine storage fridges											
45 ↑ 45 ↓	↔ 56-57 →	WKEgb 582	GrandCru		■		■	■		■	18
	↔ 56 →	WKEes 553	GrandCru		■		■	■			18



Under counter wine fridges											
UWgb 3632	Vinidor			■	■	■	■				32
UWgb 3631	Vinidor		■		■	■	■				44

Outstanding design. Award winning.

Our appliances have impressed the most prestigious design juries to win major awards such as the German Design Award, the iF Award and the Red Dot Award. The purist Liebherr look and impressive details create a stylish backdrop for your food.



XRfst 5295 ▲ Peak series



Contents

- 6

History
- 7

Quality
- 8

Sustainability
- 10

Use phase
- 12

Freshness technologies
- 14

Energy efficiency
- 16

Energy efficiency champions
- 17

10-year manufacturer's guarantee
- 18

Sustainable freezing
- 19

BluRox
- 20

XL fully integrated appliances for 194-cm recess
- 21

Veggie fridge
- 22

Convenience and flexibility
- 24

Water and ice
- 26

VarioTemp
- 27

Convenience and flexibility – freezing
- 28

AutoDoor
- 29

SmartDevice
- 30

Design
- 32

Fridge-freezers with French doors
- 34

Side-by-Side fridge-freezers with wine fridge
- 36

Fully integrated under counter appliances
- 38

Wine fridges
- 40

Wine tempering fridges
- 42

Wine storage fridges
- 44

Model overview:
- 45

Description of series
- 46


Freestanding appliances
- 55

Fully integrated appliances
- 61

Wine appliances
- 65

Accessories
- 66

Brief overview of features - refrigeration and freezing



The full range of Liebherr freestanding and fully integrated appliances can be found in a model overview from page 44 or on our website, including Liebherr specialist dealers, at: home.liebherr.com

Innovation comes in many forms.

Whatever space or requirements you have, a Liebherr is always the right choice. Whether you're looking for a chest freezer or a fridge, a huge Side-by-Side fridge-freezer, a freestanding or fully integrated appliance, or even a compact under counter appliance, you will always benefit from our innovation and attention to detail. Everything is designed to achieve our goal: long-lasting freshness for your food.

Fridges

Fridge-freezers

Side-by-Side combinations

French door

Freezers

Chest freezers

Freestanding and fully integrated under counter appliances

Wine appliances



FreshAir activated charcoal filter



FlexSystem



VarioSafe and bottle rack



Ice cube tray with lid



Bottle shelf



SmartDeviceBox

Accessories

Wine

- 1 Zone

With constant temperature throughout the interior, adjustable from +5 °C to +20 °C.
- 2 Zones

With two temperature zones, independently and precisely adjustable from +5 °C to +20 °C.
- 3 Zones

With three temperature zones, independently and precisely adjustable from +5 °C to +20 °C.
- Glass Door

The entire wine collection at a glance: behind tinted UV safety glass.
- Humidity Control

The humidity can be actively regulated in 5% increments between 50% and 80% RH**.
- Humidity Select

The humidity can be adjusted between two levels: Standard or High.
- UV Protect Plus

Triple protection: A tinted glass door with two layers of vacuum-deposited metal provides highly efficient protection from solar radiation.
- UV Protect

Double protection: A tinted glass door with one layer of vacuum-deposited metal provides efficient protection from solar radiation.
- Sommelier Board

For effective presentation and decanting: Wooden shelf with stainless steel bottle display, wooden box for decanting utensils and space for tempering wine glasses.

Special product groups

- Outdoor

This Liebherr is ideal for use outdoors thanks to its rust- and weatherproof materials, robust construction and high-quality components.
- Wine

Perfect conditions for fine wines with unique storage and tempering features.
- Cigar

Innovative features and perfect climate for fine cigars.

Freshness technologies

- Bio Fresh Professional

BioFresh Professional offers even more flexibility for your individual food-storage needs.
- Hydro Breeze

Cooling like a pro: Cold mist and a temperature in the safe of just over 0 °C ensure a longer shelf life and create a fabulous visual effect.
- Fish & Seafood

The Fish & Seafood Safe stores fish and seafood at the optimum temperature of -2 °C, just as professionally as your fishmonger.
- Bio Fresh

At a temperature just above 0 °C and an ideal humidity, fruits, vegetables, meat, fish, and dairy products stay fresh much longer than in a typical fridge compartment.
- Easy Fresh

The adjustable humidity prolongs the freshness of your fruits and vegetables.
- No Frost

Frost-free convenience.
- Smart Frost

Much less frequent defrosting.
- Stop Frost

Less frequent defrosting and easier opening of the chest lid thanks to no vacuum.
- Super Frost

SuperFrost increases the cooling power for a short time – this means the temperature remains constant when adding unfrozen food.
- Vario Temp Zone

Refrigeration or freezing? You can choose from: The VarioTempZone can be set to an accurate temperature of -18 °C to -10 °C and from -2 °C to 5 °C.

Convenience and flexibility

- Soft System

Very soft door closing, even when fully loaded, automatically below an opening angle of 30°.
- Easy Open

EasyOpen means the freezer door can be opened multiple times in succession, conveniently and easily.
- Frost Protect

A particular suitability to low-temperature environments allows the installation of freezers even in unheated rooms down to an ambient temperature of -15 °C.
- Auto Door

Unique worldwide: AutoDoor allows easy and convenient opening and closing of the door via voice command, knocking signal, and smartphone* – or simply by hand.
- Door Stop

Keep Liebherr fresh and odour-free. Door stays open when not in use. Save time, energy, and freshness.
- Telescopic Rails

Drawers on smooth telescopic rails for convenient opening and closing, and easy removal.
- Tip Open

The glass door opens by 7 cm when tapped for easy access and full opening.

Brief overview of features - refrigeration and freezing***

Water and ice

- Water & Ice Centre

The Water & Ice Centre provides sufficient cold water, ice cubes and crushed ice around the clock.
- Ice Maker

Automatic IceMaker for a plumbed-in connection.
- Easy Twist Ice

Conjure up ice cubes quickly: Fill the tank with water, let it freeze and then release the ready-made ice cubes with a twist (freestanding appliances).
- Ice Tower

Perfect for parties: automatic IceMaker and large pizza compartment on a convenient pull-out shelf.

Design

- LED

Low heat, energy-saving and maintenance-free for optimum illumination.

Connectivity

- Smart Device

The integrated SmartDeviceBox enables you to control the appliance and make use of additional services via computers and mobile devices.
- Smart Device ready

The SmartDeviceBox can be retro-fitted so that you can control the appliance and use additional services via computers and mobile devices. Available as an accessory.

Ultra-efficient models

- Ultra Efficient A -50%

This is even more economical* than appliances in the highest energy efficiency class A – Liebherr sets new standards.

* Compared to the threshold for maximum energy efficiency class A according to Directive (EU) 2029/2016 (as of December 2023).



What is different about our BluPerformance models? We have integrated all of the refrigeration technology in the appliance base. As a result, the appliances of the same size can hold a considerably greater volume. So you have noticeably more space for your food and drink. In addition, we were able to further improve energy efficiency thanks to improved ventilation and extraction in the base. And these appliances are now even quieter.



Accessories and Consumables
Find them online with your dream model at the Liebherr Domestic Appliances store home.liebherr.com or buy them from your Liebherr dealer.

* Can also be used via SmartDevice/Smart app. | **For temperatures in home environments. For very dry/cold environments such as cellars, we recommend using the specially made water tray from our range of accessories to support the system. | *** Many more differentiating features and detailed model descriptions can be found at home.liebherr.com