
L 507 E

Product information

LIEBHERR

Battery-electric wheel loader

Generation

8

Battery

32.2 / 64.4 kWh

Tipping load

3,750 kg



An high-energy concept for success



Tipping load, articulated
3,750 kg

Bucket capacity
0.9 m³

Operating weight
5,910 kg

Battery
32.2 / 64.4 kWh

Performance

- Dynamic and powerful performance due to innovative electric drive system
- Exceptional manoeuvrability and versatility thanks to the proven Stereo steering system
- The Stereo steering's combination of articulated steering and steered rear axle means a reduced articulation angle of only 30°
- A lower articulation angle results in maximum all-terrain stability
- High breakout forces in the lower lift arm range combined with strong holding forces in the upper lift arm range mean greater productivity in all applications
- Intelligent machine design makes it possible to transport heavy payloads with a low operating mass
- At a top speed of 30 km/h, the Speeder version increases the handling capacity of this wheel loader, especially over long distances

Economy

- Long battery runtimes of up to 8 hours (or optionally up to 16 hours) increases productivity in wheel loader operation
- Maximum efficiency due to energy recuperation
- No localised CO₂ emissions thanks to the battery-electric drive
- Excellent traction even on difficult terrain
- With the optional hydraulic quick coupler "Solidlink" with integrated, automatic hydraulic coupling system, changing the hydraulic attachments is done in just seconds, all right from the operator's cab – changeover is fully automatic, safe and without oil leakage
- Maximum efficiency thanks to optimum coordination between the electric motor and the other components

Maintainability

- The reduced maintenance requirements of electric machines results in maximum availability
- Effective and prompt support thanks to an expansive service network with qualified service specialists
- Spare parts service with round-the-clock delivery

Reliability

- Liebherr's decades of experience in the development, design and production of components makes these machines exceptionally durable
- Optimal coordination between individual components for significant robustness and reliability
- Liebherr's high quality standards mean dependability – even under the toughest operating conditions
- Demand-controlled cooling for improved cooling performance and reliable service
- With the clever positioning of the radiator package there is less contamination, so downtime is minimised

Comfort

- Thanks to very low noise emissions, the L 507 E is exceptionally well suited to noise-sensitive areas, providing the operator with a pleasant and peaceful work environment
- The modern ergonomic cab design allows the operator to remain better focussed, reducing fatigue
- Displays, control elements, and the operator's seat are perfectly harmonised forming a single ergonomic unit
- Numerous storage compartments and clever features provide plenty of space in the operator's cab and a comfortable interior
- With the Liebherr control lever, which moves along with the operator's seat, all working and driving functions can be controlled safely and precisely
- The optional Liebherr control lever with mini-joystick makes work more relaxed and efficient and provides proportional control of hydraulic attachments
- The high proportion of glass in the operator's cab provides excellent all-round visibility of working attachments and the operating area
- The engine bonnet was designed with optimised visibility in mind – this, together with the optional reversing camera, ensures an excellent overview
- Thanks to the side window that can open 180°, there is much better air circulation in the operator's cab and it is easier to communicate with those outside of the cab
- The damped articulated pendulum joint compensates for uneven ground and ensures excellent stability and maximum comfort

The L 507 E at a glance

Stereo steering

Balanced and one-of-a-kind – Liebherr's Stereo steering technology has been borne out by decades of excellence and is as unique as ever: It is a perfectly harmonised combination of articulated steering and rear axle steering. The Stereo concept combines the advantages of conventional articulated steering with the benefits of all-wheel steering. The result is a minimal turning circle which is particularly practical in cramped conditions. Even difficult steering manoeuvres are a breeze for the L 507 E.

Lift arms

Strong and robust – the powerful Z-bar kinematics have impressive hydraulic components, robust and durable lift arms and a strong steel construction. Safe lifting and loading without the need for manual readjustment and no loss of load, as well as quick and impressive positioning of loading material. The intelligent machine design of the L 507 E ensures risk-free transportation of loads even on rough terrain. The optional combination of electrohydraulics and angle sensors provides additional possibilities for machine coordination.



Stability and resistance to tipping over

Durable and manoeuvrable – the unique, articulated pendulum joint compensates for uneven ground and results in a comfortable and stable ride. With a tight turning radius and an articulation angle of only 30°, the one-of-a-kind Stereo steering provides additional stability and incredible manoeuvrability. The optimal ratio between operating mass and tipping load ensures maximum productivity.



Operator's cab

With excellent visibility and comfort, the ergonomically optimised cab design provides a pleasant and fatigue-free work environment. The spacious interior with an operator's seat, which can be adjusted in almost any way, offer the operator the highest level of comfort. Expansive windows and an engine bonnet designed for optimised visibility give the operator an unobstructed view in all directions. The optional, integrated reversing camera further increases visibility behind the machine. The electric-drive and the Stereoloader's simple handling, complete with steering wheel, make it easy to learn so that the operator can quickly get to grips with the machine. That saves time and increases versatility.

Battery-electric drive

Innovative and effective – the L 507 E's electric drive creates no local emissions and little noise, making this wheel loader ideal for use in urban areas as well as indoors. Through the use of energy recuperation, energy loss is kept to a minimum and efficiency is increased without compromising the power output. The full extent of the electric drive's power output is accessible at all times, ensuring that work is accomplished quickly. To guarantee operational safety, all maintenance points are easily and safely accessible from the ground.

The battery-electric wheel loader powered by innovation



Full loading power

The lithium-ion technology integrated into the L 507 E with its mean voltage of 322 V provides optimal performance. Depending on the on-board charger and power rating, the battery can be completely recharged in one and a half to three hours. The on-board charging system guarantees fast charging without additional external equipment, while making easy intermediate charging possible and increasing the machine's versatility. With just one flap to open in the cab access area of the wheel loader, the charging process is as simple as can be.



Individual power output thanks to the modular battery concept

Whether at 32.2 kWh or the optional 64.4 kWh, this battery-electric wheel loader from Liebherr is ready for any job. The modular battery concept makes it possible to individually adapt the machine's power.

Simply safe

Permanent, system-controlled monitoring of the high-voltage plug contacts and electric wiring means that circuitry is automatically switched off in the event of a defect. This mechanism significantly increases safety while the machine is in operation.






The quiet drive speaks for itself

The significantly reduced noise emissions of this battery-electric wheel loader by Liebherr provide huge advantages, especially in noise-sensitive areas like city centres. The fact that its drive is electric and emissions-free makes the L 507 E ideal for use in enclosed spaces such as recycling facility buildings.



Control units that are easy to use

The height adjustable touch function display allows work-related data to be collected quickly. Control elements that are easy and intuitive to use and an improved layout provide an ideal working environment inside the operator's cab. The progress of the charging process is shown as a percentage on the wheel loader's display along with a charge time prediction as well as multiple settings options. Using this data, there is nothing standing in the way of well-planned and efficient operation.



Intelligent energy recuperation

Regenerated energy – recuperated during braking or driving downhill – back to the battery increases its mileage. This process makes this battery-operated wheel loader from Liebherr particularly economical and resource-efficient. Lively handling and quick work sequences are easy to achieve with an electric drive that can provide full power output in a second.

Technical data

Battery

		L 507 E	
High-voltage system			
Battery type		Lithium ion	
Battery voltage	V	322	
Battery capacity	kWh	32.2	64.4*
Reference value for running time**	h	up to 8	up to 16
Emission stage		emission-free	
Charging infrastructure / charging times for internal charger, 10-90%			
Charging socket		Typ 2 / CCS2***	
230V / 12 A (3.5 kW)	h	7.1	14.2
400V / 16 A (11 kW)	h	2.1	4.2
400V / 32 A (22 kW)	h	1.1	2.1
DC rapid charging (up to 45 kW)***	h	-	1.1
Low-voltage system			
Operating voltage	V	12	
Capacity	Ah	100	

* optional, operating mass + 220 kg

** depending on use, machine configuration and ambient conditions

*** optional

Driveline

		L 507 E
Electric travel drive		
Design		Permanent magnet synchronous motor
Description of travel drive		Continuously variable electric direct drive with energy recuperation
Travel drive motor power output	kW	30
Control		By travel and inching pedal. The inching pedal makes it possible to control the tractive and thrust forces steplessly. The Liebherr control lever is used to control forward and reverse travel
Travel speed range		
Standard		Speed range: 0-20 km/h
Speeder		Speed range: 0-30 km/h* Speeds quoted apply with the tyres indicated as standard on loader model.

* Configuration, tyres and mounting tools can influence the maximum speed.

Brakes

		L 507 E
Wear-free service brake		Electric travel drive with regenerative brakes, wear-free, applied to all four wheels and additional dual-circuit brake system, drum brake and wet multi-disc brake located in the front axle
Parking brake		Negative brake system in the front axle acting on the wet multi-disc brakes

The braking system meets the requirements of the ISO 3450.

Axles

		L 507 E
Four-wheel drive		
Front axle		Fixed
Rear axle		Axle pivot steering, fixed
Height of obstacles which can be driven over	mm	370 with all four wheels remaining in contact with the ground
Differentials		
		Open differentials in both axles; 100% differential lock in front axle, manually engaged
Reduction gear		Planetary final drive in wheel hubs
Track width		1.510 mm with tyres indicated as standard

Steering

Design	Stereo steering system, hydraulic servo power steering. Central oscillating frame articulation with damper element in combination with rear-axle pivot steering	
Angle of articulation	30° to each side	
Angle of oscillation - centre-pivot steering	8° to each side	
Max. pressure	bar	180

Attachment hydraulics

Electric motor design	L 507 E	
Electric motor power output (max)	kW	30
Electric motor power output (continuous)	kW	15
Hydraulic system design	Load-sensing axial piston variable displacement pump with power regulator and flow regulator, pressure cut-off in control valve block	
Cooling	Hydraulic oil cooling using thermostatically controlled fan	
Filtration Control	Return flow in-line filter Single-lever control with electro-proportional pilot control, 1st and 2nd additional function with electro-proportional control optional	
Lifting function	Lifting, neutral, lowering Float position via latching Liebherr control lever, auto lifting and lowering via Liebherr control lever optional	
Tilt function	Tilt back, neutral, dump Automatic bucket return to dig for tipping on and off via Liebherr control lever optional	
Max. flow	l/min.	75
Max. pressure	bar	240
Hydraulic working motor power output	kW	15

Attachment

Geometry	L 507 E Powerful Z-bar linkage with tilt cylinder, hydraulic quick hitch as standard	
Bearings	Lathe-turned thick-walled bushings with lubricating grooves	
Cycle time at nominal load	ZK	
Lifting	s	4.9
Dumping	s	1.7
Lowering (empty)	s	3.5

Operator's cab

Design	Elastic mounted, noise-proof cab ROPS roll over protection per EN ISO 3471 / EN 474-1 FOPS falling objects protection per EN ISO 3449 / EN 474-1, Cat. II Operator's door with 180° opening angle with rigid window, fold-out window on right with 12° gap opener or 180° opening, single-pane safety glass ESG, heated rear window ESG, all windows are tinted. Continuously adjustable steering column optional	
Liebherr operator's seat	5 way adjustable, vibration-damped operator's seat "Standard" (mechanically sprung, adjustable to operator's weight), Liebherr control lever mounted into the operator's seat as standard	
Cab heating and ventilation	Fresh air mode, electrical heating, arrangement of the air nozzles ensures quick defrosting and defogging of the windows, electrically heated rear window	

Vibration emissions		
Vibrations in the hand/arm	m/s ²	≤ 2.5
Vibrations through the whole body	m/s ²	≤ 0.5

Sound level


Sound pressure level to ISO 6396	L 507 E	
L _{PA} (inside cab)	dB(A)	65
Sound power level to 2000/14/EC		
L _{WA} (surround noise)	dB(A)	91

Capacities

	L 507 E	
Transmission	l	2.1
HV component coolant	l	9.2
E-drive coolant	l	7.5
Front axle / differential	l	5.0
Rear axle / differential	l	4.4
Front axle / wheel hubs	l	1.6
Rear axle / wheel hubs	l	1.6
Hydraulic tank	l	51
Hydraulic system, total	l	70

Dimensions

Z-bar linkage



Excavation bucket

		L 507 E
		STD
		ZK-QH
Geometry		T
Cutting tools		T
Lift arm length	mm	2,150
Bucket capacity according to ISO 7546 **	m ³	0.9
Specific material density	t/m ³	1.8
Bucket width		2,050
A	Dumping height at max. lift height and 42° discharge	2,550
B	Dump-over height	2,870
C	Max. height of bucket bottom	3,015
D	Max. height of bucket pivot point	3,215
E	Max. operating height	4,040
F	Reach at max. lift height and 42° discharge	815
F max.	Max. reach at 42° discharge	1,500
G	Digging depth	80
H	Height above operator's cab	2,780
J	Ground clearance	285
K	Wheelbase	2,150
L	Overall length	5,495
Turning circle radius over tyres		3,520
Turning circle radius over outside bucket edge		3,885
Breakout force (SAE)		48
Tipping load, straight *		4,070
Tipping load, fully articulated *		3,750
Operating weight *		5,910
Tyre size		405/70R18

* The figures shown include the above tyres, all lubricants, batterie standard (32.2kWh), the ROPS/FOPS cab and the operator.

Different tyres and optional equipment will change the operating weight and tipping load. (Tipping load, fully articulated according to ISO 14397-1)

** Actual bucket capacity may be approx. 10% larger than the calculation according to ISO 7546 standard. The degree to which the bucket can be filled depends on the material – see page 22.


STD = Standard lift arm length

ZK-QH = Z-bar linkage incl. quick hitch

T = Welded-on tooth holder with add-on teeth

Attachment

Light material bucket



Heavy material density


		L 507 E	
		STD	STD
Geometry		ZK-QH	ZK-QH
Cutting tools		BOCE	BOCE
Bucket capacity	m ³	1.2	1.6
Specific material density	t/m ³	1.4	1.0
Bucket width	mm	2,330	2,400
A Dumping height at max. lift height	mm	2,510	2,420
E Max. operating height	mm	4,130	4,205
F Reach at maximum lift height	mm	840	870
L Overall length	mm	5,465	5,580
Tipping load, straight*	kg	3,920	3,825
Tipping load, fully articulated*	kg	3,575	3,490
Operating weight*	kg	6,035	6,090
Tyre size		405/70R18	

* The figures shown include the above tyres, all lubricants, batterie standard (32.2kWh), the ROPS/FOPS cab and the operator.
Different tyres and optional equipment will change the operating weight and tipping load. (Tipping load, fully articulated according to ISO 14397-1)

STD = Standard lift arm length
ZK-QH = Z-bar linkage incl. quick hitch
BOCE = Bolt-on cutting edge

Attachment

4 in 1 bucket



4 in 1 bucket


		L 507 E
		STD
		ZK-QH
Geometry		T
Cutting tools		0.8
Bucket capacity	m ³	1.8
Specific material density	t/m ³	2,100
Bucket width	mm	2,545
A Dumping height at max. lift height and 42° discharge	mm	3,230
A1 Max. dumping height with opened bucket	mm	2,950
C Max. height of bucket bottom	mm	4,720
E Max. operating height	mm	880
F Reach at max. lift height and 42° discharge	mm	5,585
L Overall length	mm	960
W Max. bucket opening	mm	3,975
Turning circle radius over outside bucket edge	mm	3,550
Tipping load, straight*	kg	3,240
Tipping load, fully articulated*	kg	6,195
Operating weight*	kg	405/70R18
Tyre size		

* The figures shown include the above tyres, all lubricants, batterie standard (32.2 kWh), the ROPS/FOPS cab and the operator.
Different tyres and optional equipment will change the operating weight and tipping load. (Tipping load, fully articulated according to ISO 14397-1)

STD = Standard lift arm length
ZK-QH = Z-bar linkage incl. quick hitch
T = Welded-on tooth holder with add-on teeth

Attachment

Fork carrier and fork



FEM II fork carrier and fork

		L 507 E
Geometry		STD
		ZK-QH
A	Lifting height at max. reach	mm
C	Max. lifting height	mm
E	Max. operating height	mm
F	Reach at loading position	mm
F max.	Max. reach	mm
F min.	Reach at max. lifting height	mm
G	Fork length	mm
L	Length - basic machine	mm
Tipping load, straight *		kg
Tipping load, fully articulated *		kg
Recommended payload for uneven ground = 60% of tipping load, articulated ²⁾		kg
Recommended payload for smooth surfaces = 80% of tipping load, articulated ²⁾		kg
Operating weight *		kg
Tyre size		405/70R18

* The figures shown include the above tyres, all lubricants, batterie standard (32.2kWh), the ROPS / FOPS cab and the operator.

Different tyres and optional equipment will change the operating weight and tipping load. (Tipping load, fully articulated according to ISO 14397-1)

¹⁾ Payload is limited by tilt cylinder - max. load capacity for the fork carrier FEM II 2,500 kg


²⁾ According to EN 474-3

STD = Standard lift arm length


ZK-QH = Z-bar linkage incl. quick hitch

Bucket selection

L 507 E



Bucket filling factor



Lift arm

ZK-QH	Z-bar linkage with quick hitch, standard lift arm length
-------	--

Bucket

GPB	General purpose bucket (Excavation bucket)
LMB	Light material bucket
4in1	4 in 1 bucket

Bulk material densities and bucket filling factors

		t/m ³	%			t/m ³	%			t/m ³	%
Gravel	moist	1.9	105	Earth	dry	1.3	115	Glass waste	broken	1.4	100
	dry	1.6	105		wet excavated	1.6	110		solid	1.0	100
	crushed stone	1.5	100	Topsoil		1.1	110	Compost	dry	0.8	105
Sand	dry	1.5	105	Basalt		1.95	100	wet	1.0	110	
	wet	1.9	110	Granite		1.8	95	Wood chips / Saw dust		0.5	110
Gravel and Sand	dry	1.7	105	Sandstone		1.6	100	Paper	shredded / loose	0.6	110
	wet	2.0	100	Slate		1.75	100	recovered paper / cardboard	1.0	110	
Sand / Clay		1.6	110	Bauxite		1.4	100	Coal	heavy material density	1.2	110
Clay	natural	1.6	110	Limestone		1.6	100	light material density	0.9	110	
	dry	1.4	110	Gypsum	broken	1.8	100	Waste	domestic waste	0.5	100
Clay / Gravel	dry	1.4	110	Coke		0.5	110	bulky waste	1.0	100	
	wet	1.6	100	Slag	broken	1.8	100				

Tyres



Tyre types

	Size and tread code		Change of operating weight kg	Width over tyres mm	Change in vertical dimensions* mm	Use
L 507 E						
Goodyear	405/70R20 Powerload	L2	55	1,960	22	Sand, Gravel, Asphalt (all ground conditions)
Firestone	400/70R20 Duraforce UT	L3	66	1,950	18	Gravel, Asphalt, Industry (all ground conditions)
Firestone	400/70R20 R8000 UT	L2	43	1,950	18	Earthworks, Green area (all ground conditions)
Michelin	400/70R20 BIBLOAD	L3	40	1,950	13	Gravel, Asphalt, Industry (firm ground conditions)
Michelin	400/70R20 XMCL	L2	56	1,960	19	Earthworks, Green area (all ground conditions)
Mitas	405/70R18 EM-01	L2	0	1,960	0	Gravel, Asphalt (all ground conditions)
Mitas	405/70R20 EM-01	L2	36	1,960	25	Gravel, Asphalt (all ground conditions)
Nokian	400/70R20 Hakkapeliitta TRI	L2	56	1,950	23	Winter tyres, Gravel, Asphalt (all ground conditions)
Trelleborg	400/70R20 TH400	L2	50	1,950	13	Earthworks, Green area (all ground conditions)

* The stated values are theoretical and may deviate in practice.

Before operating the vehicle with tyre foam filling or tyre protection chains, please discuss this with the Liebherr-Werk Bischofshofen GmbH.

Tipping load



What is tipping load?

Load at centre of gravity of working equipment, so that the wheel loader just begins to tip over the front axle. This is the most unfavourable static-load position for the wheel loader. Lifting arms horizontal, wheel loader fully articulated at centre pivot.

Pay load.

The pay load must not exceed 50% of the tipping load when articulated. This is equivalent to a static stability-margin factor of 2.0.

Bucket capacity.

The bucket volume is determined from the pay load.

$$\text{Pay load} = \frac{\text{Tipping load, articulated}}{2}$$

$$\text{Bucket capacity} = \frac{\text{Pay load (t)}}{\text{Specific bulk weight of material (t/m}^3\text{)}}$$

The Liebherr wheel loader

Wheel loader



		L 507 E
Tipping load	kg	3,750
Bucket capacity	m ³	0.9
Operating weight	kg	5,910
Battery	kWh	32.2 / 64.4

11.23

Equipment

Basic wheel loader

32.2 kWh lithium-ion battery	●
64.4 kWh lithium-ion battery	+
Automatic central lubrication system	+
Combined inching-braking system	●
Connection for electrical equipment 7-pole	+
Guard for headlights	+
Liebherr biodegradable hydraulic oil	+
Load lashing lugs	●
Lockable doors and engine hood	●
On-board AC charging technology up to 400V / 32A	●
On-board AC charging technology up to 400V / 32A and DC charging technology up to 65 KW	+
on-board tool kit	●
Parking brake	●
Power socket rear (13-pole, 12V)	+
Rear license panel light	+
Ride control	+
Special paint	+
Speeder version	+
Towing hitch	+
Tractive force adjustment	+
Travel light on front section LED	●
Type 2 IP67 charging cable, CEE plug, adjustable charging power 3.5 - 22 kW	+
Variable speed limit and fixed speed	+

Equipment

1st and 2nd electro-hydraulic, proportional additional function	+
1st electro-hydraulic, proportional additional function	+
Continuous mode, additional function	+
Float position	●
Fork carrier and pallet forks	●
High-dump bucket	+
Hydraulic quick hitch	●
Hydraulic quick hitch Solidlink	+
Leak oil line	+
Lift arm Z-bar linkage	●
Light material bucket	+
Loading buckets incl. a range of cutting tools	+
Pipe break protection	+
Preparation for hydraulic quick hitch Solidlink (quick hitch without Solidlink block)	+
Programmable automatic lifting and lowering	+
Tilt cylinder protection	+
Unpressurised return flow	+
Working hydraulics lockout	●

- = Standard
- + = Option
- = not available
- * = activation required free of charge

Here you can download our wheel loader brochures:



Operator's cab

3 way continuously adjustable steering column (height-adjustable, tilting, folding)	+
Air conditioning system	+
Amber beacon LED	+
Clothes hook	●
Electronical theft protection with code	+
Emergency exit	●
Exterior mirror, tiltable	●
Exterior mirror, tiltable and heatable	+
Fire extinguisher in cab 2 kg	+
First aid kit	+
Floor mat	●
Fold-out window right 180°	●
Headlights front, double design, LED	+
Headlights front, single design, LED	●
Headlights rear, double design, LED	+
Headlights rear, single design, halogen / LED	+
Hot-water heater with defroster and recirculated air mode	●
Interior rear-view mirror	●
Liebherr Connect	
MyLiebherr Maintenance	+
MyLiebherr Performance	+
MyLiebherr Portal*	●
Liebherr control lever with mini-joystick for 1st and 2nd hydraulic, proportional additional function moving with operator's seat (incl. travel direction)	●
Operating hour meter (integrated in display unit)	●
Operator seat "Comfort" – air sprung with seat heating	+
Operator seat "Standard" – mechanically sprung	●
Particle filter F5	●
Power socket 12V	●
Premium display (Touchscreen), with height adjustment and tilting function	●
Preparation for radio installation	+
Radio Liebherr "Comfort" (DAB+ / USB / AUX / BLUETOOTH / handsfree set)	+
Radio Liebherr "Standard" (USB / AUX)	+
Rear window heated electrically	●
Sliding window left	+
Soundproof ROPS / FOPS cab	●
Steering column fixed	●
Steering column folding	+
Storage box	●
Storage compartment	●
Sunblind front	●
Sunblind front / rear	+
Wide angle mirror	+
Windscreen guard	+
Wipe system front / rear	●

Safety

Back-up alarm acoustical / visual	+
Country-specific versions	+
Rear space monitoring with camera (integrated in display unit)	+

The Liebherr Group



Global and independent: more than 70 years of success

Liebherr was founded in 1949 when, with the development of the world's first mobile tower crane, Hans Liebherr laid the foundations for a family-run company which now has more than 50,000 employees and comprises over 150 companies across every continent. The holding company of the Group is Liebherr-International AG in Bulle, Switzerland, whose shareholders are exclusively members of the Liebherr family.

Technology leadership and pioneering spirit

Liebherr is a pioneer and its forward-looking approach has seen it make important contributions to technology history over a wide variety of industries. Employees throughout the world continue to share the courage of the company founder, sharing a passion to produce innovative products and a determination to provide world-leading equipment and machinery.

Diversified product programme

Liebherr is one of the world's biggest construction machine manufacturers and provides high-quality, user-oriented products and services. Its product programme includes earthmoving machinery, material handling technology, deep foundation machines, mining, mobile and crawler cranes, tower cranes, concrete technology, maritime cranes, aerospace and transportation systems, gear technology and automation systems, refrigerators and freezers, components and hotels.

Customised solutions and maximum customer value

Liebherr solutions are characterised by precision, implementation and longevity. The company is committed to technological excellence and to providing customers with solutions that match their needs exactly. For Liebherr, customer focus does not end with delivery of a product but continues through a comprehensive range of back-up and support services.

www.liebherr.com

Liebherr-Werk Bischofshofen GmbH

Postfach 49 · 5500 Bischofshofen, Austria · Phone +43 50809-10
info.lbh@liebherr.com · www.liebherr.com · www.facebook.com/LiebherrConstruction