



# Decide for yourself. Or choose them all.

With us, you only have to give up one thing: compromises. We aim to offer appliances that impress not only with their top-of-the-range, innovative freshness technologies but also their sustainable product lifecycle and "Made in Germany" quality. Year after year. Day after day.

We have continued to grow into 2025, literally as well as figuratively – with extra-high fully integrated appliances and more space for your food. We're also offering even greater flexibility than ever before, thanks to new under counter appliances available in two different height variants. Plus, a highlight for design enthusiasts: Our brand-new free standing fridge-freezers with French doors now include MoodLight plus a convenient Water & Ice centre directly on the outside of the appliance.

This is on top of the many invisible innovations that make our fridges and freezers the most energy-efficient and quietest appliances on the market.

You see: We have done everything we can to make your decision to opt for a Liebherr appliance as easy as possible. You will find a few more of these reasons on the following pages. Enjoy discovering more.

## **Contents**

- 6 History
- 7 Quality
- 8 Sustainability
- 10 Use phase
- 12 Freshness technologies
- 16 Energy efficiency
- 18 Energy efficiency champions
- 19 10-year manufacturer's guarantee
- 20 75-cm-wide fridge-freezers
- 21 XL fully integrated appliances for 194-cm recess
- 22 French door and LargeDoor
- 23 Design Awards
- 24 Sustainable freezing
- 25 BluRoX
- 26 OpenStage
- 27 Comfort and ergonomics refrigeration
- 28 Water and ice
- 30 VarioTemp
- 31 Convenience and flexibility freezing

- lity 34 Design
  - 36 Fridge-freezers with French doors

32 AutoDoor

33 SmartDevice

- 38 French-door features
- 40 Side-by-Side fridge-freezers with wine fridge
- 42 Fully integrated under counter appliances
- 44 Wine fridges
- 46 Wine tempering fridges
- 48 Wine storage fridges
- 50 Brief overview:
  Freestanding appliances
  Fully integrated appliances
  Wine appliances
- 67 Outdoor Cooler
- 68 Description of series
- 70 Accessories
- 71 Description of equipment

# The property of the property o

The full range of Liebherr freestanding and fully integrated appliances can be found in a brief overview from page 50 or on our website, including Liebherr specialist dealers, at: home.liebherr.com

## Innovation comes in many forms.

Whatever space or requirements you have, a Liebherr is always the right choice. Whether you're looking for a chest freezer or a fridge, a huge Side-by-Side fridge-freezer, a freestanding or fully integrated appliance, or even a compact under counter appliance, you will always benefit from our innovation and attention to detail. Everything is designed to achieve our goal: long-lasting freshness for your food.







Fridge-freezers



Side-by-Side combinations



French door



Freezers



Chest freezers



Under counter appliances




Wine appliances

# German engineering – then as now.

We have been manufacturing refrigerators and freezers of the highest quality and selling them worldwide since 1954. However, at heart, we are still a family business with our roots firmly established in Germany. This is where we continue to develop our long-lasting products.

German engineering – from an enduring connection with our founder and in the knowledge that engineering expertise has been pooled here for generations.



"My life has strengthened my belief that with a firm intention to do a good job and fulfil the customers' various wishes to the best of your ability, it is possible to achieve goals that at first seem almost unattainable. Don't be discouraged by setbacks, and belief in yourself can move mountains."

Dr.-Ing. e.h. Hans Liebherr (1915-1993)





The L 319 was Liebherr's "mobile showcase" in the 1960s.
Until 1968, the specially converted bus travelled around West
Germany promoting the latest refrigerators and freezers from
Upper Swabia.



Our first appliances came off the production line in Ochsenhausen back in 1954. And this is exactly where our main factory is still located today.





### Quality that will remain quality in 15 years.

MBsddi 9558 O Prime-Serie

Quality

Our aspiration to deliver quality is reflected even in the smallest details. Before we approve a door hinge, for example, it must undergo at least 100,000 opening cycles. And just like the door hinge, we test every other functional part extensively and intensively. All with one purpose in mind: ensuring that our appliances have a useful life of at least 15 years.



State-of-the-art laser technology is used to check the entire door surface as well as the precision of the Liebherr font – for quality down to the finest detail.



#### People and sustainable business

Respect for human rights is of the utmost importance to us. We place great value on treating everyone equally and ensuring the health, safety and personal development of our employees. We also want to make a positive contribution to our communities.

What is more, we emphasise responsible and economical practices, including long-term financial planning and self-financing. Fairness toward other market participants, compliance with laws and internal standards and codes of conduct are an integral part of our approach.

#### Recycling

We are aiming for a sustainable circular economy in the long term and actively design our products to maximise the reuse of the materials within them by making them easy to separate.

#### Materials

We want to reduce the environmental impact of our business activities by preparing recyclable products, increasing the use of renewable and recycled materials in our appliances, and reducing the variety of materials we use. In doing so, we consider the entire product.



#### lise

We reduce our environmental impact by continuing to offer first-class, energy-efficient products that are extremely long-lasting and easy to repair – supported by forward-thinking oustomer service. We also offer products and solutions that help to reduce food waste. More on this on the following pages.

#### Production

We want to produce in an environmentally conscious manner by reducing the energy requirements of our plants and increasingly utilising renewable energy sources. By using water responsibly, minimising waste and avoiding pollution, we reduce our environmental impact above and beyond CO<sub>2</sub> emissions.\*

Sustainability

Our path to the future

One thing unites all our product innovations: They all present a path toward greater sustainability. Taking responsibility is one of our


core values. That's why we have a decades-long tradition of research

and development into eco-friendly products, with the entire product

lifecycle in mind.



Around the world, every year around 1,052 million tonnes of food are thrown away. For an average household, this works out at around 113 kg annually.



# L L S Kilograms

The amount of food waste can be roughly broken down into the following groups:<sup>2</sup>



50% fresh fruit and vegetables



4% dairy products



5% meat and fish



cooked and ready-made food

Food has not only emotional and financial value, but also environmental value.

Food production is responsible for <sup>3</sup>

25%

of all global greenhouse emissions and


70%

of freshwater consumption.



With our carefully considered freshness technologies and digital solutions, we help you to reduce food waste in very simple ways.

For perfect food storage, alongside the ideal temperature, optimal humidity is a decisive factor. At Liebherr, we have developed innovative freshness technologies and continue to improve them year after year. This way, food tastes genuinely fresh even after several days and retains all of its vitamins and nutrients. For each type of fresh food, we have just the right freshness technology:







DuoCooling

 ${\bf 11}$ 



#### Freshness technologies



EasyFresh - ideal for fruit and vegetables

Unpackaged fruit and vegetables feel right at home here. When stored at the same temperature as the fridge compartment and sealed airtight in the safe, lettuce, for example, remains crisp and fresh even after seven days.



BioFresh Professional with HydroBreeze – refrigerate like a pro

A cold mist covers fruit and vegetables like a protective balm, ensuring crisp freshness and improving structure – the special wow effect for fruit and vegetables in the BioFresh Professional Safe.



#### DuoCooling - no drying out

Our basic technology in our fridge-freezers. The two completely separate cooling circuits ensure that there is no exchange of air between the fridge and freezer compartments. The food neither dries out nor spreads odour.



#### BioFresh - our all-rounder

The reliable BioFresh technology stores groceries at a temperature of just above 0 °C, much cooler than the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable safe. Meat, fish and dairy products benefit from ideal conditions in the Meat & Dairy safe.



## BioFresh Professional with Fish & Seafood safe – like freshly caught fish from the market.

Particularly delicate foods like fish and seafood are best stored in icy temperatures and at low humidity. The constant temperature of -2 °C in the Fish & Seafood safe is therefore ideal to keep items tasting fresh for longer.



#### NoFrost - No more defrosting

The automatic defrosting function guarantees that frozen food remains fresh. There is no longer a need to store frozen food temporarily during a manual defrost. The constant optimal freezing remains the same without any interruptions.





Because they run 24 hours a day, the biggest environmental impact of fridges and freezers is the energy they consume while in use. They account for about a fifth of the electricity used by an average household.1

Fridges and Total electricity freezers consumption

Our fridges are real all-rounders: In addition to the low power consumption across our entire product range, they also impress with a low noise level, plenty of space for food and intelligent sensor technology for optimum cooling power.



#### **Energy consumption**

Our appliances take top spots in the efficiency rankings or even outperform the highest efficiency class. This means they protect our precious environmental resources, as well as your wallet.



#### Cooling volume

From extra-large drawers down to the tiniest details, we ensure that not a litre of cooling volume is wasted, all while maintaining maximum energy efficiency.



16

#### Noise level

Kitchens are increasingly becoming part of our living areas. That's why we focus not only on maximum energy efficiency but also on 'audibly' quieter appliances.




#### **Cooling power**

Our appliances' intelligent sensor systems constantly adapt the cooling power to the current use - making them efficient and economical day to day, but fully up to the job when the weekly shopping arrives.



<sup>&</sup>lt;sup>1</sup> German Federal Environmental Agency (2021). For an average household in Germany.



#### ♦ Plus series

178

#### ICBa 5123 World first:

The first fully integrated fridge-freezer in energy efficiency class A.

#### ICNb 5123

The first Liebherr fully integrated fridge-freezer with NoFrost in energy efficiency class B.

#### Prime series



#### IRBbi 5150

The first fully integrated fridge for a 178-cm recess with BioFresh in energy efficiency class B.



#### ICBNbi 5153

The first fully integrated fridge-freezer with 0 °C technology and NoFrost in energy efficiency class B.



# Freshness without compromise

Reliability and durability are not just buzzwords for us. Why? Because at Liebherr, every tiny detail must meet our demanding requirements. Every functional part is extensively and intensively tested. We don't stop until we are convinced that our fridges and freezers are of the highest quality.

Secure your

guarantee\*:

Buy your new Liebherr appliance\* from a Liebherr specialist dealer by 31/12/2025.



10-year manufacturer's

# Register

Register your appliance within 12 months using our web form or SmartDevice app.





Enjoy 10 years of Liebherr manufacturer's guarantee and long-lasting freshness.





\*This guarantee is granted free of charge for all freestanding fridge-freezers in energy efficiency class A. With our manufacturer's guarantee, you will not incur any costs for repair and service for 10 years.

For more information, registration and guarantee conditions, go to: home.liebherr.com/guarantee




To register and see the guarantee terms and conditions, go to www.liebherr.com/guarantee

For reasons of space, only the most important distinguishing features are mentioned. Detailed model descriptions and exact dimensions can be found at home.liebherr.com




# The highest level of energy efficiency.

The CBNsda 775i freestanding fridge-freezer combines the highest energy efficiency class A with a generous width of 75 cm. Numerous freshness technologies such as VarioTemp, NoFrost and the largest-ever BioFresh safe offer the best storage conditions with unrivalled low energy consumption. Ideal for environmentally-conscious families with a long shopping list.



## For the highest demands

We are expanding our range of fully integrated fridge-freezers. Or, should we say, we're raising it. Our 194-cm-high XL fully integrated fridge-freezers fit seamlessly into high-quality kitchen designs and impress in every way: two BioFresh safes, the highest energy efficiency in their class and a timeless, elegant design. Discover our new XL fully integrated appliances from the Pure, Plus and Prime series – perfect for everyone, even those with the most exacting demands.



For reasons of space, only the most important distinguishing features are mentioned. Detailed model descriptions and exact dimensions can be found at home.liebherr.com

# Freshness in French door and LargeDoor format

The extra-large fully integrated combinations boast a grey inner liner and an updated visual design. And in even class E, they're now much more energy efficient.



←91→

ECBNe 8871

ECBNe 8870

←91→





# Upgrade for the kitchen: freestanding French door

**ECBNe 8872** 

Brushed stainless steel elements on the door and trims, a grey inner liner and improved energy efficiency to class E make our freestanding French door even more attractive.



CBNste 8872





#### Inner liner and insulating foam

Both the inner liner and the insulating foam contain recycled materials, as well as materials from organic sources. These help reduce the environmental impact while maintaining the same excellent insulation performance.

#### **Product packaging**

24

The environmental footprint of the packaging has also been reduced without compromising safety during transport.



#### Side panels and door

The door and side panels are made from 100% recycled steel, the production of which generates 80% less CO2 emissions than the production of conventional steel.

The TPE used for the door seal combines optimum functionality, durability and good recyclability.

Our pioneering BluRoX technology features perlite, finely ground volcanic rock, in vacuum insulation. This enables unmatched energy efficiency, as well as a significant increase in the freezing volume with the same exterior dimensions. Unlike conventional insulation methods, the unique and patented BluRoX technology provides optimal thermal conductivity, which significantly reduces energy consumption and sets new standards in sustainable cooling.

> To learn more about this exciting technology and the many advantages of BluRoX, visit: home.liebherr.com/blurox





The first hybrid model with BluRox in the door as well as the first NoFrost freezer (165 cm) in energy efficiency class B.



FNb 505i ○ Prime series

**OpenStage** Comfort and ergonomics - refrigeration

## Freshness with zoom factor

Our ergonomic drawers are easy to use, meaning your groceries are particularly easy to reach for maximum clarity.



The SmartSteel interior – full-surface stainless steel application on the rear wall and inner door - as well as a fan with subtle ambient lighting, makes for a striking experience every time you open the door.



Inspired by display cabinets in fine delicatessens,







#### Transform your kitchen into a market stall.

the award-winning OpenStage drawers showcase all groceries at a glance. The entire contents of the fridge are presented with maximum clarity and are ergonomically ideal to reach. We are setting new standards in ease of use and design. In the lower area, three additional BioFresh safes offer you the perfect climate for storing fruit and vegetables as well as meat, fish and dairy products.









The practical pull-out shelf made of telescopic pull-outs in the IRDdi 5120 is equipped with two removable bottle baskets for easy transport. It can also be loaded with a whole crate of beverages to quench your thirst.



Look forward to opening your BioFresh safes. And this is not just because of the fresh food but also because opening is so easy, and closing is automatic and cushioned. The telescopic rails slide the safe gently towards you. And because these extend fully, you have the best overview of the contents.



The practical GlassLine pull-out shelves and the pull-out compartment with full extension allow food and bottels to be stored safely and with optimum access. Equipped with SoftTelescopic, the pull-out compartment has a convenient and safe self-retracting system and a gentle SoftSystem.



IRBPci 5170 △ Peak series

# Specially designed for cool drinks

With Liebherr, your guests will never go without a perfectly cooled drink. This is thanks to the integrated cold water source and a never-ending supply of ice. The easy way to have constant refreshment.





#### Direct access: the Water & Ice centre

In the door of our new fridge-freezers with French doors (see also pages (36 – 38), the Water & Ice centre provides plenty of cold water, ice cubes and crushed ice around the clock.



#### Enough ice for even the largest party: the IceTower

The IceTower in our freezers sets new standards by combining two large compartments – the automatic IceMaker for up to 8 kg of ice cubes, and another spacious compartment large enough to store a few family-sized pizzas upright, for example. And because that was not convenient enough for us, both compartments glide in and out on a pull-out shelf with telescopic rails. We have even thrown in an ice shovel, so your hands can stay warm while you handle so many chilled goods.



#### Ice-cold water on tap with no heavy lifting

With the InfinitySpring, we bring a crystal clear, cold water source right into the heart of your kitchen, so you can always stay hydrated. This makes lugging of heavy crates and water in plastic bottles a thing of the past, relieving the strain on your back and on our environment. Simple and sustainable.



#### It's raining ice cubes: the IceMaker

Each day, the IceMaker produces up to 130 ice cubes, which automatically drop into two drawers. When MaxIce is activated, it is even possible to speed up the production of ice cubes if more guests than expected arrive. The IceMaker is connected to the fresh water pipe. If no plumbed-in connection is available, a model with a water tank in the fridge compartment is also available.



#### Ice in an instant: EasyTwist-Ice

Quickly rustle up a supply of ice cubes – without a plumbed-in connection. Simply fill the tank with water, let it freeze and then release the ice cubes with a twist. EasyTwist-Ice is easy to clean and is installed in most of the freestanding appliances in our Pure series.



# No more defrosting thanks to NoFrost



# The NoFrost automatic defrosting function guarantees that frozen foods remain fresh.

There is no longer a need to store frozen food temporarily during a manual defrost, as the food is frozen with cooled recirculated air and the air humidity is also diverted. This keeps the freezer compartment ice-free at all times, and food is no longer covered in frost. The constant optimal freezing remains the same without any interruptions.



#### Open the door multiple times with ease: EasyOpen

Have you experienced this problem? Once you've put your shopping away in the freezer, you notice that you've left something on the side and you have to pull hard to open the door again. This does not happen with a Liebherr: EasyOpen means the door can be opened multiple times in succession, conveniently and easily.



Fridge compartment (-2 °C to +9 °C)



Cellar compartment (+14 °C)



Freezer compartment (-18 °C)

Vario Temp

# Versatile freshness with a freezer compartment that can also be a fridge.

With VarioTemp, you can set the temperature of the freezer compartment in your fridge-freezer from -2 °C to +14 °C. This allows you to use this space as an extra cooling zone at parties or as a 'cellar compartment'. Don't need the freezer compartment? Switch it off independently of the fridge compartment and save energy and money.



#### When below zero is a big plus

No room for a freezer in the kitchen or other heated areas in your home? We have some great news: with FrostProtect, all components are designed for temperatures as low as –15 °C, no matter what groceries you are storing. If the ambient temperature falls below 0 °C, our freezers continue working just as efficiently, saving just as much energy and keeping your frozen food just as well protected. This means that you can put them in unheated spaces like a garden shed or garage, giving you more room for more important things.













# One less task for you.

Our AutoDoor feature perfectly complements the handle-less kitchen, as the Liebherr appliances open automatically in response to a knock, via the SmartDevice app, or by voice command.

Plus, the door does more than just open automatically, it makes things easier for you in every way by adjusting the settings to suit your needs. The opening angle and how long the door stays open before it closes automatically can be individually selected. Anybody who still prefers to open and close our fully integrated appliances by hand is, of course, free to do so.








# Always well connected

Almost all Liebherr appliances are either factory-equipped with a network connection module or can be retrofitted with the SmartDeviceBox.


This way, you will benefit from the many possibilities offered by our SmartDevice app and from connecting your fridges, freezers or wine fridges to your existing smart home environment. Important status and alarm notifications are sent directly to your smartphone, such as notification of an open fridge door via door alarm. Our SmartDevice app offers much more than that: In addition to simple management and remote control of your appliances, the app also helps you with tips and tricks for your Liebherr appliance. The right accessories for each appliance, access to instruction manuals and much more can also be found here.













#### FlexDoorSystem

Quiet opening and closing: With the patented FlexDoorSystem, the French doors can be opened and closed one at a time. The doors open easily, close securely and the 100% tight closure helps save energy.




#### Water & Ice centre

The Water & Ice centre supplies cold water, ice cubes and crushed ice 24 hours a day. Practical: The water volume of the water dispenser can be set individually for each desired container.




#### VarioTempZone

Maximum flexibility: The VarioTempZone can be set to the exact degree from -18 to -10 °C and from -2 to +5 °C, turning it into an extra cooling zone, if required.







39

#### Surface options

No matter which material you choose, one thing is certain: your appliance will draw the eye.

For reasons of space, only the most important distinguishing features are mentioned. Detailed model descriptions and exact dimensions can be found at home.liebherr.com





Qualities that surpass even those of a wine cellar.

They not only match wine cellars in terms of the five essentials of perfect storage but surpass them, thanks to our engineering expertise. We take care of every detail.

Constant temperatures protect the character of the wine.



Temp Protect Plus

Liebherr wine fridges monitor the temperature twice over with TempProtect Plus.

The right humidity keeps corks supple to protect the wine.



Select

Humidity Control With HumiditySelect or HumidityControl, the humidity in Liebherr wine fridges can be individually adjusted.

Keeping out ultraviolet light protects against unwanted ageing processes in the wine.



UV Protect

UV Protect Plus Liebherr glass door models have unique double, or even triple, anti-ultraviolet glazing.

Keeping out foreign odours stops them from spoiling the taste of the wine.



Fresh Air The FreshAir activated charcoal filter in a Liebherr wine fridge neutralises foreign odours.

Preventing vibrations allows the wine to mature undisturbed.



Vibrate Safe Liebherr wine fridges have a fully vibration-insulated cooling system.

#### Wine tempering fridges



#### SommelierBoard

An absolute highlight in our Vinidor Selection Series. There's room to show off everything you need for decanting. The high-quality shelf made of natural beechwood comes with a stainless-steel bottle presenter, a wooden box for decanting utensils and a space for tempering wine glasses for that extra-special enjoyment.



#### LightTower

One of the most important design elements is lighting. In our Vinidor Selection models, the LightTower vertical lights on each side beautifully illuminate the wine collection. The lighting can be activated each time the door is opened, or remain on at all times when the dimmable presentation light is set.



#### Vertical recessed grip


All models in the Vinidor Selection series have a recessed vertical grip extending the entire length, allowing for ergonomic and comfortable opening from any position. Models with the optically discreet grip integrate harmoniously into handle-free kitchens and living-dining areas.



#### FlexFit wooden shelves

The removable slats of the FlexFit wooden shelves ensure they accommodate any bottle, even magnums. Plus, thanks to the individual placement of the slats in the frame, all bottles are stored safely.





More information on wine storage and our wine fridges, including detailed model descriptions, can be found in our special wine brochure available from a Liebherr specialist dealer or at: home.liebherr.com/wine





#### **Humidity regulation**

With HumiditySelect, the humidity of GrandCru models can be adjusted in two stages: dehumidify or humidify. GrandCru Selection models are equipped with HumidityControl, which allows the humidity to be set as required within the range of 50% to 80% RH\*. If the value falls below 50% RH, the appliance indicates this.



#### LightColumn, one-sided

For a perfect view of your wine: The LED LightColumn runs from the top to the bottom of your glass-door appliance. It evenly illuminates the interior of your GrandCru Selection wine storage fridge. A special highlight is the dimmable presentation light for attractively showing off your wine collection even when the door is closed.



#### Neck-to-neck storage for maximum bottle capacity


A Liebherr wine storage fridge also makes it easier to organise a growing wine collection. To take full advantage of its capacity, the interior has been designed so that your wine bottles can be stored neck-to-neck on the wooden shelves. This means there is plenty of room even for ever-increasing wine collections. So feel free to keep collecting.



#### FreshAir activated charcoal filter

To ensure that your wine can mature in optimum air quality, all Liebherr wine storage fridges have an activated charcoal filter that reliably protects wine from all odours. This means your wine will keep its pure bouquet. To make sure that it stays that way, your Liebherr reminds you every six months to change the filter, which you can easily do yourself.

<sup>\*</sup> For temperatures in the living environment. Such as very dry or cold cellars, we recommend supporting the system with the tailor-made water box from our range of accessories.



#### Model overview - freestanding appliances









MBbsdi 9556



lodel /	series	

Energy



















### French door fridge-freezers

	Federicans		3											
203	<b>←91</b> →	CBNste 8872*		E A		•		•					•	
181	<b>←91</b> →	MBsddi 9558**	Prime	D A G	-			•	•	•	•	•		
with 2	drawers	MBsddi 9556**	Prime	D A G	•			•		•	•		•	•
		MBbsdi 9556**	Prime	D A G	•			•		•	•		•	•
		MBsddi 9528**	Plus	D A G		•		•	•			•		
		MBbsdi 9528**	Plus	D A		•		•	•			•		
		MBtsdi 9528**	Plus	D A G		•		•	•			•		
		MBsddi 9524**	Plus	D A G		•		-	•				•	
with 4	doors	MBsddi 9028**	Plus	D A		•		•	•			•		
		MBbsdi 9028**	Plus	D A G		•		•	•			•		
		MBsddi 9024**	Plus	D A		•		•	•				•	
		MBbsdi 9024**	Plus	D A		-		-	•				•	
		Msdd 9012**	Pure	D A			•	•	•					

Key to appliance material:

- \_st SmartSteel \_sd SmartSteel door \_bs BlackSteel \_bd BlackSteel door \_ts TerraSteel \_sf SteelFinish \_ White

Key to handle solutions:

1 Handle with opening mechanism

Model/series



SFNsfd 5237 + SRsfd 5230 XRFsf 5230

SWNbsd 529i + SRBbsc 529i



SFNsfd 5227 + SRsfd 5220

S	Bio Fresh Professional	Hydro Breeze		No Frost		Infinity Spring	Smart Device	Smart Device ready	Wir

#### Fixed Side-by-Side sets: freezer + fridge

0 →	XRFsf 5230	Plus														
181	SFNsfd 5237	Plus	D A G						•						•	
	SRsfd 5230	Plus	D †					-							•	
	XRF 5230	Plus														
	SFNd 5237	Plus	D †						•						•	
	SRd 5230	Plus	D A					-							•	
	†	SFNsfd 5237  SRsfd 5230  XRF 5230  SFNd 5237	SFNsfd 5237 Plus  SRsfd 5230 Plus  XRF 5230 Plus  SFNd 5237 Plus	SRsfd 5237 Plus  SRsfd 5230 Plus  XRF 5230 Plus  SFNd 5237 Plus  D :  C	SFNsfd 5237 Plus  SRsfd 5230 Plus  XRF 5230 Plus  SFNd 5237 Plus  D 2 6  D 3 6	SFNsfd 5237 Plus  SRsfd 5230 Plus  XRF 5230 Plus  SFNd 5237 Plus  D 2  D 3	SFNsfd 5237 Plus  SRsfd 5230 Plus  XRF 5230 Plus  SFNd 5237 Plus  D 2 0 2 0 2 0 0 0 0 0 0 0 0 0 0 0 0 0 0	SFNsfd 5237 Plus  SRsfd 5230 Plus  XRF 5230 Plus  SFNd 5237 Plus  D 1	11 SFNsfd 5237 Plus  SRsfd 5230 Plus  XRF 5230 Plus  SFNd 5237 Plus  □ 1 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	11	11/2 SFNsfd 5237 Plus	SFNsfd 5237   Plus   D	11	11/2 SFNsfd 5237 Plus	11 SFNsfd 5237 Plus  SRsfd 5230 Plus   XRF 5230 Plus  SFNd 5237 Plus  □ 1 □ 1 □ 1 □ 1 □ 1 □ 1 □ 1 □ 1 □ 1 □	11

#### For Side-by-Side placement: wine/freezer combinations

←121→¹	SWNstd 529i <sup>1</sup>	Peak	D A		•	-		
←123→² ↑ 181	SWNbsd 529i <sup>1</sup>	Peak	D A G		-	•	•	•

#### For Side-by-Side placement: fridges

SRBstc 529i <sup>1</sup>	Peak	C A G	•				•		•	•		
SRBbsc 529i <sup>1</sup>	Peak	C A	-				-		-	-		
SRBsdd 526i <sup>1</sup>	Prime	D †	-	•			-			-		
SRsdc 525i <sup>1</sup>	Prime	C A				-	-			-		
SRBsfc 5220 <sup>2</sup>	Plus	C A			•						•	
SRbdd 5220 <sup>2</sup>	Plus	D A				-					•	
SRsfd 5220 <sup>2</sup>	Plus	D †				•					•	

#### For Side-by-Side placement: fridge-freezer

SCNsdc 525i <sup>1</sup> Pr	rime C f			•		•	
	ida nlaaamanti	_					

#### For Side-by-Side placement: freezers

SFNbsd 529i1	Peak	D f			•	•	•	•	•		
SFNstd 529i <sup>1</sup>	Peak	D A				-	-	•	-		
SFNsdd 526i1	Prime	D A			•	•	•	•	-		
SFNsfd 5247²	Plus	D A			•		•	•		•	
SFNsdd 5237 <sup>1</sup>	Plus	D A			•					-	
SFNbdd 5227 <sup>2</sup>	Plus	D A G			•					-	
SFNsfd 5227 <sup>2</sup>	Plus	D A			-					-	
SFNd 5227 <sup>2</sup>	Plus	D A									

Model overview - freestanding appliances Model overview - freestanding appliances



Model / series



CBNa 572i



CBNbsc 778i

Energy



























Fridge-freezers with EasyFresh

Model / series





Energy















#### Fridge-freezers with BioFresh Professional / BioFresh

202	<b>←75</b> →	CBNbsc 778i	Peak		C A		•		•		-	•						
		CBNsda 775i	Prime		A †	•				•	•	-				-		-
202	<b>←60</b> →	CBNstb 579i	Peak		B A f		•	•			•	•	•		•	•		-
		CBNbsa10 575i	Prime	A -10%	A A	•				•	•	•				•		-
		CBNbsa 575i	Prime		A A	•				•	•	•				•		
		CBNa 572i	Plus		A A	•				•	•			•		•		-
		CBNsfc 572i	Plus		C f					•	•			-		-		-
		CBNsfc 57vi	Plus		C A					•	•			•		•		
		CBNc 5723	Plus		C A					•	•			•			•	-
<b>1</b> 86	<b>-60</b> →	CBNsda 5223	Plus		A A	•				•	•			-			-	-
		CBNbda 5223	Plus		A A	•				•	•			•			•	
		CBNsfc 5223	Plus		C f					•	•			•			-	-
		CBNc 5223	Plus		C A A						•						•	SCAN



With our manufacturer's guarantee, you will not incur any costs for repair and service for 10 years. It is granted free of charge for all freestanding fridge-freezers in energy efficiency class A.

For more information, registration and guarantee conditions, go to: home.liebherr.com/guarantee

Key to appliance material:

\_st SmartSteel
\_sd SmartSteel door
\_bs BlackSteel
\_bd BlackSteel door
\_ts TerraSteel
\_sf SteelFinish
\_white

202	<b>←75</b> →	CNsfd 7723	Plus	D A G		•			•		-
		CNd 7723	Plus	D A		-			•		•
202	<b>←60</b> →	CNsfc 574i	Plus	C A		•		•		•	
		CNc 5724	Plus	C A		•			•		•
		CNsda 5723	Plus	A A	•	•			•		•
		CNbda 5723	Plus	A A	•	•					•
		CNsdb 5723	Plus	BA		•					•
		CNd 5704	Pure	D A		•					•
		CNd 5703	Pure	D A		•					•
		CNsfd 5703	Pure	D A		•					•
186	<b>←60</b> →	CNsfd 5204	Pure	D A f		•					•
		CNd 5204	Pure	D A		•					•
		CNsfd 5203	Pure	D A		•					•
		CNc 5203	Pure	C A		•					•
		CNd 5203	Pure	D A		•					•
166	<b>←60</b> →	CNc 5023	Plus	C A							•

#### Fridge-freezers

1 <b>8</b> 1	<b>←55</b> →	CUele 3331	E		•			
		CUe 3331	E A		•			
161 1	<b>←55</b> →	CUele 2831	EA		•			
		CUe 2831	E A		•			
1 <b>3</b> 7	<b>←55</b> →	CUele 2331	E		•			
		CUe 2331	E A		•			
1 <b>5</b> 7	<b>←55</b> →	CTele 2931	E		•			
		CTe 2931	E		•			
140	<b>←55</b> →	CTele 2531	E A		•			
		CTe 2531	E					
12 <b>4</b>	<b>←55</b> →	CTele 2131	EA		•			
		CTe 2131	EA		•			

For reasons of space, only the most important distinguishing features are mentioned. Detailed model descriptions and exact dimensions can be found at home.liebherr.com

You can find the full range of efficiency ratings on page 59. According to (EU) 2017/1369 6a.

Model overview - freestanding appliances Model overview - freestanding appliances







Model / series Energy rating















### Fridges with BioFresh Professional / BioFresh

<b>→</b>	RBbsc 528i	Peak	C f	•	•	•			•	•	
	RBsdc 525i	Prime	C A				•		•	-	
	RBbsb 525i	Prime	BA				-		-	-	
	RBsfc 5220	Plus	C A				•				•
	RBc 5220	Plus	C A				-				•
	RBsfd 5221	Plus	D A G				-	■.			•

\* with 4\* freezer compartment







Model / series Energy

rating







#### BIU Fridges with/without EasyFresh

	Fertemans	i iiagoo ii	1111/ 11111100	Lacyino	••	
1 <b>8</b> 6	<b>←60→</b>	RDsfd 5220	Plus	D A G		
		Rsfd 5220	Plus	D A G		
166	<b>←60</b> →	Rd 5000	Pure	D A G	•	•
146	<b>←60→</b>	Rsfd 4600	Pure	D A G	•	•
		Rd 4600	Pure	D A G	•	•
126	<b>←60</b> →	Rd 4200	Pure	D A G	•	•
140	<b>←55</b> →	Ke 2834*	Comfort	A A G		
114	<b>←55→</b>	Ke 2350	Comfort	EA		

For reasons of space, only the most important distinguishing features are mentioned. Detailed model descriptions and exact dimensions can be found at home.liebherr.com



#### Under counter refrigerators

8 <del>5</del>	<b>←60</b> →	Rsdci 1620	Plus	C A	-		-	-	
		Rci 1620	Plus	C A	•		•	•	
		Rsdci 1621	Plus	C A	•	■,		•	
		Rci 1621	Plus	C A	•	■,		•	
		Rdi 1620	Plus	D A	•		•	•	
		Rdi 1621	Plus	D A	•	■.		•	
8 <del>5</del> ↓	<b>←55</b> →	Rc 1400	Pure	C A			•		
		Rc 1401	Pure	C A		■.			
		Re 1400	Pure	E A			•		
		Re 1401	Pure	E A		■.			
8 <del>5</del> ↓	<b>←50</b> →	Re 1200	Pure	E			•		
		Re 1201	Pure	E A		■.			
68	<b>←55</b> →	Re 1000	Pure	E			-		
82 ↓	<b>←60</b> →	OKes 1750		B A					

\* with 4\* freezer compartment





FNdi 1624



Fe 1404

Model / series

Energy rating









#### **Under counter freezers**

8 <b>5</b>	<b>←60</b> →	FNsddi 1624	Plus	D A	•		•	•	•
		FNdi 1624	Plus	D A	•		•	•	
		Fci 1624	Plus	C A		•	•	•	•
		Fdi 1624	Plus	D A		•	•	•	•
85 ↓	<b>←55→</b>	FNe 1404	Pure	E A	•		•	•	
		Fc 1404	Pure	C A		•	•	•	
		Fe 1404	Pure	E A		•	•	•	
∱ 68	<b>←55</b> →	Fe 1003	Pure	E A		•		•	

#### Model overview - freestanding appliances







FNc 7227

FNh	505i	

Model / series



Energy













#### Freezers with NoFrost

<b>1</b> 86	<b>←70</b> →	FNc 727i	Peak	C A	-	-	•	•	•	•	-	
		FNc 7227	Plus	C A G	-			-				•
		FNd 7227	Plus	D A	-		•	•				•
1 <b>6</b> 6	<b>←70</b> →	FNc 7026	Plus	C A	-		-	-				-
1 <del>4</del> 6	<b>←70</b> →	FNa 6635	Plus 🚭	A A	•		•	•				•
		FNa 6625	Plus	A A G	-		•	•				•
		FNc 6625	Plus	C A G	-		•	-				•
<b>1</b> 86	<b>←60</b> →	FNc 527i	Peak	C A	-	•	•	•	-	•	-	
		FNd 525i	Prime	D A	-		•	•	-	•	-	
1 <b>6</b> 6	<b>←60</b> →	FNb 505i	Prime S BluRoX	BA	•		•	•	•	•	•	
		FNd 5026	Plus	D A G	-		•	•				•
		FNe 5006	Pure	E A G	-		•	•				•
1 <del>4</del> 6	<b>←60</b> →	FNd 4625	Plus	D A	-		•	•				•
		FNe 4605	Pure	E A	-		•	•				•
12 <b>6</b>	<b>←60</b> →	FNd 4224	Plus	D A G	-		•	•				•
		FNe 4204	Pure	E A	•		•	•				•





CFc 1875

CFe 2080

Energy rating







#### **Chest freezer**

Model / series

58

8 <sup>†</sup> 3	<b>←126</b> →	CFe 2080	Pure	E A	•	-		•	
8 <b>3</b> ↓	<b>←105</b> →	CFc 1875	Plus	C A	•	-	•	•	SCAN

Fully integrated appliances

#### Your individual freshness centre

Combine your Liebherr fully integrated appliance with complete flexibility to suit your freshness needs. Many models can

be vertically and / or horizontally combined to form an individual freshness centre, providing perfect solutions to all your storage needs.

Ask your Liebherr dealer or kitchen specialist about the Liebherr Side-by-Side concept.









ECBNe 8872

ECBNe 8870

ECBNe 7870

Model / series

Energy rating

#### Integrated fridge-freezers French door / LargeDoor with BioFresh

203	<b>←91,5</b> →	ECBNe 8872	A † G	•		•	-
		ECBNe 8870	EA	•	•	•	•
		ECBNe 8871	EA	•	•	•	•
203	<b>←76,2→</b>	ECBNe 7870	EA	•	•	•	•
		ECBNe 7871	EA	•	•	•	•

For reasons of space, only the most important distinguishing features are mentioned. Detailed model descriptions and exact dimensions can be found at home.liebherr.com You can find the full range of efficiency ratings on page 59. According to (EU) 2017/1369 6a.

Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.

Model overview - fully integrated appliances Model overview - fully integrated appliances



Model / series





ICNb 5123























#### Integrated fridge-freezers with BioFresh Professional / BioFresh

<b>194</b> ↓	<b>←56-57</b> →	ICBNci 5663	Prime	C A			-	•		•	•		•	
		ICBNc 5623	Plus	C A			-	•		•				•
1 <b>7</b> 8	<b>← 56-57</b> →	ICBNci 5183	Peak	C A	•	•		•		•	•	•	•	
		ICBNbsci 5173	Peak	C A	•	•		-		•	•		•	
		ICBNdi 5163	Prime	D A C			-	•		•	•		•	
		ICBNbi 5153	Prime	B A			-	-		•			•	
		ICBNdi 5123	Plus	D A C			•	•		•			•	
		ICBNSd 5123**	Plus	D A A			-	•						•
		ICBbi 5152	Prime	B A			-		•	•			•	
		ICBa 5123	Plus	A A			-		•	•				•

#### Integrated fridge-freezers with EasyFresh

1 <b>94</b>	<b>←56-57</b> →	ICNd 5603	Pure	D	A ↑ G		•	•						•
1 <b>7</b> 8	<b>←56-57</b> →	ICNbsci 5173	Peak	C	A † G		-	-		•	•		-	
		ICNd 5133	Plus	D	A † G		•	-		•		•		•
		ICNb 5123	Plus	В	A † G		-	-		•				•
		ICNSd 5103**	Pure	D	A † G		•	-						•
		ICNc 5103	Pure	C	A ↑ G		•	-						•
		ICNe 5103	Pure	E	A † G		•	-						
		ICNSe 5103**	Pure	E	A † G		•	-						•
		ICd 5103	Pure	D	A † G		-		-					
		ICe 5103	Pure	E	A † G		-		-					•
		ICSe 5103**	Pure	E	A † G		-		-					•







IRBPci 5170

IRBc 4520

Model / series	En
	ra

IRBAc 5190


















ntegrated	fridges with	. BioFresh	Professional,	/ BioFresh
nicegrateu	IIIuges with	1 DIOI 1 COII	i i di Cooldiiat /	DIOLICOL

178	<b>←56-57</b> →	IRBAc 5190-001	Peak	I	C A	•	-				•	-	•	•	
		IRBAc 5190-617	Peak	I	C A	•	•				•	•	•	•	
		IRBci 5180	Peak		C A	•	•				-		•	•	
		IRBPci 5170	Peak		C A				•		•			•	
		IRBbsci 5170	Peak		C A	•	•				•			•	
		IRBci 5170	Peak		C A	•	-				•			•	
		IRBdi 5170	Peak		D A	-	•	•			•			•	
		IRBbi 5150	Prime		BAG				•		•			•	
		IRBci 5150	Prime		C A				•		•			•	
		IRBd 5120	Plus		D A				•		•				•
		IRBSd 5120**	Plus		D A G				•						•
		IRBd 5121	Plus		D A G				•	■.	•				•
140	<b>←56-57</b> →	IRBc 4520	Plus		C A				•		•				•
122 1	<b>←56-57</b> →	IRBc 4120	Plus		C A				•		•				•

\*with 4\* freezer compartment

#### The current EU energy label for electrical appliances



- 1. The QR code to identify the product in the EU database EPREL (European Product Registry for Energy Labelling).
- 2. The model identifier for manual identification of the product in the EU database EPREL, using the article number for example.
- 3. The new efficiency scale from A to G. However, "G" is only intended for wine fridges.
- 4. The total volume\* of all freezer compartments.
- 5. The total volume\* of all cold storage and refrigerator compartments.
- 6. The noise level is now classified into classes "A" to "D".
- \* The term "volume" is defined in the current Regulation (EU) 2019/2016.

Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.

Model overview – fully integrated appliances

Model overview – fully integrated appliances



#### Integrated fridges with EasyFresh

<b>1</b> 78	<b>← 56-57</b> →	IRDdi 5120	Plus	D A t	•		•	•	
		IRd 5100	Pure	D A G	•				•
		IRd 5101	Pure	D A f	•	■.			•
		IRe 5100	Pure	E A	•				•
		IRe 5101	Pure	EA	•	■.			•
140	<b>←56-57</b> →	IRd 4520	Plus	D A	•				•
122 ↓	<b>← 56-57</b> →	IRd 4120	Plus	D A	•		•		•
		IRd 4121	Plus	D A	•	■.	•		•
		IRd 4100	Pure	D A	•				
		IRe 4100	Pure	E A	•				•
		IRd 4101	Pure	D A		■.			


\* with 4\* freezer compartment



#### Under-worktop fridges

		Olluel-wi	Jiktop illuge	55					
86 <del>-</del> 92	<b>←60</b> →	URPc 375i	Prime	C A				•	
		URc 375i	Prime	C A G	•		•	•	
		URc 3700	Pure	C A f					_
		URc 3701	Pure	C A G		a.			
82 <sup>†</sup> -88	<b>←60</b> →	URPd 365i	Prime	D A G			•	•	
		URd 365i	Prime	D A G	•		•	•	
		URd 3600	Pure	D A G					
		URd 3601	Pure	D A G		<b>a</b> ·			SCAN

\* with 4\* freezer compartment



Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

Prime

Prime

Prime

D A

140 ←56-57→ SIFNdi 4556

-56-57→ IFNci 3954

←**56-57**→ IFNbi 3553

IFNd 3503

For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.



#### Under-worktop freezers

86 <del>-</del> 92	<b>←60</b> →	SUFNc 375i	Prime	C A	•			•	
		SUFc 3703	Pure	C A G		-			
82- 1 88	<b>←60</b> →	SUFNd 365i	Prime	D A G	•		-	•	_
		SUFd 3603	Pure	D A G		•			SCAN











Model	/ carias
moael/	series

















	BLU	Freestan	ding wine ter	npering	fridges	;									
<b>2</b> 01 ↓	<b>←70</b> →	WPgbi 7483	Vinidor Selection	F		•	•	•	•	•	•	•		149	
		WPgbi 7473	Vinidor Selection	F		-	-	•	•		•	-		182	-
		WPgbi 7472	Vinidor Selection	F	•		-	•	•		•	•		204	-
<b>1</b> 85	<b>←60</b> →	WPgbi 5283	Vinidor Selection	FA		•	-	•	•	•	•	•		85	
		WPgbi 5273	Vinidor Selection	FA		•	-	-	•		•	•		104	_
		WPgbi 5272	Vinidor Selection	FA	•		-	•	•		•	•		106	
		WPbsi 5252	Vinidor	FG	•		-	•	•		•	-		155	
		WSbsi 5252	Vinidor	E A	•			•			•	•		155	-
		WPsd 5252	Vinidor	FAG	•		-	•	•				•	155	-
<b>1</b> 45	<b>←60</b> →	WPsd 4652	Vinidor	FA	•		•	•	•				•	107	SCAN



Energy





odel/series	
-------------	--

1 Zone	











#### Freestanding wine storage fridges


<b>2</b> 0 <b>4</b>	<b>←75</b> →	WSbli 7731	GrandCru Selection	EA	•		•			•		324
188	<b>←60</b> →	WPbli 5231	GrandCru Selection	FG	-	•	•		•	•		229
		WSbli 5231	GrandCru Selection	EG	-		-			-		229
168	<b>←60</b> →	WPbli 5031	GrandCru Selection	FG	•	•	•		•	•		196
		WPbl 5001	GrandCru	FG	-	-		•	•		•	196
1 <del>4</del> 8	<b>←60</b> →	WPbl 4601	GrandCru	FG	-	•		•	•		•	166
128 128	<b>←60</b> →	WSbl 4201	GrandCru	D A T	-			•			•	141



Model/series	Energy rating	Glass Door	Humidity Control	UV Protect	Cigar
--------------	------------------	---------------	---------------------	---------------	-------

#### Freestanding compact appliance

ZKes 453 Humidor ■ ■ ■	CAN
------------------------	-----



Bordeaux bottle size (0.75 l) All specifications regarding bottle capacity refer to these dimensions.

\_gb GlassBlack \_ bl Black \_es SmartSteel \_df/pr Panel ready

Key to appliance material:

#### Model overview - wine fridges







EWTdf 3553

Model / series















#### Integrated wine tempering fridges

1 <b>7</b> 8	<b>← 56-57</b> →	EWTdf 3553***	Vinidor	G A	•	•			•		80
		EWTgb 3583	Vinidor	G A	•	•	•	•	•	•	83
1 <b>2</b> 2	<b>← 56-57</b> →	EWTdf 2353***	Vinidor	G A	•	•	•	•	•		48
		EWTgb 2383	Vinidor	G A	•	•	•	•	•	•	51
8 <b>8</b> ↓	<b>←56-57</b> →	EWTdf 1653***	Vinidor	G A	•	•			•		30
		EWTgb 1683	Vinidor	G A	•	•	•	•	•	•	33



WKEgb 582

#### Integrated wine storage fridge

← **56-57**→ WKEgb 582 GrandCru







UWgbi 3782

UWpri 3762

#### Under worktop wine fridges

		Olluci Woll	Ktop wille illu	ges								
86 <del>-</del> 92	<b>-60</b> →	UWgbi 3782	Vinidor Selection	E A A			•	•	•	•	•	38
		UWpri 3782***	Vinidor Selection	FA		•	•	•	-	-	•	38
		UWpri 3762***	Vinidor Selection	FA			•	•	-	-		38
		UWpri 3761***	Vinidor Selection	FA	•		•	•	•	•		44
82 <del>-</del> 88	<b>←60</b> →	UWgbi 3682	Vinidor Selection	E A		•	•	•	•	•	•	32
		UWpri 3662***	Vinidor Selection	FA		•	-	•	-	-		32
		UWpri 3661***	Vinidor Selection	FA	•		•	•	-	-		44
		UWgb 3632	Vinidor	FA		•	•	•	•			32
		UWgb 3631	Vinidor	FA	•		-	•	-			44
		-										







#### Optimised for food and drinks

Both beverages and food such as grilled vegetables, sauces or meat can be perfectly stored thanks to the flexible interior. The interior setup is easy to adapt to suit the height of the food, bottle sizes or vessels you are storing. The temperature can also be adjusted between +2 °C and +14 °C.



The Outdoor Cooler performs well even at low temperatures. In fact, outdoor temperatures ranging from +2 °C to +35 °C have no effect on the appliance. If the temperature drops below +2 °C, the appliance automatically protects itself by shutting down.

Description of series Series

For a clear overview – before you even open the fridge

## O Pure $\Diamond$ Plus $\Diamond$ Prime $\Delta$ Peak

Which appliance is right for me? This question is not always easy to answer when you are buying a new appliance. That's why we have made it even easier for you to find your way around our range of products by dividing our fridges and freezers into four series.

#### O Pure series

The Pure series is our basic class: simple, clear and perfectly equipped to cover all essential requirements. Pure series appliances have been reduced to the basics, but are full to the brim with the highest Liebherr quality.









#### ♦ Plus series

The Plus series builds on our Pure series and has many impressive additional details. "Plus" here specifically signifies enhanced convenience. These kitchen appliances are not only first-class in their refrigeration and freezing capabilities but also smarter and more user-friendly. This means they simplify many manual tasks, making life a little easier.



The Prime series is all about class. It makes a distinctive impression when it comes to design and material. For example, top-quality materials like stainless steel are used in the interiors of our freestanding appliances. Additionally, unique lighting solutions enhance the visual appeal of this series, making it truly stand out.









#### △ Peak series

The Peak series represents our top-of-the-line offering. Here, the best is combined with the best.
There is no compromise. Innovative Liebherr technology is blended with exceptional high-end design and solutions for convenience.
Appliances in this series are for anyone who wants to have it all.

#### Accessories



FreshAir activated charcoal filter



FlexSystem



VarioSafe and bottle shelf



Ice cube tray with lid



Bottle shelf



SmartDeviceBox

#### Wine



With constant temperature throughout the interior, adjustable from  $\pm 5$  °C to  $\pm 20$  °C.



With two temperature zones, independently and precisely adjustable from +5 °C to +20 °C.



With three temperature zones, independently and precisely adjustable from  $\pm 5\,^{\circ}\text{C}$  to  $\pm 20\,^{\circ}\text{C}$ .



The entire wine collection at a glance: behind tinted UV



The humidity can be actively regulated in 5% increments between 50% and 80% RH\*\*.



The humidity can be adjusted between two levels: Standard or High.



Triple protection: A tinted glass door with two layers of vacuum-deposited metal provides highly efficient protection from color radiation.



Double protection: A tinted glass door with one layer of vacuum-deposited metal provides efficient protection from solar radiation



For effective presentation and decanting: Wooden shelf with stainless steel bottle display, wooden box for decanting utensils and space for tempering wine glasses.

#### Special product groups



This Liebherr is ideal for use outdoors thanks to its rust- and weatherproof materials, robust construction and high-quality components.



Perfect conditions for fine wines with unique storage and tempering features.



Innovative features and perfect climate for fine clears



You'll find our accessories online with your dream model in the Liebherr-Appliances shop at home.liebherr.com/shop, or from your Liebherr specialist dealer.

#### Freshness technologies



BioFresh Professional offers even more flexibility for your individual food-storage needs.



Cooling like a pro: Cold mist and a temperature in the safe of just over 0°C ensure a longer shelf life and create a fabulous visual effect.



The Fish & Seafood safe stores fish and seafood at the optimum temperature of -2 °C, just as professionally as your fishmonger.



At a temperature just above 0°C and an ideal humidity, fruits, vegetables, meat, fish, and dairy products stay fresh much longer than in a typical fridge compartment.



The adjustable humidity prolongs the freshness of your fruits and vegetables.



Frost-free convenience.



Much less frequent defrosting.



Less frequent defrosting and easier opening of the chest lid thanks to no vacuum.



SuperFrost increases the cooling power for a short time – this means the temperature remains constant when adding unfrozen food.



Refrigeration or freezing? You can choose from:
The VarioTempZone can be set to an accurate temperature
of -18 °C to -10 °C and from -2 °C to 5 °C.

#### Convenience and flexibility



Very soft door closing, even when fully loaded, automatically below an opening angle of 30°.



EasyOpen means the freezer door can be opened multiple times in succession, conveniently and easily.



A particular suitability to low-temperature environments allows the installation of freezers even in unheated rooms down to an ambient temperature of –15  $^{\circ}$ C.



Unique worldwide: AutoDoor allows easy and convenient opening and closing of the door via voice command, knocking signal, and smartphone\* – or simply by hand.



Keep Liebherr fresh and odour-free. Door stays open when not in use. Save time, energy, and freshness.



Drawers on smooth telescopic rails for convenient opening and closing, and easy removal.



The glass door opens by 7 cm when tapped for easy access and full opening.

#### Water and ice

Brief description of the key equipment details | Fully integrated and freestanding appliances\*\*\*



The Water & Ice Centre provides sufficient cold water, ice cubes and crushed ice around the clock.



Automatic IceMaker for a plumbed-in connection.



Automatic IceMaker with a water tank, if a plumbed-in connection is unavailable or not wanted.



Conjure up ice cubes quickly: Fill the tank with water, let it freeze and then release the ready-made ice cubes with a twist (freestanding appliances).



Perfect for parties: automatic IceMaker and large pizza compartment on a convenient pull-out shelf.



The water dispenser is flush-mounted in the left side wall of the fridge compartment, for plumbed-in connections.

#### Design



Low heat, energy-saving and maintenance-free for optimum illumination.



MoodLight – a highlight in your living environment: the indirect lighting design elegantly showcases the Water & Ice Centre and recessed grips.

#### Connectivity



The integrated SmartDeviceBox enables you to control the appliance and make use of additional services via computers and mobile devices.



The SmartDeviceBox can be retro-fitted so that you can control the appliance and use additional services via computers and mobile devices. Available as an accessory.

#### Ultra-efficient models



This is even more economical° than appliances in the highest energy efficiency class A – Liebherr sets new standards.

 $^{\rm o}$  Compared to the threshold for maximum energy efficiency class A according to Directive (EU) 2029/2016 (as of December 2023).



What is different about our BluPerformance models? We have integrated all of the refrigeration technology in the appliance base. As a result, the appliances of the same size can hold a considerably greater volume. So you have noticeably more space for your food and drink. In addition, we were able to further improve energy efficiency thanks to improved ventilation and extraction in the base. And these appliances are now even quieter.

71

\*Can also be used via SmartDevice/Smart app. | \*\*For temperatures in home environments. For very dry/cold environments such as cellars, we recommend using the specially made water tray from our range of accessories to support the system. | \*\*\* Many more differentiating features and detailed model descriptions can be found at home.liebherr.com

