

Below zero, zero problem.


FrostProtect guarantees flawless operation, even in ambient temperatures as low as -15°C .

LIEBHERR


Freezers

LIEBHERR

Frost
Protect



Frost
Protect




When below zero is a big plus: FrostProtect.

No room for a freezer in the kitchen or other heated areas in your home?

We have some great news: With FrostProtect, all components are designed for temperatures as low as -15 °C . If the ambient temperature falls below 0 °C , our freezers continue working just as efficiently, saving just as much energy and your frozen food is just as well protected.

So you can put them in unheated rooms like a garden shed or garage and have more room for more important things.



**New: FrostProtect now in
NoFrost models with
BluPerformance technology**

All of the refrigeration technology is in the appliance base. So appliances with BluPerformance with the same outer dimensions have a much greater usable volume. Meaning you have noticeably more space for your food. And we were able to further improve energy efficiency thanks to improved ventilation and extraction in the base.

No
Frost

Convenience of never having to defrost.


Smart
Frost

Much less frequent defrosting.

Stop
Frost

Less frequent defrosting and easier opening of the chest lid thanks to no vacuum.

Freezers



← 60 →

FNC 5277 Peak	FNC 5076 Peak	FNC 4675 Peak	FNSdd 5257 Prime	FNd 525i Prime	FNb 5056 Prime
Total volume¹ 277 l	Total volume¹ 238 l	Total volume¹ 199 l	Total volume¹ 277 l	Total volume¹ 277 l	Total volume¹ 238 l
Exterior dimensions in cm (H/W/D) 185.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 165.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 145.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 185.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 185.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 165.5 / 59.7 / 65.5
Fig. front page		Side walls: Silver / door: Stainless steel w/SmartSteel			



Freezers



← 70 →

FNC 7277 Peak	FNC 7076 Peak	FNC 6675 Peak	FNC 7227 Plus	FNd 7227 Plus
Total volume¹ 363 l	Total volume¹ 311 l	Total volume¹ 260 l	Total volume¹ 363 l	Total volume¹ 363 l
Exterior dimensions in cm (H/W/D) 185.5 / 69.7 / 76	Exterior dimensions in cm (H/W/D) 165.5 / 69.7 / 76	Exterior dimensions in cm (H/W/D) 145.5 / 69.7 / 76	Exterior dimensions in cm (H/W/D) 185.5 / 69.7 / 76	Exterior dimensions in cm (H/W/D) 185.5 / 69.7 / 76

Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

FNC 7026 Plus	FNd 7026 Plus	FNC 6625 Plus	FNd 6625 Plus
Total volume¹ 311 l	Total volume¹ 311 l	Total volume¹ 260 l	Total volume¹ 260 l
Exterior dimensions in cm (H/W/D) 165.5 / 69.7 / 76	Exterior dimensions in cm (H/W/D) 165.5 / 69.7 / 76	Exterior dimensions in cm (H/W/D) 145.5 / 69.7 / 76	Exterior dimensions in cm (H/W/D) 145.5 / 69.7 / 76

Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)


FNd 5056 Prime	FNd 4655 Prime	FNd 4254 Prime	FNSfe 5227 Plus	FNe 5227 Plus	FNe 5026 Plus
Total volume¹ 238 l	Total volume¹ 199 l	Total volume¹ 160 l	Total volume¹ 277 l	Total volume¹ 277 l	Total volume¹ 238 l
Exterior dimensions in cm (H/W/D) 165.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 145.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 125.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 185.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 185.5 / 59.7 / 67.5	Exterior dimensions in cm (H/W/D) 165.5 / 59.7 / 67.5
Side walls: Silver / door: SteelFinish					

Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

Chest freezers



CFd 2505 Plus	CFd 2085 Plus	CFf 2500 Pure	CFf 2080 Pure	CFf 1870 Pure
Total volume¹ 359 l	Total volume¹ 248 l	Total volume¹ 497 l	Total volume¹ 353 l	Total volume¹ 281 l
Exterior dimensions in cm (H/W/D) 82.5 / 167.5 / 70.9	Exterior dimensions in cm (H/W/D) 82.5 / 125.5 / 70.9	Exterior dimensions in cm (H/W/D) 82.5 / 167.5 / 70.2	Exterior dimensions in cm (H/W/D) 82.5 / 125.5 / 70.2	Exterior dimensions in cm (H/W/D) 82.5 / 104.5 / 70.2

Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

Table-height freezers



GP 1496 Premium	GP 1486 Premium	GPesf 1476 Premium	GP 1476 Premium	GP 1386 Premium	GP 1376 Premium
Total volume¹ 102 l	Total volume¹ 102 l	Total volume¹ 102 l	Total volume¹ 102 l	Total volume¹ 102 l	Total volume¹ 102 l
Exterior dimensions in cm (H/W/D) 85.1 / 60.2 / 62.8	Exterior dimensions in cm (H/W/D) 85.1 / 60.2 / 62.8	Exterior dimensions in cm (H/W/D) 85.1 / 60.2 / 61	Exterior dimensions in cm (H/W/D) 85.1 / 60.2 / 62.8	Exterior dimensions in cm (H/W/D) 85.1 / 55.3 / 62.4	Exterior dimensions in cm (H/W/D) 85.1 / 55.3 / 62.4
Side walls: Silver / door: Stainless steel w / SmartSteel					

Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

Gsl 1223 Comfort	G 1223 Comfort	Gbe 1213 Comfort	GP 1213 Comfort	GX 823 Comfort
Total volume¹ 97 l	Total volume¹ 97 l	Total volume¹ 97 l	Total volume¹ 97 l	Total volume¹ 68 l
Exterior dimensions in cm (H/W/D) 85.1 / 55.3 / 62.4	Exterior dimensions in cm (H/W/D) 85.1 / 55.3 / 62.4	Exterior dimensions in cm (H/W/D) 85.1 / 55.3 / 62.4	Exterior dimensions in cm (H/W/D) 85.1 / 55.3 / 62.4	Exterior dimensions in cm (H/W/D) 63.1 / 55.3 / 62.4
Side walls: Silver / door: Silver		Housing: Beige / door: Beige		

Energy efficiency class

Total volume¹

Exterior dimensions in cm (H/W/D)

¹ In accordance with regulation EU 2019/2016, we indicate the total volume to the nearest integer (rounded off).
The term "volume" refers to the term "capacity", which is used in the current Regulation.

You can find the entire range of efficiency ratings on the reverse side. According to (EU) 2017/1369 6a.

For complete model descriptions, visit home.liebherr.com



BluRoX

The future is circular.

The newly developed BluRoX technology from Liebherr is going to change the market for refrigerators and freezers sustainably. Instead of polyurethane foam, we use a much more effective form of cold insulation: a vacuum. Finely ground lava stone, known as perlite, stabilises the vacuumed components.

The first freezer using vacuum perlite technology in the door and built for the circular economy of re-use has already been certified with the "B" efficiency rating. And with every new BluRoX appliance we design, we will set new standards in terms of energy efficiency and capacity – and humanity and the environment will be the winners.




To learn more about this exciting technology and the many advantages of BluRoX, visit:
home.liebherr.com/blurox



FNb 5056
Available from the
2nd quarter of 2023



The current EU energy label for electrical appliances



1. QR code to identify the product in the EU database EPREL (European Product Registry for Energy Labelling).
2. The model identifier for manual identification of the product in the EU database EPREL, using the article number for example.
3. The new efficiency scale from "A" to "G". However, "G" is only intended for wine cabinets.
4. The total volume* of all freezer compartments.
5. The sum of the volume* of all cold-storage and refrigerator compartments.
6. The noise level is now classified into classes "A" to "D".

* The term "volume" is defined in current regulation EU 2019/2016.

home.liebherr.com

Subject to technical changes, errors and deviations in image and text. Deviations in colour due to media used. For latest available data, see home.liebherr.com. Printed in Germany by WPP Offsetdruck GmbH 7901 671-00/02.23 EN/LEX

