

---

# XRFsdh 5220

---

Side-by-Side combination  
◇ Plus

# LIEBHERR

Freestanding



**SFNsdh 5227**

Freestanding freezer with NoFrost

◇ Plus



← 60 →



Energy consump. in 365 days/24 h	<b>256 kWh<sup>1</sup></b>
Total net capacity	<b>271 l</b>
Noise output	<b>37 dB(A)</b>
Climate rating	<b>SN-T (+10 °C to +43 °C)</b>
Frequency / voltage	<b>50-60 Hz / 220-240 V~</b>
Connection Rating	<b>1.3 A 264.6 W</b>
Door / Side walls	<b>SmartSteel / silver</b>
Exterior dimensions in cm (h / w / d)	<b>185.5 / 59.7 / 67.5<sup>1</sup></b>
<b>Controls</b>	
Type of Control	LC monochrome display behind-the-door, touch electronic Digital temperature display
Interface	SmartDeviceBox: optional accessory (Only available in selected countries)
Door alarm	visual and acoustic
Alarm in case of malfunction	visual and acoustic
<b>Freezer compartment</b>	
Number of drawers	7 drawers, VarioSpace Top drawer with convenient tilting function
Freezing capacity in 24 hours	<b>18 kg</b>
Temperature rise time	<b>16 h</b>
VarioSpace	yes
<b>Features</b>	
Side-by-Side concept	Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
Door hinges	Reversible door hinge, left
Replaceable door seal	yes
EAN-Nr.	4016803090014

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

# Features

---



## NoFrost

When you open your freezer, you want to see frozen food – and certainly not ice and frost. NoFrost protects the freezer compartment from unwanted icing, which consumes a lot of energy and can be expensive. NoFrost means no more tedious and time-consuming defrosting of the freezer compartment, more time for other things – and saving money.



## Retrofitable SmartDeviceBox

Want to be prepared for the future of the Smart Home? Your Liebherr will be happy to help. You can retrofit it with a SmartDeviceBox which will connect your Liebherr to the Internet. The SmartDeviceBox can be installed in just a few steps and will open up the whole world of digital possibilities to you today.



## Touch display

Fingertip control: the touch display enables easy and intuitive operation of your Liebherr. All functions are clearly arranged on the display. By gently tapping a finger, for example, you can easily select the functions or check the current temperature of your refrigerator.




## SmartSteel

The SmartSteel surface makes your high-end quality Liebherr a real eye-catcher – and a real piece of designer furniture. The horizontal effect perfectly accentuates the stainless steel and gives the surface a silky gloss, making it pleasant to the touch. The anti-fingerprint coating reduces the visibility of finger prints and is easy to clean.



## EasyTwist Ice

Whether it's a summer day or a party: Thanks to EasyTwist Ice, you can prepare a supply of ice cubes quickly and easily – without the need for a fixed water connection. Simply fill the tank with water, let it freeze and then release the finished ice cubes with a simple twist – and you're ready to serve cool drinks. The EasyTwist Ice is easy to clean and ensures hygienic ice cube production at all times.



## EasyOpen

Done this before? After putting all the shopping in the freezer you remember an item of food you have forgotten – and have to give the door a good pull to open it again. With your Liebherr, you don't need to do this. EasyOpen means the door can be opened multiple times one after another, conveniently and easily.

# SRsdh 5220

Refrigerator with EasyFresh

◇ Plus



← 60 →



Energy consump. in 365 days/24 h	122 kWh <sup>1</sup>
Total net capacity	384 l
Noise output	35 dB(A)
Climate rating	SN-T (+10 °C to +43 °C)
Frequency / voltage	50-60 Hz / 220-240 V~
Connection Rating	1.2 A
Door / Side walls	SmartSteel / silver
Exterior dimensions in cm (h / w / d)	185.5 / 59.7 / 67.5 <sup>1</sup>
<b>Controls</b>	
Type of Control	LC monochrome display behind-the-door, touch electronic Digital temperature display for fridge compartment
Interface	SmartDeviceBox: optional accessory (Only available in selected countries)
Door alarm	visual and acoustic
<b>Fridge compartment</b>	
Forced air system	PowerCooling with FreshAir activated charcoal filter
Door interior	Plastic door shelves with bottle holder
VarioSafe	yes
Bottle shelf	Bottle shelf
Interior light	LED ceiling lighting
Fruit and vegetable bins	1 EasyFresh safe on running rails 1 spacious fruit and vegetable drawer
<b>Features</b>	
Side-by-Side concept	Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
Door hinges	Reversible door hinging
Replaceable door seal	yes
EAN-Nr.	4016803057819

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

## Features

---



### EasyFresh

The guarantee of market freshness in the home is our EasyFresh-Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



### Retrofitable SmartDeviceBox

Want to be prepared for the future of the Smart Home? Your Liebherr will be happy to help. You can retrofit it with a SmartDeviceBox which will connect your Liebherr to the Internet. The SmartDeviceBox can be installed in just a few steps and will open up the whole world of digital possibilities to you today.



### Touch display

Fingertip control: the touch display enables easy and intuitive operation of your Liebherr. All functions are clearly arranged on the display. By gently tapping a finger, for example, you can easily select the functions or check the current temperature of your refrigerator.



### SmartSteel

The SmartSteel surface makes your high-end quality Liebherr a real eye-catcher – and a real piece of designer furniture. The horizontal effect perfectly accentuates the stainless steel and gives the surface a silky gloss, making it pleasant to the touch. The anti-fingerprint coating reduces the visibility of finger prints and is easy to clean.



### SmartSteel rear wall

The rear wall in elegant SmartSteel gives your Liebherr a stylish look and feel. Your food will also love SmartSteel as stainless steel is food-safe and hygienic. SmartSteel also reduces the visibility of fingerprints – making the appearance even more pleasing.




### Slimline door handle (with integrated opening mechanism)

Opening made easy: The practical and elegant slimline door handle with an integrated opening mechanism allows you to open the appliance door effortlessly, even when it's opened multiple times in quick succession. The classy, minimalistic handles are also an eye-catcher on your appliance.

# Technical drawing

---



Products and their details are staged for advertising purposes. Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any damage. (04.09.2023)

