

---

# ZKes 453

---

Humidor  
Humidor

# LIEBHERR

Freestanding



# The perfect climate for your cigars

To provide perfect enjoyment, cigars mature for some time after production in special climate chambers at humidity of 68% to 75%. Maintaining this humidity and keeping to a storage temperature of +16 °C to +20 °C is essential for preserving the quality or for aging cigars. Storing cigars in conditions of insufficient humidity is detrimental to their aroma and quality. If the humidity is too high there is a risk of mould forming on the precious tobacco leaves. Liebherr's new humidor provides the perfect climatic conditions for storing or aging cigars over a long period. A high-quality touch electronic control system in conjunction with humidity sensors ensures accurate compliance with the temperature and humidity required.



# Quality in every detail




The precision **electronic control system** allows the temperature to be set within a range of +16 °C to +20 °C. The humidity can also be set between 68% and 75%. The temperature alarm alerts the user to any irregularities within the interior.



The integrated water tank is filled with one litre of distilled water. **Humidity** sensors regulate the water requirement and ensure that the humidity is kept exactly to the level selected. A visual display tells the user in good time when water has to be replenished.



Liebherr's humidor has **LED lighting**, with dimmer function, incorporated in the glass door. As the LEDs emit virtually no heat, the cigars can be showcased bathed in light for lengthy periods, without compromising their quality.



The two presentation boxes, varying in height and the two wooden shelves are crafted from **Spanish cedar wood**.



The **presentation boxes** are ideal for storing loose cigars and can easily be removed for presentation purposes.



The humidor can also be **wall-mounted** as an attractive eye-catcher and for convenient access.

Freestanding

# ZKes 453

Humidor  
Humidor

# LIEBHERR



Smart  
Steel

Cigar

← 43 →



Energy consump. in 365 days/24 h	162 / 0.443 kWh
Total net capacity	39 l
Noise output	40 dB(A)
Climate rating	N (+16 °C to +32 °C)
Frequency / voltage	50 Hz / 220-240 V-
Connection Rating	0.5 A
Door	Glass door with stainless steel frame and SmartSteel
Side walls	stainless steel with SmartSteel
Exterior dimensions in cm (h / w / d)	61.2 / 42.5 / 47.8
<b>Controls</b>	
Type of Control	LCD display in the interior, touch electronic Digital display of temperature and humidity
Alarm in case of malfunction	visual and acoustic
Door alarm	acoustic
Child proof function	yes
<b>Features</b>	
Temperature zones	1
Temperature range	+16 °C to +20 °C
Air humidity	68% to 75%
Adjustable cooling circuits	1
Forced air system	Convection cooling, fresh air supply via FreshAir activated charcoal filter
Interior light	LED lighting permanently on, dimmable
Design	HardLine-Design
Shelf material	Spanish cedar wood fittings
Storage shelves	2
Door hinges	Fixed door hinge, right
Presentation boxes	2
Lock	mechanisch
EAN-Nr.	9005382100837

## Features

---




### SmartSteel

SmartSteel significantly reduces the visibility of finger marks and is very easy to clean.




### Precision control

Using the precision electronic control system, the temperature can be set between +16 °C and +20° C. The humidity can be set between 68% and 75%, as required. The temperature alarm alerts the user to any irregularities in the inside temperature.



### Humidor: Presentation box

The cedar wood boxes are ideal for storing loose cigars and can be easily removed for presentation purposes.



### Door alarm

The audible door alarm alerts the user if the door has been open for longer than 60 seconds for safe protection of the food.



### Child lock

The child lock is programmed so as to prevent the appliance being inadvertently switched off. A symbol in the MagicEye indicates when the child lock is switched on.




### Wall-mounting

The compact appliances (WKes 653, ZKes 453, CMes 502) can also be wall-mounted without difficulty as an attractive eye-catcher with convenient access for serving.

# Technical drawing

---



---

Products and their details are staged for advertising purposes. Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any damage. (20.06.2023)

