CBS 2092G

Freestanding / Semi Built-in



Refrigeration and Freezing






home.liebherr.com

	CBS 2092G
Energy consumption (kWh / y)	550
Estimated Yearly Energy Cost* in US \$	77
Sound rating** dB(A)	42
Refrigerator capacity cu.ft. (l)	12.9 (365)
BioFresh compartment cu.ft. (l)	2.4 (69)
Freezer capacity cu.ft. (l)	6.0 (170)
Electronic control	Display, touch electronic
Defrost type	Automatic
Interior light	LED light column / LED ceiling
Number of shelves	4
Number of door racks	6
Number of BioFresh drawers	2
Number of freezer drawers	2
Refrigerator Temperature range °F (°C)	+37°F to +45°F (+3°C to +7°C)
Freezer Temperature range °F (°C)	+7°F to -17°F (-14°C to -27°C)
Water filter	Yes
Ice maker	Fixed water connection
Ice cube output lbs. (kg.)	3.1(1.4)
Ice cube stock lbs. (kg.)	6(2.7)
Door hinges	left/right
Product dimensions	
in inch (H / W / D)	80 5/16" / 35 7/8" / 24 1/4"
in cm (H / W / D)	203.9/91/61.5
Cut out dimensions	
in inch (H / W / D)	80 1/2" / 36" / 24 1/16"
in cm (H / W / D)	204.5/91.5/61
Net weight lbs. (kg)	377.0 (171.0)
Voltage V / Hz	115/60

* Energy Cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 14 cents per KWh.





Accessories	
Water Filter	9880980/7440002
Top Ventillation Grill 84" cabinets, single unit	9900199

Features



Preserve just-bought groceries for optimum food freshness, while sealing in flavors and maintaining essential vitamins and minerals.



Lengthen the shelf life and preserve the flavor of your foods with a dual refrigeration system that creates ideal conditions in both the refrigerator and freezer.




Liebherr's automatic IceMaker produces perfect ice cubes and keeps a constant supply on hand for every occasion.




Store food securely within reach thanks to fully extendable pull-out drawers. The SoftTelescopic system provides convenient and reliable self-retraction with soft closing.

Diagrams

Product Dimensions





00

IMPORTANT Do not install the shut-

off valve for the water

supply behind the

appliance.

Water line opening

7-5/8"

24"

610 mm

195 mm

15-3/8"

Water supply line

Free length at least

31 - 1/2" (800 mm)

36" 914 mm


390 mm

80-1/2" 2045 mm

Û

78'

max.



Semi built-in look - Cut out dimensions

The appliance can be used freestanding or semi built-in. If semi built-in, consider the cabinet opening dimensions specified below.

Minimum opening height for the french door 36" model is 80-1/2" to accommodate the top mounted hinges.

The requirements for water supply and electrical outlet are the same for both applications.

IMPORTANT


With 24" depth cabinets, the water line opening must be in the location as shown as there will not be room to route a water line behind the appliance for risk of pinching. Also, for this cabinet depth the electrical outlet cannot be behind the unit or the unit will not be able to be pushed all the way back into the opening. With cabinets deeper than 24" there is room to fit the pipe behind the appliance and the wall so there are no requirements for the water line lead out position.

nax

92"

40"

Ventilation Requirements



CBS 20 appliances don't need any ventilation openings in the cabinet. The required airfl ow is directed through the toe kick area.

It is important to use the provided cover grille for the ventilation opening. This opening must not be covered with a cabinet base.

Subject to modification. For up-to-date information, visit home.liebherr.com.

Specifications are for planning purposes only. For more detailed information, refer to installation instructions or Design Guide.