

EN

Solutions for deep foundation work

Drilling rigs, piling rigs, duty cycle crawler cranes

LIEBHERR

Liebherr-Werk Nenzing GmbH







The applications

- 06 Drilling
- 08 Pile driving
- 10 Slurry wall installation
- 12 Ground improvement

The machines

- 16 **Drilling rigs LB series**
- 18 Characteristics
- 24 Attachments for the LB and LRB series
- 25 Drilling and mixing tools
- 26 Application and configuration examples
- 28 Concrete technology

- 20 **Piling and drilling rigs LRB series**
- 22 Characteristics
- 24 Attachments for the LB and LRB series
- 25 Drilling and mixing tools
- 26 Application and configuration examples
- 28 Concrete technology

- 30 **Piling rigs LRH series**
- 32 Characteristics LRH 600
- 34 Characteristics LRH100.1 and LRH 200
- 35 Attachments for the LRH series

- 36 **Carrier machine for slurry wall construction LBX 600**
- 38 Characteristics

- 40 **Duty cycle crawler cranes HS series**
- 42 Characteristics
- 44 Attachments for the HS series
- 46 Slurry wall cutter
- 48 Slurry wall package

- 50 **Unplugged**

The certain extras

- 54 Operator comfort
- 56 Control and assistance systems
- 58 Digital solutions
- 60 Transport and set-up
- 62 Fuel costs matter
- 63 Corporate responsibility
- 64 Application and process technology
- 66 Customer service

The applications

Drilling

Liebherr's deep foundation machines can be applied for all common drilling processes. These include Kelly drilling, continuous flight auger drilling, full displacement drilling, double rotary drilling, grab drilling and down-the-hole drilling.

The appropriate process is chosen in accordance with the prevailing ground conditions or depending on the required depth and/or diameter of the borehole. The drilled cavity can be used for many purposes, for example to install a so-called cast-in-place pile when filled with fresh concrete. Precast concrete and steel elements serving as load-bearing or support elements can also be inserted.



Kelly drilling

As the most common drilling process, it is suitable for almost all types of soil and rock. Characteristic are the relatively short drilling tools as well as a telescopic Kelly bar, which enable large drilling depths.



Continuous flight auger drilling

This process is used for pre-drilling as well as for the installation of cast-in-place piles. The loosened soil is constantly conveyed using a continuous flight auger.



Full displacement drilling

Full displacement tools are frequently used for the production of cast-in-place piles. The soil is displaced by a smooth casing with an auger starter piece and only a small amount is conveyed to the surface.



Double rotary drilling

For this process, the casing and auger (inside the casing) are inserted simultaneously and subsequently extracted. It is used for the production of cast-in-place piles and for pre-drilling.



Down-the-hole drilling

Here, a simultaneously rotating and impacting hammer, activated by compressed air, is driven into the ground. A flushing current conveys the loosened drill cuttings to the surface. This method is mainly applied for rock and/or for penetrating large boulders.



Grab drilling

Grab drilling is a common process which loosens the ground with a cutting or impacting action depending on the tool used. Duty cycle crawler cranes are equipped with either a pile grab, a chisel or special tools.

Pile driving


With pile driving, so-called piling elements can be installed in the ground and extracted again. Common piling elements include steel profiles and piles made of reinforced concrete or timber.

Nowadays, mainly sheet pile walls for supporting or securing purposes, as well as foundation piles or cut-off walls are produced using the various pile driving processes. The erection of quay facilities in port construction presents difficult conditions and requires particularly heavy piling work with long piling elements. For this purpose, mainly powerful duty cycle crawler cranes with lattice booms and special leader systems are used. Pile driving processes are divided into two categories, namely impact driving and vibrating.



Vibrating

High frequency vibrators with variable static moment have especially low noise and vibration levels when operating. The piling element is set into harmonious oscillation. Thanks to the weight of the vibrator and pushing with the aid of the crowd system, the piling element can be installed in the ground.



Impact driving

The piling elements are installed dynamically. A hydraulic hammer, usually mounted on a piling rig with leader, impacts on the piling element with the aid of a drop weight. Impact driving is used for the same applications as vibrating, whereby the hydraulic hammers currently available are able to transfer much higher dynamic forces.

Slurry Wall Installation

Slurry walls are wall structures, which are installed deep into the ground and made of concrete or reinforced concrete. They have a static and/or sealing function. Trenches are excavated in panels, And a support fluid, usually bentonite suspension, prevents the soil around the trenches from caving in.

In the single-phase process a self-hardening suspension remains in the trench. In the two-phase method the support fluid is pumped out of the trench and simultaneously replaced, for example, with concrete, after the final depth has been reached. In the combined process, additional precast concrete elements, steel elements or sealing panels are inserted in the suspension before it hardens. The powerful Liebherr duty cycle crawler cranes are used as carrier machines.



Mechanical slurry wall grabs

Mechanical grabs are the most common excavation tools used for slurry wall installation. They are opened and closed via rope. Trenches up to a depth of 50 metres are possible.



Hydraulic slurry wall grabs

Hydraulic slurry wall grabs are opened and closed via hydraulic cylinders. This facilitates extremely high closing forces. Additionally, they can be fitted with flexible guiding strips on the grab frame, which enable the alignment of the grab within the trench.



Slurry wall cutters

Slurry wall cutters are suitable for great depths and particularly when very hard soil conditions prevail. In the process the soil is loosened and crushed by a cutter head on the lower end of the guide frame. The loosened material is continuously pumped to the surface in the support fluid.

Ground improvement

This process involves the stabilisation of the ground on the jobsite through treatment and/or the addition of other materials. A number of processes are available for this purpose. Ground improvement means changing the natural properties of the ground with a view to meeting the constructional requirements of the jobsite.

The natural load-bearing capacity of the ground to support construction loads is enhanced and/or the compressibility (settlement) of the ground is reduced. Several different products can be installed for this purpose. These include various types of columns, retaining walls, cut-off walls and sealing slabs, as well as embankment and compaction structures.



Impact compaction

A heavy drop weight is dropped from a height of up to 40 metres onto the ground which is to be compacted. This dynamic input of energy increases the density. Liebherr duty cycle crawler cranes facilitate efficient compaction thanks to free-fall winches and an automatic control system.



Cutter soil mixing

For this process rotating wheels break up the ground structure. Simultaneously, a self-hardening binding agent suspension is added. The wheels of the mixing tool rotate around the horizontal axis so producing soil mixing elements with a rectangular cross-section.



Wet soil mixing

For wet soil mixing the mixing tools rotate around the vertical axis of the mixing shaft. The tools break up the soil matrix and mix the suspension with the soil. Cements are used as binding agents. These are mixed to a suspension by adding water.



Vibro-replacement

A deep vibrator, fitted on a leader, compacts the ground through vibration and the simultaneous addition of a coarse extraneous material. Thus load-bearing gravel or crushed stone columns, which stabilise the ground, are produced.



Vibro-compaction

With this process, non-cohesive soil is compacted using a vibro-flot. Through the vibration the soil grains change from their initial loose layering to a denser layering. A cylindrical compacted soil structure is created around the vibro-flot.

The machines

Drilling rigs LB series



Multiple applications

The drilling rigs of the LB series are suitable for a wide range of applications in the deep foundation industry. In addition to the Kelly drilling process, they are also commonly used for the continuous flight auger, full displacement and double rotary drilling processes. Down-the-hole drilling is an exceptionally efficient method when working in hard ground or rock.

Successful on the market since 2007

Liebherr presented its first drilling rig in the successful LB series, namely the LB 28, at the Bauma 2007. Today, the LB series consists of six models with torques between 200 and 550 kNm. Depending on the process, drilling depths down to 120 metres and drilling diameters up to 4800 millimetres are possible.



Weight
Max. torque
Max. pull / crowd force
Kelly drilling max. drilling depth
Kelly drilling max. drilling diameter
Engine power
Available as battery-powered version

	LB 20.1	LB 25	LB 30	LB 35.1	LB 45.1	LB 55
Weight	52.8 t	71.5 t	78.5 t	100.1 t	116 t	159 t
Max. torque	200 kNm	250 kNm	300 kNm	347 kNm	452 kNm	550 kNm
Max. pull / crowd force	200 kN	300 kN	320 kN	400 kN	400 kN	560 kN
Kelly drilling max. drilling depth	34.5 m	58.8 m	70.8 m	77 m	95 m	120 m
Kelly drilling max. drilling diameter	1500 mm	3300 mm	3400 mm	4100 mm	4500 mm	4800 mm
Engine power	230 kW	320 kW	320 kW	450 kW	450 kW	565 kW
	LB 16 unplugged	LB 25 unplugged	LB 30 unplugged			

Characteristics

The drilling rigs from Liebherr are distinguished through a compact design meaning they can be efficiently transported and quickly mobilized on the jobsite. Their powerful diesel engines convince with both low fuel consumption and low emissions. User-friendly rotary drives allow for high torques. Designed for continuous operation, the drilling rigs achieve fast working cycles.

Leader design

The leader is rigid and fitted with a wide leader profile, on which all winches are directly mounted. Thanks to this robust and rigid construction, it can resist high torques and transfer high pull forces through the Kelly winch and the rope crowd system.

Parallel kinematics

Thanks to the leader system's proven parallel kinematics, the drilling rigs have a large working range and, at the same time, work precisely.

High stability

The long crawlers give the undercarriage a high level of stability and durability while minimising the ground pressure.

Swing ring

The drilling rigs are equipped with a triple-row roller bearing ring which increases the stability of the machine when in operation. Thanks to an optimum adjustment of the tooth flank clearance, only a minimum clearance exists between the uppercarriage and undercarriage.

Drive system

The complete drive system comprises Liebherr components, including engine, pumps, distributor and on-board hydraulics. These are perfectly harmonised and so achieve high efficiency. This results in low fuel consumption, high drilling performance and thus economic machine operation.

Rope crowd system

The rope crowd system featuring extremely high pull and crowd forces contributes to the excellent performance of the drilling rigs.

Robust steel structure

Drilling rigs are sometimes subjected to high stresses in deep foundation applications. These are taken into account in the steel structure of the machines of the LB series. Through optimum force transmission low wear and a long service life is achieved.

Small swing radius

The machines in the LB series have a relatively small swing radius.



Safety concept

The drilling rigs have a consistent safety concept that includes railings and walkways, as well as an installation for winch inspection. The complete assembly and loading activities can also be carried out outside the operator's cab with a radio remote control unit.



Video LB 45

Piling and drilling rigs LRB series



All-round machines

Since the end of the 1990s, Liebherr in Nenzing has been developing and manufacturing a range of combined piling and drilling rigs. Today, the series has four models, which perfectly cover the various requirements of our customers.

Wide range of applications

Piling and drilling rigs from Liebherr are deployed for various applications on the jobsite. A typical application for smaller models is the vibration of sheet pile walls. The LRB 355.1 was specially developed for drilling with full displacement tools. It is also suitable for all further common drilling applications as well as operation with hydraulic hammer or vibrator.



	LRB 19	LRB 23	LRB 355.1
Weight	48.2 – 50.7 t	73 – 83 t	95 – 109 t
Max. crowd distance	19 m	23 m	27 m
Max. pull / crowd force	250 / 165 kN	320 kN	400 kN
Max. torque rotary drive	180 kNm	300 kNm	450 kNm
Engine power	450 kW	600 kW	600 kW 750 kW

Characteristics

With the LRB series Liebherr offers its customers combined piling and drilling rigs for a diverse range of applications on the jobsite. The universal machines are characterised by both high performance and efficiency, as well as reliability. Easy transportation and quick set-up are only two of the fundamental characteristics for the flexible application of the LRB machines on jobsites. For example, the leader can simply be folded backwards during transportation and does not need to be dismantled.

Innovative leader design

The leader absorbs large torque and is fitted with a rope crowd system for high pull and crowd forces. All winches are mounted directly on the leader meaning it is not necessary to shift the ropes when adjusting the inclination or radius of the leader.

Parallel kinematics

A large working area is possible thanks to the parallel kinematics. At the same time, the leader can thus be folded back.

Compact uppercarriage

Despite their high performance the machines in the LRB series have a compact uppercarriage. This results in a relatively small swing radius and therefore efficient work in restricted spaces.

Robust undercarriage

Thanks to an extremely solid undercarriage the machines in the LRB series have excellent stability and low ground bearing pressure.

Modular leader top

The leader top can be appropriately equipped for the actual application (only possible with LRB 23 and LRB 355.1). Both the radius and the rope lead-off are adjustable.





Increased pull force

Thanks to an additional or Kelly winch and a pulling device, the retraction force can be significantly increased during drilling processes or the device can be used for Kelly drilling.

Attachments for the LB and LRB series



Rotary drive (BAT series)

The powerful rotary drive delivers the torque for many different drilling applications. A major advantage is the automatic torque regulation. Thanks to its continuous speed optimisation, it can be flexibly adjusted to suit the prevailing ground conditions on the jobsite.

The Kelly shock absorber can be adjusted to suit the weight of the Kelly bar.



Double rotary drives (DBA series)

Secant drilled piles and foundation piles can be installed using double rotary drives. The inner continuous flight auger is driven independently from the casing by two separate rotary drives. The compact design allows for work in close proximity to buildings (front-of-wall drilling).



Rotary drives for down-the-hole drilling (DTH)

Liebherr offers special rotary drives which are used for applications with DTH hammer. Through shift and folding functions these can be adapted to the respective requirements.



Hydraulic hammers

Liebherr's own H series of hydraulic free-fall hammers comprises seven types with a maximum impact energy of 225 kNm. These are guided on the leader when installed on Liebherr's piling and drilling rigs. Through the mounting of modular drop weights the hammers can be perfectly adapted to the particular piling requirements.



High frequency vibrator with slim design

The powerful high frequency vibrators are particularly easy to maintain, mainly due to a new cooling system and also the use of state-of-the-art components. Thanks to the symmetrical layout and linear guiding of the vibrator, energy loss is minimised.



Casing oscillators

Hydraulic casing oscillators of various sizes can be attached to the basic machines. These are driven by the on-board hydraulics of the carrier machine. Together with the robust design of the casing oscillators this facilitates efficient operation on the jobsite.

Drilling and mixing tools

Tools are available for displaceable, mixable, loose and densely layered soil types, as well as for rock. They offer a high level of performance, low wear and a long service life.



Mixing drives

Should the piling and drilling rigs be required for ground improvement processes, mixing drives are used. These are characterised through their compact design. The drives are either designed for mixing with single equipment or modularly designed so they can be fitted with single, double or triple mixing equipment.



Further information



Kelly drilling

- Drilling augers, drilling buckets, core barrels, cluster drills
- Cross cutters, belling buckets
- Casing drivers
- Double-walled casings
- Cutting shoes



Continuous flight auger drilling

- Augers
- Auger starters
- Drill bits



Double rotary drilling

- Augers
- Auger starters
- Casing drivers
- Single and double-walled casings
- Cutting shoes



Full displacement drilling

- Drive tubes
- Displacers
- Drill bits



Down-the-hole drilling

- Down-the-hole hammers
- Casing tubes
- Drill bits



Wet soil mixing

- Mixing shafts
- Mixing tools with paddles, blades or auger screws

Application and configuration examples



Vibrating with high frequency vibrator



Impact driving



Wet soil mixing



Down-the-hole drilling

Flexible application on the jobsite

The LB and LRB machines from Liebherr are available in different configurations and are highly flexible in their application depending on the prevailing conditions on the jobsite. Additional equipment is available as an option for drilled piles with very large diameters and great depths. This includes an extension of the drilling axis, additional counterweight as well as a leader extension.



Kelly drilling with Low Head



Kelly drilling



Continuous flight auger
drilling with Kelly extension



Double rotary drilling



Full displacement drilling with
lattice boom extension


The drilling rigs can also be fitted with a shortened leader, therefore making them ideal for use on jobsites with height restrictions. Through a lattice boom extension the drilling depth can be significantly increased when using the full displacement drilling process.

Concrete technology



All you need in one kit

Liebherr is a highly diversified complete provider of concrete technology developing and manufacturing high-quality truck mixers, mixing plants and concrete pumps. This enables economic manufacturing, as well as trouble-free transportation and installation of concrete.



Flexible application

The crawler concrete pumps require minimum space, are quickly set up and can be positioned anywhere on the jobsite.



High-pressure concreting

High concrete conveyance ensures quick cycles when installing cast-in-place piles.



Concrete pumps

The trailer and crawler concrete pumps offer high conveyance output and low emissions. The pumps are especially suitable for the conveyance of concrete via concrete lines or concrete distribution systems. Innovative pump units, the hydraulic system and state-of-the-art control ensure extremely cost-effective operation of the concrete pumps.

Thanks to an integrated solution, the main parameters of the concrete pump can be controlled from the control panel in the operator's cab of the deep foundation machine. This means the machine operator has control of the concreting process, which leads to safer and more efficient jobsite assignments.



Crawler concrete pumps provide fresh concrete to the drilling rig for the manufacture of cast-in-place piles.



Designed for tough everyday jobsite operation

Whether in 40 °C heat or severe winter conditions, they are designed for worldwide operation.

Piling rigs LRH series




Flexible piling application

The piling rigs in the LRH series are suitable for jobs involving the installation of piling elements in widely varied types of soil. Liebherr's piling rigs are the first choice especially when very large radii and extreme angles are required. Depending on the requirements, the carrier machine is selected from the successful series of Liebherr duty cycle crawler cranes, drilling rigs or crawler cranes, which are fitted with stable leader systems.

Efficiency on the jobsite

Combined with a stable leader the piling rigs convince with excellent performance characteristics and flexibility. Thanks to the sophisticated hydraulic system of the carrier machines, equipment such as vibrators, hammers or rotary drives can be operated without an additional power pack. This leads to significant savings in running costs and underlines their reputation as highly efficient machines.



Max. pile length
Max. pile weight
Max. inclination
Radius
Hammer
Impact energy

Carrier machines

Available as
battery-powered version

LRH 100.1	LRH 200	LRH 600
19 m	24.5 m	34/44/55 m
8 t	16 t	40 t
1:3	1:3	1:4 / 1:3
8.7 m	7.8 m	15 m
H 6	H 6, H 10	H 15
72 kNm	120 kNm	225 kNm
LB 25	LB 30	HS 8200 LR 1300.1 SX
LRH 100.1 unplugged	LRH 200 unplugged	LR 1300.2 SX unplugged (carrier machine)

Characteristics

LRH 600

Fixed leader

Ideal for heavy piling work with a large radius – that's how the LRH 600 can be characterised. The piling rig convinces with sophisticated leader kinematics which enable a working radius of up to 15 metres and a leader length of 51 metres. Furthermore, inclinations up to 14° to the rear and up to 9.5° to the fore are possible. The leader's lattice design provides a high level of stability.

Vertical leader adjustment

The leader is connected to the boom head via supporting tubes. This allows to change the leader height without influencing the leader inclination.

Applications

In addition to pile driving with a hammer or a vibrator, these include drilling processes with continuous flight auger or down-the-hole hammer, as well as diverse ground improvement processes.




Swinging leader

For this design, the leader hangs on a special traverse together with the attachment on a crawler crane or duty cycle crawler crane. This so-called swinging leader is especially suitable for installing long piling elements of up to 50 metres as well as for piling work with large inclinations. The swinging leader is therefore often used for marine constructions.

Easy assembly

Pin connections allow for quick and easy assembly of the newly designed leader.



Characteristics LRH 100.1 and LRH 200

With these piling rigs Liebherr offers its customers two compact machines with especially flexible leader kinematics. This allows for large radii as well as inclination in all directions.

The machines are based on the LB 25 and LB 30, two proven drilling rigs from the LB series. The design of these carrier machines enables quick and economic transportation, fully assembled, so allowing for quick set-up on the jobsite. Both LRH machines are especially suitable for the installation of various piling elements made of timber, concrete or steel.


Leader kinematics

Thanks to the special leader system, the LRH 200 achieves a radius of 8 metres as well as a continuous inclination adjustment of 18° in all directions.



Mobility

The LRH 100.1 can erect and lower the leader independently (no auxiliary machines required) and is transported with mounted hammer.



Battery-powered version

We offer the piling rigs in an emission-free “unplugged” version. The machine has no restrictions in terms of performance and application compared with the conventional version.

Attachments for the LRH series



Rotary drives

The Liebherr rotary drives in the BAT series are powerful and deliver high torque. Considerable advantages are the automatic torque regulation as well as four electronically adjustable speed ranges.



Hydraulic hammers (H series)

The hydraulic free-fall hammers from Liebherr are leader mounted. Through the mounting of modular drop weights the hammers can be perfectly adapted to the particular piling requirements. Thanks to their short and lightweight design they are user-friendly in terms of transportation and maintenance.



Pre-drilling drives

These drives are used for pre-drilling prior to pile work.



Mixing drives

Mixing drives are used for ground improvement processes. These are characterised through their compact design.

Carrier machine for slurry wall construction LBX 600



Compact design

The LBX 600 has a particularly impressive slim design. Thanks to its compact size, the carrier machine for slurry wall construction can easily cope with limited space and is therefore particularly suitable for urban jobsites. The basic machine can be transported in one piece as, thanks to the telescopic undercarriage, the track width can be reduced to 3 metres.

Modular boom system for flexible application

The LBX 600 can be flexibly equipped and customised to meet site requirements thanks to a modular system with three different box-type booms. The standard version of the machine has a total height of 17.8 metres. For applications with restricted height, for example, working under bridges, the Low Head with 11 metres or Ultra Low Head with 5.8 metres can be used.



Max. working depth
Max. pull force in grab operation
Max. pull force in recovery mode
Working height
Battery-powered version

LBX 600	LBX 600 Low Head	LBX 600 Ultra Low Head
80 m	35 m (with adapted drum flange)	35 m (with adapted drum flange)
450 kN (dual-winch operation)	450 kN (dual-winch operation)	450 kN (dual-winch operation)
600 kN (dual-winch operation)	600 kN (dual-winch operation)	600 kN (dual-winch operation)
under 18 m	under 11 m	under 5.8 m
LBX 600 unplugged	LBX 600 unplugged	LBX 600 unplugged

Characteristics


The LBX 600 is designed for work with a hydraulic or mechanical grab and with a chisel. The two free-fall winches deliver a pulling force of 450 kN in grab mode and as much as 600 kN in recovery mode. In combination with the HSG 5-18 hydraulic slurry wall grab, the carrier machine offers very intuitive operation, which also allows hydraulic corrections to the grab alignment resulting in higher verticality of the slurry wall.

Slurry wall grab HSG 5-18

The grab is modularly designed and has a particularly robust base body. The term "C" (compact) stands for the compact standard design for the Low Head Version of the LBX 600, while the base body of the "L" (large) version is 2.5 metres longer. The resulting total height of the grab at 9.5 metres and the high weight with low centre of gravity provide for even better vertical positioning and are especially advantageous when installing larger dimensioned slurry walls. Depending on the design, diaphragm wall thicknesses of 500-1800 millimetres are possible.



Various attachments



Emission-free

The LBX 600 is available as both conventional and battery-powered version, the LBX 600 unplugged. The unplugged version does not produce any emissions and is extremely quiet. This strikes the right note especially in noise-sensitive regions and finds favour with jobsite personnel and residents.

The battery is charged using a conventional jobsite electricity supply. Unplugged machines can be operated both connected to the power supply (plugged in) or powered by battery (unplugged).

Animation



Duty cycle crawler cranes HS series



Universal machines for deep foundation work

In addition to machines purely for deep foundation work, Liebherr also offers a series of duty cycle crawler cranes which are deployed with appropriate attachments. The machines can be fitted, for example, with pile grabs and casing oscillators for drilling processes, slurry wall grabs or cutters for the installation of slurry walls, as well as with drop weights for carrying out dynamic soil compaction.

Proven in tough construction assignments

Thanks to their robust design the HS series of machines is ideally suited to the demands of deep foundation work. The three duty cycle crawler cranes with lifting capacities between 70 and 130 tonnes are especially popular for deep foundation applications. Additionally, Liebherr also offers smaller classes of machines with lifting capacities below 70 tonnes, as well as two larger types with lifting capacities up to 300 tonnes. These machines are applied, above all, for material handling with dragline buckets or grabs, but are also sometimes applied for deep foundation work or marine construction.



Max. capacity
Min. transport weight
Min. transport width
Max. drilling diameter*
Max. drop weight**
Engine power

HS 8070.1	HS 8100.2	HS 8130.1	HS 8200
70 t	100 t	130 t	200 t
47 t	40 t	51 t	47.4 t
3000 mm	3500 mm	3500 mm	3500 mm
1800 mm	2000 mm	3300 mm	3800 mm
19 t at 8 m radius	25 t at 8 m radius	34.1 t at 8 m radius	35 t at 8 m radius
320 kW	450 kW	565 kW	750 kW

* Casing oscillator
** Impact compaction

Characteristics

Duty cycle crawler cranes are exposed to high stresses in their various jobsite applications. A high level of stability is a basic requirement for efficiency when carrying out deep foundation work. Thus, the uppercarriage of the machine has a robust box design and is mounted on a large undercarriage. This not only meets the operating demands on the duty cycle crawler crane, but also extends its service life.

Winches

The low-maintenance hydraulic free-fall winches are installed as complete units. Depending on the model, they have a maximum line pull of 350 kN. Thanks to state-of-the-art variable flow hydraulic engines, the rope speed is automatically adapted for all working ranges without any output losses.

Control system

The duty cycle crawler crane is fitted with an intelligent control system which also includes a multitude of monitoring functions. Service and machine functions are clearly displayed on high contrast colour monitors. Depending on the requirements and the application, further assistance systems, such as the slurry wall grab control, are available.

Self-assembly system

No additional auxiliary crane is necessary for the assembly of duty cycle crawler cranes. All components, such as crawlers and counterweight, have a space-saving design and weights are optimised. These can be autonomously assembled using the sophisticated self-assembly system.

Hydraulic system

Thanks to the innovative hydraulic design with a closed circuit, the duty cycle crawler cranes are fuel-saving and therefore economic. The available hydraulic power is optimally split between the winches, swing and luffing gears or the external devices. Thus, parallel operation of all gears is possible.

Crawlers

Depending on the machine's size the crawlers can be dismounted with the aid of the self-assembly system or, thanks to hydraulic cylinders, they can be retracted to transport width.

Safety

The duty cycle crawler cranes meet the highest safety standards. Platforms, railings and ladders are wholly integrated in the machine design.



Attachments for the HS series in deep foundation applications



Pile grab

Duty cycle crawler cranes are equipped with universal pile grabs when installing pile foundations with casing oscillator. These can be deployed for various ground conditions. The universal pile grabs are extremely robust and are fitted with hard-wearing components.



Casing oscillator

For the installation of casings, the duty cycle crawler cranes are always fitted with a casing oscillator. These are coupled with the carrier machine and excel through their extremely robust design. They are driven by the carrier machine's hydraulic system.



Slurry wall grab

Mechanical grabs are opened and closed via a rope, hydraulic grabs via hydraulic cylinders. The verticality measuring system is fully integrated in the Liebherr control system. Additionally, hydraulic slurry wall grabs make it possible to carry out a vertical correction. This allows for a high level of accuracy, even at great depths.



Slurry wall cutter



Like a knife through butter: LSC 8-20


Liebherr's innovative slurry wall cutter is deployed when especially great depths are required and the ground conditions are extremely hard. Unlike a grab, the slurry wall cutter works continuously during excavation. In the process, the existing soil is loosened and crushed by the rotating cutter wheels.



Cutter wheel drive
Torque: 147 kNm



Slurry wall
thickness



Bite length
2800/3200 mm



800-2000 mm
Max. working depth
150 m

Slurry walls can be installed practically vibration-free using a cutter (hydromill). Cutter wheels are mounted on the bottom of a steel profile frame and continuously break up and crush the ground at the bottom of the trench. The loosened soil particles are pumped from the trench to the surface together with the support fluid via a hose.


An important advantage of the slurry wall cutter is that it can be deployed for almost all types of soil, including rock. Furthermore, work can be carried out at depths down to 150 metres.

Modularity




Standard

The slurry wall cutter from Liebherr is modularly built so that the customer can adapt the system to their own requirements and technical challenges.



Low Head

For construction sites with limited height, the modular cutting frame can be shortened by 4 metres.



Slurry wall package



Animation



As a systems provider, Liebherr offers not only the slurry wall cutter but also the necessary equipment such as separation plant, centrifuges, mixers and silos. The new pay-per-use model enables maximum gain with low investment and calculable maintenance costs.



Separation plant SP 600 C


- Modular design with high flexibility
- Extended walkways for easy access to all components
- Powerful integrated feed pump with a maximum capacity of 450 m³/h
- Durable design

Carrier machine HS 8130.1 with slurry wall cutter LSC 8-20

The HS 8130.1 is equipped with a particularly robust undercarriage. A powerful Liebherr engine with an output of 565 kW and free-fall winches with line pull of 350 kN each, make it an optimum carrier machine for the slurry wall cutter and ensure an excellent performance even under extreme conditions.

Hose drum system DS 150

- Crowd winch
- Additional diesel tank
- Return filter
- Hose drum carrier frame
- Drums for mud hose and energy chain
- Optional platforms
- Special boom head



Further
information



Unplugged



Zero emission

Our contribution to a greener future

Liebherr consciously demonstrates its responsibility towards society and the environment and strives for the best possible combination of environmental compatibility, customer benefit and efficiency.

With battery-powered equipment, we already offer a wide range of emission-free construction machines. The unplugged series is being continuously expanded.



Further
information



LB 25 unplugged



LRH 100.1 unplugged



LB 30 unplugged



LRH 200 unplugged



LBX 600 unplugged

The certain extras

Operator comfort

Modern cabins

With Liebherr machines, the focus is on the operator. High operator comfort makes the handling of the deep foundation machines considerably easier. The innovative design of the cabin sets new standards in the construction industry regarding ergonomics, interior fittings and air conditioning. Furthermore, the optimum view from the cabin allows for precise and safe operation.



Ingenious interior

An optional cooler for provisions, various storage areas and surfaces, as well as a holder and USB port for mobile phones are all within easy reach of the comfortable seat.



Ergonomic operating elements

All operating elements including redesigned joysticks, control keys and pedals are ergonomically arranged and allow for precise control of all machine functions.

Optimised visibility

Safety on site is Liebherr's highest priority. An unobstructed view from the cabin combined with a camera system for all working areas ensures this important factor.

Comfortable operator seat

The orthopaedic seat with automatic adjustment can be heated or cooled as required.



Sunshade

A standard sliding window and sunshade serve as additional features for improving comfort.



Control and assistance systems

Innovative and user-friendly

The integration of information technology into daily working processes simplifies many tasks, can improve safety on site, ensures transparency and thus provides clearer understanding and improved quality. All control and assistance systems are user-friendly solutions from Liebherr.






Obstacle recognition

Assistance systems

Liebherr offers a large number of different operator assistance systems in order to facilitate machine operation. This is all the more important in the deep foundation sector as a lot of the work is performed underground and outside the operator's field of vision.

Therefore, the operator profits from simplified handling even for challenging tasks. At the same time, the assistance systems increase both the level of performance as well as safety on the jobsite.



Ground pressure assistant

Control system

Liebherr's Litronic control system is based on the latest control software and includes all control and monitoring functions. Developed in-house, it is designed for tough jobsite applications even under harsh environmental conditions.

All information regarding service and machines is clearly displayed on touchscreens. Numerous functions make the handling of the machines considerably easier. This helps to achieve quicker working cycles. These include electro-hydraulic proportional control for precise operation or the handling of all machine functions with the control levers.



Further
information

Digital solutions

The deep foundation machines from Liebherr move in a digitalised world.

Precise positioning, data recording and transmission, central data management and analysis are all topical issues on the digital construction site. Performance and operational analyses in real time immediately reveal trends, irregularities or bottlenecks. This ability to react and work faster is the competitive edge of the future.

For Liebherr, as a manufacturer of construction machinery, the target is thus clearly defined. The digital integration of the machines is being continuously improved. Work optimisation, quality control, performance record, cost efficiency and safety for operator and machine are the main objectives.


LIPOS – Liebherr positioning system

Using pre-installed components, LIPOS enables the direct integration of machine control systems from Trimble and Leica. These systems are based on modern DGNSS technology (Differential Global Navigation Satellite System) and so achieve the best possible conditions for a precise and efficient positioning of Liebherr machines and their attachment tools.

PDE – process data recording

All working processes can be electronically recorded and visualised using the process data recording system PDE. The system is operated and displayed on the PDE touchscreen in the operator's cab. PDE records operating data from the Litronic control system, as well as data from external sensors.





MyJobsite – your jobsite at a glance

Using the MyJobsite software solution all relevant process, machine, jobsite and positioning data (LIPOS) can be recorded, displayed, analysed, managed and evaluated in one central location. The collected data can be accessed via a web browser when an internet connection is active.

With the recorded PDE data, a working protocol is automatically generated as proof of quality directly after completion of a work process. The parameters of the driving protocol can be defined and assigned in advance, which is an enormous time-saver.



Further information
about digital solutions



MyJobsite

Transport and set-up

Focus on cost-efficiency

Special attention was given to the uncomplicated and economic transportation of Liebherr's deep foundation machines. Thanks to minimum set-up work, the machine can be quickly mobilised between jobsites so promoting economic deployment.



In one piece

If necessary, smaller drilling rigs can also be transported with mounted attachment.

Easy transportation and straightforward set-up

Duty cycle crawler cranes

All components in Liebherr's duty cycle crawler cranes have a space-saving design and weights are optimised so allowing for smooth transportation on all roads in accordance with current international transport regulations. Pendant straps and pins remain in the intended mountings during transportation so speeding up assembly.

The smaller duty cycle crawler cranes can be transported in one piece so reducing assembly and disassembly work to a minimum. For the larger models, the basic machines are transported without the crawlers. First of all, the uppercarriage is unloaded independently using a jack-up system, whereby the duty cycle crawler crane is supported by hydraulic jack-up cylinders. Subsequently, the uppercarriage unloads the crawlers, counterweight, and boom sections using either its A-frame or boom foot. Hydraulically activated pins, quick connections and an auxiliary rope winch simplify and accelerate the assembly process.



Intelligent assembly

Through the self-assembly system no additional crane is necessary for the set-up or disassembly of Liebherr's duty cycle crawler cranes.

Piling and drilling rigs

The LB series of drilling rigs, the LRB series of piling and drilling rigs as well as the smallest piling rig LRH 100 can all be transported without extensive disassembly thanks to their compact measurements and low weights. This means that ropes need not be dismantled and the leader can simply be folded back. Therefore, the set-up work is completed in a considerably shorter time.

If the counterweight of a larger machine is transported separately, it can be mounted on site using the leader without the need for an auxiliary crane. This means significant cost savings.



Rapid mobilisation

The rotary drive is mounted using an auxiliary winch without the need for an additional crane. If the attachment is exchanged, this is carried out using a quick connection system.

Fuel costs matter

Reduction of noise emission and fuel consumption

The latest drive and control systems help to reduce fuel consumption and emissions and at the same time increase the reliability and performance of deep foundation machines.



HVO ready

Up to 90 % CO₂ emissions reduction

LIEBHERR

Deep foundation machines are fitted with Liebherr's own diesel engines. The latest generation complies with Stage V/TIER 4f and can be operated with HVO fuel.

Engine functions for enhanced efficiency

Downsizing of the engine

Thanks to the machine's optimised hydraulic system the size of the primary source can be reduced without negative effects on the performance.

Automatic engine stop control

This control system switches the engine off automatically during longer idling periods, after having checked certain system functions.




Eco-silent mode

With the aid of this feature the engine speed is reduced to a required predefined level.



Lower engine speed while idling

All diesel engines in the latest generation have a reduced maximum speed of only 1,700 rpm. The speed has been lowered from 950 rpm to 750 rpm while idling.



Corporate responsibility



As a globally active family-run company, Liebherr bears a great responsibility towards society and the environment.

Liebherr-MCCtec GmbH, which includes Liebherr-Werk Nenzing GmbH, promotes environmentally conscious, socially responsible and sustainable behaviour and aims to live up to its responsibility to society and the environment at all times.

The company supports the ten principles of the United Nations Global Compact on human rights, labour standards, the environment and anti-corruption. It is also committed to making an active contribution to the United Nations Sustainable Development Goals. Liebherr-MCCtec GmbH was awarded a gold medal by the independent rating agency EcoVadis for its long-standing commitment to sustainability.

Liebherr is convinced that long-term success is only possible if one remains aware of this responsibility in all activities.

Application and process technology

Practical advice from professionals for professionals

The application of sometimes very complex technologies and the correct choice of suitable equipment require special knowledge and practical experience. Our application specialists use their wide experience in various working methods and processes in order to get the most from your machine – maximum utilisation for maximum performance.



Machine consulting

In combination with the choice of the most suitable machine, our application specialists also provide advice regarding the best choice of attachments and tools in consideration of site conditions. The aim is maximum efficiency during the production of the required product. Furthermore, fuel consumption as well as wear and tear must be minimised in the process.



Application and process specialists

Application specialists provide assistance for a full range of tasks in the deep foundation industry, for example, drilling and vibration processes, slurry wall installations, etc. They are pleased to help in providing expert knowledge when facing particular challenges such as difficult ground conditions or confined working spaces.

Application and performance optimisation


Thanks to the detailed communication of new technological features, our customers are always well-informed about the latest developments and can so increase performance, improve operative safety or comply with new directives.



The compendium provides a comprehensive overview of methods, equipment and applications in the field of deep foundation.

Part 1: Drilling

Part 2: Ground improvement



Training on site

Our application specialists are at your disposal for training purposes directly on jobsites throughout the world. Ranging from the assembly or disassembly of the machine, through upgrades and retrofits, up to the optimisation of the jobsite itself, Liebherr offers a broad spectrum of training possibilities including Liebherr's own digital solutions.



Training for machine operators

Liebherr offers training courses specifically tailored to the needs of your machine operators. These cover a wide range of topics from general operation up to comprehensive understanding and take place either on site or independently at special training facilities. Using simulators several operators can be trained at once.

Customer service

Your reliable service partner

The combination of customer focus, high quality, innovation and commitment ensure the highest level of service. Based on many years of experience, we offer you effective support in all matters worldwide.



Field service and technical support

Professional field engineers are on hand from the moment the machine leaves the factory and accompany it throughout its entire service life. Whether ad hoc or on a contractual basis, they have the knowledge and equipment to solve every problem. Technical advice from our service partners on site or via XpertAssist, our tried-and-tested remote service, enables immediate fault analysis and offers the best possible support. In order to provide optimum service around the world, continuous improvement and expansion of the service network is one of our most fundamental commitments.

Parts and service products

Liebherr original parts are optimally suited to Liebherr machines and fulfil the highest quality standards and so increase productivity and value retention. The availability of cost-effective new parts is ensured over the lifetime of your machine. A wide range of products that makes your daily tasks easier is also available.

All parts and products can be viewed and ordered online to provide round-the-clock service.

Remote service XpertAssist

With our XpertAssist remote service, we offer first-class technical support that is optimised for routine maintenance, thorough machine diagnostics or rapid problem solving, regardless of location. It comprises several services that can be used either individually or in combination. Remote access to the machine and engine control gives you the best possible support and increased efficiency when servicing is required.



Parts Assistant

Our new Parts Assistant offers you a comprehensive solution for the coordination of your service materials. In future, parts can be identified using image recognition, QR codes or text searches. You are automatically notified of service intervals and a list of the required materials is provided. The parts can then be ordered conveniently and easily online.



Further
information



Deep foundation methods



Download brochure

Liebherr-Werk Nenzing GmbH • Dr. Hans Liebherr Str. 1 • 6710 Nenzing, Austria
Phone +43 50809 41-473 • Fax +43 50809 41-499 • foundation.equipment@liebherr.com
facebook.com/LiebherrConstruction • www.liebherr.com