

FDBI36S

36"Counter Depth 4-Door French Door Refrigerator

◆ Plus Series



Key Features

DuoCooling: Uses two completely separate refrigeration circuits to ensure no air is exchanged between the refrigerator and freezer compartments.

InfinitySpring is a source of fresh, cool drinking water in your kitchen. The water dispenser enables drip-free water dispensing and provides fresh, cold water.

BioFresh creates the perfect climate for all: fruit and vegetables as well as meat and dairy stay fresh for up to 5x longer.

FlexDoorSystem enables smooth, quiet door operation—even independently—while a precision sealing system ensures an airtight closure for improved energy efficiency.

Accessories

9882460	FreshAir charcoal filter
9883057	Water filter



Energy Consumption (kWh/y)	488
Estimated Yearly Energy Cost in US \$*	68
Sound rating dB(A)**	39
Total Capacity cu.ft. (l)	20.7 (585)
Refrigerator Capacity cu.ft. (l)	9 (254)
BioFresh Capacity cu.ft. (l)	3.5 (100)
Freezer Capacity cu.ft. (l)	8.2 (231)
Cooling Technology	DuoCooling
Air circulating system	PowerCooling with FreshAir activated charcoal filter
Defrost Type	Automatic
Control	2.4" TFT color display, Touch & Swipe display
FlexDoorSystem	Yes
SoftSystem	Yes
Smart Device - WiFi connected	Yes

Refrigerator

Refrigerator Temperature range °F (°C)	37 to 48°F (3 to 9°C)
Interior Light	LED ceiling lighting, LED BioFresh lighting
Number of shelves	4 Convenient height adjusted tempered glass shelves
Number of door racks	4 Gallon GlassLine racks with bottle holder and 2 Tilttable door racks
Crisper drawers	2 BioFresh drawers with SoftTelescopic, 1 Fruit & Vegetable drawer, 1 Meat & Dairy drawer
Bottle rack	Integrated

Freezer

Freezer temperature range °F (°C)	5 to -11°F (-15 to -24°C)
Freezer Light	LED lighting
Number of freezer drawers	2 + 1 internal

Water & Ice system

Water Dispenser	InfinitySpring
IceMaker	Fixed water connection
Ice cube output lbs. (kg) / 24h	2.9 (1.3)
Ice cube capacity lbs. (kg)	5.1 (2.3)
Water filter	Yes

Materials & Finishes

Door Material	SmartSteel
Handles	Recessed
MoodLight on IceCenter and Recessed handles	-
Backwall finishing	Stainless steel look

Dimensions & Weight


Product Dimensions (H / W / D) inch (cm)	71 1/8 / 35 11/16 / 29 5/16 (180.5 / 90.6 / 74.5)
Cut out Dimensions (H / W / D) inch (cm)	72 / 36 / 25 (183 / 91.4 / 63.5)
Net weight lbs. (kg)	300.7 (130.6)
Voltage V / Hz	115 / 60

* Estimated energy cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 14 cents per KWh.


** Noise output - according to EN 60704-3.

LIEBHERR

Product Dimensions



Cut-out Dimensions



Warranty: Please visit home.liebherr.com/warranty for complete warranty terms and conditions.

Liebherr reserves the right to modify product materials, specifications, and features at any time without prior notice. For the most accurate and up-to-date dimensional data and installation requirements, please refer to the product's official installation instructions before proceeding with any cabinetry cutouts or installation work.

For more information on our entire product line visit home.Liebherr.com



home.liebherr.com

