

# IRB5160

Fully Integrated Appliances

# LIEBHERR

## Refrigeration and Freezing



home.liebherr.com

| IRB5160                                |                                                   |
|----------------------------------------|---------------------------------------------------|
| Energy consumption (kWh / y)           | 280                                               |
| Estimated Yearly Energy Cost in US \$  | 39                                                |
| Sound rating dB(A)                     | 32                                                |
| Total capacity cu.ft. (l)              | 10.5                                              |
| Refrigerator capacity cu.ft. (l)       | 7.0 (198)                                         |
| BioFresh compartment cu.ft. (l)        | 3.5 (98)                                          |
| Electronic control                     | Touch & Swipe                                     |
| Defrost type                           | Automatic                                         |
| Interior light                         | LightTower                                        |
| Number of shelves                      | 8 / 7 adjustable                                  |
| Number of door racks                   | 4 + 2 VarioBoxes                                  |
| Refrigerator Temperature range °F (°C) | +37F to 48F (+3C to 9C)                           |
| Internal Water Dispenser               | Yes                                               |
| Ice maker                              | No                                                |
| Ice cube output lbs. (kg.)             | N/A                                               |
| Ice cube stock lbs. (kg.)              | N/A                                               |
| Door hinges                            | right, reversible                                 |
| Door installation                      | Door on door                                      |
| <b>Product dimensions</b>              |                                                   |
| in inch (H / W / D)                    | 69 11/16" + 11/16" / 22" / 21 1/2                 |
| in cm (H / W / D)                      | 177.2-178.88/56- 57.8/55                          |
| <b>Cut out dimensions</b>              |                                                   |
| in inch (H / W / D)                    | 69 13/16-70 7/16   22 11/16-<br>22 1/2   21 11/16 |
| in cm (H / W / D)                      | 177,2 - 178,8/56 - 57/55,0                        |
| Net weight lbs. (kg)                   | 161.2 (73.1)                                      |
| Voltage V / Hz                         | 115/60                                            |

\* Energy Cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 14 cents per KWh.

\*\* Noise output – according to EN 60704-3

(08/2026)



## Accessories

|                                                             |         |
|-------------------------------------------------------------|---------|
| <b>Door opening limitation (hinge pin)</b>                  | 9096214 |
| <b>Stainless steel panel w/ handle for 1 door appliance</b> | 9902007 |
| <b>Water filter</b>                                         | 9883057 |
| <b>FreshAir activated carbon filter</b>                     | 9882460 |

## Features

### Power Cooling

The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.

### Super Silent

Noise levels are kept to a minimum thanks to virtually silent, speed-controlled, and sound-absorbing compressors

### Infinity Spring

The seamlessly integrated, flush-mounted InfinitySpring internal water dispenser is there when you need it, and virtually invisible when you don't.

### Light Tower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.

### Bio Fresh


Preserve just-bought groceries for optimum food freshness, while sealing in flavors and maintaining essential vitamins and minerals.

### Smart Device Box

Want to be prepared for the future of the Smart Home? The SmartDeviceBox can be installed in just a few steps and will open up the whole world of digital possibilities to you today.


# Diagrams

## Product Dimensions



**Important:**  
Stated product height dimensions consider leveled feet are fully inserted.

## Frameless Dedicated Cabinet Box Dimensions



This is a fully integrated refrigerator appliance designed to be completely enclosed in a dedicated kitchen cabinet. This dedicated cabinet box must be constructed in accordance with the specified dimensions and must allow for sufficient air circulation to ensure proper operation. For more details about ventilation requirements, please refer to Design Guide.


A ventilation grill (included with the appliance) must be installed in the base of the dedicated box, for dimensions of the toe kick ventilation grill, please refer to page 45. The toe kick area of the Dedicated Cabinet Box can be recessed like the rest of the kitchen cabinets.

We recommend that the power outlet be located outside the dedicated cabinet box for easy access. Free length of the power cord is 6.9 ft. (2.1m).

3" of the cabinet needs to be surface finished as it is visible when the door is open.

The appliance water connection and inlet solenoid valve are suitable for a water pressure of up to 1Mpa (10bar). The solenoid valve is 2 1/8"(55mm) at the bottom on the back of the appliances. Water inlet recommended maximum distance is 4 ft (1200mm)

## Door Panel Dimensions



Custom panels should be at least 5/8"(16mm) and a maximum of 3/4"(19mm) thick and they should cover the front of the dedicated cabinet box.

For the exact size and design method, please refer to Design Guide.

Panel and handle max weight is 57 lbs. (26kg).

If using a "shaker style" panel that undershoots the minimum panel thickness, please be aware that you will need to use shorter screws than those supplied in the accessory pack.