

---

# Core Range 2026

---

## **LIEBHERR**

Refrigeration and freezing



## Tasty for longer.

---

You don't compromise when you're shopping. You look for natural ingredients, the best quality and maximum freshness. Of course, anyone who values good food wants to keep it fresh for as long as possible. That is precisely why we have developed innovative freshness technologies and improve them year after year, so your food still tastes fresh after some time in the refrigerator.





**EasyFresh. Ideal for fruit and vegetables.**

Unpackaged fruit and vegetables feel right at home here. Stored at the same temperature as the fridge compartment and sealed airtight in the safe, lettuce, for example, is still crisp and fresh after 7 days.



**BioFresh. Our all-rounder.**

The reliable BioFresh technology stores groceries at a temperature just above 0 °C, much cooler than in the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable Safe. Meat, fish and dairy products can enjoy ideal conditions in the Meat & Dairy Safe.



**BioFresh Professional with HydroBreeze. Refrigerate like the professionals.**

A cold mist that covers fruit and vegetables like a protective balm. It ensures crisp freshness and improves structure - the special wow effect for fruit and vegetables in the BioFresh Professional Safe.



**BioFresh Professional with Fish & Seafood Safe. Like freshly caught fish from the market.**

Particularly delicate foods like fish and seafood are best stored in icy temperatures and at low humidity. The constant temperature of -2 °C in the Fish & Seafood Safe is therefore ideal to keep items tasting fresh for longer.



**DuoCooling. No drying out.**

Our basic technology in selected models. The two completely separate refrigeration circuits ensure that there is no air exchange between the fridge and freezer compartments. Groceries do not dry out or spread odour.



**NoFrost. No more defrosting.**

The automatic defrosting function guarantees that frozen foods remain fresh. There is no longer a need to store frozen food temporarily during manual defrosting. The constant optimal freezing remains the same without interruptions.



+10 days

+8 days

+3 days

Easy Fresh

+10 days

Specifications made in days are comparisons to the normal fridge compartment.



Bio  
Fresh

+11 days

+12 days

+40 days

+40 days

+48 days



You can find out more about the shelf life of many types of food in the BioFresh storage list online.

## Even the smallest detail deserves the utmost attention.

---

We prioritise uncompromising quality – down to the tiniest screw. And we have done so from the very start. We have been manufacturing high-quality refrigerators and freezers and selling them worldwide since 1954. However, at heart we are still a family business with deep roots in Germany. It is here that we continue to develop all our products just as before. German engineering – out of loyalty to our founder and with the knowledge built up by generations of engineers.

### Convenience for everybody.

Our new freestanding units are available in different series: Pure, Plus, Prime and Peak. But whatever series you opt for, every single Liebherr comes with uncompromising Liebherr quality. This is because even in the Pure series, every appliance comes with a wide range of features. One example is NoFrost – the automatic defrosting function. Another is our EasyFresh technology for storing fruit and vegetables. Then there is our DuoCooling feature. With two separate refrigerant circuits, it ensures that no air is exchanged between the fridge and freezer compartments. The stored groceries do not dry out and no odours are transferred.

---

 Made  
in Germany

---

---

 German  
Engineering

---





CNsda 5723 ◊ Plus series

### **Built to last.**

You can experience our quality standards in the smallest of details. For example, before a door hinge is approved by us, it must pass through at least 100,000 opening cycles. This corresponds to a usage period of more than 15 years. We also test all other functional parts to ensure that they can last just as long.

And if, contrary to expectations, a small detail no longer meets your requirements, you or our premium service partners can usually correct it quickly. Because all our appliances are extremely repair-friendly. We keep all essential spare parts in stock for well over 10 years. This practice is not just sustainable, it also saves you money on minor repairs or the purchase of a new appliance.



Magnetic door gasket ensures safe closing.

### **We don't just say it. We also guarantee it.**

During manufacturing we inspect all components of our refrigerators with great care and test them far more rigorously than required by law – and we do this for the last time just before they are packaged. It is only then that our appliances can relax a little. All of our manufacturing sites are certified in accordance with the international standards for quality ISO 9001, energy management ISO 50001 and environmental management ISO 14001. Therefore, nothing could be easier for us than to guarantee for at least two years that our products are free of material and manufacturing faults and are particularly easy to install.

Selected appliances have the extended guarantee promotion to 7 or 10 years - T&C's apply, and maybe subject to change or seasonal promotions. Selected fridge-freezers appliances come with a 10-year guarantee. And selected products come with a 5-year guarantee. Subject to terms, conditions and registration.

In short: one thing is certain – you will be able to enjoy your Liebherr for a long time.



## Our path to the future

Liebherr has established a comprehensive Corporate Responsibility strategy that defines how we work – from fair working conditions and use of resources to sustainable product design. Innovations like the BluRoX insulation, renewable energy at our sites, and spare parts availability for 15 years are part of our commitment to making a lasting impact on people, the environment, and generations to come.

For this commitment, we have received the EcoVadis Silver Medal – a globally recognised assessment of corporate responsibility.



### People and sustainable business

We value equality and provide safe, fair, long-term jobs. As a family business, we take responsibility with a view to the future – not just the next quarter.

### Recycling

We design for recyclability by using sustainable, simplified materials and more recycled content. Increasingly, our appliances are built for disassembly, enabling resource recovery and supporting our journey towards a circular economy.



### Materials

We focus on durable, safe, and lower-impact materials– including increased use of recycled steel, plastics, and bio-based foams – making recycling easier.

### Usage

Appliances run 24/7, so energy efficiency and durability matter. Many of our models are among the most efficient available, with spare parts readily available. Features like BioFresh keep food fresh for longer and help reduce waste.

### Production

We are always improving the efficiency and environmental performance of our production sites – increasing the use of green electricity, reducing emissions, monitoring water use, and avoiding harmful substances wherever possible.



### Learn more about our corporate responsibility

To get facts, figures, and background information, visit [home.liebherr.com/sustainability](https://home.liebherr.com/sustainability)





## Saving food with Liebherr

Each year around the world, roughly 1,052 million tonnes of food are thrown away<sup>1</sup>. Households account for around 60 percent of this total, with each person wasting around 132 kg annually<sup>2</sup>.

# 132 Kilograms<sup>2</sup>

The amount of food waste can be roughly broken down into the following groups<sup>2</sup>:



50%

Fresh fruit and vegetables



4%

Dairy



5%

Meat and fish



7%

Cooked and ready-made food

Food has not only emotional and financial value, but also environmental value.

Food production is responsible for<sup>3</sup>

25%

of all global greenhouse emissions and

70%

of freshwater consumption and

50%

land suitable for farming.



<sup>1</sup> UNEP Food Waste Index Report (2021)

<sup>2</sup> GfK (2021). For a two-person household in Germany

<sup>3</sup> Our World in Data (2022)



Find out more about our freshness technologies here

With our carefully considered freshness technologies and digital solutions, we help you to reduce food waste in very simple ways.

For perfect food storage, alongside the ideal temperature, optimal humidity is a decisive factor. At Liebherr, we have developed innovative freshness technologies and improve them year after year. This way, food tastes genuinely fresh even after days, and loses none of its vitamins and nutrients. For each type of fresh food, we have just the right freshness technology:

**Easy Fresh**

0 °C

**Bio Fresh**

0 °C

0 °C

**Bio Fresh Professional**

Hydro Breeze

Fish & Seafood

0 °C

0 °C

-2 °C



## Side-by-Side fridge-freezer




### BlackSteel interior

Refine your dark kitchen with our BlackSteel interior appliances. The rear wall and inner door impress with surfaces made of black stainless steel. The anti-fingerprint finish makes this resistant to fingerprints. All trims are accentuated in BlackSteel to complete a dark appearance. A Liebherr with BlackSteel interior perfectly fits into modern dark kitchens and stands out with elegance.



### BioFresh with HydroBreeze

Do you want to cool fruit and vegetables like professionals? You'll be inspired by HydroBreeze. The cold mist combined with a temperature in the safe of around 0 °C gives food that extra boost for longer shelf life. And it creates a genuine visual wow effect. HydroBreeze is activated every 90 min. for 4 seconds and for 8 seconds when the door is opened.




## XRFst 5295

Peak

←121→




### SFNstd 529i

|  |   |
|--|---|
| Energy efficiency class:               |  |
| Energy consumption year / 24 hrs:      | 199 / 0.545 kWh <sup>1</sup>  |
| Total volume <sup>2</sup> :            | 277 l   |
| Noise output / noise class:            | 34 dB(A) / B, SuperSilent   |
| Climate rating:                        | SN-T (from +10 °C to +43 °C)  |
| Door / side walls:                     | Stainless steel / SmartSteel  |
| Exterior dimensions in cm (h / w / d): | 185.5 / 59.7 / 67.5 <sup>1</sup>  |

|             |             |              |           |             |                  |              |                       |           |
|-------------|-------------|--------------|-----------|-------------|------------------|--------------|-----------------------|-----------|
| No Frost    | Super Frost | LED          | Ice Tower | Soft System | Telescopic Rails | Super Silent | Touch & Swipe Display | Space Box |
| Vario Space | Easy Open   | Smart Device |           |             |                  |              |                       |           |

### SRBstc 529i

|  |   |
|--|---|
| Energy efficiency class:               |  |
| Energy consumption year / 24 hrs:      | 108 / 0.295 kWh <sup>1</sup>  |
| Total volume <sup>2</sup> :            | 386 l   |
| Volume:                                | Fridge: 246.2 l / BioFresh compartment: 140.6 l                                       |
| Noise output / noise class:            | 34 dB(A) / B, SuperSilent   |
| Climate rating:                        | SN-T (from +10 °C to +43 °C)  |
| Door / side walls:                     | Stainless steel / SmartSteel  |
| Exterior dimensions in cm (h / w / d): | 185.5 / 59.7 / 67.5 <sup>1</sup>  |

|                        |              |            |                        |             |                 |             |                       |              |
|------------------------|--------------|------------|------------------------|-------------|-----------------|-------------|-----------------------|--------------|
| Bio Fresh Professional | Hydro Breeze | Super Cool | Glass & Steel Interior | Light Tower | Infinity Spring | Soft System | Soft-Telescopic Rails | Super Silent |
| Touch & Swipe Display  | Smart Device |            |                        |             |                 |             |                       |              |

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Side-by-Side fridge-freezer



XRFbs 5295 Δ Peak series

## Side-by-Side fridge-freezer



### BioFresh with HydroBreeze

Do you want to cool fruit and vegetables like professionals? You'll be inspired by HydroBreeze. The cold mist combined with a temperature in the safe of around 0 °C gives food that extra boost for longer shelf life. And it creates a genuine visual wow effect. HydroBreeze is activated every 90 minutes for 4 seconds and for 8 seconds when the door is opened.



### LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.




## XRCbs 5295

Peak

←120→




### SWNbsd 529i

|  |  |
|--|--|
| Energy efficiency class:               |  <sup>1</sup> |
| Energy consumption year / 24 hrs:      | 190 / 0.520 kWh <sup>1</sup>   |
| Total volume <sup>2</sup> :            | 303 l  |
| Noise output / noise class:            | 36 dB(A) / C   |
| Climate rating:                        | SN-T (from +10 °C to +43 °C)   |
| Door / side walls:                     | BlackSteel / BlackSteel  |
| Exterior dimensions in cm (h / w / d): | 185.5 / 59.7 / 67.5 <sup>1</sup>   |



### SRBbsc 529i

|  |  |
|--|--|
| Energy efficiency class:               |  <sup>1</sup> |
| Energy consumption year / 24 hrs:      | 108 / 0.295 kWh <sup>1</sup>   |
| Total volume <sup>2</sup> :            | 386 l  |
| Noise output / noise class:            | 34 dB(A) / B, SuperSilent  |
| Climate rating:                        | SN-T (from +10 °C to +43 °C)   |
| Door / side walls:                     | BlackSteel / BlackSteel  |
| Exterior dimensions in cm (h / w / d): | 185.5 / 59.7 / 67.5 <sup>1</sup>   |



<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



### SpaceBox

Accommodate the “big stuff” in your Liebherr: An XL turkey or a multi-layered ice cream cake simply needs more space. Your Liebherr has the SpaceBox for exactly that purpose: At a generous height of 250 mm, it offers lots of extra space, even for large frozen goods. Helpful for you when storing food flexibly.



### EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



## XRFsf 5220

Plus

←123→



### SFNsf 5227

|  |  |
|--|--|
| Energy efficiency class:                                     | <b>D</b> <sup>A</sup> / <sub>G</sub>   |
| Energy consumption year / 24 hrs:                            | <b>199 / 0.545 kWh<sup>1</sup></b>     |
| Total volume <sup>2</sup> :                                  | <b>277 l</b>                           |
| Noise output / noise class:                                  | <b>36 dB(A) / C</b>                    |
| Climate rating:  | <b>SN-T (from +10 °C to +43 °C)</b>    |
| Designed to operate in ambient temperatures as low as -15 °C |  |
| Door / side walls:   | <b>SteelFinish / silver</b>            |
| Exterior dimensions in cm (h / w / d):                       | <b>185.5 / 59.7 / 67.5<sup>1</sup></b> |

- No Frost
- Super Frost
- Touch Display
- Space Box
- Vario Space
- Easy Open
- Smart Device Ready

### Rsf 5220

|  |  |
|--|--|
| Energy efficiency class:               | <b>D</b> <sup>A</sup> / <sub>G</sub>   |
| Energy consumption year / 24 hrs:      | <b>98 / 0.268 kWh<sup>1</sup></b>      |
| Total volume <sup>2</sup> :            | <b>399 l</b>                           |
| Noise output / noise class:            | <b>35 dB(A) / B, SuperSilent</b>       |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>    |
| Door / side walls:                     | <b>SteelFinish / silver</b>            |
| Exterior dimensions in cm (h / w / d): | <b>185.5 / 59.7 / 67.5<sup>1</sup></b> |

- Easy Fresh
- Super Cool
- Super Silent
- Touch Display
- Smart Device Ready

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.  
You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



CBNste 8872



### BioFresh drawers

Both BioFresh drawers are mounted on telescopic rails which extend effortlessly providing easy access to and a full view of your food. The lateral LED lights ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.




### IceMaker

The IceMaker with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated water filter ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The NoFrost technology keeps the freezer constantly frost-free.



## CBNste 8872

← 91 →

|  |  |
|--|--|
| Energy efficiency class:               |             |
| Energy consumption year / 24 hrs:      | <b>328 / 0.898 kWh</b>   |
| Total volume <sup>1</sup> :            | <b>522 l</b>   |
| Volume:                                | Fridge: <b>292.2 l</b> / BioFresh compartment: <b>70.6 l</b> / Freezer compartment: <b>160 l</b> |
| Noise output / noise class:            | <b>42 dB(A) / D</b>  |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>  |
| Door / side walls:                     | <b>Stainless steel / stainless steel</b>   |
| Exterior dimensions in cm (h / w / d): | <b>202.7 / 91 / 62.5</b>   |



<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.

## Fridge-freezer



### VarioTemp

VarioTemp means you have plenty of scope when storing food in your fridge freezer. This is because you can also set the accurate temperature in the freezer compartment in a range between -2 °C and +14 °C – and therefore also use this compartment as a further cooling zone. For example, it can be used over the short term for drinks and snacks at parties – or over the long term as a cellar compartment for storing potatoes.



### EasyTwist-Ice

Whether it's a summer day or a party: Thanks to EasyTwist-Ice, you can prepare a supply of ice cubes quickly and easily – without the need for a fixed water connection. Simply fill the tank with water, let it freeze and then release the finished ice cubes with a simple twist – and you're ready to serve cool drinks. The EasyTwist-Ice is easy to clean and ensures hygienic ice cube production at all times.



← 75 →



## CBNsdc 765i

Prime

|  |   |
|--|---|
| Energy efficiency class:               |   |
| Energy consumption year / 24 hrs:      | 189 / 0.517 kWh <sup>1</sup>  |
| Total volume <sup>2</sup> :            | 423 l   |
| Volume:                                | Fridge: 216.3 l / BioFresh compartment: 68.7 l / Freezer compartment: 138 l |
| Noise output / noise class:            | 34 dB(A) / B, SuperSilent   |
| Climate rating:                        | SN-T (from +10 °C to +43 °C)  |
| Door / side walls:                     | SmartSteel / silver   |
| Exterior dimensions in cm (h / w / d): | 185.5 / 74.7 / 67.5 <sup>1</sup>  |

|             |                       |              |                       |             |              |                        |             |                |
|-------------|-----------------------|--------------|-----------------------|-------------|--------------|------------------------|-------------|----------------|
| Bio Fresh   | Duo Cooling           | No Frost     | Super Cool            | Super Frost | Vario Temp   | Glass & Steel Interior | Light Tower | Easy Twist Ice |
| Soft System | Soft-Telescopic Rails | Super Silent | Touch & Swipe Display | Vario Space | Smart Device |                        |             |                |

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



### EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



### Replaceable door seal

Do you think the door seal on your Liebherr needs to be replaced after a few years? This is very easy to do yourself. The replaceable door seal can be removed in a few simple steps – and the new seal is just as easy to insert. As a result, this part of the refrigerator is always spotless and hygienically clean.



### CNsda 5723 Plus

|  |  |
|--|--|
| <b>BLU</b><br>Performance              |  |
| Energy efficiency class:               | <b>A</b> <sup>1</sup>                                      |
| Energy consumption year / 24 hrs:      | <b>104 / 0.284 kWh<sup>1</sup></b>                         |
| Total volume <sup>2</sup> :            | <b>371 l</b>   |
| Volume:                                | Fridge: <b>267.9 l</b> / Freezer compartment: <b>103 l</b> |
| Noise output / noise class:            | <b>34 dB(A) / B, SuperSilent</b>                           |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>                        |
| Door / side walls:                     | <b>SmartSteel / silver</b>                                 |
| Exterior dimensions in cm (h / w / d): | <b>201.5 / 59.7 / 67.5<sup>1</sup></b>                     |

- Easy Fresh
  - Duo Cooling
  - No Frost
  - Super Cool
  - Super Frost
  - Easy Twist Ice
  - Super Silent
  - Touch Display
  - Vario Space
- Smart Device Ready



### CNsfd 5203 Pure

|  |  |
|--|--|
| <b>BLU</b><br>Performance              |  |
| Energy efficiency class:               | <b>D</b> <sup>1</sup>                                      |
| Energy consumption year / 24 hrs:      | <b>201 / 0.550 kWh<sup>1</sup></b>                         |
| Total volume <sup>2</sup> :            | <b>330 l</b>   |
| Volume:                                | Fridge: <b>227.1 l</b> / Freezer compartment: <b>103 l</b> |
| Noise output / noise class:            | <b>35 dB(A) / B, SuperSilent</b>                           |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>                        |
| Door / side walls:                     | <b>SteelFinish / silver</b>                                |
| Exterior dimensions in cm (h / w / d): | <b>185.5 / 59.7 / 67.5<sup>1</sup></b>                     |

- Easy Fresh
- Duo Cooling
- No Frost
- Super Cool
- Super Frost
- Super Silent
- Touch Display
- Vario Space
- Smart Device Ready

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



CUele 2831



### Bottle shelf

The bottle shelf is the practical and elegant answer for storing drinks. As many as five bottles can be chilled and stored neatly.



### LED light

The space-saving integrated LED light ensures that the whole interior of the refrigerator is evenly and harmoniously lit. With its low energy consumption, the long-lasting LED light is an environmentally friendly solution for a perfect overview of the food in the fridge.



**CUEle 2831**

|  |   |
|--|---|
| Energy efficiency class:               |   |
| Energy consumption year / 24 hrs:      | 192 / 0.526 kWh <sup>1</sup>                |
| Total volume <sup>2</sup> :            | 265 l                                       |
| Volume:                                | Fridge: 212.4 l / Freezer compartment: 54 l |
| Noise output / noise class:            | 38 dB(A) / C                                |
| Climate rating:                        | SN-ST (from +10 °C to +38 °C)               |
| Door / side walls:                     | Stainless steel look / silver               |
| Exterior dimensions in cm (h / w / d): | 161.2 / 55 / 63 <sup>1</sup>                |



**CUe 2831**

|  |   |
|--|---|
| Energy efficiency class:               |   |
| Energy consumption year / 24 hrs:      | 192 / 0.526 kWh <sup>1</sup>                |
| Total volume <sup>2</sup> :            | 265 l                                       |
| Volume:                                | Fridge: 212.4 l / Freezer compartment: 54 l |
| Noise output / noise class:            | 38 dB(A) / C                                |
| Climate rating:                        | SN-ST (from +10 °C to +38 °C)               |
| Door / side walls:                     | white / white                               |
| Exterior dimensions in cm (h / w / d): | 161.2 / 55 / 63 <sup>1</sup>                |



<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.

## Fridge and under counter fridge



### EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresher for longer.



### TouchControl

A gentle finger tap and you set your Liebherr to 3, 5, 7 or 9°C with TouchControl. So simple – and efficient, as the sleek button is integrated into the interior, creating more space for all your fresh goods.



← 60 →

**RsfD 5220**  
Plus



← 55 →

**Re 1400**  
Pure



|  |   |
|--|---|
| Energy efficiency class:               | <b>D</b> <sup>A</sup> / <sub>G</sub> <sup>1</sup> |
| Energy consumption year / 24 hrs:      | <b>98 / 0.268 kWh</b> <sup>1</sup>                |
| Total volume <sup>2</sup> :            | <b>399 l</b>                                      |
| Noise output / noise class:            | <b>35 dB(A) / B, SuperSilent</b>                  |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>               |
| Door / side walls:                     | <b>SteelFinish / silver</b>                       |
| Exterior dimensions in cm (h / w / d): | <b>185.5 / 59.7 / 67.5</b> <sup>1</sup>           |



|  |   |
|--|---|
| Energy efficiency class:               | <b>E</b> <sup>A</sup> / <sub>G</sub> <sup>1</sup> |
| Energy consumption year / 24 hrs:      | <b>90 / 0.246 kWh</b> <sup>1</sup>                |
| Total volume <sup>2</sup> :            | <b>125 l</b>                                      |
| Noise output / noise class:            | <b>35 dB(A) / B, SuperSilent</b>                  |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>               |
| Door / side walls:                     | <b>white / white</b>                              |
| Exterior dimensions in cm (h / w / d): | <b>85 / 55 / 60.7</b> <sup>1</sup>                |



<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm (BluPerformance 1.5 cm). If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



### EasyOpen

Thanks to the new EasyOpen technology, our freezers can be opened smoothly and easily at any time. Even without a handle. How do we do it? With the help of an innovative door gasket and the new BluPerformance technology module, we have managed to reduce the door-opening force by half. Space-saving, simple, convenient.




### SmartFrost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean. Freezer drawers and glass shelves made of safety glass can be removed easily.



## Fe 1404 Pure

|  |   |
|--|---|
| Energy efficiency class:                                     |  |
| Energy consumption year / 24 hrs:                            | 172 / 0.471 kWh <sup>1</sup>  |
| Total volume <sup>2</sup> :                                  | 107 l   |
| Noise output / noise class:                                  | 37 dB(A) / C  |
| Climate rating:  | SN-T (from +10 °C to +43 °C)  |
| Designed to operate in ambient temperatures as low as -15 °C |   |
| Door / side walls:   | white / white   |
| Exterior dimensions in cm (h / w / d):                       | 85 / 55 / 60.7 <sup>1</sup>   |



<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.

Fridge-freezer for integrated use



ECBNe 8872



### BioFresh drawers

Both BioFresh drawers are mounted on telescopic rails which extend effortlessly providing easy access to and a full view of your food. The lateral LED lights ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



### LED side lighting on both sides

For a quick overview of everything in the refrigerator: thanks to the LED side lighting on both sides, your food is in view at all times. The LEDs are positioned so that your large refrigerator is also illuminated with food inside it. And the LEDs integrated flush into the side walls mean that the valuable usable area is fully maintained.

Available with steel doors or cabinetry doors



**ECBNe 8872**

← 91 → 203  
↑  
↓

Fixed door / Built-in appliance for integrated use

|  |                                       |
|--|---------------------------------------|
| Energy efficiency class:   | <b>E</b> <small>A G</small>           |
| Energy consumption year / 24 hrs:  | <b>339 / 0.928 kWh</b>                |
| Total volume <sup>1</sup> :  | <b>522 l</b>                          |
| Volume: Fridge: <b>292.2 l</b> / BioFresh compartment: <b>70.6 l</b> / Freezer compartment: <b>160 l</b> |                                       |
| Noise output / noise class:  | <b>39 dB(A) / C</b>                   |
| Climate rating:  | <b>SN-T (from +10 °C to +43 °C)</b>   |
| Aperture dimensions in cm (h / w / d):   | <b>203.2-207.2 / 91.5 / min. 63.5</b> |

|           |             |          |            |             |             |           |                  |             |
|-----------|-------------|----------|------------|-------------|-------------|-----------|------------------|-------------|
| Bio Fresh | Duo Cooling | No Frost | Super Cool | Super Frost | Light Tower | Ice Maker | Flex Door System | Soft System |
|-----------|-------------|----------|------------|-------------|-------------|-----------|------------------|-------------|

<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.

## Fridge-freezers for integrated use



### XL fully integrated appliances for 194-cm recess

We are expanding our range of fully integrated fridge-freezers. Or, should we say, we're raising it. Our 194-cm-high XL fully integrated fridge-freezers fit seamlessly into high-quality kitchen designs and impress in every way: two BioFresh Safes, the highest energy efficiency in their class and a timeless, elegant design.



### LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



### ICBNci 5663

Prime

Fixed door/Built-in fridge-freezer for integrated use

|  |   |
|--|---|
| Energy efficiency class:               | <b>C</b> <small>A<sub>1</sub> B</small>   |
| Energy consumption year / 24 hrs:      | <b>162 / 0.443 kWh</b>  |
| Total volume <sup>1</sup> :            | <b>276 l</b>  |
| Volume:                                | Fridge: <b>134 l</b> / BioFresh compartment: <b>71.2 l</b> / Freezer compartment: <b>71 l</b> |
| Noise output / noise class:            | <b>33 dB(A) / B, SuperSilent</b>  |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>   |
| Aperture dimensions in cm (h / w / d): | <b>194-195 / 56-57 / min. 55</b>  |

|             |                       |              |                       |             |              |                        |             |           |
|-------------|-----------------------|--------------|-----------------------|-------------|--------------|------------------------|-------------|-----------|
| Bio Fresh   | Duo Cooling           | No Frost     | Super Cool            | Super Frost | Vario Temp   | Glass & Steel Interior | Light Tower | Ice Maker |
| Soft System | Soft-Telescopic Rails | Super Silent | Touch & Swipe Display | Vario Space | Smart Device |                        |             |           |



### ICBNdi 5163

Prime

Fixed door/Built-in fridge-freezer for integrated use

|  |   |
|--|---|
| Energy efficiency class:               | <b>D</b> <small>A<sub>1</sub> B</small>   |
| Energy consumption year / 24 hrs:      | <b>208 / 0.569 kWh</b>  |
| Total volume <sup>1</sup> :            | <b>246 l</b>  |
| Volume:                                | Fridge: <b>104.1 l</b> / BioFresh compartment: <b>71.2 l</b> / Freezer compartment: <b>71 l</b> |
| Noise output / noise class:            | <b>34 dB(A) / B, SuperSilent</b>  |
| Climate rating:                        | <b>SN-ST (from +10 °C to +38 °C)</b>  |
| Aperture dimensions in cm (h / w / d): | <b>177.2-178.8 / 56-57 / min. 55</b>  |

|             |                       |              |                       |             |              |                        |             |           |
|-------------|-----------------------|--------------|-----------------------|-------------|--------------|------------------------|-------------|-----------|
| Bio Fresh   | Duo Cooling           | No Frost     | Super Cool            | Super Frost | Vario Temp   | Glass & Steel Interior | Light Tower | Ice Maker |
| Soft System | Soft-Telescopic Rails | Super Silent | Touch & Swipe Display | Vario Space | Smart Device |                        |             |           |



### Transparent FrostSafe drawers

All transparent FrostSafe drawers are extra deep. They are designed so that all frozen foods, from a duck to a boxed pizza, will fit conveniently and neatly, and are easy to remove. Every drawer can be used for both freezing and storage, so there's no need to repack the food once it has been frozen.



### EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



**ICBa 5123**  
Plus

↑  
178  
↓

Fixed door / Built-in fridge-freezer for integrated use

|  |   |
|--|---|
| Energy efficiency class:               | <b>A</b> <small>A+ A</small>  |
| Energy consumption year / 24 hrs:      | <b>105 / 0.287 kWh</b>  |
| Total volume <sup>1</sup> :            | <b>255 l</b>  |
| Volume:                                | Fridge: <b>103.3 l</b> / BioFresh compartment: <b>70.9 l</b> / Freezer compartment: <b>81 l</b> |
| Noise output / noise class:            | <b>32 dB(A) / B, SuperSilent</b>  |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>   |
| Aperture dimensions in cm (h / w / d): | <b>177.2-178.8 / 56-57 / min. 55</b>  |

- Bio Fresh
- Duo Cooling
- Smart Frost
- Super Cool
- Super Frost
- Soft System
- Super Silent
- Touch Display
- Vario Space
- Smart Device Ready



**ICNSe 5103**  
Pure

↑  
178  
↓

Sliding door / Built-in fridge-freezer for integrated use

|  |   |
|--|---|
| Energy efficiency class:               | <b>E</b> <small>A+ A</small>                              |
| Energy consumption year / 24 hrs:      | <b>227 / 0.621 kWh</b>                                    |
| Total volume <sup>1</sup> :            | <b>253 l</b>  |
| Volume:                                | Fridge: <b>183.3 l</b> / Freezer compartment: <b>70 l</b> |
| Noise output / noise class:            | <b>34 dB(A) / B, SuperSilent</b>                          |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>                       |
| Aperture dimensions in cm (h / w / d): | <b>177.2-178.8 / 56-57 / min. 55</b>                      |

- Easy Fresh
- Duo Cooling
- No Frost
- Super Cool
- Super Frost
- Super Silent
- Touch Display
- Vario Space
- Smart Device Ready

## Fridges for integrated use



IRBci 5180 ▲ Peak series



### InfinitySpring

A source of fresh, cool drinking water in your kitchen. InfinitySpring sounds like something from a fairy tale. The water dispenser enables water dispensing and provides fresh, cold water. Simply press the panel with the carafe or glass, and enjoy the water. This enables you to save on purchasing bottles of water and to live more sustainably.



 **reddot** winner 2021  
best of the best




↑  
**178**  
↓

### IRBci 5180

Peak

Fixed door / Built-in fridge for integrated use

|  |   |
|--|---|
| Energy efficiency class:               |  |
| Energy consumption year / 24 hrs:      | <b>100 / 0.274 kWh</b>  |
| Total volume <sup>1</sup> :            | <b>296 l</b>  |
| Volume:                                | Fridge: <b>198.1 l</b> / BioFresh compartment: <b>97.9 l</b>                          |
| Noise output / noise class:            | <b>32 dB(A) / B, SuperSilent</b>  |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b>   |
| Aperture dimensions in cm (h / w / d): | <b>177.2-178.8 / 56-57 / min. 55</b>  |

|                        |              |            |                        |             |                 |             |                       |              |
|------------------------|--------------|------------|------------------------|-------------|-----------------|-------------|-----------------------|--------------|
| Bio Fresh Professional | Hydro Breeze | Super Cool | Glass & Steel Interior | Light Tower | Infinity Spring | Soft System | Soft-Telescopic Rails | Super Silent |
| Touch & Swipe Display  | Smart Device |            |                        |             |                 |             |                       |              |

<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.



### VarioBoxes

The two detachable, fridge-to-table VarioBoxes are perfect for storing ready-to-serve foods in the refrigerator. The Liebherr egg tray for 12 eggs fits perfectly in the large VarioBox. The accessories set comprises of two VarioBoxes and a robust stainless steel securing rail. VarioBoxes can be securely attached to the door interior at various levels.




### Door hinge exchange, integrated freezer compartment

Switch the doors' opening direction on your 4\* freezer compartment quickly and easily: The clever slide control means this can be done in seconds and without any manual skills. Simply slide the control on the 4\* freezer compartment right or left – that's it, done!




**IRBbi 5150**  
Prime

|   |  |
|---|--|
| Fixed door / Built-in fridge for integrated use |  |
| Energy efficiency class:                        | <b>B</b> <small>A+ G</small>                                 |
| Energy consumption year / 24 hrs:               | <b>80 / 0.219 kWh</b>  |
| Total volume <sup>1</sup> :                     | <b>296 l</b>   |
| Volume:   | Fridge: <b>197.7 l</b> / BioFresh compartment: <b>98.4 l</b> |
| Noise output / noise class:                     | <b>29 dB(A) / A, UltraSilent</b>                             |
| Climate rating:                                 | <b>SN-T (from +10 °C to +43 °C)</b>                          |
| Aperture dimensions in cm (h / w / d):          | <b>177.2-178.8 / 56-57 / min. 55</b>                         |



**IRBbi 5151**  
Prime

|   |   |
|---|---|
| Fixed door / Built-in fridge for integrated use |   |
| Energy efficiency class:                        | <b>B</b> <small>A+ G</small>  |
| Energy consumption year / 24 hrs:               | <b>104 / 0.284 kWh</b>  |
| Total volume <sup>1</sup> :                     | <b>276 l</b>  |
| Volume:   | Fridge: <b>151.3 l</b> / BioFresh compartment: <b>98.4 l</b> / Freezer compartment: <b>27 l</b> |
| Noise output / noise class:                     | <b>32 dB(A) / B, SuperSilent</b>  |
| Climate rating:                                 | <b>SN-T (from +10 °C to +43 °C)</b>   |
| Aperture dimensions in cm (h / w / d):          | <b>177.2-178.8 / 56-57 / min. 55</b>  |



## Fridges for integrated use



### SoftSystem

The stylish white SoftSystem mechanism, integrated in the door, conveniently cushions door movement to ensure extremely soft closure even when the door shelves are fully loaded. The door closes automatically from an opening angle of about 30°.



### EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



### IRBd 5120

Plus

↑  
178  
↓

Fixed door / Built-in fridge for integrated use

Energy efficiency class: **D** A B

Energy consumption year / 24 hrs: **125 / 0.342 kWh**

Total volume<sup>1</sup>: **294 l**

Volume: Fridge: **195.8 l** / BioFresh compartment: **98.2 l**

Noise output / noise class: **33 dB(A) / B, SuperSilent**

Climate rating: **SN-T (from +10 °C to +43 °C)**

Aperture dimensions in cm (h / w / d): **177.2-178.8 / 56-57 / min. 55**



### IRe 5100

Pure

↑  
178  
↓

Fixed door / Built-in fridge for integrated use

Energy efficiency class: **E** A B


Energy consumption year / 24 hrs: **114 / 0.312 kWh**

Total volume<sup>1</sup>: **308 l**

Noise output / noise class: **33 dB(A) / B, SuperSilent**

Climate rating: **SN-T (from +10 °C to +43 °C)**

Aperture dimensions in cm (h / w / d): **177.2-178.8 / 56-57 / min. 55**





### PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



### Touch display

Fingertip control: the touch display enables easy and intuitive operation of your Liebherr. All functions are clearly arranged on the display. By gently tapping a finger, for example, you can easily select the functions or check the current temperature of your refrigerator.



↑  
140  
↓

**IRd 4520**  
Plus

Fixed door / Built-in fridge for integrated use

|                                    |                                      |
|------------------------------------|--------------------------------------|
| Energy efficiency class:           | <b>D</b> <small>A+ G</small>         |
| Energy consumption year / 24 hrs:  | <b>84 / 0.230 kWh</b>                |
| Total volume <sup>1</sup> :        | <b>235 l</b>                         |
| Noise output / noise class:        | <b>33 dB(A) / B, SuperSilent</b>     |
| Climate rating:                    | <b>SN-T (from +10°C to +43°C)</b>    |
| Aperture dimensions in cm (h/w/d): | <b>139.7-141.3 / 56-57 / min. 55</b> |

- Easy Fresh
- Super Cool
- Soft System
- Super Silent
- Touch Display
- Smart Device Ready



↑  
122  
↓

**IRe 4100**  
Pure

Fixed door / Built-in fridge for integrated use

|                                    |                                      |
|------------------------------------|--------------------------------------|
| Energy efficiency class:           | <b>E</b> <small>A+ G</small>         |
| Energy consumption year / 24 hrs:  | <b>101 / 0.276 kWh</b>               |
| Total volume <sup>1</sup> :        | <b>201 l</b>                         |
| Noise output / noise class:        | <b>35 dB(A) / B, SuperSilent</b>     |
| Climate rating:                    | <b>SN-T (from +10°C to +43°C)</b>    |
| Aperture dimensions in cm (h/w/d): | <b>121.6-123.1 / 56-57 / min. 55</b> |

- Easy Fresh
- Smart Device Ready
- Touch Display
- Super Silent
- Super Cool

## Freezer for integrated use



### IceTower

You will never run out of cold drinks at your party. The IceTower, which holds 8 kg of ice cubes, makes sure of that. The ice cube scoop and the pull-out tray on telescopic rails allow easy access to the ice cubes. An extra insert tray means you can also store less ice and make room for frozen food underneath. The adjacent drawer provides storage space for frozen goods.



### Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your freezer intuitively and with ease. Simply select functions such as SuperFrost on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? Well, it then shows you the actual temperature.



### VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



Side  
by  
Side

178

## SIFNdi 5188

Peak

Fixed door / Built-in freezer for integrated use

Energy efficiency class:



Energy consumption year / 24 hrs:

190 / 0.520 kWh

Total volume<sup>1</sup>:

213 l

Noise output / noise class:

33 dB(A) / B, SuperSilent

Climate rating:

SN-T (from +10 °C to +43 °C)

Aperture dimensions in cm (h / w / d):

177.2-178.8 / 56-57 / min. 55

|              |             |     |           |             |                  |              |                       |             |
|--------------|-------------|-----|-----------|-------------|------------------|--------------|-----------------------|-------------|
| No Frost     | Super Frost | LED | Ice Tower | Soft System | Telescopic Rails | Super Silent | Touch & Swipe Display | Vario Space |
| Smart Device |             |     |           |             |                  |              |                       |             |

<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.



### Freezer drawers

The top drawer in the freezer is often a bit of a mystery because you just can't see what's up there. A simple tilting function on the drawer allows it to be angled downwards when opened. This gives you a complete overview all the time. It also makes it easier to add and remove frozen goods. And the pull-out stop ensures the compartment does not fall out.



### LED-lighting

The LED lighting is positioned above the drawers in order to save space. It ensures the best overview of your goods, saves energy and has a long life.



## SIFNe 5108

Pure



|  |                                      |
|--|--------------------------------------|
| Fixed door / Built-in freezer for integrated use |                                      |
| Energy efficiency class:                         | <b>E</b> <small>A+ G</small>         |
| Energy consumption year / 24 hrs:                | <b>237 / 0.649 kWh</b>               |
| Total volume <sup>1</sup> :                      | <b>213 l</b>                         |
| Noise output / noise class:                      | <b>33 dB(A) / B, SuperSilent</b>     |
| Climate rating:                                  | <b>SN-T (from +10 °C to +43 °C)</b>  |
| Aperture dimensions in cm (h/w/d):               | <b>177.2-178.8 / 56-57 / min. 55</b> |

- No Frost
- Super Frost
- Super Silent
- Touch Display
- Vario Space
- Smart Device Ready



## SIFNdi 4556

Prime



|  |                                      |
|--|--------------------------------------|
| Fixed door / Built-in freezer for integrated use |                                      |
| Energy efficiency class:                         | <b>D</b> <small>A+ G</small>         |
| Energy consumption year / 24 hrs:                | <b>173 / 0.474 kWh</b>               |
| Total volume <sup>1</sup> :                      | <b>156 l</b>                         |
| Noise output / noise class:                      | <b>34 dB(A) / B, SuperSilent</b>     |
| Climate rating:                                  | <b>SN-T (from +10 °C to +43 °C)</b>  |
| Aperture dimensions in cm (h/w/d):               | <b>139.7-141.3 / 56-57 / min. 55</b> |

- No Frost
- Super Frost
- LED
- Soft System
- Super Silent
- Touch & Swipe Display
- Vario Space
- Smart Device



### SuperSilent

The boundaries between the kitchen and living areas are becoming ever more blurred in modern households. This underlines the importance of particularly quiet appliances. The URPd 365i reach the ultra-quiet level of 32dB.



### SmartDevice

With the SmartDeviceBox (pre-installed in "i" models), you can adjust your appliance's settings or view status messages using your smartphone and the SmartDevice app while on the go.



### Pull-out trolley

There's no better way to see food than on smooth-running telescopic rails with self-closing and soft stop mechanisms. The two fully extendable glass pull-outs ensure that everything is stored safely and is optimally accessible.



### URPd 365i Prime

Fully extendible pull-out drawer / Built-under fridge for integrated use

|  |                                     |
|--|-------------------------------------|
| Energy efficiency class:               | <b>D</b> <small>A B</small>         |
| Energy consumption year / 24 hrs:      | <b>74 / 0.202 kWh</b>               |
| Total volume <sup>1</sup> :            | <b>124 l</b>                        |
| Noise output / noise class:            | <b>32 dB(A) / B, SuperSilent</b>    |
| Climate rating:                        | <b>SN-T (from +10 °C to +43 °C)</b> |
| Aperture dimensions in cm (h / w / d): | <b>82-88 / 60 / min. 56</b>         |



<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.



### Fruit and vegetable box /multi-purpose box

Store fresh products neatly and clearly in the practical fruit and vegetable box. There's lots of space in the multi-purpose box for small refrigerated goods. Transparent, spacious and easy to clean.

### Built-under fridges and freezers for integrated use



### VarioSpace

All freezers with NoFrost and SmartFrost feature drawers and intermediate glass shelves underneath them which can be conveniently removed. This results in VarioSpace – the practical system for extra storage space so that space can be created quickly even for larger frozen food items.




82-88

### URd 3600

Pure

Fixed door / Built-under fridge for integrated use

|                                    |                                     |
|------------------------------------|-------------------------------------|
| Energy efficiency class:           | <b>D</b> <small>A+ G</small>        |
| Energy consumption year /24 hrs:   | <b>74 / 0.202 kWh</b>               |
| Total volume <sup>1</sup> :        | <b>127 l</b>                        |
| Noise output / noise class:        | <b>34 dB(A) / B, SuperSilent</b>    |
| Climate rating:                    | <b>SN-T (from +10 °C to +43 °C)</b> |
| Aperture dimensions in cm (h/w/d): | <b>82-88 / 60 / min. 56</b>         |




86-92

### URDd 375i

Prime

Pull-out trolley / Built-under fridge for integrated use

|                                    |                                     |
|------------------------------------|-------------------------------------|
| Energy efficiency class:           | <b>D</b> <small>A+ G</small>        |
| Energy consumption year /24 hrs:   | <b>82 / 0.224 kWh</b>               |
| Total volume <sup>1</sup> :        | <b>118 l</b>                        |
| Volume:                            | Fridge compartment: <b>60.3 l</b>   |
| Noise output / noise class:        | <b>34 dB(A) / B SuperSilent</b>     |
| Climate rating:                    | <b>SN-T (from +10 °C to +43 °C)</b> |
| Aperture dimensions in cm (h/w/d): | <b>86 - 92 / 60 / min. 56.0</b>     |







### VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



### NoFrost

Liebherr's NoFrost appliances provide expert refrigeration technology to ensure long-term freshness. The food is frozen with chilled recirculating air, and any humidity is expelled. As a result, the freezer is always free of ice, and food no longer frosts over. NoFrost convenience makes defrosting a thing of the past.



**SUFNd 365i**  
Prime

Fixed door / Built-under freezer for integrated use

|                                    |                                     |
|------------------------------------|-------------------------------------|
| Energy efficiency class:           | <b>D</b> <small>A+ G</small>        |
| Energy consumption year / 24 hrs:  | <b>150 / 0.411 kWh</b>              |
| Total volume <sup>1</sup> :        | <b>74 l</b>                         |
| Noise output / noise class:        | <b>34 dB(A) / B, SuperSilent</b>    |
| Climate rating:                    | <b>SN-T (from +10 °C to +43 °C)</b> |
| Aperture dimensions in cm (h/w/d): | <b>82-88 / 60 / min. 56</b>         |



**SUFNpC 365i**  
Prime

Pull-out trolley / Built-under freezer for integrated use

|                                    |                                     |
|------------------------------------|-------------------------------------|
| Energy efficiency class:           | <b>C</b> <small>A+ G</small>        |
| Energy consumption year / 24 hrs:  | <b>120 / 0.28 kWh</b>               |
| Total volume <sup>1</sup> :        | <b>75 l</b>                         |
| Volume:                            | Freezer compartment: <b>75 l</b>    |
| Noise output / noise class:        | <b>32 dB(A) / B SuperSilent</b>     |
| Climate rating:                    | <b>SN-T (from +10 °C to +43 °C)</b> |
| Aperture dimensions in cm (h/w/d): | <b>82 - 88 / 60 / min. 56.0</b>     |



Wine fridges for integrated use



EWtd 3553 Vinidor

1 These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm). You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



### Presentation shelf

The presentation shelf is ideal for keeping open bottles at the perfect temperature and without the risk of spills.



### Wooden shelves mounted on telescopic rails

The Vinidor appliances are equipped with solid wooden shelves mounted on telescopic rails. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. The clip-on labelling system provides a quick and clear overview of your wine store.

Door requires furniture or s/steel frame & handle kit - Order no. 9901573



↑  
178  
↓

## EWTdf 3553

Vinidor

Insulated glass door / Built-in appliance with decor panel

|  |  |
|--|--|
| Energy efficiency class:               |  |
| Energy consumption year / 24 hrs:      | <b>162 / 0.443 kWh</b>   |
| Max. Bordeaux bottles 0.75 l:          | <b>80<sup>1</sup></b>  |
| Total volume <sup>2</sup> :            | <b>259 l</b>   |
| Noise output / noise class:            | <b>32 dB(A) / B, SuperSilent</b>   |
| Climate rating:                        | <b>SN-ST (from +10 °C to +38 °C)</b>   |
| Door:                                  | <b>Insulated glass door prepared for cabinet door or stainless steel front</b> |
| Aperture dimensions in cm (h / w / d): | <b>177.2-178 / 56-57 / min. 55</b>   |

|              |                    |           |            |              |                |     |             |                  |
|--------------|--------------------|-----------|------------|--------------|----------------|-----|-------------|------------------|
| 2 Zones      | Humidity Select    | Fresh Air | UV Protect | Vibrate Safe | Steel Interior | LED | Soft System | Telescopic Rails |
| Super Silent | Presentation Board |           |            |              |                |     |             |                  |

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

## Wine fridges for integrated use



### Decor options

Decor panel-ready appliances can be fitted with a kitchen front to match the kitchen plan or (as a Liebherr accessory) with a stainless steel panel and separate handle options. It can even be handle-free with the TipOpen feature.



### Touch & Swipe display

Perfect enjoyment is what our Vinidor selection wine tempering fridges are all about – which is why we designed every detail to support your moment of bliss. Like the Touch & Swipe colour display that lets you select functions intuitively by tapping and swiping and makes setting temperature almost as enjoyable as savouring the wine later on.

#### Optional accessories:

Stainless steel frame (9904931)

Premium Stainless Steel Round 586mm Handle (9904734)

Brushed Aluminium, S/S Look Handle (9901561)



82-88

### UWgbi 3682

Vinidor Selection

Fixed door / Under-worktop appliance

|  |                                      |
|--|--------------------------------------|
| Energy efficiency class:               | <b>E</b> <small>A G</small>          |
| Energy consumption year / 24 hrs:      | <b>83 / 0.227 kWh</b>                |
| Max. Bordeaux bottles 0.75 l:          | <b>32<sup>1</sup></b>                |
| Total volume <sup>2</sup> :            | <b>95 l</b>                          |
| Noise output / noise class:            | <b>32 dB(A) / B, SuperSilent</b>     |
| Climate rating:                        | <b>SN-ST (from +10 °C to +38 °C)</b> |
| Door:                                  | <b>Black insulated glass door</b>    |
| Aperture dimensions in cm (h / w / d): | <b>82-88 / 60 / min. 58</b>          |

|                  |                   |                 |                       |                 |              |                |             |             |
|------------------|-------------------|-----------------|-----------------------|-----------------|--------------|----------------|-------------|-------------|
| 2 Zones          | Temp Protect Plus | Humidity Select | Fresh Air             | UV Protect Plus | Vibrate Safe | Steel Interior | Light Tower | Soft System |
| Telescopic Rails | Tip Open          | Super Silent    | Touch & Swipe Display | Smart Device    |              |                |             |             |



82-88

### UWpri 3662

Vinidor Selection

Fixed door / Under-worktop appliance for integrated use

|  |                                      |
|--|--------------------------------------|
| Energy efficiency class:               | <b>F</b> <small>A G</small>          |
| Energy consumption year / 24 hrs:      | <b>104 / 0.284 kWh</b>               |
| Max. Bordeaux bottles 0.75 l:          | <b>32<sup>1</sup></b>                |
| Total volume <sup>2</sup> :            | <b>92 l</b>                          |
| Noise output / noise class:            | <b>34 dB(A) / B, SuperSilent</b>     |
| Climate rating:                        | <b>SN-ST (from +10 °C to +38 °C)</b> |
| Door:                                  | <b>Insulated glass door</b>          |
| Aperture dimensions in cm (h / w / d): | <b>82-88 / 60 / min. 58</b>          |

|              |                       |                 |              |                 |              |     |             |                  |
|--------------|-----------------------|-----------------|--------------|-----------------|--------------|-----|-------------|------------------|
| 2 Zones      | Temp Protect Plus     | Humidity Select | Fresh Air    | UV Protect Plus | Vibrate Safe | LED | Soft System | Telescopic Rails |
| Super Silent | Touch & Swipe Display | Door Lock       | Smart Device |                 |              |     |             |                  |

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

Something for every taste. In drinks and design.

Built-under appliance beverage fridge



FreshAir activated charcoal filter

The integrated FreshAir activated charcoal filter purifies the internal air and traps unpleasant odours. It is easy to replace and guarantees optimum air quality.



↑  
86-92  
↓

UBCgb 3731 ◊ Plus series

**UBCgb 3731**  
Plus

Door-on-door / Built-under appliance

|                                    |  |
|------------------------------------|--|
| Energy efficiency class:           | <b>B</b> <small>A+ G</small>           |
| Energy consumption year / 24 hrs:  | <b>161 / 0,441 kWh</b>                 |
| Volume:                            | Fridge compartment: <b>136 l</b>       |
| Noise output / noise class:        | <b>34 db(A) / 34 db(A) SuperSilent</b> |
| Aperture dimensions in cm (h/w/d): | <b>86 - 92 / 60 / min. 56.5</b>        |



It's nice to have options when choosing a drink – or a beverage fridge. That's why the new built-under beverage fridges by Liebherr give your customers plenty of choices for their living spaces.

The new built-under beverage fridges by Liebherr

[home.liebherr.com/beverage-fridge](http://home.liebherr.com/beverage-fridge)

## Overview of features | Refrigeration and freezing

### Freshness technologies

#### Bio Fresh Professional

BioFresh Professional offers even more flexibility for your individual food-storage needs.

#### Hydro Breeze

Cooling like a pro: Cold mist and a temperature in the safe of just over 0°C ensure a longer shelf life and create a fabulous visual effect.

#### Fish & Seafood

The Fish & Seafood safe stores fish and seafood at the optimum temperature of -2°C, just as professionally as your fishmonger.

#### Bio Fresh Plus

The advantages of BioFresh with additional controllable temperature zone -2°C, perfect for fish & seafood (freestanding appliances).

#### Bio Fresh

At a temperature just above 0°C and an ideal humidity, fruits, vegetables, meat, fish, and dairy products stay fresh much longer than in a typical fridge compartment.

#### Easy Fresh

The adjustable humidity prolongs the freshness of your fruits and vegetables.

#### Duo Cooling

Two separate controllable cooling circuits are used to independently control the fridge and freezer compartments. Prevents odour transfer and groceries drying out.

#### No Frost

Frost-free convenience.

#### Smart Frost

Much less frequent defrosting.

#### Super Frost

SuperFrost increases the cooling power for a short time – this means the temperature remains constant when adding unfrozen food.

#### Vario Temp Zone

Refrigeration or freezing? You can choose from: The VarioTempZone can be set to an accurate temperature of -18°C to -10°C and from -2°C to +5°C.

#### Vario Temp

The freezer section becomes an alternative additional cooling zone by setting an accurate temperature of between -2°C and +14°C (freestanding appliances).

#### Vario Cool Drawers

Temperatures in the drawers can be independently set between 0 and +16°C. This allows ice cold drinks and delicate foods to be stored separately.

### Design

#### Glass & Steel-look Interior

Elegant glass and stainless steel elements in the interior for special design requirements.

#### Light Tower

The LightTower concept evenly illuminates the interior while supporting the glass shelves. Flexible, space-saving, unique.

#### LED

Low heat, energy-saving and maintenance-free for optimum illumination.

### Water and ice

#### Infinity Spring

The water dispenser is flush-mounted in the left side wall of the fridge compartment, for plumbed-in connections.

#### Ice Tower

Perfect for parties: automatic IceMaker and large pizza compartment on a convenient pull-out shelf.

#### Ice Maker

Automatic IceMaker for a plumbed-in connection.

#### Ice Maker Water tank

Automatic IceMaker with a water tank, if a plumbed-in connection is not available or required.

#### Easy Twist Ice

Conjure up ice cubes quickly: Fill the tank with water, let it freeze and then release the ready-made ice cubes with a twist (selected freestanding appliances).

## Convenience and flexibility

|                                  |   |
|----------------------------------|---|
| <b>Soft System</b>               | Very soft door closing, even when fully loaded, automatically below an opening angle of 30°.  |
| <b>Soft-Telescopic Rails</b>     | Drawers on fully extendable telescopic rails with self-closing and soft stop mechanisms for convenient use.   |
| <b>Telescopic Rails</b>          | Drawers on smooth telescopic rails for convenient opening and closing, and easy removal.  |
| <b>Ultra Silent</b>              | You've probably never heard this Liebherr – simply because it's so quiet.   |
| <b>Super Silent</b>              | Shhhhh – listen carefully: Your Liebherr is so quiet you have to strain your ears to hear it.   |
| <b>Touch &amp; Swipe-Display</b> | Intuitive fridge control – simply by touching and swiping the colour display.   |
| <b>Touch-Display</b>             | A Liebherr is really simple to use with a gentle tap of a finger on the clear touch display.  |
| <b>Touch Control</b>             | The one touch control of your appliance.  |
| <b>Space Box</b>                 | For flexible food storage: At a height of 250 mm, the space box offers lots of extra room even for the really large frozen items.   |
| <b>Side by Side</b>              | With the Side-by-Side concept, fridges and freezers as well as wine fridges can be individually combined to suit personal needs.  |
| <b>Vario Space</b>               | For extra high storage space: Simply take out the individual freezer drawers and the glass horizontal dividers below and make space for extra tall frozen items.              |
| <b>Door Stop</b>                 | Keep Liebherr fresh and odour-free. Door stays open when not in use. Save time, energy, and freshness.  |
| <b>Easy Open</b>                 | EasyOpen means the freezer door can be opened multiple times in succession, conveniently and easily.  |
| <b>Frost Protect</b>             | A particular suitability to low-temperature environments allows the installation of freezers even in unheated rooms down to an ambient temperature of -15°C.                  |
| <b>Door Lock</b>                 | The mechanical door lock ensures that the contents of the refrigerator are secure at all times. The lock is flush-mounted and blends inconspicuously into the overall design. |

## Connectivity

|                           |   |
|---------------------------|---|
| <b>Smart Device</b>       | The integrated SmartDeviceBox enables you to control the appliance and make use of additional services via computers and mobile devices.                              |
| <b>Smart Device ready</b> | The SmartDeviceBox can be retro-fitted so that you can control the appliance and use additional services via computers and mobile devices. Available as an accessory. |

## Special product groups

|                 |  |
|-----------------|--|
| <b>Beverage</b> | Specially designed for the perfect cooling and presentation of beverages   |
| <b>Outdoor</b>  | Ideal for outdoor use thanks to its rust- and weatherproof materials, robust construction and high-quality components. |
| <b>Wine</b>     | Perfect conditions for fine wines with unique storage and tempering features.  |

\* Can also be used via SmartDevice / Smart app.

## Liebherr After Sales & Customer Care



### 7-Year Guarantee

Select appliances have a 7-year guarantee, covering parts and labour. If any part of the machine fails or a fault develops through normal use, it will be repaired free of charge (Subject to registration and guarantee terms and conditions).



This guarantee is granted free of charge for qualifying appliances. With our manufacturer's guarantee, you will not incur any costs for repair and service for 10 years.

For more information, registration and guarantee conditions, go to: [home.liebherr.com/guarantee](http://home.liebherr.com/guarantee)

Customer must register and install appliance as per manufacturer's instructions.

Accidental damages and consumable accessories to parts are not covered.

For further information please go to: [home.liebherr.com](http://home.liebherr.com)



### Customer Care

Our National Customer Care Centre can be contacted should you require instructions or service.

Please call 01 4600064 or you can email [appliances@naa.ie](mailto:appliances@naa.ie).

### Spare Parts Direct

To order spare parts or accessories please visit our website, call 01 4600064 or email [appliances@naa.ie](mailto:appliances@naa.ie) with the model and 9 digit service number.

The parts or accessories can be quickly despatched direct to your home.

## Liebherr's Killarney Hotels Ltd.



Ard na Sidhe Country House



The Dunloe Hotel & Gardens



The Europe Hotel & Resort

Liebherr's Killarney Hotels Ltd. owns and operates two five-star luxury hotels in Killarney, including The Europe Hotel & Resort, situated on the famous Lakes of Killarney and The Dunloe Hotel & Gardens overlooking the Gap of Dunloe. The company also owns and manages Ard na Sidhe Country House, a delightful Victorian style manor house, which is situated on the shores of Caragh Lake just outside Killorglin. The Liebherr Group has been active in Ireland since 1958, when Liebherr (Ireland) Ltd. was founded in Killarney, Co. Kerry. Initially, this company manufactured large tower cranes. During the following decades, Liebherr's portfolio in Ireland has been significantly enlarged. Today, the Liebherr Group comprises three Irish companies operating in the sectors of maritime cranes, construction machinery and hotels, which are employing a total workforce of about 1200 people.

**N.A.A. Appliances Ltd, Crosslands Business Park, Lower Ballymount Road, Dublin, D12 E292**  
**Tel.: 01 4600064**  
**[home.liebherr.com](http://home.liebherr.com)**