

Simple design.
Simply unmissable.

Freestanding appliances
in Liebherr's new DarkGrey
colour tone

An added touch of elegance for your kitchen:
The new DarkGrey colour tone (RAL 7024)
combines modern design with stylish subtlety.
The calm aesthetic adds a warm touch to
the kitchen and blends harmoniously with
materials such as wood, stone, or concrete.
The appliance becomes an elegant eye-catcher
in any tastefully designed kitchen.

For the highest standards

Discover our new XL fully integrated
appliances with 194-cm recess. Perfect for
anyone who demands the highest standards.

194

Bio
Fresh

Light
Tower

Glass &
Steel
interior

No
Frost

Soft-
Telescopic

Soft
System

Smart
Device

A
G D

ICBNd 5653 © Prime series



home.liebherr.com

Made
in Germany

Products and their details are staged for advertising purposes. Subject to technical changes. Deviations in colour are due to printing processes. The models shown are not available in all countries.

LIEBHERR

For moments to savour

Refrigeration and freezing



LIEBHERR



The front and rear fold-out pages explain
important features and are particularly
helpful – with both sides folded out – for
the product range overview from page 52.

For moments to savour.

Before you start browsing...

Take a moment to pause. Your new appliance will be your companion around the clock for many years to come. When you make such an important decision like this, it's about more than just dimensions, energy consumption, and price.

You love fresh ingredients, special moments, and quality – just like us. Our fridges and freezers are designed to make your life easier and more enjoyable.

As specialists in refrigeration and freezing, Liebherr represents the quality of German engineering and the biggest range of freestanding and fully integrated appliances on the market.

Discover the models and features that will make your everyday life easier and keep your food fresher for longer. You'll find many good reasons to choose a Liebherr on the following pages and even more online.

But even better: Experience the tangible Liebherr difference for yourself in person at your nearest Liebherr specialist retail partner!

Enjoy exploring what's on offer!

Why you should choose Liebherr

History _____ 8 Quality _____ 9 Responsibility _____ 10

For over 70 years, we've been the refrigeration specialists for high-quality fridges and freezers, and we distribute them worldwide. We are at heart a family business with our roots firmly established in Germany – German engineering, based on an enduring connection with our founder.

The quality of our products is the solid foundation for the high level of trust that customers place in the Liebherr brand. We work continuously to keep developing and optimising all our appliance components and materials.

As a family-run company, we think in terms of generations, not just business cycles – we are committed to making long-term decisions that benefit people, the planet, and our business.

Freshness technology _____ 13 Energy efficiency _____ 17 Manufacturer's guarantee _____ 19

We were pioneers in developing the BioFresh technology in 1996, and we keep improving it year after year. With our motto 'Keep Pioneering', we continue to drive innovation so we can use our freshness technologies to significantly reduce the amount of food that goes to waste.

Our appliances take top spots in the efficiency rankings, and in some cases, even outperform the highest efficiency class. This helps them protect our precious environmental resources and your wallet.

Our appliances offer the best quality and durability. For selected models, we even provide a 10-year guarantee for your peace of mind.

Features

Freshness technology _____ 13 Design _____ 20 Ergonomics _____ 23

EasyFresh _____	14	Door fronts _____	20	Telescopic rails _____	23
BioFresh _____	15	Handle options _____	20	VarioSpace _____	24
BioFresh Professional _____	15	Glass and steel look interior _____	22	VarioSafe _____	24
🌿 HydroBreeze _____	15	LightTower _____	22	VarioCool drawers _____	24
🐟 Fish & Seafood Safe _____	15	Divisible glass shelf _____	22		

Water and ice _____ 32 Freezing _____ 34 Overviews _____ 50

Water & Ice Centre _____	32	VarioTemp _____	34	Series _____	50
EasyTwist-Ice _____	33	NoFrost _____	35	Freestanding appliances	
InfinitySpring _____	33	EasyOpen _____	35	product range _____	52
IceTower _____	33	FrostProtect _____	35	Fully integrated appliances	
IceMaker _____	33	Sustainable freezing _____	36	product range _____	59
				Wine appliances product range _____	65
				SmartDevice _____	68
				Accessories _____	68

Features | Consult the front and back fold-out pages for a brief explanation

Product group



Fridge	Fridge-freezers	Side-by-side combinations	Fridge-freezers with French doors	XL fridge-freezers	Freezers	Chest freezers	Freestanding and fully integrated under counter appliances	Wine appliances
Freestanding _____ 56	Freestanding _____ 55	Freestanding _____ 30 53	Freestanding _____ 26 52	Built-in _____ 39 60	Freestanding _____ 35 58	Freestanding _____ 58	Freestanding _____ 57	Freestanding _____ 44 65
Built-in _____ 18 61	Built-in _____ 18 60	FrenchDoor _____ 38	Built-in _____ 38 59		Fully integrated _____ 62		Under counter _____ 40 63	Fully integrated _____ 67
		Built-in _____ 40 63 (SBS concept)					Beverages _____ 42 64	Under counter _____ 67
							Outdoor _____ 43 64	
							Compact Appliances _____ 66	

German engineering – then as now.

We have been manufacturing refrigerators and freezers of the highest quality and selling them worldwide since 1954. However, at heart we are still a family business with our roots firmly established in Germany. This is where we continue to develop our long-lasting products.

German engineering – from an enduring connection with our founder, and in the knowledge that engineering expertise has been pooled here for generations.



Dr.-Ing. e.h. Hans Liebherr (1915 – 1993)

Pioneering entrepreneur and visionary

With an unflinching will, Hans Liebherr developed groundbreaking inventions, and with an unmistakable instinct he developed future-oriented products. On 1st April 2015, the company founder would have turned 100.



The L 319 was Liebherr's "mobile showcase" in the 1960s. Until 1968, the specially converted bus travelled around West Germany promoting the latest refrigerators and freezers from Upper Swabia.



Main factory of Liebherr-Hausgeräte in Ochsenhausen, Baden-Württemberg, Germany


Liebherr-Hausgeräte GmbH is one of 13 product segments of the Liebherr Group. The Group is one of the largest manufacturers of construction machinery in the world. Its wide range of products is recognised in international markets for their high precision and exceptional durability.

The Domestic Appliances division employs more than 6,000 staff, developing and manufacturing a wide range of high-quality fridges and freezers for the domestic and commercial markets at its main site in Ochsenhausen (Germany) and in Lienz (Austria), Marica (Bulgaria), Kluang (Malaysia), and Chhatrapati Sambhaji Nagar (India). (Last revised: 2025)



No compromises in quality, down to the last detail

Designed in Germany, tested thoroughly and guaranteed for years: the high quality and durability of our appliances can be seen in every detail. This is why we now offer a 10-year manufacturer's guarantee on selected appliances and provide spare parts for all models produced since 1 January 2021 – for up to 15 years, covering all functional components and stockable equipment parts.





Our path to the future

Liebherr has established a comprehensive Corporate Responsibility strategy that defines how we work – from fair working conditions and use of resources to sustainable product design. Innovations like the BluRoX insulation, renewable energy at our sites, and spare parts availability for 15 years are part of our commitment to making a lasting impact on people, the environment, and generations to come.

For this commitment, we have received the EcoVadis Silver Medal – a globally recognised assessment of corporate responsibility.



People and sustainable business

We value equality and provide safe, fair, long-term jobs. As a family business, we take responsibility with a view to the future – not just the next quarter.

Recycling

We design for recyclability by using sustainable, simplified materials and more recycled content. Increasingly, our appliances are built for dis-assembly, enabling resource recovery and supporting our journey towards a circular economy.



Materials

We focus on durable, safe, and lower-impact materials– including increased use of recycled steel, plastics, and bio-based foams – making recycling easier.

Usage

Appliances run 24/7, so energy efficiency and durability matter. Many of our models are among the most efficient available, with spare parts readily available. Features like BioFresh keep food fresh for longer and help reduce waste.

Production

We are always improving the efficiency and environmental performance of our production sites – increasing the use of green electricity, reducing emissions, monitoring water use, and avoiding harmful substances wherever possible.



Learn more about our corporate responsibility

To get facts, figures, and background information, visit home.liebherr.com/sustainability





 Saving food with Liebherr


Each year around the world, roughly 1,052 million tonnes of food are thrown away¹. Households account for around 60 percent of this total, with each person wasting around 132 kg annually².

132 Kilograms²

The amount of food waste can be roughly broken down into the following groups²:



Food has not only emotional and financial value, but also environmental value.



¹ UNEP Food Waste Index Report (2021)
² GfK (2021). For a two-person household in Germany
³ Our World in Data (2022)



Find out more about our freshness technologies here

With our carefully considered freshness technologies and digital solutions, we help you to reduce food waste in very simple ways.

For perfect food storage, alongside the ideal temperature, optimal humidity is a decisive factor. At Liebherr, we have developed innovative freshness technologies and improve them year after year. This way, food tastes genuinely fresh even after days, and loses none of its vitamins and nutrients. For each type of fresh food, we have just the right freshness technology:

Easy Fresh
0 °C

Bio Fresh
0 °C

Bio Fresh Professional
0 °C, -2 °C

DuoCooling

Easy Fresh

+10 Days

+8 Days

+3 Days

+10 Days

Extended storage time compared to the fridge compartment, verified by food preservation experts at UAS Münster.



EasyFresh – ideal for fruit and vegetables

Unpackaged fruit and vegetables feel right at home here. Stored at the same temperature as the fridge compartment and sealed airtight in the safe, lettuce, for example, remains crisp and fresh after seven days.



BioFresh – our all-rounder

The reliable BioFresh technology stores groceries at a temperature of just above 0 °C, much cooler than in the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable safe. Meat, fish and dairy products can enjoy ideal conditions in the Meat & Dairy safe.



BioFresh Professional with HydroBreeze – refrigerate like a pro

A cold mist covers fruit and vegetables like a protective balm, ensuring crisp freshness and improving structure – the special wow effect for fruit and vegetables in the BioFresh Professional safe.



BioFresh Professional with Fish & Seafood Safe – like freshly caught fish from the market

Particularly delicate foods like fish and seafood are best stored in icy temperatures and at low humidity. The constant temperature of -2 °C in the Fish & Seafood safe is therefore ideal for keeping food tasting fresh for longer.



DuoCooling – no drying out

Our basic technology in all fridge-freezers. The two completely separate cooling circuits ensure that there is no exchange of air between the fridge and freezer compartments. The food neither dries out nor spreads odour.



NoFrost – No more defrosting

The automatic defrosting function guarantees that frozen food remains fresh. There is no longer a need to store frozen food temporarily during a manual defrost. The constant optimal freezing remains the same without any interruptions.



Bio Fresh

Fruit & Vegetable safe

You can find out more about the shelf life of many types of food in the BioFresh storage list online.



+12 Days

+11 Days

+40 Days


+40 Days

+48 Days

Extended storage time compared to the fridge compartment, verified by food preservation experts at UAS Münster.

Efficiency without compromise

Because they run non-stop, fridges and freezers have their greatest environmental impact during daily use – through the electricity they consume. In many households, they account for around 20 percent of total energy consumption.¹



Our fridges are real all-rounders: They combine low energy consumption with quiet operation, generous storage space, and intelligent sensors that deliver optimum cooling performance.



Energy consumption

Our appliances rank among the most energy-efficient on the market – in some cases even exceeding the highest efficiency class. That saves valuable resources and reduces energy costs over the long term.



Cooling volume

From spacious drawers to the smallest design details, our appliances make the most of every litre of cooling volume – without compromising on energy efficiency.



Noise level

Kitchens are increasingly becoming part of the living area. That's why we aim to deliver not just maximum energy efficiency, but also quieter appliances.



Refrigeration

Intelligent sensors continuously adjust cooling performance to match how the appliance is being used – keeping it efficient in everyday operation and powerful when the weekly shopping arrives.

¹Source: German Environment Agency (UBA), 2023. Based on an average household in Germany.

Our promise:
Globally unmatched
energy efficiency.



ICBa 5123 ◊ Plus series



Freshness without
compromise

Reliability and durability are not just buzzwords for us. Why? Because at Liebherr, every tiny detail must meet our demanding requirements. Every functional part is extensively and intensively tested. This continues until we are satisfied that our fridges and freezers are of the highest quality.



Secure your
10-year manufacturer's
guarantee*:



Buy

Buy your new Liebherr appliance* from a Liebherr specialist dealer by 31/12/2026.



Registration

Register your appliance within 12 months using our web form or SmartDevice app.



Enjoy

Enjoy 10 years of Liebherr manufacturer's guarantee and long-lasting freshness.



◊ Plus series

178



ICBa 5123
The first fully integrated
fridge-freezer in energy
efficiency class A



ICNb 5123
The first Liebherr fully
integrated fridge-freezer
with NoFrost in energy
efficiency class B

◊ Prime series



IRBbi 5150
The first fully integrated
fridge for a 178-cm recess
with BioFresh in energy
efficiency class B

*This guarantee is granted free of charge on all freestanding fridge-freezers in energy efficiency class A, B or C and on all fully integrated appliances in energy efficiency classes A and B. With our manufacturer's guarantee, you won't incur any repair and service costs for 10 years.

For more information, registration and guarantee conditions, go to home.liebherr.com/guarantee



To register and see the guarantee conditions, go to home.liebherr.com/guarantee

Make a statement.

The puristic design language of a Liebherr appliance catches the eye with its exceptional lines and elegant surfaces. A classic, exclusive look that allows our appliances to blend seamlessly into any modern kitchen while still standing out.



XRFsf 5245 ◊ Plus series



XRCst 5295 △ Peak series

Door fronts

You can choose from the following surfaces:

SmartSteel




SteelFinish



BlackSteel



DarkGrey



White




TerraSteel
(only with French Door)



Recessed grip

This handle does not extend into the room. The elegant recess blends in with your kitchen's sleek, handle-free design.



Handle with opening mechanism

The door handle adapts gently to your hand movement, making it particularly easy to open.



Fits perfectly.

With InteriorFit, our freestanding appliances fit into the kitchen and save space – they do not require any ventilation gap at the side facing any walls or adjacent furniture. Only the fridge door protrudes into your kitchen. Everything else is invisible.



Big interior

For all baking enthusiasts, our fully integrated appliances even provide space for a baking tray.



Drawers on telescopic rails

Easy to open and close, even when full – so that all your groceries are always in easy reach.


Tasteful inside and out

No matter how much you love the exterior of a Liebherr, at some point, you actually have to open it. So it's a good job that the interior is visually appealing as well.



Glass and steel look interior

The inner door also features elegant glass and real metal components. The precise machining, an eye for detail and the harmonious combination of materials, shapes and colours create an appealing overall appearance.



LightTower

This special lighting concept illuminates the interior evenly and supports the glass shelves. Flexible, space-saving, unique.



Divisible glass shelf

To quickly create space for tall containers, the front half of the glass shelf can be slid under the back half. This means you don't have to remove the whole glass shelf.

The features shown are dependent on the model.

A refined interior design elevates selected models, with a rear wall finished in high-quality, genuine steel to create a sleek and sophisticated backdrop inside the appliance.

This subtle yet striking detail enhances the overall interior, complementing premium kitchen environments. The result is an interior that feels considered, elevated, and a pleasure to experience every time the door is opened.



Freshness with zoom factor

Our ergonomic drawers are easy to use. They are therefore particularly easy to reach, for maximum clarity.



VarioSafe

This allows you to arrange smaller items neatly in the interior – at whatever height you like.



Flexibly chilled: separate drawers for all storage needs

The VarioCool drawers can be set independently to a temperature of between 0 and +14 °C. This allows ice-cold drinks and delicate foods to be stored in separate, individually adjustable compartments.



Flexible storage space

Extra storage space – thanks to VarioSpace: In our integrated and under counter freezers and freezer compartments, individual drawers can be removed. Perfect for storing even oversized frozen food items.



One beverage store. Two options.

The practical pull-out shelf on telescopic rails in the IRDdi 5120 is equipped with two removable bottle baskets for easy transport. It can also be loaded with a whole crate of beverages to quench your thirst.



All BioFresh safes are also very easy to open when full: The telescopic rails mean the drawers will slide gently towards you. And thanks to SoftTelescopic, the safes also close almost by themselves with just a slight push.



For the best overview

Both the GlassLine drawers and the pull-out drawer in our under counter models close conveniently and safely – thanks to SoftTelescopic with a self-closing mechanism and soft closing mechanism.



The features shown are dependent on the model.

URPd 365i Prime series

Superb, even down to the smallest detail

How would we describe our new French Door appliances? Superb, in the truest sense of the word. With maximum storage space for freshness and quality down to the finest detail, the appliances cater for your every wish.

Visually, the impressive fridge-freezers boast sophisticated design elements and features, including the MoodLight, the Water & Ice centre, and the VarioTempZone. Ample space for freshness behind the French doors – whether with EasyFresh, BioFresh or BioFresh Professional with HydroBreeze. Open the doors individually and easily thanks to our patented FlexDoorSystem. Plus, these combination appliances are available in two versions: as a French-door fridge compartment with two freezer drawers or with four French doors, one pair on the fridge and one on the freezer compartment. So 'superb' is no understatement when it comes to the new French Door appliances.



← 91 →

↑ 181 ↓



MBsddi 9558 ○ Prime series

MoodLight
The indirect lighting concept aesthetically highlights the Water & Ice Centre and the recessed grips of the freezer drawers, and can be dimmed to suit your taste.



Mood Light

Water & Ice Centre

Vario Temp Zone

Flex Door System

Bio Fresh Professional

Hydro Breeze

Glass & Steel Interior

No Frost

Soft System

Smart Device



← 91 →

↑
181
↓

Easy Fresh

Vario Temp Zone

Flex Door System

No Frost

Smart Device ready



Msd9012 ○ Pure series



FlexDoorSystem

Quiet opening and closing: With the patented FlexDoorSystem, the French doors also open and close individually very easily and securely, and the 100% tight closure saves energy.



Water & Ice Centre

The Water & Ice Centre supplies cold water, ice cubes, and crushed ice 24 hours a day. Practical: The water volume of the water dispenser can be set individually for each container size.




VarioTempZone

Maximum flexibility: The VarioTempZone can be set to the exact degree from -18 to -10 °C and from -2 to +5 °C, turning it into an extra cooling zone if required.

SmartSteel

BlackSteel

TerraSteel



Surface options

Whichever material you choose, one thing is certain: Your appliance will catch the eye.

Designed for exquisite kitchens and the highest aspirations

The generous BioFresh Professional safes, including HydroBreeze in the top safe, plenty of space in the NoFrost freezer compartment with IceMaker, and a separate wine-tempering compartment make our side-by-side fridge-freezers an elegant freshness hub in your kitchen. And thanks to InfinitySpring in the fridge compartment, chilled water is always available on tap.



2 Zones

max. 44

No Frost

Ice Maker

Bio Fresh Professional

Hydro Breeze

Infinity Spring

Glass & Steel-look Interior



SmartSteel

BlackSteel



↑
185
↓

←121→

XRCst 5295 Δ Peak series

XRCbs 5295 Δ Peak series

XRCbs 5295 Δ Peak series

Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com

Specially designed for cool drinks

With Liebherr, your guests will always be able to enjoy drinks that are perfectly chilled. This is thanks to the integrated cold water source and a never-ending supply of ice. The easy way to have constant refreshment.



Water & Ice Centre

Direct access: the Water & Ice Centre

In the door of our new fridge-freezers with french doors (see also page 26 – 29), the Water & Ice Centre provides you with plenty of cold water, ice cubes, and crushed ice 24 hours a day.



Easy Twist Ice

Ice in an instant: EasyTwist-Ice

Quickly rustle up a supply of ice cubes – without a plumbed-in connection. Simply fill the tank with water, let it freeze and then release the ice cubes with a twist. EasyTwist-Ice is easy to clean and is a feature in most of the freestanding appliances in our Pure series. Alternatively, it can also easily be added as an accessory.




Ice Tower

Enough ice for even the largest party: the IceTower

The IceTower in the freezers of our side-by-side combinations sets new standards by combining two large compartments – the automatic IceMaker for up to 8 kg of ice cubes and another spacious compartment – large enough to store a few family-sized pizzas upright, for example. And because we wanted to make this even more convenient, both of them glide in and out on a pull-out shelf with telescopic rails.

The features shown are dependent on the model.



Infinity Spring

Ice-cold water on tap with no heavy lifting

With InfinitySpring, we bring a crystal-clear, cold water source right into the heart of your kitchen, so you can always stay hydrated. Making the lugging of heavy crates and water in plastic bottles a thing of the past. This relieves the strain on your back and on our environment. Simple and sustainable.



Ice Maker

It's raining ice cubes: the IceMaker

Each day the IceMaker produces up to 130 ice cubes, which automatically drop into two drawers. When MaxIce is activated, it's even possible to speed up ice production if more guests than expected turn up. The IceMaker is connected to the fresh water pipe. If no plumbed-in connection is available, there is also a model with a water tank in the fridge compartment.



CBNsda 575i ◯ Prime series

Freezing – made easy



No Frost

Convenience of never having to defrost

There's no longer any need to store frozen food temporarily during a manual defrost, thanks to NoFrost technology. This is possible because the frozen food is frozen with cooled recirculated air, and the humidity in the air is also dissipated. This keeps the freezer compartment ice-free at all times so food is no longer covered in frost. The constant optimal freezing remains the same without any interruptions.



Easy Open

Open the door multiple times with ease: EasyOpen

Done this before? After putting all the shopping in the freezer you remember an item of food you have forgotten – and have to give the door a good pull to open it again. With your Liebherr, you don't need to do this. EasyOpen means the door can be opened multiple times, one after another, conveniently and easily.



Fridge compartment
(-2 °C to +9 °C)



Cellar compartment
(+14 °C)



Freezer compartment
(-18 °C)

VarioTemp


Versatile freshness with the freezer compartment that can also refrigerate

With VarioTemp, you can accurately set the temperature of the freezer compartment in your fridge-freezer from -2 °C to +14 °C. This means, for example, you can use this space as an extra cooling zone at parties – or as a 'cellar compartment'. Don't need the freezer compartment? Then switch it off independently of the fridge compartment and save energy and money.



When below zero is a big plus

No room for a freezer in the kitchen or other heated areas in your home? We have good news: with FrostProtect, all the relevant components are designed for temperatures as low as -15 °C, no matter what groceries you're storing. If the ambient temperature drops below 0 °C, our freezers continue working efficiently, saving as much energy and keeping your frozen food protected. This means that you can put them in unheated spaces like a garden shed or garage, giving you extra space for more important things.



Frost Protect



The features shown are dependent on the model.

It's what's inside that counts.

At first glance, the FNa 6635 looks like any other Liebherr freezer, but there's much more inside. Each component has been selected carefully to develop an appliance that not only offers optimum energy efficiency, but also has the lowest impact on the environment.



FNa 6635 ◊ Plus series

Made in Germany

Sustainable freezing revolutionised – with vacuum and volcanic rock.

Our vacuum perlite technology is an innovation that will transform refrigeration and freezing. Introducing BluRoX.



BluRoX

Made in Germany

Inner liner and insulating foam

Both the inner liner and the insulating foam contain recycled materials and materials obtained from organic sources. These reduce the environmental impact while providing the same excellent insulation performance.

Product packaging

The environmental footprint of the packaging has also been reduced without compromising safety during transport.



Side panels and door

The door and side panels are made from 100% recycled steel, the production of which generates 80% less CO₂ emissions than the production of conventional steel.

Door seal

The TPE used for the door seal combines optimum functionality, durability and good recyclability.

Our pioneering BluRoX technology features perlite, finely ground volcanic rock, in a vacuum insulation. This enables unmatched energy efficiency as well as a significant increase in the freezing volume with the same exterior dimensions. Unlike conventional insulation methods, the unique and patented BluRoX technology provides optimum thermal conductivity, which significantly reduces energy consumption and sets a new benchmark in sustainable cooling.



FNb 505i ◊ Prime series

B A ↑ G

The first hybrid model with BluRoX in the door, as well as the first NoFrost freezer (165 cm) in energy efficiency class B.





- Bio Fresh
- No Frost
- Ice Maker
- Soft System
- A+G E




ECBNe 8872



194

- Bio Fresh
- Light Tower
- Glass & Steel-look Interior
- No Frost
- Soft-Telescopic Rails
- Soft System
- Smart Device
- D A+G




ICBNd 5653 ◊ Prime series

Freshness in a French door and large door format

The extra-large, fully integrated fridge-freezers with a grey interior lining offer plenty of room for fresh produce in the fridge compartment with two BioFresh safes. There's plenty of space for frozen items in two NoFrost drawers on smooth telescopic rails, and the IceMaker produces ice cubes fully automatically. What more could you want?

For the highest standards

We are expanding our range of fully integrated fridge-freezers. Or, should we say, we're raising it – literally. Our 194 cm-tall XL fully integrated fridge-freezers fit seamlessly into high-quality kitchen designs and impress in every way: two BioFresh safes, the highest energy efficiency in their class, and a timeless, elegant design. Discover our new XL fully integrated appliances from the Pure, Plus and Prime series – perfect for anyone with the very highest aspirations.



Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com

Got a recess? How about a kitchen island? There are lots of integration options

They are easy to plan, simple to install and impressively equipped: The Liebherr under counter appliances are now available in both 82 to 88 cm and 86 to 92 cm heights, which means they fit perfectly under any work surface.

With many clever interior solutions, the compact fridges, freezers and wine fridges are real space-saving wonders. We are certain that with a wide range of models and equipment options, every customer will find exactly what they are looking for.

What's more, our side-by-side concept allows you to design your individual freshness centre. Combine a fridge with a freezer and/or wine fridge. The Liebherr technology prevents condensation, protecting the appliances and the kitchen furniture perfectly.




82-88


86-92

82-88


86-92





UWgb 3682 Vinidor Selection



SUFNd 365i Prime series



URc 3700 Pure series



Designed to suit every taste

It's nice when things just work – whatever you like to drink, and however you like to entertain. Liebherr's integrated built-under beverage fridge is designed to fit seamlessly into modern living, offering flexible storage in a beautifully considered design. Thoughtfully laid out and easy to integrate into your kitchen, it keeps your favourite drinks perfectly chilled and ready to enjoy.

86-92



UBCpr 376i ○ Prime series

Store bottles securely and in style

The sturdy metal shelf with an elegant wooden front combines functionality with an attractive design. It provides a secure hold for bottles while adding a touch of elegance to the fridge.

Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com



A companion for your barbecue.

Our outdoor built-under appliances are the ideal solution for patios, gardens or pool areas. Their robust construction and high-quality materials are designed to withstand temperatures from -10 °C to +32 °C, guaranteeing perfect performance all year round.



Easily accessible at any time

Elegant and extremely practical: The pull-out shelf made of satin-finish glass slides smoothly on rails. One-handed operation and safety stops deliver convenience and protection during use – and the satin finish makes scratches virtually invisible.



UORpr 366i ○ Prime series

Also available with solid door



Treasuring true taste.

Discover our wine fridges – and find out how you can not only store your collection under the perfect conditions, but also preserve the very essence of the wine.



Qualities that surpass even those of a wine cellar.

They not only match wine cellars in terms of the five essentials of perfect storage but surpass them, thanks to our engineering expertise. We take care of every detail.

Constant temperatures protect the character of the wine.



Temp Protect Plus

Liebherr wine fridges monitor the temperature twice over with TempProtect Plus.

The right humidity keeps corks supple, to protect the wine.



Humidity Select
Humidity Control

With HumiditySelect or HumidityControl, the humidity in Liebherr wine fridges can be individually adjusted.

Keeping out ultraviolet light protects against unwanted ageing processes in the wine.



UV Protect
UV Protect Plus

Liebherr glass door models have unique double, or even triple, anti-ultraviolet glazing.

Keeping out foreign odours stops them from spoiling the taste of the wine.



Fresh Air

The FreshAir activated charcoal filter in a Liebherr wine fridge neutralises foreign odours.

Preventing vibrations allows the wine to mature undisturbed.



Vibrate Safe

Liebherr wine fridges have a fully vibration-insulated cooling system.



SommelierBoard

A real highlight in our Vinidor Selection series! There's room to show off everything you need for decanting. The high-quality shelf made of natural beechwood comes with a stainless-steel bottle presenter, a wooden box for decanting utensils and a space for tempering wine glasses for that extra-special enjoyment.



LightTower

One of the most important design elements is the lighting. In our Vinidor Selection models, the LightTower vertical lights on each side showcase the wine collection beautifully. The lighting can be activated each time the door is opened, or remain on at all times when the dimmable presentation light is set.



Vertical recessed grip

All models in the Vinidor Selection series have a recessed vertical grip extending the entire length, allowing for ergonomic and comfortable opening from any position. Models with the optically discreet grip integrate particularly harmoniously into handle-free kitchens and living-dining areas.



FlexFit wooden shelves



The removable slats of the FlexFit wooden shelves ensure they accommodate any bottle, even magnums. Thanks to the individual placement of the trims in the frame, all bottles are stored safely.



More information about wine storage and tempering and our wine fridges, including detailed model descriptions, can be found in our Wine Special magazine, which is available from your Liebherr specialist dealer or at home.liebherr.com/wine



- 3 Zones
- Temp Protect Plus
- Flex Fit
- Humidity Select
- Super Silent
- Smart Device
- Vibrate Safe



WPgbi 7473 Vinidor Selection

With two or three separate temperature zones that can be independently set to an accurate temperature of between +5 °C and +20 °C, our wine fridges can be used in the most flexible ways. This means that red wines, white wines, and champagnes can all be stored at the same time and at the ideal temperature for drinking in one single appliance that has three temperature zones. With their temperature zones of different sizes and temperature settings that offer complete flexibility, these appliances are perfect for each wine collection.



1
Zone

WSbl 5001 GrandCru

1
Zone

Humidity
Select

Smart
Device
Ready

Single-zone wine fridges are specially designed to enable a large number of bottles to be stored and to age over time, but they can also keep a larger supply of wine at the perfect temperature for drinking. For the most energy-efficient storage without any outside influences, we recommend solid-door models. Models with a glass door are also available if you want to be able to see directly inside.

Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com



Humidity regulation

On GrandCru models, HumiditySelect allows the humidity to be adjusted to two settings: Dehumidify or humidify. GrandCru Selection models are equipped with HumidityControl. This function allows the humidity to be set as required within the range of 50% to 80% RH*. If the value falls below 50% RH, the appliance indicates this.



Neck-to-neck storage for maximum bottle capacity

A Liebherr wine storage fridge also makes it easier to organise a growing wine collection. To take full advantage of its capacity, the interior has been designed so that your wine bottles can be stored neck-to-neck on the wooden shelves. This means there is plenty of room even for ever-increasing wine collections. So feel free to keep collecting.



For a protected view inside

To minimise the effect of harmful ultraviolet light, our glass-door models are fitted with special UV-resistant insulated glass. Depending on the model, we offer UV-Protect with double glazing or UV-Protect Plus with triple anti-UV glazing for maximum protection.



FreshAir activated charcoal filter

To ensure that your wine can mature in air of the best quality, all Liebherr wine fridges have an activated charcoal filter that reliably protects wine from all kinds of odours. This means your wine will retain its pure bouquet. To make sure that it stays that way, your Liebherr will remind you every six months to change the filter, which you can easily do yourself.

*Within home environments, Such as very dry or cold cellars, we recommend supporting the system with the tailor-made water box from our range of accessories.


Freshness in many forms, sizes, and to suit every need

If you want to know more details, you will find our extensive range of fridges, freezers, and wine fridges on the following pages.



○ Pure series

The Pure series is our basic class: simple, clear and perfectly equipped to cover all essential requirements. Pure series appliances have been reduced to the basics, but are full to the brim with the highest Liebherr quality.



◇ Plus series

The Plus series builds on our Pure series and stands out with additional details. Plus here particularly means a plus in convenience. The appliances are not only first-class in their refrigeration and freezing capabilities, but they are also that little bit smarter. This means they help make lots of manual tasks a little easier.

For a clear overview – before you even view the product range

○ Pure ◇ Plus ◻ Prime △ Peak

Which appliance is right for me?

This question is not always easy to answer when you are buying a new appliance. That's why we have made it even easier for you to find your way around our range of products by dividing our fridges and freezers into four series.

◻ Prime series

The Prime series is all about class. It makes an unmistakable mark in terms of design and material. In particular, real materials are used inside the appliances. Special lighting solutions also ensure that appliances in this series have a captivating appearance.



△ Peak series

The Peak series is our top-of-the-line series. Here, the best is combined with the best. There is no compromise. Innovative Liebherr technology combines with exceptional high-end design and convenience in a class of its own. Appliances in this series are for those who want to have it all.

Freestanding appliances



MBsddi 9558 ○ Prime series

Key to series:
 ○ = Pure series
 ◇ = Plus series
 ◊ = Prime series
 △ = Peak series



CBNste 8872





MBtsdi 9528



MBbsdi 9024

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Vario Temp Zone	Water & Ice Centre	Ice Maker	Easy Twist Ice	Mood Light	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	----------	-----------------	--------------------	-----------	----------------	------------	--------------

French door fridge-freezers

203 ↑ 181 ↓	-- 91 --	CBNste 8872*	⬢	■	■	■			■			
with 2 drawers 	-- 91 --	MBsddi 9558	◊	☁		■	■	■			■	■
		MBtsdi 9528	◇		■	■	■					■
		MBbsdi 9528	◇		■	■	■					■
		MBsddi 9524	◇		■	■			■			■
with 4 doors 		MBsddi 9058	◊	☁		■	■	■				■
		MBsddi 9028	◇		■	■	■					■
		MBsddi 9024	◇		■	■	■		■			■
		MBbsdi 9024	◇		■	■	■		■			■
		Msdd 9012	○		■	■	■			■		ready

LGB

*Without BluPerformance technology
 Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com

Key to handle solutions:
¹ Handle with opening mechanism
² Recessed grip



XRCst 5295



XRCbs 5295

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	2 Zones
------------	----------------	---------------	------------------------	-----------	------------	----------	-------------	-----------	-----------	-----------------	--------------	---------

Side-by-Side fridge-freezers with BioFresh Professional / Wine

-- 120 -- ↑ 186 ↓		XRCst 5295 ¹	△	⬢			■	■		■	■	■
		SWNstd 529i		⬢					■		■	■
		SRBstc 529i		⬢	☁				■		■	■
		XRCbs 5295 ¹	△	⬢			■	■		■	■	■
		SWNbsd 529i		⬢					■		■	■
		SRBbsc 529i		⬢	☁				■		■	■



XRFbs 5295



XRCsd 5255



XRFsf 5245

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	2 Zones
------------	----------------	---------------	------------------------	-----------	------------	----------	-------------	-----------	-----------	-----------------	--------------	---------

Side-by-Side fridge-freezers with BioFresh Professional / BioFresh

-- 121 -- ↑ 186 ↓		XRFst 5295 ¹	△	⬢			■	■	■		■	■
		SFNstd 529i		⬢					■		■	■
		SRBstc 529i		⬢	☁				■		■	■
		XRFbs 5295 ¹	△	⬢			■	■		■	■	■
		SFNbsd 529i		⬢					■		■	■
		SRBbsc 529i		⬢	☁				■		■	■
		XRCsd 5255 ¹	◊	⬢			■	■		■	■	■
		SBNsdd 526i		⬢					■		■	■
		SRsdc 525i		⬢					■		■	■
-- 123 -- ↑ 186 ↓		XRFsf 5245 ²	◇	⬢			■		■			ready
		SFNsfd 5247		⬢					■			ready
		SRBsf 5220		⬢	■							ready
		XRFsf 5225 ²	◇	⬢			■					ready
		SFNsfd 5227		⬢								ready
		SRBsf 5220		⬢	■							ready

LGB

You can find the full range of efficiency ratings on page 75. According to (EU) 2017/1369 6a.

Key to handle solutions:
¹ Handle with opening mechanism
² Recessed grip



Dimensions	Model/series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	2 Zones
------------	--------------	---------------	------------------------	-----------	------------	----------	-------------	-----------	-----------	-----------------	--------------	---------

BLU Side-by-Side fridge-freezers with EasyFresh

Dimensions	Model/series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	2 Zones
123 186	XRFsf 5240² ◊											
	SFNsfd 5247	D				■		■	■			ready
	SRsfd 5220	D			■							ready
123 186	XRFsf 5220² ◊											
	SFNsfd 5227	D				■						ready
	SRsfd 5220	D			■							ready
123 186	XRFbd 5220² ◊											
	SFNbdd 5227	D				■						ready
	SRbdd 5220	D			■							ready
123 186	XRF 5220² ◊											
	SFNd 5227	D				■						ready
	SRd 5220	D			■							ready

LGB



Dimensions	Model/series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Easy Twist Ice	Infinity Spring	Smart Device
------------	--------------	---------------	------------------------	-----------	------------	----------	-------------	-----------	----------------	-----------------	--------------

BLU Fridge-freezers with BioFresh Professional / BioFresh

Dimensions	Model/series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Easy Twist Ice	Infinity Spring	Smart Device
202	-75-- CBNbsc 778i	C	■				■	■			■
	-60-- CBNstb 579i	B	■				■	■		■	■
186	CBNsda 575i	A	■				■	■			■
	CBNbdc 573i	C	■				■				■
	CBNsda 572i	A	■				■			■	■
	CBNbda 572i	A	■				■			■	■
	CBNa 572i	A	■				■			■	■
	CBNdgc 5723	C	■				■				ready
	CBNc 5723	C	■				■			■	ready
	-60-- CBNsda 5223	A	■				■			■	ready
	CBNbda 5223	A	■				■			■	ready
	CBNsf 5223	C	■				■			■	ready
CBNc 5223	C	■				■			■	ready	

BLU Fridge-freezers with EasyFresh

Dimensions	Model/series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Maker	Easy Twist Ice	Infinity Spring	Smart Device
202	-75-- CNSdd 776i	D					■	■			■
	CNsfa 7723	A	■				■	■			ready
186	-60-- CNsda 5723	A	■				■	■		■	ready
	CNbda 5723	A	■				■	■		■	ready
	CNc 5724	C	■				■	■		■	ready
	CNdgc 5703	C	■				■	■			ready
	CNsfd 5703	D					■	■			ready
	CNd 5703	D					■	■			ready
	CNsfd 5704	D					■	■			ready
	CNd 5704	D					■	■			ready
	-60-- CNsdb 5223	B	■				■	■		■	ready
	CNdgc 5203	C	■				■	■			ready
CNsfd 5203	D					■	■			ready	
CNd 5203	D					■	■			ready	
CNsfd 5204	D					■	■			ready	
CNd 5204	D					■	■			ready	

LGB



CUEle 3331



CUE 2831



CTele 2531

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Smart Frost	Soft System	Ice Maker	Easy Twist Ice	Infinity Spring	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	----------	-------------	-------------	-----------	----------------	-----------------	--------------

Fridge-freezers

181	--55--	CUEle 3331					■					
161	--55--	CUEle 2831					■					
		CUE 2831					■					
137	--55--	CUEle 2331					■					
		CUE 2331					■					

Fridge-freezers with top mounted freezer

157	--55--	CTele 2931					■					
		CTe 2931					■					
140	--55--	CTele 2531					■					
		CTe 2531					■					
124	--55--	CTele 2131					■					
		CTe 2131					■					



RBsdc 525i



RBa30 425i

A
-30%



Rd 5000

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	Smart Frost	Super Silent	Soft System	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	-------------	--------------	-------------	--------------

BLU Fridges with BioFresh Professional / BioFresh

186	--60--	RBsdc 525i					■	■	■
		RBc 5220					■		ready
126	--60--	RBa30 425i					■		■

BLU Fridges with EasyFresh

186	--60--	Rd 5220					■		ready
166	--60--	Rd 5000					■		ready
146	--60--	Rd 4600					■		ready
126	--60--	Rd 4200					■		ready

LEG

Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com



Rsdci 1620



Rdgd 1401



Rd 1200

Dimensions	Model / series	Energy rating	Easy Fresh	Smart Frost	Door Stop	Smart Device
------------	----------------	---------------	------------	-------------	-----------	--------------

Under counter fridges

85	--60--	Rsdci 1620				■	■
		Rdi 1620					■
		Rsdci 1621				■*	■
		Rdi 1621				■*	■
85	--55--	Rdgd 1400					■
		TK 14Vd00					
		Rdgd 1401				■*	
		Re 1400					■
		Re 1401				■*	
85	--50--	Rd 1200					■
		Rd 1201				■*	
		Re 1200					■

with 4 freezer compartment



FNsddi 1624



FNdi 1624



Fdgd 1404

Dimensions	Model / series	Energy rating	No Frost	Smart Frost	Frost Protect	LED	Smart Device
------------	----------------	---------------	----------	-------------	---------------	-----	--------------

Under counter freezers

85	--60--	FNsddi 1624					■
		FNdi 1624					■
		Fdi 1624					■
85	--55--	TGN 14Ve04					■
		Fdgd 1404					■
		Fd 1404					■
		Fe 1404					■

LEG

You can find the full range of efficiency ratings on page 75. According to (EU) 2017/1369 6a.



Dimensions	Model/series	Energy rating	No Frost	Telescopic Rails	Easy Open	Frost Protect	Easy Twist Ice	LED	Smart Device
------------	--------------	---------------	----------	------------------	-----------	---------------	----------------	-----	--------------

Freezers with NoFrost									
186	--70--	FNC 7227	◇	C	■	■	■	■	ready
146	--70--	FNA 6635 ¹	◇	A	■	■	■	■	ready
		FNA 6625	◇	A	■	■	■	■	ready
186	--60--	FNC 527i	△	C	■	■	■	■	■
		FNE 5207	○	E	■	■	■	■	ready
166	--60--	FNB 505i	◇	B	■	■	■	■	■
		FND 5026	◇	D	■	■	■	■	ready
146	--60--	FNB 465i	◇	B	■	■	■	■	■
		FND 4625	◇	D	■	■	■	■	ready
126	--60--	FNB 425i	◇	B	■	■	■	■	■
		FND 4224	◇	D	■	■	■	■	ready
		FNE 4204	○	E	■	■	■	■	ready



Dimensions	Model/series	Energy rating	Smart Frost	Stop Frost	Super Frost	Soft System	Frost Protect	LED
------------	--------------	---------------	-------------	------------	-------------	-------------	---------------	-----

Chest freezers								
82	--167--	CFe 2500	○	E	■	■	■	■



Fully integrated appliances

Your individual freshness centre

Combine your Liebherr fully integrated appliance with complete flexibility to suit your freshness needs. Many models can be vertically and / or horizontally combined to form an individual freshness centre, providing perfect solutions to all your storage needs.

Ask your Liebherr dealer or kitchen specialist about the Liebherr Side-by-Side concept.

SIFNDi 5178 △ Peak series | IRBbi 5150 ○ Prime series



Dimensions	Model/series	Energy rating	Bio Fresh	No Frost	Soft System	Ice Maker
------------	--------------	---------------	-----------	----------	-------------	-----------

Integrated fridge-freezers						
203	--91,5--	ECBNe 8872	◇	E	■	■

¹Special order only



Dimensions	Model/series	Energy rating	10	Bio Fresh	Easy Fresh	No Frost	Smart Frost	Soft System	Ice Maker	Smart Device
------------	--------------	---------------	----	-----------	------------	----------	-------------	-------------	-----------	--------------

Integrated fridge-freezers with BioFresh Professional / BioFresh

194	-56-57-	ICBNd 5653	⬡	D		■	■	■		ready
178	-56-57-	ICBNdi 5163	⬡	D		■	■	■	■	■
		ICBNci 5153	⬡	C		■	■	■		■
		ICBNdi 5123	◇	D		■	■	■		■
		ICBa 5123	◇	A	■	■		■	■	ready
		ICBbi 5122	◇	B	■	■	■	■		■



Integrated fridge-freezers with EasyFresh

194	-56-57-	ICNd 5603	○	D		■	■			ready
		ICNSd 5603**	○	D		■	■			ready
178	-56-57-	SICNdi 5153	⬡	D		■	■	■		■
		ICNb 5123	◇	B	■	■	■	■		ready
		ICNd 5123	◇	D		■	■	■		ready
		ICNc 5103	○	C		■	■			ready
		ICNe 5103	○	E		■	■			ready
		ICe 5103	○	E		■		■		ready
		ICSe 5103**	○	E		■		■		ready

LGB



Dimensions	Model/series	Energy rating	10	Bio Fresh	Easy Fresh	Smart Frost	Soft System	Smart Device
------------	--------------	---------------	----	-----------	------------	-------------	-------------	--------------

ⓘ Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

ⓘ For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.

Integrated fridges with BioFresh Professional / BioFresh

178	-56-57-	IRBbi 5150	⬡	B		■	■	■	■
		IRBd 5120	◇	D				■	ready
		IRBSd 5120**	◇	D					ready
140	-56-57-	IRBc 4520	◇	C				■	ready
122	-56-57-	IRBSd 4120**	◇	D				■	ready

Integrated fridges with EasyFresh

178	-56-57-	IRDdi 5120	◇	D				■	■
		IRe 5100	○	E				■	ready
		IRe 5101	○	E			■*		ready
140	-56-57-	IRd 4520	◇	D				■	ready
122	-56-57-	IRe 4100	○	E				■	ready
		IRe 4101	○	E			■*		ready
88	-56-57-	IRci 3950	⬡	C				■	■
		IRc 3920	◇	C				■	ready
		IRc 3921	◇	C			■*	■	ready
		IRe 3900	○	E				■	ready
		IRSe 3900**	○	E				■	ready
		IRSe 3901**	○	E			■*		ready

* with 4* freezer compartment

LGB

Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.



SIFNdi 5188



SIFNdi 4556



SIFNci 3954

Dimensions	Model / series	Energy rating	No Frost	Smart Frost	Soft System	Ice Maker	Ice Tower	LED	Smart Device
------------	----------------	---------------	----------	-------------	-------------	-----------	-----------	-----	--------------

Integrated freezers

178 ↓ ↑	- 56-57 →	SIFNdi 5188	△		■		■	■	■	■	
		SIFNdi 5178	△		■			■	■		
		SIFNe 5128	◇		■	■				ready	
		SIFNSe 5128**	◇		■					ready	
		SIFNe 5108	○		■					ready	
140 ↓ ↑	- 56-57 →	SIFNdi 4556	○		■	■		■	■		
		SIFNdi 4155	○		■	■		■	■		
88 ↓ ↑	- 56-57 →	SIFNci 3954	○		■	■		■	■		
		IFNd 3924	◇		■	■			ready		
		IFd 3904	○			■				ready	
		IFSd 3904**	○			■				ready	
72 ↓ ↑	- 56-57 →	IFNd 3503	○		■				ready		

LGB



URDd 375i



URPd 365i



URd 3600

Dimensions	Model / series	Energy rating	Easy Fresh	Smart Frost	Vario Cool Drawers	Soft System	Touch & Swipe-Display	Touch Control	Smart Device
------------	----------------	---------------	------------	-------------	--------------------	-------------	-----------------------	---------------	--------------

Under counter fridges

86-92 ↓ ↑	- 60 →	URDd 375i	○			■	■	■	■
		URc 3700	○					■	
		URc 3701	○			■*			■
82-88 ↓ ↑	- 60 →	URPd 365i	○			■	■		■
		URd 365i	○		■		■	■	■
		URd 3600	○						■
		URd 3601	○			■*		■	

* with 4* freezer compartment



SUFc 3703



SUFNpc 365i



SUFd 3603

Dimensions	Model / series	Energy rating	No Frost	Smart Frost	Soft System	Touch & Swipe-Display	Touch Control	LED	Smart Device
------------	----------------	---------------	----------	-------------	-------------	-----------------------	---------------	-----	--------------

Under counter freezers

86-92 ↓ ↑	- 60 →	SUFc 3703	○			■		■	
82-88 ↓ ↑	- 60 →	SUFNpc 365i	○		■		■	■	■
		SUFNd 365i	○		■		■	■	■
		SUFd 3603	○			■		■	

LGB



UBCgb 3731

Dimensions	Model/series	Energy rating	Soft System	LED	Smart Device	Beverage
		10	■	■	■	■

Integrated built-under beverage fridge

Dimensions	Model/series	Energy rating	Soft System	LED	Smart Device	Beverage
86-92 --60--	UBCgb 3731	◆ B A ****	■	■	ready	■



UORpr 366i



UORpr 365i

Dimensions	Model/series	Energy rating	Soft System	Door Lock	LED	Smart Device	Outdoor
		10	■	■	■	■	■

Integrated built-under outdoor fridges¹

Dimensions	Model/series	Energy rating	Soft System	Door Lock	LED	Smart Device	Outdoor
82-88 --60--	UORpr 366i***	◇ B A ****	■	■	■	■	■
	UORpr 365i***	◇ B A ****	■	■	■	■	■

LGB



WPgbi 7473 Vinidor Selection



WPgbi 7473



WPsd 5252



WPbsi 5052

Dimensions	Model/series	Energy rating	3 Zones	2 Zones	Glass Door	Humidity Select	UV Protect Plus	Soft System	Smart Device	Wine Bottle
------------	--------------	---------------	---------	---------	------------	-----------------	-----------------	-------------	--------------	-------------

BLU Freestanding wine fridges

201 --70--	WPgbi 7473 Vinidor Selection	F A	■		■	■	■	■	■	182
185 --60--	WPgbi 5273 Vinidor Selection	F A	■		■	■	■	■	■	104
	WPsd 5252 Vinidor	F A		■	■	■	■		ready	155
165 --60--	WPbsi 5052 Vinidor	F A		■	■	■	■	■	■	131
145 --60--	WPsd 4652 Vinidor	F A		■	■	■	■		ready	107

LGB

¹Special order only | ***décor panel ready | ****beverage and outdoor fridges correspond to EU regulation 2019/2018 for commercial appliances. Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com

*Maximum capacity of Bordeaux bottles (0.75 l) based on: H: 300.5 mm, ø: 76.1 mm. You can find the full range of efficiency ratings on page 75. According to (EU) 2017/1369 6a.



WSbli 7731



WPbli 5231



WSbl 5001

Dimensions	Model/series	Energy rating	1 Zone	Glass Door	Humidity Control	Humidity Select	UV Protect Plus	Smart Device	
------------	--------------	---------------	--------	------------	------------------	-----------------	-----------------	--------------	--

Freestanding wine fridges

204	--75--	WSbli 7731	GrandCru Selection		■		■		■	324
188	--60--	WPbli 5231	GrandCru Selection		■	■	■		■	229
168	--60--	WPbli 5031	GrandCru Selection		■	■	■		■	196
		WSbl 5001	GrandCru		■		■		ready	196
148	--60--	WPbl 4601	GrandCru		■	■	■		ready	166
128	--60--	WPbl 4201	GrandCru		■	■	■		ready	141



WKes 653




ZKes 453

Dimensions	Model/series	Energy rating	1 Zone	Glass Door	Humidity Control	Humidity Select	UV Protect	Cigar	
------------	--------------	---------------	--------	------------	------------------	-----------------	------------	-------	--

Freestanding compact appliances

61	--43--	WKes 653	GrandCru		■	■		■	■	12
		ZKes 453	Humidor			■	■		■	



Bordeaux bottle size (0.75 l)
All specifications regarding bottle capacity refer to these dimensions.

LOB



EWTgb 3583



EWTdf 2353



EWTgb 1683

Dimensions	Model/series	Energy rating	2 Zones	1 Zone	Glass Door	Humidity Select	UV Protect Plus	UV Protect	Soft System	Tip Open	Smart Device	
------------	--------------	---------------	---------	--------	------------	-----------------	-----------------	------------	-------------	----------	--------------	--

Integrated wine fridges

178	--56-57--	EWTgb 3583	Vinidor		■		■		■	■	■	83
		EWTdf 3553***	Vinidor		■		■		■	■		80
122	--56-57--	EWTgb 2383	Vinidor		■		■		■	■	■	51
		EWTdf 2353***	Vinidor		■		■		■	■		48
88	--56-57--	EWTgb 1683	Vinidor		■		■		■	■	■	33
		EWTdf 1653***	Vinidor		■		■		■	■		30



WKEgb 582



WKEes 553

Integrated wine fridges

45	--56-57--	WKEgb 582	GrandCru			■	■	■		■	■	18
		WKEes 553	GrandCru			■	■	■		■		18



UWgbi 3782



UWpri 3762



UWgb 3631

Built-under wine fridges

86-92	--60--	UWgbi 3782	Vinidor Selection		■		■	■		■	■	38
		UWpri 3782***	Vinidor Selection		■		■	■		■	■	38
		UWpri 3762***	Vinidor Selection		■		■	■		■		38
		UWpri 3761***	Vinidor Selection			■	■	■		■		44
82-88	--60--	UWgbi 3682	Vinidor Selection		■		■	■		■	■	32
		UWpri 3662***	Vinidor Selection		■		■	■		■		32
		UWgb 3632	Vinidor		■		■	■				ready 32
		UWpri 3661***	Vinidor Selection			■	■	■		■		44
		UWgb 3631	Vinidor			■	■	■				ready 44

LOB

Practical accessories for every need

Discover the versatility of the Liebherr range of accessories and make your daily life that little bit easier.



VarioSafe and bottle shelf



FlexSystem



Bottle shelf



SmartDeviceBox

You can retrofit your Liebherr with a SmartDeviceBox to connect it to the internet. The SmartDeviceBox can be installed in just a few steps and will open up the whole world of digital possibilities to you.



FreshAir activated charcoal filter

Cleans the circulating air, is easy to replace, and ensures optimum air quality.



Ice cube tray with lid

Freshness technology

- Bio Fresh Professional** BioFresh Professional offers even more flexibility for your individual food-storage needs.
- Hydro Breeze** Cooling like a pro: A cold mist and a temperature in the Fruit & Vegetable safe of just over 0 °C ensure a longer shelf life and create a fabulous visual effect.
- Fish & Seafood** The Fish & Seafood safe stores fish and seafood at the optimum temperature of -2 °C, just as professionally as your fishmonger.
- Bio Fresh** At a temperature just above 0 °C and with ideal humidity, fruits, vegetables, meat, fish, and dairy products stay fresh for much longer than they would in the standard fridge compartment.
- Easy Fresh** The adjustable humidity prolongs the freshness of your fruits and vegetables.
- No Frost** Frost-free convenience
- Smart Frost** Much less frequent defrosting
- Stop Frost** Less frequent defrosting and easier opening of the chest lid thanks to no vacuum.
- Super Frost** SuperFrost increases the cooling power for a short time – this means the temperature remains constant whenever you add any unfrozen food.
- Vario Temp Zone** Refrigeration or freezing? You can choose from: The VarioTempZone can be set to an accurate temperature between -18 °C and -10 °C or between -2 °C and +5 °C.

Convenience and flexibility

- Soft System** Very soft door closing, even when fully loaded, automatically below an opening angle of 30°.
- Easy Open** EasyOpen means the freezer door can be opened multiple times, one after another, conveniently and easily.
- Frost Protect** As the freezers are particularly suitable for low temperatures, they can also be placed in unheated rooms, down to an ambient temperature of no less than -15 °C.
- Auto Door** Unique worldwide: AutoDoor allows easy and convenient opening and closing of the door via smart speaker voice command, knocking signal, or smartphone – or simply by hand.
- Door Stop** Keep your Liebherr appliance fresh and odour-free. The door stays open when the appliance is not in use. Save time, energy, and freshness.
- Telescopic Rails** Drawers on smooth telescopic rails for convenient opening and closing, and easy removal.
- Tip Open** The glass door opens by 7 cm when tapped for easy access and full opening.

* Lots more differentiating features and detailed model descriptions can be found at home.liebherr.com

Water and ice

- Water & Ice Centre** The Water & Ice centre provides plenty of cold water, ice cubes, and crushed ice, around the clock.
- Ice Maker** Automatic IceMaker with a plumbed-in connection.
- Easy Twist Ice** Conjure up ice cubes quickly: Fill the tank with water, let it freeze and then release the ready-made ice cubes with a twist (selected freestanding appliances).
- Infinity Spring** The water dispenser is flush-mounted in the left side wall of the fridge compartment, for plumbed-in connections.
- Ice Tower** Perfect for parties: automatic IceMaker and large pizza compartment on a convenient pull-out shelf.

Design

- Mood Light** MoodLight – a highlight in your living environment: The indirect lighting concept beautifully showcases the Water & Ice-Centre and recessed grips.
- Light Tower** The lighting concept illuminates the interior evenly and supports the glass shelves – flexible, space-saving, and unique.
- LED** Low heat, energy-saving, and maintenance-free for optimum illumination.

Connectivity

- Smart Device** The SmartDeviceBox enables you to control the appliance and make use of additional services via a tablet or mobile phone.
- Smart Device ready** The SmartDeviceBox (available as an accessory) can be retrofitted so that you can control the appliance and use additional services via a tablet or mobile phone.

Ultra-efficient models

- Ultra Efficient A-30%** Even more economical¹ than appliances in the highest energy efficiency class A, which means Liebherr is setting new standards in the industry.

¹Compared to the threshold for maximum energy efficiency class A according to Regulation (EU) 2029/2016 (as of December 2023).

Series (see page 54 for an explanation)

- Pure ♦ Plus ○ Prime ▲ Peak


BLU Performance All the refrigeration technology is integrated in the appliance plinth of the freestanding BLUPerformance appliances. As a result, appliances of the same size have a considerably greater storage capacity, meaning more space for food and drinks. Energy efficiency is significantly better thanks to improved ventilation and extraction in the plinth. Plus, these appliances are quieter.



Always well connected

Almost all Liebherr appliances are either factory-equipped with a network connection module or can be retrofitted with the SmartDeviceBox.

This allows you to benefit from the many possibilities that our SmartDevice app offers and from integrating your fridges, freezers, and wine fridges into your existing smart home environment. Important status and alarm notifications are sent directly to your smartphone, for example notification via the door alarm of a fridge door being left open. Our SmartDevice app has much more to offer besides: As well as simple management and remote control of your appliances, the app also helps you with tips and tricks for your Liebherr appliance. The right accessories for each appliance, access to instruction manuals and much more can also be found here.




Wine fridges

- 1 Zone** With a constant temperature throughout the interior, adjustable between +5 °C and +20 °C.
- 2 Zones** With two temperature zones, independently and precisely adjustable between +5 °C and +20 °C.
- 3 Zones** With three temperature zones, independently and precisely adjustable between +5 °C and +20 °C.
- Glass Door** Your entire wine collection at a glance: behind tinted UV safety glass.
- Humidity Control** The humidity can be actively regulated in 5% increments between 50% and 80% RH**.
- Humidity Select** The humidity can be adjusted in two stages: Standard or High.
- UV Protect Plus** Triple protection: A tinted glass door with two layers of vacuum-deposited metal provides highly efficient protection from sunlight.
- UV Protect** Double protection: A tinted glass door with one layer of vacuum-deposited metal provides efficient protection from sunlight.
- Sommelier Board** For effective presentation and decanting: Wooden shelf with stainless steel bottle display, wooden box for decanting utensils and space for tempering wine glasses.

Our series of wine fridges:

- Vinidor | Vinidor Selection** Primarily for wine tempering
- GrandCru | GrandCru Selection** Primarily for wine storage

The current energy label for electrical appliances




- The QR code for identifying the product in EPREL (European Product Database for Energy Labelling).
- The model identifier for manual identification of the product in the EU database EPREL, using the article number, for example.
- The new efficiency scale from "A" to "G". However, "G" is only intended for wine coolers.
- The total volume* of all freezer compartments.
- The total volume* of all cold storage and refrigerator compartments.
- The noise level is now classified into classes "A" to "D".

* The term 'Volume' is taken from the current Regulation (EU) 2019/2016.
 ** Such as very dry or cold cellars, we recommend supporting the system with the tailor-made water box from our range of accessories.

Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

For models where the door hinge is factory-installed on the left or cannot be interchanged, the entry also indicates the models with a left hinge.



Our complete Liebherr product range of freestanding and fully integrated appliances with detailed product descriptions and our Liebherr specialist dealers can be found on our website – visit us at: home.liebherr.com