


**Technical data**  
**Hydraulic crawler crane**


**HS 855 HD**  
Litronic®



**LIEBHERR**

# Dimensions

## Basic machine with undercarriage



## Operating weight

The operating weight includes the basic machine with HD undercarriage, 2 main winches 250 kN including wire ropes (90 m) and 11 m main boom, consisting of A-frame, boom foot (5.5 m) and boom head (5.5 m), 26.3 t basic counterweight, 800 mm 3-web grousers and 50 t hook block.

Total weight \_\_\_\_\_ approx. 89 t

## Ground pressure

Ground bearing pressure \_\_\_\_\_ 1.04 kg/cm<sup>2</sup>

## Equipment


Main boom (No. 1311.xx) max. length \_\_\_\_\_ 68 m  
Fixed jib (No. 0806.xx) \_\_\_\_\_ 11 m - 32 m  
Modular designed equipment for operation as crane, with dragline or clamshell. For dragline operation, a rotating fairlead is fitted into the boom foot. This minimizes the rope angle to drum, which results in lower rope wear.

## Remarks

1. The lifting capacities stated are valid for lifting operation only (corresponding with crane classification according to F.E.M. 1.001, crane group A1).
2. Crane standing on firm, horizontal ground.
3. The weight of the lifting device (hoisting ropes, hook block, shackle etc.) must be deducted from the gross lifting capacity to obtain a net lifting value.
4. Additional equipment on boom (e.g. boom walkways, auxiliary jib) must be deducted to get the net lifting capacity.
5. For max. wind speed please refer to lift chart in operator's cab or manual.
6. Working radii are measured from center of swing and under load.
7. The lifting capacities are valid for 360 degrees of swing.
8. Calculation of stability under load is based on ISO 4305 Table 1 + 2, tipping angle 4°.
9. The structures are calculated according to F.E.M. 1.001 - 1998 (EN 13001-2 / 2004).


# Transport dimensions and weights

## Basic machine and boom (No. 1311.22)



\*) Including pendant ropes

## Fixed jib (No. 0806.xx)



\*) Including pendant ropes

### Basic machine

with HD undercarriage, boom foot (No. 1311.22), A-frame, 2x 250 kN winches including wire ropes (90 m), without basic counterweight

Width	3500 mm
Weight	59400 kg

### Basic machine

with boom foot (No. 1311.22), A-frame, 2x 250 kN winches including wire ropes (90 m), without basic counterweight and crawlers

Width	3500 mm
Weight	40100 kg

### Crawler

3-web grousers	800 mm
Width	915 mm
Weight	9650 kg

### Boom section (No. 1311.22) 3 m

Width	1430 mm
Weight*	470 kg

### Boom section (No. 131.22) 6 m

Width	1430 mm
Weight*	730 kg

### Boom section (No. 1311.21) 12 m

Width	1430 mm
Weight*	1260 kg

### Boom head<sup>1)</sup> (No. 1311.22)

Width	1430 mm
Weight*	1610 kg

1) Polyamide sheaves

### Fixed jib head (No. 0806.16)

Width	1140 mm
Weight	475 kg

### Fixed jib section (No. 0806.15) 3 m

Width	950 mm
Weight*	150 kg

### Fixed jib section (No. 0806.15) 6 m


Width	950 mm
Weight*	255 kg

### Fixed jib foot with A-frame (No. 0806.16)

Width	1500 mm
Weight*	1210 kg

# Transport dimensions and weights

## Counterweight



### Counterweight 6x

option **10 x**

Width	850 mm
Weight*	1500 kg

### Counterweight

**1 x**


Width	1050 mm
Weight*	17330 kg

### Carbody counterweight

option **2 x**

Width	1640 mm
Weight*	7500 kg

## Hooks



### 100 t hook block - 2 sheaves

Width	320 mm
Weight*	1200 kg

### 50 t hook block - 1 sheave

Width	400 mm
Weight*	900 kg

### 40 t hook block - 1 sheave

Width	250 mm
Weight*	515 kg

### 25 t single hook

Width	400 mm
Weight*	400 kg

### 20 t single hook

Width	350 mm
Weight*	350 kg

# Technical description



## Engine

Power rating according to ISO 9249, 450 kW (603 hp) at 1900 rpm  
Engine type ——— Liebherr D 9508 A7  
Fuel tank ——— 830 l capacity with continuous level indicator and reserve warning  
Engine complies with NRMM exhaust certification EPA / CARB Tier 3 and 97/68 EC Stage III.



## Main winches

Winch options:  
Line pull (nom. load) ——— 160 kN ——— 200 kN ——— 250 kN  
Rope diameter ——— 26 mm ——— 30 mm ——— 34 mm  
Drum diameter ——— 580 mm ——— 630 mm ——— 750 mm  
Rope speed ——— 0–99 m/min - 0–101 m/min — 0–81 m/min  
Rope capacity 1st layer - 51.9 m ——— 40.6 m ——— 38.8 m  
The winches are outstanding in their compact design and easy assembly. Clutch and braking functions on the free fall system are provided by a compact designed, low wear and maintenance-free multi-disc brake. The drag and hoist winches use pressure controlled, variable flow hydraulic motors.  
This system features sensors that automatically adjust oil flow to provide max. winch speed depending on load.  
Option:  
Auxiliary winch — 70 kN in boom foot  
Tagline winch — 30 kN with free fall



## Hydraulic system

The main pumps are operated by a distributor gearbox. Axial piston displacement pumps work in closed and open circuits supplying oil only when needed (flow control on demand). To minimize peak pressure an automatically working pressure cut-off is integrated. This spares pumps and saves energy. The hydraulic oil is cleaned through electronically controlled pressure and return filters.  
Possible contamination is signalled in the cabin. The use of synthetic environmentally friendly oils is possible. Ready made hydraulic retrofit kits are available to customize requirements e. g. powering casing oscillators, VM vibrators, hydraulic grabs, fixed leaders etc.  
Working pressure — max. 350 bar  
Oil tank capacity — 820 l



## Crawlers

The track width of the undercarriage is changed hydraulically. Propulsion through axial piston motor, hydraulically released spring loaded multi-disc brake, maintenance-free crawler tracks, hydraulic chain tensioning device.  
3-web grousers —————— 800 mm  
Drive speed —————— 0 – 1.34 km/h  
Option:  
• 2-speed hydraulic motor for higher travel speed  
• Self-assembly system, jack-up system



## Boom winch

Line pull ——— max. 105 kN  
Rope diameter ——— 20 mm  
Boom up ——— 44 sec. from 15° to 86°



## Control

The control system – developed and manufactured by Liebherr – is designed to withstand extreme temperature changes and the rough heavy duty tasks common in the construction industry. Complete machine operating data are shown on a high resolution display. The crane is equipped with proportional control for all movements, which can be carried out simultaneously.

Dragline operation: A special "Interlock" control system is an option available. It is designed for power lifting of the dragline bucket without using the drag winch brake.

On request, Liebherr also offers special custom designed control systems for free fall winches.

Operation: Left joy stick for boom winch and swing, right two directional levers for winch I and II. Crawler control is actuated with the two central foot pedals. Additionally, hand levers can be attached to the pedals.

Options:

- Special demolition control system
- MDE: Machine data recording
- PDE: Process data recording
- GSM modem



## Swing

Consists of roller bearing with external teeth for lower tooth flank pressure, fixed axial piston hydraulic motor, spring loaded and hydraulically released multi-disc holding brake, planetary gearbox and pinion. Swing speed from 0 – 4.6 rpm continuously variable, selector for 3 speed ranges to increase swing precision.

Option:

Second swing drive




## Noise emission

Noise emissions correspond with 2000/14/EC directive on noise emission by equipment used outdoors.


# Equipment (26.3 t counterweight)

## Casing oscillator and slurry wall grab

Boom 1313.22



Boom 1313.22



### Casing oscillator\*

Winch options	2 x 200 kN	2 x 250 kN
Line speed 1st layer (m/min)	0-101	0-81
Drilling diameter	2000 mm	2000 mm



\*) Load chart for duty cycle operation see page 8

### Slurry wall grab\*

Winch options	2 x 200 kN	2 x 250 kN
Line speed 1st layer (m/min)	0-101	0-81
Max. chisel weight	12 t	16 t

# Equipment (26.3 t counterweight)

## Dynamic soil compaction



Capacities in metric tons for boom lengths (21 m - 33 m)

Radius (m)	Boom length (m)				
	21	24	27	30	33
8	25	25	20	20	19
9	20	19	19	18	17

Capacities in metric tons for boom lengths (20 m - 32 m)

Radius (m)	Boom length (m)				
	20	23	26	29	32
8	25	25	20	20	19
9	20	19	19	18	17

Max. capacities in metric tons do not exceed 75% of tipping load.

All loads given are max. values and must not be exceeded. They are only permitted in 2-rope automatic operation and are valid for work on a surface with max. inclination of 1%. Lifting heights must not exceed 25 m.

# Load chart for duty cycle operation (main boom No. 1311.22)

## 26.3 t counterweight

Capacities in metric tons for boom lengths (11 m - 32 m) - with 250 kN winches

Radius (m)	Boom length (m)								Radius (m)
	11 t	14 t	17 t	20 t	23 t	26 t	29 t	32 t	
4.3				37.9					4.3
5	37.9	37.9	37.9	37.9	37.9	31.7			5
6	37.9	37.7	37.9	36.9	37.9	31.7	25.5	22.1	6
7	36.6	36.5	35.3	32.7	32.9	31.4	25.5	22.1	7
8	30.3	29.8	29.0	28.1	26.8	26.0	23.9	22.1	8
9	24.9	24.4	24.0	23.5	23.0	22.2	21.3	20.1	9
10	21.9	21.5	21.1	20.7	20.3	19.6	19.3	18.3	10
12		17.7	17.4	16.9	16.7	16.1	15.7	15.3	12
14		14.8	14.6	14.3	14.0	13.5	13.2	12.9	14
16			12.6	12.3	12.0	11.7	11.3	11.1	16
18				10.8	10.5	10.2	9.9	9.7	18
20					9.3	9.2	8.7	8.4	20
22						8.1	8.0	7.7	22
24							7.0	6.9	24
26								6.2	26
28								5.4	28
30								4.7	30

TLT 10537251 M00000 Vorab3

### Maximum capacity in duty cycle operation with standard ropes

Line pull (1st layer)	kN	160	200	250
Rope diameter	mm	26	30	34
Minimum breaking load	kN	615	846	1046
Line pull - 1-rope duty cycle operation	t	16	20	25
Line pull - 2-rope duty cycle operation <sup>1)</sup>	t	24.2	30.3	37.9

- 1) Lifting a load exceeding the line pull of one winch is only allowed if it can be ensured that each individual winch is not overloaded. When working with a mechanical 2-rope grab the total load to be lifted is limited by the line pull of one winch. Rigging and ropes are part of the load.
- 2) Max. capacities in metric tons do not exceed 75% of tipping load. Crane standing on firm, horizontal ground.


Capacities in duty cycle operation are for reference only and are not programmed in the LMI system.

All loads and counterweight configurations are max. values and must not be exceeded.

Weight of additional equipment on boom (e.g. walkways, hose drums etc.) must be deducted to get the net capacity.

# Dragline equipment (main boom No. 1311.22)

## 26.3 t counterweight



	Capacities in metric tons for boom lengths (14 m - 29 m)												counterweight 26.3 t		
	Boom length (m)														
alpha	14			17			20			23			26		
	C (m)	J (m)	t	C (m)	J (m)	t	C (m)	J (m)	t	C (m)	J (m)	t	C (m)	J (m)	t
45	11.9	11.4	17.8	14.1	13.5	14.6	16.2	15.6	12.2	18.3	17.8	10.4	20.4	19.9	8.8
40	12.7	10.4	16.5	15.0	12.4	13.7	17.3	14.3	11.4	19.6	16.2	9.5	21.9	18.2	8.0
35	13.4	9.4	15.6	15.9	11.2	12.8	18.3	12.9	10.5	20.8	14.6	8.8	23.2	16.3	7.3
30	14.0	8.4	14.8	16.6	9.9	12.0	19.2	11.4	9.8	21.8	12.9	8.2	24.4	14.4	6.9
25	14.5	7.3	14.2	17.3	8.5	11.4	20.0	9.8	9.3	22.7	11.1	7.7	25.4	12.3	6.5

Max. capacities in metric tons do not exceed 75% of tipping load.


Capacities in duty cycle operation are for reference only and are not programmed in the LMI system. The size of the bucket has to be determined according to local conditions.

## Digging diagram

- C = Radius / dumping radius
- D = Max. digging radius = approx.  $C + \frac{1}{3}$  to  $\frac{1}{2}J - K$
- E = Digging depth = approx. 40 - 50% of C
- J = Height to centre rope pulley boom head
- K = Length of dragline bucket (according to manufacturer's specification)

# Clamshell equipment (main boom No. 1311.22)

## 26.3 t counterweight



	Capacities in metric tons for boom lengths (14 m - 29 m)												counterweight 26.3 t		
	Boom length (m)														
alpha	14			17			20			23			26		
	C (m)	J (m)	t	C (m)	J (m)	t	C (m)	J (m)	t	C (m)	J (m)	t	C (m)	J (m)	t
65	8.1	14.4	29.4	9.3	17.1	22.8	10.6	19.8	19.5	11.9	22.5	16.8	13.2	25.2	14.6
60	9.1	13.7	23.9	10.6	16.3	19.8	12.1	18.9	16.8	13.6	21.5	14.4	15.1	24.1	12.5
55	10.1	13.0	21.3	11.9	15.5	17.6	13.6	18.0	14.8	15.3	20.4	12.7	17.0	22.9	10.9
50	11.1	12.3	19.3	13.0	14.6	15.9	14.9	16.9	13.3	16.9	19.1	11.4	18.8	21.4	9.7
45	11.9	11.4	17.8	14.1	13.5	14.6	16.2	15.6	12.2	18.3	17.8	10.3	20.4	19.9	8.8
40	12.7	10.4	16.5	15.0	12.4	13.6	17.3	14.3	11.2	19.6	16.2	9.4	21.9	18.2	7.9
35	13.4	9.4	15.6	15.9	11.2	12.6	18.3	12.9	10.3	20.8	14.6	8.6	23.2	16.3	7.3
30	14.0	8.4	14.8	16.6	9.9	11.8	19.2	11.4	9.6	21.8	12.9	8.0	24.4	14.4	6.8
25	14.5	7.3	14.1	17.3	8.5	11.2	20.0	9.8	9.1	22.7	11.1	7.6	25.4	12.3	6.4


Max. capacities in metric tons do not exceed 66.7% of tipping load.

Capacities in duty cycle operation are for reference only and are not programmed in the LMI system.

- C = Radius / dumping radius
- J = Height of boom head sheave centre above ground level
- K = Length of clamshell (depending on type and capacity of bucket)

# Working range - main boom (No. 1311.22) 86° - 15°

26.3 t counterweight and 15 t carbody counterweight



## Main boom configuration (Table 1 - No. 1311.xx)

Configuration for boom lengths (11 m - 68 m)

	Length	Amount of boom extensions																		
Boom foot	5.5 m	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1			
Boom section	3.0 m		1		1		1		1		1		1		1		1			
Boom section	6.0 m			1	1	2	2	3	3	2	2	3	3	2	2	3	3			
Boom section	12.0 m								1	1	1	1	2	2	2	3	3			
Boom head	5.5 m	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1			
Boom length (m)	11	14	17	20	23	26	29	32	35	38	41	44	47	50	53	56	59	62	65*	68*

\*) Additional counterweight allows self-erection of boom up to 68 m.

# Load chart for lift crane operation (main boom No. 1311.22)

## 26.3 t counterweight

Capacities in metric tons for boom lengths (11 m - 62 m) - with 250 kN winches and 26.3 t counterweight																				
Radius (m)	Boom length (m)																			Radius (m)
	11	14	17	20	23	26	29	32	35	38	41	44	47	50	53	56	59	62		
3.2				90.0															3.6	
4	84.3	86.1	83.7	77.9	72.8	68.3	64.2	60.0											4	
5	72.4	68.0	64.0	60.5	57.2	54.3	51.6	49.1	47.0	44.9	39.8	32.6							5	
6	57.2	54.3	51.7	49.2	47.0	44.9	43.0	41.1	39.6	38.1	36.6	32.6	28.7	25.2	21.9	19.5	16.2		6	
7	46.8	45.1	43.2	41.4	39.7	38.2	36.7	35.3	34.2	32.9	31.7	30.6	28.7	25.2	21.9	19.5	16.2	14.4	7	
8	38.3	38.5	37.1	35.6	34.3	33.1	31.9	30.8	29.9	28.9	27.9	27.0	26.2	25.2	21.9	19.5	16.2	14.4	8	
10	27.8	28.0	28.1	27.7	26.8	25.9	25.1	24.3	23.8	23.0	22.3	21.6	21.1	20.6	19.9	18.5	15.6	14.1	10	
11	24.3	24.5	24.6	24.6	24.1	23.3	22.6	21.9	21.5	20.9	20.3	19.7	19.3	18.7	18.2	17.5	15.1	13.5	11	
12	20.6	21.7	21.8	21.8	21.8	21.3	20.6	20.0	19.7	19.1	18.5	18.0	17.6	17.1	16.6	16.1	14.6	13.0	12	
14		17.6	17.8	17.7	17.7	17.6	17.3	16.8	16.6	16.1	15.6	15.2	14.9	14.5	14.1	13.6	13.2	12.0	14	
18			12.5	12.5	12.5	12.4	12.3	12.2	12.3	12.0	11.6	11.3	11.1	10.8	10.5	10.1	9.9	9.6	18	
20			10.7	10.7	10.7	10.6	10.5	10.6	10.5	10.2	9.9	9.8	9.4	9.1	8.8	8.7	8.4	8.4	20	
22					9.3	9.3	9.2	9.1	9.2	9.1	9.0	8.7	8.6	8.3	8.0	7.8	7.6	7.3	22	
26						7.1	7.1	7.0	7.1	7.0	6.9	6.7	6.8	6.6	6.3	6.0	6.0	5.7	26	
28							6.3	6.2	6.3	6.2	6.1	5.9	6.0	5.9	5.6	5.4	5.3	5.0	28	
32								4.8	5.0	4.9	4.8	4.6	4.7	4.6	4.4	4.2	4.2	3.9	32	
34									4.5	4.4	4.3	4.1	4.2	4.0	3.9	3.8	3.7	3.5	34	
38										3.5	3.4	3.2	3.3	3.2	3.0	2.9	2.9	2.7	38	
40											3.0	2.9	2.9	2.8	2.7	2.5	2.5	2.4	40	
44												2.2	2.3	2.2	2.0	1.9	1.9	1.8	44	
46													2.0	1.9	1.8	1.6	1.6	1.5	46	
50														1.4	1.3	1.1	1.1	1.0	50	
52																		52		

TLT 983335514 M 48668

Above load chart is for reference only. For actual lift duty please refer to load chart in operator's cab or manual.

# Load chart for lift crane operation (main boom No. 1311.22)

## 32.3 t counterweight and 15 t carbody counterweight

Capacities in metric tons for boom lengths (11 m - 68 m) - with 250 kN winches																				
32.3 t counterweight and 15 t carbody counterweight																				
Radius (m)	Boom length (m)																			Radius (m)
	11	14	20	26	29	32	35	38	41	44	47	50	53	56	59	62	65	68		
3	105.0*																		3	
4	104.5*	103.7*	94.1*	80.8	71.5	62.4													4	
5	89.9	84.4	75.1	67.6	64.3	61.2	53.7	45.8	39.8	32.6									5	
6	71.2	67.6	61.3	56.0	53.6	51.4	49.6	45.8	39.8	32.6	28.7	25.2	21.9	19.5	16.2				6	
7	58.3	56.3	51.7	47.7	45.9	44.2	42.8	41.3	39.6	32.6	28.7	25.2	21.9	19.5	16.2	14.4	12.8	11.4	7	
10	34.9	35.1	34.8	32.7	31.7	30.7	30.1	29.2	28.3	27.2	25.7	23.3	20.5	18.5	15.6	14.1	12.8	11.4	10	
11	30.6	30.8	30.9	29.5	28.6	27.8	27.3	26.5	25.7	25.0	24.3	22.3	19.7	18.0	15.1	13.5	12.2	11.1	11	
14		22.2	22.3	22.2	22.0	21.4	21.1	20.6	20.0	19.5	19.2	18.7	17.7	16.1	13.6	12.0	10.9	10.0	14	
20			13.9	13.8	13.7	13.6	13.7	13.6	13.4	13.0	12.9	12.5	12.2	11.9	11.3	10.3	9.4	8.6	20	
26				9.5	9.4	9.3	9.5	9.3	9.2	9.1	9.1	9.0	8.7	8.4	8.3	8.1	7.7	7.4	26	
28					8.4	8.3	8.5	8.3	8.2	8.1	8.1	8.0	7.9	7.6	7.5	7.2	6.9	6.7	28	
32						6.7	6.9	6.8	6.6	6.5	6.6	6.4	6.3	6.2	6.1	5.9	5.7	5.4	32	
36							5.9	5.5	5.4	5.3	5.4	5.2	5.1	5.0	5.0	4.8	4.6	4.4	36	
38								5.0	4.9	4.8	4.9	4.7	4.6	4.5	4.5	4.3	4.2	3.9	38	
40									4.5	4.3	4.4	4.3	4.1	4.0	4.0	3.9	3.7	3.5	40	
44										3.5	3.6	3.5	3.4	3.2	3.2	3.1	3.0	2.8	44	
46											3.3	3.1	3.0	2.9	2.9	2.8	2.6	2.5	46	
50												2.5	2.4	2.3	2.3	2.2	2.0	1.9	50	
55													1.7	1.7	1.6	1.4	1.3	55		
60														1.0				60		


TLT 983335514 M 48668

Above load chart is for reference only. For actual lift duty please refer to load chart in operator's cab or manual.

\*) With heavy duty boom head

# Working range - fixed jib (No. 0806.xx) 15° and 30°

Main boom 86° - 30°



**Boom configuration for boom lengths (11 m - 56 m)** — see table 1, page 10

**Fixed jib configuration for fixed jib lengths (11 m - 32 m)**

	Length	Amount of jib extensions								
		1	1	1	1	1	1	1	1	1
Fixed jib foot	5.5 m	1	1	1	1	1	1	1	1	1
Fixed jib section	3.0 m		1		1		1		1	
Fixed jib section	6.0 m			1		1	2	2	3	3
Fixed jib head	5.5 m	1	1	1	1	1	1	1	1	1
Fixed jib length (m)		11	14	17	20	23	26	29	32	

# Load chart - fixed jib (No. 0806.xx)

Offset 15°

## Main boom 11 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
5.3	27.4			
10	20.5	12.3		
12	18.4	11.2		
13	17.6	10.8	7.1	
15	16.5	10.2	6.6	4.7
16	16.0	9.9	6.4	4.6
18	15.0	9.3	6.0	4.4
19	14.4	9.1	5.8	4.3
20	13.9	8.9	5.7	4.2
28		7.1	4.6	3.7
34			4.2	3.5
40				3.3

## Main boom 20 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
6.2	25.4			
11	20.1	11.6		
14	18.2	10.5	6.9	
16	17.3	10.0	6.5	4.6
20	14.0	9.4	5.9	4.3
22	12.3	9.1	5.7	4.2
24	10.9	8.8	5.5	4.0
26	9.7	8.4	5.2	3.9
28	8.7	8.0	5.0	3.8
36		6.3	4.4	3.5
42			4.1	3.3
48				3.2

## Main boom 26 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
6.8	23.9			
11	20.1	11.2		
14	18.1	10.3	6.8	
17	16.6	9.8	6.4	4.4
20	13.7	9.5	6.1	4.3
24	10.6	9.0	5.6	4.1
28	8.4	8.5	5.2	3.9
30	7.5	8.1	5.0	3.8
32	6.8	7.3	4.9	3.7
42		4.6	4.3	3.4
48			3.7	3.2
50				3.2

## Main boom 32 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
7.5	22.0			
12	18.7	10.5		
15	17.1	9.8	6.6	
18	15.0	9.5	6.2	4.3
22	11.7	9.1	5.9	4.1
26	9.1	8.7	5.5	4.0
30	7.2	7.8	5.2	3.8
34	5.8	6.3	4.9	3.6
38	4.7	5.2	4.6	3.5
46		3.5	3.8	3.3
50			3.1	3.3
55				2.6

## Main boom 38 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
8.1	19.8			
13	16.9	9.7		
15	15.9	9.4	6.4	
18	14.3	9.1	6.1	4.2
24	10.0	8.7	5.7	4.0
28	8.0	8.2	5.4	3.8
32	6.4	6.9	5.1	3.7
36	5.1	5.6	4.8	3.6
40	4.1	4.6	4.6	3.5
44	3.3	3.8	4.0	3.4
50		2.8	3.0	3.1
55			2.3	2.5

## Main boom 44 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
8.7	17.3			
13	15.3	9.0		
16	14.1	8.6	6.1	
19	12.5	8.4	5.8	4.1
28	7.5	7.8	5.3	3.8
32	6.1	6.4	5.1	3.7
36	4.8	5.3	4.8	3.6
40	3.8	4.3	4.5	3.4
44	3.0	3.5	3.7	3.3
48	2.4	2.8	3.0	3.1
50		2.5	2.7	2.9
55			2.0	2.2

## Main boom 50 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
9.3	15.0			
14	13.2	8.1		
17	12.2	7.9	5.7	
19	11.3	7.8	5.6	3.9
24	8.9	7.5	5.3	3.8
28	7.1	7.1	5.1	3.7
32	5.7	6.0	4.9	3.6
36	4.6	4.9	4.7	3.5
40	3.7	4.0	4.1	3.4
44	2.9	3.3	3.4	3.3
48	2.2	2.6	2.8	2.9
50	2.3	2.5	2.6	

## Main boom 53 m

Radius (m)	Fixed jib length (m)			
	11	20	23	26
9.7	13.7			
14	12.1	7.8		
16	11.5	7.5	6.5	
17	11.3	7.5	6.4	5.5
24	8.6	7.1	6.2	5.2
28	6.8	6.7	5.9	5.0
32	5.4	5.8	5.7	4.8
36	4.4	4.7	4.8	4.6
40	3.5	3.8	3.9	3.9
44	2.7	3.0	3.1	3.2
48	2.1	2.4	2.5	2.6
50		2.1	2.2	2.3

## Main boom 56 m

Radius (m)	Fixed jib length (m)			
	11	14	17	
10	12.6			
12	12.0	10.4		
13	11.6	10.1	8.7	
16	10.7	9.5	8.3	
20	9.6	8.9	7.9	
24	8.3	7.9	7.4	
28	6.5	6.7	6.7	
32	5.2	5.3	5.4	
36	4.1	4.2	4.4	
40	3.2	3.3	3.5	
46	2.2	2.3	2.4	
48			2.1	

(TLT 983335514 M 48668)

Capacities in metric tons with fixed jib (No. 0806.xx) 32.3 t counterweight + 15 t carbody counterweight. Above load chart is for reference only. For actual lift duty and complete chart with all available configurations please refer to load chart in operator's cab or manual.

# Load chart - fixed jib (No. 0806.xx)

Offset 30°

## Main boom 11 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
7.9	18.3	t	t	t
14	12.6	8.2		
19	10.6	6.8	5.3	
20	10.3	6.6	5.1	
24		5.8	4.6	3.6
26		5.5	4.4	3.4
28		5.4	4.2	3.3
30		5.2	4.0	3.1
32			3.8	3.0
36			3.7	2.8
38				2.7
42				2.7

## Main boom 20 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
8.9	17.9	t	t	t
15	13.7	8.1		
19	12.1	7.2	5.3	
24	10.7	6.4	4.8	3.7
26	9.8	6.1	4.6	3.5
28	8.8	5.9	4.5	3.4
32		5.5	4.1	3.1
38		5.2	3.8	2.9
40			3.7	2.8
44			3.7	2.7
46				2.7
50				2.7

## Main boom 26 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
9.5	17.6	t	t	t
16	13.9	7.9		
20	12.5	7.2	5.3	
24	10.8	6.6	4.9	3.7
26	9.6	6.4	4.7	3.5
28	8.6	6.1	4.6	3.4
30	7.7	5.9	4.5	3.3
32	6.9	5.8	4.3	3.2
34	6.2	5.6	4.2	3.1
42		4.7	3.8	2.8
48			3.7	2.7
55				2.7

## Main boom 32 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
10.1	16.9	t	t	t
17	14.0	7.8		
22	12.1	7.0	5.1	
26	9.4	6.5	4.8	3.5
30	7.4	6.1	4.5	3.3
34	5.9	5.8	4.3	3.2
36	5.3	5.7	4.2	3.1
38	4.8	5.4	4.1	3.0
46		3.6	3.8	2.8
48		3.2	3.6	2.7
50			3.3	2.7
60				2.1

## Main boom 38 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
10.7	15.8	t	t	t
17	13.9	7.7		
22	11.6	7.1	5.0	
26	9.3	6.6	4.8	3.5
30	7.3	6.3	4.6	3.3
34	5.9	5.9	4.4	3.2
38	4.7	5.3	4.2	3.1
42	3.8	4.4	4.0	2.9
44	3.4	4.0	3.9	2.9
50		2.9	3.2	2.7
55			2.4	2.7
60				2.1

## Main boom 44 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
11.4	14.5	t	t	t
18	12.8	7.4		
22	11.0	7.0	4.9	
26	8.7	6.7	4.7	3.4
30	7.0	6.3	4.6	3.3
34	5.6	6.0	4.4	3.2
38	4.5	5.1	4.2	3.1
42	3.5	4.1	4.0	3.0
46	2.8	3.3	3.7	2.8
48	2.4	3.0	3.3	2.8
50		2.7	3.0	2.8
55			2.2	2.5

## Main boom 50 m

Radius (m)	Fixed jib length (m)			
	11	20	26	32
12	12.7	t	t	t
19	11.0	7.1		
24	9.3	6.7	4.7	
28	7.4	6.4	4.5	3.3
30	6.7	6.3	4.5	3.2
34	5.4	5.9	4.3	3.1
38	4.3	4.8	4.2	3.0
42	3.4	3.9	4.0	2.9
46	2.7	3.2	3.4	2.9
48	2.3	2.9	3.1	2.8
50	2.0	2.5	2.8	2.8
55		2.1	2.3	

## Main boom 53 m

Radius (m)	Fixed jib length (m)			
	11	20	23	26
12.3	11.5	t	t	t
19	10.0	6.8		
22	9.3	6.6	5.7	
24	8.8	6.4	5.6	4.6
28	7.2	6.1	5.4	4.5
32	5.7	5.8	5.2	4.4
36	4.6	5.1	5.0	4.2
40	3.7	4.2	4.3	4.1
44	2.9	3.4	3.5	3.6
46	2.5	3.0	3.1	3.2
48	2.2	2.7	2.8	3.0
50	2.4	2.5	2.5	2.6

## Main boom 56 m

Radius (m)	Fixed jib length (m)			
	11	14	17	
12.6	10.6	t	t	
15	10.1	8.8		
17	9.7	8.5	7.5	
20	9.3	8.1	7.3	
24	8.2	7.7	7.0	
28	6.9	6.9	6.5	
32	5.5	5.7	5.9	
36	4.4	4.6	4.8	
40	3.4	3.6	3.8	
44	2.7	2.8	3.0	
48	2.0	2.2	2.3	
50			2.0	


(TLT 983335514 M 48668)

Capacities in metric tons with fixed jib (No. 0806.xx) 32.3 t counterweight + 15 t carbody counterweight. Above load chart is for reference only. For actual lift duty and complete chart with all available configurations please refer to load chart in operator's cab or manual.


# Self-assembly system




Unloading of basic machine (option)



Unloading and assembly of crawlers




Unloading of basic machine (standard)




Unloading and assembly of carbody counterweight

Unloading and assembly of boom



Unloading and assembly of counterweight



Assembly of boom and reeving of hoist ropes

