


# LIEBHERR


### **Concept and characteristics**



- High engine output with automatic engine speed control
- Controlled entirely from cab
- Sturdy and solid rig design
- Wide longitudinal and lateral supporting system on the basic machine through triangles
- · High push and pull forces
- High torque
- Completely self–rigging (no auxiliary machines required)
- Large range of working tools (all piling and drilling works can be performed)
- Stepless leader inclination 1:6 forward 1:3 backward depending on type of equipment

- Leader swing range ± 90°
- Increase of effective leader length (5 m) via vertical travel device
- · Automatic vertical alignment
- · High alignment forces
- Simultaneous control of several movements via Load–sensing multi–circuit hydraulics
- Quick change of equipment possible through quick connection
- Equipment design according to latest European regulations and standards
- High manufacturing quality through quality control by PDE-system

### **Transport dimensions and weights**




#### **Transport weight**

Without attachment,
with telescopic undercarriage and counterweight — 43 t
Without attachment and counterweight,
with telescopic undercarriage — 39.1 t

Weights can vary with the final configuration of the machine. The figures in this brochure may include options which are not within the standard scope of supply of the machine.

### **Dimensions**

#### **Basic machine LRB 125**



#### **Technical data**

100111110011 0101101	
Leader length —	12.5 m
Capacity hammer including cap plus pile —  Max. hammer weight —  Max. pile weight —  Max. pull —  Max. torque —	6 t 6 t 200 kN
Working radius machine Center of rotation — center pile ————	3.15 — 5.35 m
Stepless rig inclination adjustment  Lateral inclination ————————————————————————————————————	1:6
Vertical leader adjustment above ground level (depending on radius) ————————————————————————————————————	5 m ± 90°

## Operating weight and ground pressure

The operating weight includes the basic machine LRB 125 (leader length 12.5 m, with attachment). Weights can vary depending on the final configuration of the machine.

### **Technical description**



#### **Engine**

Power rating according to ISO 9249, 450 kW (603 hp) at 1900 rpm Engine type Liebherr D 9508 A7

Fuel tank -870 I capacity with continuous level indicator and reserve warning

Engine complies with NRMM exhaust certification EPA/CARB Tier 3 and 97/68 EC Stage III.



#### Swing

Consists of single row ballbearing, fixed axial piston hydraulic motor, spring loaded and hydraulically released multi-disc holding brake, planetary gearbox and pinion.

Swing speed from 0 – 3.3 rpm is continuously variable.



#### **Hydraulic system**

The main pumps are operated by a distributor gearbox. Axial piston displacement pumps work in open circuits supplying oil only when needed (flow control on demand).

The hydraulic pressure peaks are absorbed by the integrated automatic pressure compensation, which relieves the pump and saves fuel.

Pumps for working tools —	2x 350 l/min
Separate pumps for kinematics —	2x 190 l/min
Hydraulic oil tank —	825 I
Max. working pressure —	350 bar

No auxiliary power packs are required as application specific hydraulics supply power to all components.

The cleaning of the hydraulic oils occurs via an electronically monitored pressure and return filter.

Any clogging is shown on the display in the cab.

The use of synthetic environmentally friendly oil is also possible.



The control system – developed and manufactured by Liebherr – is designed to withstand extreme temperatures and the many heavyduty construction tasks for which this machine has been designed. Complete machine operating data are displayed on a high resolution monitor screen.

To ensure clarity of the information on display, different levels of data are shown in enlarged lettering and symbols. Control and monitoring of the sensors are also handled by this high technology system. Error indications are automatically displayed on the monitor in clear

The machine is equipped with proportional control for all movements, which can be carried out simultaneously.

Two joysticks are required for operation. Pedal control can be changed to hand control.

Options:

PDE: Process data recording GSM modem



Propulsion through axial piston motor, hydraulically released spring loaded multi-disc brake, maintenance free crawler tracks, hydraulic chain tensioning device.

Drive speed —	0 – 2.3 km/h
Track force —	437 kN
Width of 3-web track shoes —	700 mm



### **Auxiliary winch**

Line pull (effective)	- 50 kN
Rope diameter —	- 17 mm
Drum diameter —	420 mm

The winch is noted for compact, easily mounted design. Propulsion is via a maintenance-free planetary gearbox in oil bath. Load support by the hydraulic system; additional safety factor by a spring-loaded, multi-disc holding brake.



Noise emissions correspond with 2000/14/EC directive on noise emission by equipment used outdoors.



#### Rope crowd system


Crowd force push/pull —	150/200 kN
Line pull (nominal load)	100 kN
Rope diameter —	18/20 mm


The ropes are actuated by a powerful hydraulic cylinder.

# High frequency vibrator slim design




Effective length – 15.5 m





Vibrating of single pile between two other piles



Display for vibrating


### **High frequency vibrator**

### Model 23 VML with hydraulic sheet pile feeder




Effective length – 15.5 m





Double clamp and hydraulic sheet pile feeder




Display for vibrating

# Pre-drill Model BA 45



Effective length – 15.5 m

Technical data	
Drilling drive – torque –	45 kNm
Drilling drive – speed —	95 rpm
Max. drilling diameter	800 mm



Display for continuous flight auger drilling


## High frequency ring vibrator

### **Model 20 VMR**




Effective length – 27 m

Technical data	
Static moment — Max. frequency — — — — — — — — — — — — — — — — — — —	0 – 20 kgm ————————————————————————————————————
Max. centrifugal force — Diameter	1160 kN 355 – 510 mm
Total weight —	6200 kg



Concrete supply system



Display for vibrating


## **Hydraulic hammer**

### Model H 50



Effective length – 13.5 m

Technical data	
Ram mass — Max. rated energy — Max.	——— 4000 kg ——— 51 kNm
Blow rate max. energy — Max. blow rate —	
Basic hammer weight —	8000 kg



Display for impact driving


### **Double rotary drilling**

#### **Model DBA 80**




Effective length – 12.8 m





Hydraulic casing guide




Display for double rotary drilling


### **Kelly drilling**

### Model BA 150 and Kelly bar 12/3/20





Shock absorber for Kelly bar



Display for Kelly drilling

Technical data		
Drilling drive – torque — — — Drilling drive – speed — — —	1st gear — 120 kN 1st gear — 32 rpr	
Drilling drive – torque — — — Drilling drive – speed — — — — — — — — — — — — — — — — — —	2 <sup>nd</sup> gear 60 kN 2 <sup>nd</sup> gear 60 rpr	

Technical data Kelly bar	
Diameter — Number of sections — — — — — — — — — — — — — — — — — — —	
Extended length ————————————————————————————————————	
2	— 200 mm - 3200 kg

Technical data Kelly winch	
Line pull (effective)	- 110 kN
Winch speed — 0	– 100 m/min
villon opocu	100 11/111111

<sup>\*)</sup> other Kelly bars on request


Performance data	
Max. drilling diameter ———————————————————————————————————	——————————————————————————————————————
Max. clearance below drilling tool —	6.5 m


## Continuous flight auger drilling

**Model BA 150** 




Effective length – 14.6 m





Auger with hydraulic auger cleaner



Display for continuous flight auger drilling

## Twin mix equipment

### **Model DMA 35**




Effective length – 15.2 m

Technical data		
Drilling drive – torque — Drilling drive – speed — — — — — — — — — — — — — — — — — —	— 1 <sup>st</sup> gear —— — 1 <sup>st</sup> gear ——	— 35 kNm — 60 rpm
Drilling drive – torque — Drilling drive – speed — — — — — — — — — — — — — — — — — —	— 2 <sup>nd</sup> gear —— — 2 <sup>nd</sup> gear ——	— 17.5 kNm — 120 rpm




Set up for operation on dams



Display for soil mixing

### Process data recording system - PDE® (additional equipment)

The Liebherr process data recording system PDE® constantly records the relevant process data during the working process.



Depending on the application the recorded and processed data are displayed on the PDE® touchscreen in the operator's cab, e.g. in the form of an online cast-in-place pile.

At the same time the PDE® is operated using this touchscreen. The operator can enter various details (e.g. jobsite name, pile number, etc.) and start and stop recordings. A recording of every start-stop cycle carried out in the PDE® is established on a CompactFlash memory card.

The PDE® can be configured in a number of ways, e.g. for the connection of external sensors, for the generation of a simple protocol as graphic file and/or for a printout directly in the operator's cab.

### Process data reporting - PDR (additional equipment)

Comprehensive data evaluation and generation of reports on a PC is possible using the software SCULI PDR.

**Recordings management -** The recordings generated by the PDE® system can be imported and managed in SCULI PDR. The data can be imported directly from the CompactFlash card or via the Liebherr telematics system LiDAT. Certain recordings, e.g. for a particular day or jobsite, can be found using filter functions.

**Viewing data -** The data in each record is displayed tabularly. Combining several recordings provides results, for example, regarding the total concrete consumption or the average depth. Furthermore, a diagram editor is available for quick analysis.

**Generating reports** - A vital element of SCULI PDR is the report generator, which allows for the generation of individual reports. These can be printed out directly or stored as pdf files. In the process the size, colour, line thickness or even the desired logo can be configured. Moreover, the reports can be displayed in different languages, e.g. in English and in the national language.

