

R 9600

Generation 8

LIEBHERR

Mining excavator



Technologies

- Liebherr Power Efficiency
- IoMine ready

Powertrain options

- Liebherr ICEs - Diesel: 2,700 kW (FCO)
3,620 HP
- Cummins ICEs - Diesel: 2,500 kW (Tier 4f)
3,350 HP
- GE E-Motors: 2,400 kW (50 Hz, 60 Hz)
3,220 HP

Backhoe configuration

- Overall weight: 633 tonnes
698 tons
- Bucket payload: 68 tonnes
75 tons

Face shovel configuration

- Overall weight: 645 tonnes
711 tons
- Bucket payload: 67 tonnes
74 tons

Overview

R 9600



Diesel drive 2,700 kW / 3,620 HP
Electric drive 2,400 kW / 3,220 HP



BH 37.5 m³ / 49.1 yd³
FS 37.0 m³ / 48.4 yd³



BH 633 tonnes / 698 tons
FS 645 tonnes / 711 tons

High performance
execution

Patented EVO bucket

Weight-optimised attachment

The R 9600 attachment makes use of smart component design such as the patented “EVO” backhoe bucket, hydraulic cylinders, shift levers, bucket links and attachment pins. The result is an increased overall production rate without compromising component lifetime.

Standard heavy-duty bucket

- Highest bucket capacity in its class with proven EVO bucket design
- Maximised payload with versatile Liebherr bucket solution
- Shift levers and bucket links with integrated greasing system

Perfect shovel truck match

4 pass loading of 240 tonne trucks
5 pass loading of 300 tonne trucks
5-6 pass loading of 330 tonne trucks



Latest cutting-edge technologies

Latest cabin generation technologies

Sustainable & efficient performance

Latest cabin generation

Increased comfort and ergonomics

- User-friendly operator station
- Suspended operator & trainer seats
- Slim line dash and ambient lighting
- Refrigerator and optional vacuum cleaner

Latest cutting-edge technologies

- Liebherr Assistance Systems
- Advanced machine monitoring with modern 7" and 15" touchscreens (day & night mode)
- 270° vision system with large dedicated 15" monitor

Sustainable performance

- Cummins QSK50 US EPA Tier 4f / EU Stage V compliant SCR after-treatment technology
- Serial implementation of Liebherr Power Efficiency solutions
- Electric drive version

Performance & sustainability

Powertrain

+40 %

Fuel efficiency



Diesel drives

The R 9600 can be fitted with two versions of diesel drive systems. Customers can choose between the Liebherr D9812 and the Cummins QSK50 engine, both providing superior performance for increased productivity.

Liebherr 2x D9812

2,700kW / 3,620 HP at 1,500RPM

12 cylinder V-engine

Displacement 62l / 3,786 in³



Cummins 2x QSK50

2,500kW / 3,350 HP at 1,800RPM

16 cylinder V-engine

Displacement 50.3l / 3,067 in³



US EPA Tier 4 / EU Stage V

The Cummins engines use selective catalytic reduction technology to comply with latest emission regulations. The R 9600 combines its flexible design with this technology to meet customer expectations without compromising productivity.



Electric drive

Liebherr offers an alternative to diesel engines allowing customers to balance performance with environmental consciousness. Building on 40 years' experience in electric drive excavators, the electric drive option allows lower maintenance costs and reduced noise pollution. With high motor efficiency, the electric drive gives maximum performance.

- Lower maintenance costs
- 6,000V (other voltage on request)
- Integrated design elements on all machine structures
- Optional cable reel

No exhaust emission

Liebherr electric R 9600 provides class leading cycle times using electric motors without exposing people and the environment to diesel exhaust emissions. Complying with all Non Road Mobile Machinery (NRMM) emission regulations, the R 9600 E can be operated all around the world.

Less noise level

Liebherr electric driven machines can be operated without restrictions in noise sensitive areas.



Productivity Attachment

Setting new standards in the mining industry



Backhoe

37.5 m³ / 49.1 yd³



330 t trucks
5-6 passes



T 274
300 t trucks
5 passes



T 264
240 t trucks
4 passes



Face shovel

37 m³ / 48.4 yd³



330 t trucks
6 passes



T 274
300 t trucks
5-6 passes



T 264
240 t trucks
4-5 passes

Site-specific factors like loose material density, bucket size, fill factors, truck body size and payload capacity will influence pass match. Contact your local Liebherr affiliate or sales partner for analysis of your site.

Smart component design

The optimised design of the R 9600 attachment increases the overall productivity without compromising component lifetime.

Maximised payload

Designed for best force distribution, the attachment design delivers high digging and hoisting forces, which ensures maximum payload during each cycle. The EVO bucket allows the operator to take advantage of each pass and therefore increase productivity.

Optimised cost per tonne

Built to outperform all competitors in the 600 t class, the R 9600 offers superior durability through its brand new machine and component design, delivering state-of-the-art capabilities and reliability.



+15 % Productivity



IoMine

"The R 9600 guaranties optimal force transmission."

Automation

Bucket Filling Assistant

The first automation product of the Liebherr hydraulic excavator portfolio allows easier bucket filling and consistent bucket fill factors, especially in blocky or hard digging conditions. As a result overall productivity improves while operator's fatigue decreases.



Anti-stalling function

Prevents the bucket from being stalled during the digging phase.



Semi-automatic bucket filling function

Allows the machine electronic to realise fully automatic attachment movements.



Discover more.

Comfort Operator cabin




Latest cabin generation

- Spacious interior
- Modern and large touchscreens
- Indirect ambient LED lights
- Drawer refrigerator
- User-friendly piloting station
- Best in class visibility



Superior comfort

- Only 69dB noise level
- Suspended and heated seats
- Synthetic leather interior
- Pressurised A/C system (single or double)
- Reading spotlights with tablet
- Phone and cup holders



Vision system

The R 9600 offers superior visibility of the machine's surroundings. The dedicated monitor inside the cabin provides continuous 270 degree vision around the machine, from the four cameras strategically fixed on the uppercarriage. The operator has 90 degrees of direct visibility in front of the cabin.



Visibility
+30%

Working environment

Operator comfort

Resiliently mounted, the cab design reduces vibrations and limits noise to provide a comfortable and safe workspace (FOPS). Standard ambient lighting ensures even at night a serene working environment.

Perfect working position

The slim line dash allows positioning of operator's seat as far left as possible providing best visibility of the working area.

Additional features

Dedicated mounting points for additional customer devices, modules or antennas.

First class cabin

Operator and trainer seats are air-suspended and heated offering a high level of comfort. Beyond these outstanding features, Liebherr offers as standard a 20 litre drawer refrigerator and an optional vacuum cleaner fitted directly into the cabin.

Optional

- Double A/C system
- Vacuum cleaner
- Premium cooled seats
- Four point harness
- HEPA filtration system

IoMine

Unleash the full potential of your mine.



Your connected mining ecosystem

IoMine, Liebherr Mining's cutting-edge technology product line, supports customers' transition to integrated operations. By adopting IoMine, customers can improve decision-making and provide greater operational safety – all while fostering sustainable development and ensuring cost optimisation in the management of their mines. IoMine is a reliable partner for achieving a more efficient, cost-effective, and productive mining operation.

Partnering for mining success

IoMine, Liebherr Mining's advanced technology product line, optimises operations by improving asset availability, efficiency and productivity. These products enhance fleet capabilities, simplify operations and improve fleet management for more profitability and smarter energy use.



Unlock peak performance



Enhanced decision-making

Optimise your mining operations and increase efficiency by making informed decisions supported by accurate, real-time data.



Increased safety

Real-time machine monitoring and operator alerts from assistance systems enhance safety while autonomous technology reduces risks, ensuring a safer worksite.



Increased operational efficiency

Real-time operator assistance, streamlined maintenance and autonomous technologies work together to enhance integration, productivity, efficiency and profitability.



Maximised machine availability

Proactive maintenance, operational insights and advanced automation collectively prevent breakdowns, minimise downtime and boost efficiency, productivity and profitability for continuous operations.



Let's journey together on the path to data-driven decision-making and autonomy in digging, dozing and hauling.



Operate – Empower mining success.

Find the right IoMine products dedicated to operations to optimise processes, reinforce safety and increase the profitability of your mining operations.



Maintain – Less downtime, more mining.

Keep your mining fleet running at peak performance with IoMine's dedicated maintenance products, whose innovative maintenance solutions are designed to minimise downtime and increase efficiency.



Automate – Safe. Efficient. Automated.

Liebherr's advanced automation solutions integrate seamlessly into your existing systems for real-time monitoring and intelligent automation.




Assistance Systems

The best performance. Easy.



Get the best out of your Liebherr mining excavator

Available today on the R 9600, the Liebherr Assistance Systems are advanced onboard applications designed to support operators to become more efficient through analytics and actionable insights. Systems will assist the operator to obtain optimal productivity and efficiency by providing realtime operational information.



Want to live the real experience?



Measure and analyse every bucket payload for optimal truck loading



Data visualised within different views & advanced filtering



Display targeted productivity and actual payload with 99% accuracy



Provide transparency of performance, operating time and fuel efficiency



Identify operational conformance and improve operator effectiveness




State-of-the-art on-board touchscreen displays



Make informed decisions



Increase productivity





Truck Loading Assistant

Assists the operator to obtain target truck payloads.

With 99% measurement accuracy

- Measures instantaneously the bucket payload
- Provides real-time information to the operator
- Strategises the number of passes required
- Computes the best truck loading strategy
- Automatic truck recognition (optional)



Performance monitoring

Measures and analyses the overall performance.

Using KPIs, histograms and time-related charts

- Production KPIs
- Loading indicators
- Time distribution
- Energy efficiency



Application severity

Quantifies application, reports severity indicators and provides an overall application severity score.

KPIs to indicate and display the application as sensed by the machine

- Underfoot and digging conditions
- Abrasiveness and travel ratio
- Engine load factor and temperature variation
- Machine inclination, loading, etc.



Operational conformance

Detects and counts events to improve operator effectiveness.

Several filtering criteria to identify specific events

- Swinging into digging face
- Digging with swing brake activated
- Turning the machine with the attachment
- Bucket hitting track pads, etc.



Highest
digging force

1,560 kN

Breakout force

1,730 kN

in its class

Performance

Advanced hydraulic system

Fast & precise movement

Intelligent power management system

The Liebherr R 9600 mining excavator is equipped with a closed loop swing circuit. Kinetic energy is recovered when the swing motion is used during deceleration to drive the main and auxiliary pumps resulting in fuel consumption reduction. Cylinder dampening through IMUs provides smoother attachment movements without affecting attachment speed.

Independent cooling system

Oil and water cooling fans are independently and electronically managed. The oversized cooling systems reduce parasitic demand on engine horsepower ensuring maximum available horsepower is provided to the excavator working circuits.

New valve bank control system


- Under slung arch hoses to improve lifetime
- Flow optimized hose fittings
- Less hydraulic pressure losses by design
- Pilot valves integrated into valve blocks

Moving more with less

Patented Liebherr Power Efficiency


Specific engine and hydraulic management, drastically reducing fuel consumption without any compromise on machine productivity.

- Adapted piloting processes according to operator requirements and machine condition
- Electronically controlled pressure and oil flow
- Reduce hydraulic throttling and load profile of the engine for increased component lifetime



● Previous R 996B ■ New R 9600 G8

Up to **20 %**
less fuel consumption



"Adapt the power and the hydraulic flow specifically to the load profile."


Safety

Protecting your most important asset



Machine accessibility

The R 9600 is fitted with an ergonomic hydraulically controlled 45 degree stairway with handrails, providing safe access to the upper-carriage.



Wide catwalks for inspection

Enlarged walkways allow easy and safe access for inspection and maintenance around engines, fans, and pumps. All routine service items have been located to allow effortless inspection and replacement.




Emergency stops and emergency exits

Emergency stops are specifically located throughout the machine, increasing safety. A mechanical emergency egress guarantees safe and quick exit from the machine. An additional emergency drop down ladder is provided in the pump bay.



Advanced engine fire protection

After treatment systems and turbochargers are heat shielded. The engines are mechanically segregated from hydraulic components, further improving on machine safety.



LED lighting system

Thanks to LED long-reach lights located on attachment, uppercarriage and counterweight, the machine offers best visibility to the operator and to the people/equipment around.



Safe surrounding area

Horn, LED working lights, LED service lights, LED access lights, flashing lights and travel alarm guarantee safe 24 / 7 operation and maintenance conditions.

Maintenance
Easy & safe operations

24/7
Operations





Centralised service

Service flap

Uppercarriage of the R 9600 has been designed for easier maintenance and quicker servicing. The central service area provides accessibility to uppercarriage fluid compartments

reducing machine downtime. Refill and separate drain points of the R 9600 are easily accessed from the ground with fast couplings and depressurised valves.



Automatic greasing system

- Grease tank for the attachment, uppercarriage and swing ring bearing
- Grease tank for the swing ring teeth
- Simplified component layout
- Automatic greasing cycles
- Reduced number of injectors & hoses
- Electric shut-off valve in the refill line



Superior engine accessibility

- Walkways all around the engines
- Service-friendly maintenance items installation
- Service interval 500 hours (Optional 1000 hours)
- Sampling-point for all liquids on deck



Ease of troubleshooting

- Signal panels
- Control system hardware and software completely developed and managed by Liebherr
- Reduced number of connections and connectors

Optional

- Service folding platform on front swing boxes
- Service doors on travel drive protection
- Additional Cummins oil reserve tank
- Banlaw or Wiggins couplings
- Kidney loop filtration system

Reliability

Long-lasting performances

Vertical integration

As an OEM, Liebherr has built a solid reputation for its development and production of high quality strategic mining components. The R 9600 integrates robust and reliable mining optimised components that are developed and manufactured by Liebherr, which ensures the best reliability and highest performance.

Mining know-how

Liebherr mining excavators are conceptualised, designed and dedicated to the mining industry. The engineering department uses specific 3D simulation solutions in order to meet possible requirements, such as finite element and fatigue life analysis.


80,000

Operational hours



Robust undercarriage

- Hydraulic track tensioning system
- Final drive with double lifetime sealing in series
- Fatigue resistant steel structure design
- Sealed for life heavy-duty carrier and track rollers
- Patented track pad design





Super structure

- Complete new development
- Optimised welding penetration
- Increased structural rigidity and life
- Heavy duty conception through advanced 3D design and validation softwares



Quality: the Liebherr trademark

Providing reliable machinery is the highest priority for Liebherr mining. Utilised in tough mining applications all around the world, our R 9600 is built to last over 80,000 operational hours. Liebherr's engineering expertise and continuous improvement programs combine to deliver industry leading machines.

Future proof

One modular platform, many possibilities


Liebherr has a modular design approach for its largest excavators. The company's engineers follow this approach from the earliest stages of machine design when developing our e-drive powerpack and internal combustion engines (ICE).



Modular maintenance

Liebherr's modular maintenance program offers customers an opportunity to optimise the replacement of major component assemblies (modules). This program effectively delivers required maintenance for mobile equipment while minimising downtime, maximising efficiencies and improving overall safety.


Reduce
downtime
by up to **50 %**



Repowering of internal combustion engines

Liebherr's repowering solutions involve replacing the existing internal combustion engine (ICE) within one of the company's large excavators with Liebherr's D9812 ICE. This engine provides a proven increase in productivity, HVO compatibility, up to 5% less fuel consumption and less stress on the excavator's components.

Reduce fuel
consumption
by up to **5 %**



Repowering from internal combustion engine to electric

Customers can convert their diesel-powered Liebherr excavators to electric drive with our repower solutions as Liebherr's diesel-powered and electric-drive excavators share 70% component commonality. Further, these repowers can be carried out during major overhauls of the excavators, meaning that they can be upgraded throughout their lives to meet customers' evolving decarbonisation strategies.

Decarbonise
your mining
operations



Retrofit solutions

Liebherr retrofits are the right solution for customers wanting to upgrade their equipment by adding new features and/or products. They enable customers to:

- Flexibly upgrade their equipment to make it future proof
- Implement assistance systems that provide insights for operational decision-making and safety
- Comply with regulatory emission requirements and standards

***Unlock the full potential
of your excavator***

*For more information, please contact your
local Liebherr sales and service company
or sales partner.*

The four pillars of the Liebherr mining division

With more than 50 years of experience in the mining industry, Liebherr has identified four key factors of customer satisfaction: Performance, Safety, Service, and Sustainability. These pillars provide structure and focus for all our activities, and embody Liebherr's customer commitments.



**Performance**

Productive, efficient and reliable

**Safety**

Protecting your most important assets

**Service**

Where you need it, when you need it

**Sustainability**

Committed to our future



Technical data

Powertrain

2 Liebherr ICEs – Diesel	
Rating ECE-R.24 / ISO 9249	2 x 1,350 kW (2 x 1,810 HP) at 1,500 rpm
Model	Liebherr D9812 (Fuel consumption optimized setting)
Type	12 cylinder V-engine
Bore / Stroke	175 / 215 mm / 6.89 / 8.46 in
Displacement	62 l / 3,786 in ³
Engine cooling system	fans driven via hydraulic piston motors
Liebherr Power Efficiency – Engine Control	engine management systems adapting the power specifically to the load profile
Air cleaner	dry-type air cleaner with pre-cleaner, with automatic dust ejector, primary and safety elements
Fuel tank capacity	14,067 l / 3,716 gal
Fuel filtration	3 stage fuel filtration with water separator and electric priming pump
Oil lubrication	spin-on filters and oil centrifuge filter
Electrical system	
Voltage	24 V
Batteries	8 x 180 Ah / 12 V starting battery 4 x 180 Ah / 12 V service systems
Alternator	24 V / 370 A
Engine idling	automatic engine idling

or

2 Cummins ICEs – Diesel	
Rating per SAE J1995	2 x 1,250 kW (2 x 1,675 HP) at 1,800 rpm
Model	Cummins QSK50 (US EPA Tier 4f / EU Stage V compliant or fuel consumption optimized setting)
Type	16 cylinder V-engine
Bore / Stroke	159 / 159 mm / 6.26 / 6.26 in
Displacement	50.3 l / 3,067 in ³
Engine cooling system	fans driven via hydraulic piston motors
Liebherr Power Efficiency – Engine Control	engine management systems adapting the power specifically to the load profile
Air cleaner	dry-type air cleaner with pre-cleaner, with automatic dust ejector, primary and safety elements
Fuel tank capacity	14,067 l / 3,716 gal
DEF tank capacity	1,330 l / 351 gal
Fuel filtration	2 stage fuel filtration with water separator and electric priming pump
Oil lubrication	spin-on filters (4x)
Electrical system	
Voltage	24 V
Batteries	8 x 180 Ah / 12 V starting battery 4 x 180 Ah / 12 V service systems
Alternator	24 V / 260 A
Engine idling	automatic engine idling

or

2 GE E-Motors	
Power output	2 x 1,200 kW (2 x 1,610 HP)
Type	3-phase AC squirrel cage motor
Voltage	6,000 V, other voltage on request
Frequency	50 Hz (or 60 Hz)
Revolutions	1,500 rpm or 1,800 rpm
Motor cooling	integrated air-to-air heat exchanger
Starting method	inrush current limited to 2.2 full load current
Starting sequence	successive startup of electric motors

Electro-hydraulic controls

Servo circuit	independent, electronic over hydraulic proportional controls of each functions
Emergency control	emergency lowering of the attachment to the ground, via accumulators
Power distribution	via monoblock control valves with integrated primary relief valves, proportional and safety valves. Integrated secondary relief valves on functional blocks and motors
Attachment and swing	proportional via joystick levers
Travel	proportional via foot pedals
Electronic dampening system	Liebherr designed electronic control of cylinder position via inertial measurement units

Swing drive

Hydraulic motor	4 Liebherr axial piston motors
Swing gear	4 Liebherr planetary reduction gears
Swing ring	Liebherr, sealed triple roller swing ring, internal teeth
Swing speed	0–3.7 rpm
Swing-holding brake	4 hydraulically released, maintenance-free, external multi-disc brakes

Hydraulic system

Hydraulic pump	
for attachment and travel drive	8 Liebherr variable flow axial piston pumps
Max. flow	8 x 800 l/min. / 8 x 211 gpm
Max. pressure	320 bar / 4,641 psi
for swing drive	4 Liebherr reversible swashplate pumps, closed-loop circuit
Max. flow	4 x 530 l/min. / 4 x 140 gpm
Max. pressure	320 bar / 4,641 psi
Pump management	electronically controlled pressure and flow management with oil flow optimisation
Hydraulic tank capacity	5,425 l / 1,433 gal
Hydraulic system capacity	9,600 l / 2,536 gal
Hydraulic oil filter	1 high pressure safety filter after each main pump + fine filtration of the entire return flow (15 / 5 µm) dedicated leak-oil filtration
Hydraulic oil cooler	4 separated coolers with 3 temperature controlled fans driven via hydraulic piston motors
Liebherr Power Efficiency – Hydraulic Control	hydraulic management system adapting the hydraulic flow specifically to the load profile

Electric system

Electric isolation	easily accessible battery isolations (single isolation point)
Working lights	LED lights arrangement around the attachment and the upper-carriage
Emergency stop switches	at ground level, in engine and pumps compartment, at valve bank and in operator cab
Electrical wiring	heavy duty execution in IP 65 standard for operating conditions of -55 °C to 13 °C / -67 °F to 275 °F

Uppercarriage

Design	torsion resistant designed upper frame in box-type construction for superior strength and durability
Attachment mounting	parallel longitudinal main girders in box section construction
Machine access	45° access system with handrails on the cab side of the upper-carriage, full controlled descent in case of emergency stop. Emergency egress fitted near the cab and emergency ladder in the pump bay.

Cab

Design	resiliently mounted, sound insulated, large windows for all around visibility, integrated falling object protection (ISO 10262)
Operator's seat	suspended pneumatic seat, body-contoured with shock absorber, adjustable to operator's weight, additional suspended pneumatic passenger / trainer seat, seat heating
Cabin windows	tinted armored glass for front window and right-hand side window P5A (EN 356), all other safety windows tinted, high pressure windshield-washer system with 75 l / 20 gal watertank, sun louvers on all windows in heavy duty design
Heating system / Air conditioning	heavy duty, fully automatic, "plug & play" system, high output air conditioner and heater unit, contains fluorinated greenhouse gases HFC 134a with a Global Warming Potential (GWP) of 1430, the AC circuit contains 4.1 kg / 9 lb of HFCa-134 representing an equivalent of 5.9 tonnes / 6.5 tons of CO ₂ , the 2 nd AC circuit (optional) contains 4.1 kg / 9 lb of HFCa-134 representing an equivalent of 5.9 tonnes / 6.5 tons of CO ₂
Cabin pressurization	ventilation with filters, minimum pressurisation of 50 Pa (ISO 10263-4)
Controls	joystick levers integrated into armrest of seat, armrest adjusted to seat position
Display	15" machine touch panel for machine control and Liebherr Assistance Systems, 7" auxiliary touch panel for auxiliary / comfort control, 15" camera display
Condition monitoring	machine condition monitoring system with error reporting and operational information
Vision system	4 cameras providing 270° view
Safety functions	automatic engine shut off safety mode for engine speed control and pumps regulation
Noise level (ISO 6396)	Diesel: L _{PA} (inside cab) = 69 dB(A) Electric: L _{PA} (inside cab) = < 69 dB(A)
Hand-arm vibrations	≤ 2.5 m/s ²
Whole-body vibrations	≤ 0.5 m/s ²

Undercarriage

Design	3-piece undercarriage, box-type structure for center piece and side frames, stress relieved
Hydraulic motor	2 axial piston motors per side frame
Travel gear	Liebherr planetary reduction gear
Travel speed	Diesel: 0-1.7-2.2 km/h / 0-0.6-1.2 mph
Parking brake	spring engaged, hydraulically pressure released external wet multi-disc brakes for each travel motor, maintenance-free
Track chain	dual pin monobloc casted pads, maintenance-free
Track rollers / Carrier rollers	6 / 3 per side frame
Automatic track tensioner	pressurised hydraulic cylinder with accumulator, maintenance-free

Service flap

Design	hydraulically actuated service flap, easily accessible from ground level, including: <ul style="list-style-type: none"> - fast fuel refill line - hydraulic oil refill - engine oil exchange - splitterbox oil exchange - swing gearbox oil exchange (4 x draining / 4 x refill) - swing ring teeth grease barrel refilling with grease filter and shut off valve when high level reached - attachment / swing ring bearing grease barrel refilling with grease filter and shut off valve when high level reached - connection for windshield washer water refilling oil reserve system refilling (optional) - DEF exchange - coolant filling
--------	---


Central lubrication system

Type	single-line lubrication system for the entire attachment / swing ring bearing and teeth
Grease pumps	2 hydraulic grease pumps for attachment / swing ring bearing lubrication, 1 hydraulic grease pump for swing ring teeth
Capacity	600 l / 158.5 gal bulk container for attachment / swing ring bearing, separated 80 l / 21 gal container for swing ring teeth
Refill	via the service flap
Monitoring	via a specific Liebherr control module with data memory

Attachment

Design	box-type structure with large steel castings in all high-stress areas
Stick	wear protection underneath lower beam plate
Pivots	two floating pins per pivot, sealed covers, all bearings with wear resistant steel bushings, bolts hardened and chromium-plated
Hydraulic cylinder	Liebherr design, electronically controlled end-cushioning
Hydraulic connections	pipes and hoses equipped with SAE connections
Pivots bucket-to-stick Pivots bucket-to-link	O-ring sealed and completely enclosed
Lubrication	connected to the centralised lubrication system, each lubrication point independently lubricated

Dimensions




	mm / ft in
A	7,310 / 24'
A1	8,160 / 26' 9"
A2	9,220 / 30' 3"
B	7,870 / 25'10"
C	9,610 / 31' 6"
D	7,950 / 26' 1"

	mm / ft in
F	3,331 / 10' 9"
G	8,175 / 26'10"
H	6,760 / 22' 2"
H2	8,290 / 27' 2"
H3	9,980 / 32' 9"
K	3,100 / 10' 2"

	mm / ft in
L	7,850 / 25' 9"
N	1,350 / 4' 5"
P	3,010 / 9'11"
Q	1,390 / 4' 7"
S	6,330 / 20' 9"
U	10,325 / 33'10"

	mm / ft in
V	15,210 / 49'11"
W	9,500 / 31' 2"
W2	9,950 / 32' 8"
X	21,950 / 72'
Z	13,100 / 43'
OEL (Operator's eye level)	8,360 / 27' 5"



	mm / ft in
A	7,310 / 24'
A1	8,160 / 26' 9"
A2	9,220 / 30' 3"
B	7,870 / 25'10"
C	9,610 / 31' 6"
D	7,950 / 26' 1"

	mm / ft in
F	3,331 / 10' 9"
G	8,175 / 26'10"
H	6,760 / 22' 2"
H2	8,290 / 27' 2"
H3	9,980 / 32' 9"
K	3,100 / 10' 2"


	mm / ft in
L	7,850 / 25' 9"
N	1,350 / 4' 5"
P	3,010 / 9'11"
Q	1,390 / 4' 7"
S	6,330 / 20' 9"
U	10,325 / 33'10"

	mm / ft in
V	18,400 / 60'4"
W	8,760 / 28'9"
W2	9,500 / 31'2"
X	24,530 / 80'6"
Z	13,100 / 43'
OEL (Operator's eye level)	8,360 / 27'5"

According to ISO 9248, measurements of general machinery dimensions, performances and capacities may vary within tolerances given by this norm.

Backhoe attachment

with mono boom 10.90 m / 35'9"



Digging envelope

Stick length	m	5.00
	ft in	16'5"
Max. digging depth	m	8.10
	ft in	26'7"
Max. reach at ground level	m	19.20
	ft in	63'
Max. dumping height	m	10.60
	ft in	34'9"
Max. teeth height	m	16.20
	ft in	53'2"

Forces

Max. digging force (ISO 6015)	kN	1,575
	lbf	354,074
Max. breakout force (ISO 6015)	kN	1,740
	lbf	391,168

Machine shown without option with a bucket for average material abrasiveness and 1.8t/m³ (3,034 lb/yd³) density.
The characteristics of the material to be extracted and additional options can change the bucket volume, its shape, its radius and therefore may also change the work area reachable by the bucket.

Operating weight and ground pressure

The operating weight includes the basic machine with backhoe attachment and backhoe bucket 37.50 m³ / 49.05 yd³.

Pad width	mm	1,350
	ft in	4'5"
Weight	kg	633,000
	lb	1,395,526
Ground pressure*	kg/cm ²	2.69
	psi	38.26

* according to ISO 16754

Backhoe buckets

For materials class according to VOB, Section C, DIN 18300		3-4	5-6	5-6	7-8
Typical operation according to VOB, Section C, DIN 18300		GP	HD	HD	XHD
Capacity ISO 7451	m ³	39.00	40.00	37.50	33.30
	yd ³	51.01	52.32	49.05	43.56
Suitable for material up to a specific weight of	t/m ³	1.8	1.65	1.8	2.05
	lb/yd ³	3,035	2,782	3,035	3,457
Cutting width	mm	4,800	4,800	4,600	4,600
	ft in	15'8"	15'8"	15'1"	15'1"
Weight	kg	34,000	38,200	36,800	36,300
	lb	74,957	84,216	81,130	80,028


GP: General purpose bucket
HD: Heavy-duty bucket
XHD: Heavy-duty rock bucket

Other buckets for other densities and / or material classes on request

According to ISO 9248, measurements of general machinery dimensions, performances and capacities may vary within tolerances given by this norm.

Face shovel attachment

with shovel boom 7.90 m / 25'11"



Digging envelope

Stick length	m	5.10
	ft in	16'9"
Max. reach at ground level	m	15.90
	ft in	52'2"
Max. dumping height	m	12.40
	ft in	40'8"
Max. crowd length	m	4.80
	ft in	15'9"
Max. teeth height	m	19.50
	ft in	64'
Bucket opening width T	m	3.20
	ft in	10'6"

Forces

Max. crowd force at ground level (ISO 6015)	kN	2,425
	lbf	545,162
Max. crowd force (ISO 6015)	kN	2,625
	lbf	590,124
Max. breakout force (ISO 6015)	kN	2,125
	lbf	477,719

Machine shown without option with a bucket for average material abrasiveness and 1.8t/m³ (3,034 lb/yd³) density.

The characteristics of the material to be extracted and additional options can change the bucket volume, its shape, its radius and therefore may also change the work area reachable by the bucket.

Operating weight and ground pressure

The operating weight includes the basic machine with shovel attachment and bucket 37.00 m³ / 48.40 yd³.

Pad width	mm	1,350
	ft in	4'5"
Weight	kg	645,000
	lb	1,421,982
Ground pressure*	kg/cm²	2.74
	psi	38.97

* according to ISO 16754

Face shovel buckets

For materials class according to VOB, Section C, DIN 18300		3-4	5-6	5-6	7-8
Typical operation according to VOB, Section C, DIN 18300		GP	HD	HD	XHD
Capacity ISO 7451	m³	38.50	39.00	37.00	34.00
	yd³	50.36	51.01	48.40	44.47
Suitable for material up to a specific weight of	t/m³	1.8	1.65	1.8	2.00
	lb/yd³	3,035	2,782	3,035	3,373
Cutting width	mm	5,200	5,200	5,200	5,200
	ft in	17'	17'	17'	17'
Weight	kg	61,000	66,000	63,900	62,500
	lb	134,482	145,505	140,875	137,789

GP: General purpose bucket

HD: Heavy-duty bucket

XHD: Heavy-duty rock bucket

Other buckets for other densities and/or material classes on request

According to ISO 9248, measurements of general machinery dimensions, performances and capacities may vary within tolerances given by this norm.

Optional equipment

Undercarriage

Large track pads
Center girder lower cover plate
Swing ring scrapers

Uppercarriage

Steel grease lines on swing ring
Rock protection for fuel tank
Rock protection for hydraulic tank
Wiggins or Banlaw fast refilling systems
Coolant draining / filling from service flap
Additional RHS catwalks for windshield access
Automated sampling point
Additional fast fuel refill line

Hydraulic system

Oil cooler inlet screens
Kidney loop filtration system
Additional catwalks inside hydraulic tank

Powertrain

Cummins US EPA Tier 4f engine version
Cummins oil reserve system

Cab

4-points seat belt
Premium cooled seats
Vacuum cleaner
Double A/C system
Front protective grid
Leatherette seats
Cabin pressurisation with HEPA filters

Specific solutions

Arctic package (different stages available)
High altitude package
Oil sand package

Safety

Automatic fire fighting system
Isolation & energy dissipation system – MDG 41 compliant
Service folding platform over front swing boxes
Starter inhibition from ground level
Fall restraint cable on boom (CE certified)
Fall restraint cable on boom (AS / NZL certified)

General

Maritime transport packaging
Delivery without batteries

E-drive

Automatic cable reel

IoMine

Truck Loading Assistant
Operational Analytics
Bucket Filling Assistant

The photos in this brochure represent machines in operation that may be equipped with local options not developed by, or available from, a Liebherr factory. Please contact your Liebherr representative if you have any questions about options not mentioned above.



Quality commitment

- Liebherr-Mining Equipment Colmar, France, ISO 9001 certified
- Compliance of materials tested in laboratory
- Quality control during all stages of production
- CE certified, MDG 15 & MDG 41 compliant

Subject to technical modifications. All comparisons and claims of performance are made with respect to the prior Liebherr model unless specifically stated.

Liebherr-Mining Equipment Colmar SAS

49 rue Willi Liebherr • 68025 Colmar Cedex, France • Phone +33 369 49 20 00
info.lec@liebherr.com • www.liebherr.com • www.facebook.com/LiebherrMining