


For moments to savour

Refrigeration and freezing 2026



LIEBHERR

Freshness technology

- Bio Fresh Professional** BioFresh Professional offers even more flexibility for your individual food-storage needs.
- Hydro Breeze** Cooling like a pro: A cold mist and a temperature in the Fruit & Vegetable safe of just over 0 °C ensure a longer shelf life and create a fabulous visual effect. 
- Fish & Seafood** The Fish & Seafood safe stores fish and seafood at the optimum temperature of -2 °C, just as professionally as your fishmonger. 
- Bio Fresh** At a temperature just above 0 °C and with ideal humidity, fruits, vegetables, meat, fish, and dairy products stay fresh for much longer than they would in the standard fridge compartment.
- Easy Fresh** The adjustable humidity prolongs the freshness of your fruits and vegetables.
- No Frost** Frost-free convenience
- Smart Frost** Much less frequent defrosting
- Stop Frost** Less frequent defrosting and easier opening of the chest lid thanks to no vacuum.
- Super Frost** SuperFrost increases the cooling power for a short time - this means the temperature remains constant whenever you add any unfrozen food.
- Vario Temp Zone** Refrigeration or freezing? You can choose from: The VarioTempZone can be set to an accurate temperature between -18 °C and -10 °C or between -2 °C and +5 °C.

Convenience and flexibility

- Soft System** Very soft door closing, even when fully loaded, automatically below an opening angle of 30°.
- Easy Open** EasyOpen means the freezer door can be opened multiple times, one after another, conveniently and easily.
- Frost Protect** As the freezers are particularly suitable for low temperatures, they can also be placed in unheated rooms, down to an ambient temperature of no less than -15 °C.
- Auto Door** Unique worldwide: AutoDoor allows easy and convenient opening and closing of the door via smart speaker voice command, knocking signal, or smartphone - or simply by hand.
- Door Stop** Keep your Liebherr appliance fresh and odour-free. The door stays open when the appliance is not in use. Save time, energy, and freshness.
- Telescopic Rails** Drawers on smooth telescopic rails for convenient opening and closing, and easy removal.
- Tip Open** The glass door opens by 7 cm when tapped for easy access and full opening.

Water and ice

- Water & Ice Centre** The Water & Ice centre provides plenty of cold water, ice cubes, and crushed ice, around the clock.
- Ice Maker** Automatic IceMaker with a plumbed-in connection.
- Easy Twist Ice** Conjure up ice cubes quickly: Fill the tank with water, let it freeze and then release the ready-made ice cubes with a twist (selected freestanding appliances).
- Infinity Spring** The water dispenser is flush-mounted in the left side wall of the fridge compartment, for plumbed-in connections.
- Ice Tower** Perfect for parties: automatic IceMaker and large pizza compartment on a convenient pull-out shelf.

Design

- Mood Light** MoodLight - a highlight in your living environment: The indirect lighting concept beautifully showcases the Water & Ice-Centre and recessed grips.
- Light Tower** The lighting concept illuminates the interior evenly and supports the glass shelves - flexible, space-saving, and unique.
- LED** Low heat, energy-saving, and maintenance-free for optimum illumination.

Connectivity

- Smart Device** The SmartDeviceBox enables you to control the appliance and make use of additional services via a tablet or mobile phone.
- Smart Device ready** The SmartDeviceBox (available as an accessory) can be retrofitted so that you can control the appliance and use additional services via a tablet or mobile phone.

Ultra-efficient models

- Ultra Efficient A -20%**
- Ultra Efficient A -30%** Even more economical¹ than appliances in the highest energy efficiency class A, which means Liebherr is setting new standards in the industry.

¹ Compared to the threshold for maximum energy efficiency class A according to Regulation (EU) 2029/2016 (as of December 2023).

Series (see page 58 for an explanation)

○ Pure ◇ Plus ◻ Prime △ Peak

BLU Performance
All the refrigeration technology is integrated in the appliance plinth of the freestanding BluPerformance appliances. As a result, appliances of the same size have a considerably greater storage capacity, meaning more space for food and drinks. Energy efficiency is significantly better thanks to improved ventilation and extraction in the plinth. Plus, these appliances are quieter.


Wine fridges

- 1 **Zone**
 With a constant temperature throughout the interior, adjustable between +5 °C and +20 °C.
- 2 **Zones**
 With two temperature zones, independently and precisely adjustable between +5 °C and +20 °C.
- 3 **Zones**
 With three temperature zones, independently and precisely adjustable between +5 °C and +20 °C.
- Temp Protect Plus
 Liebherr wine fridges monitor the temperature twice over with TempProtect Plus.
- Glass Door
 Your entire wine collection at a glance: behind tinted UV safety glass.
- Vibrate Safe
 Liebherr wine fridges have a fully vibration-insulated cooling system.
- Humidity Control
 The humidity can be actively regulated in 5% increments between 50% and 80% RH**.
- Humidity Select
 The humidity can be adjusted in two stages: Standard or High.
- UV Protect Plus
 Triple protection: A tinted glass door with two layers of vacuum-deposited metal provides highly efficient protection from sunlight.
- UV Protect
 Double protection: A tinted glass door with one layer of vacuum-deposited metal provides efficient protection from sunlight.
- Sommelier Board
 For effective presentation and decanting: Wooden shelf with stainless steel bottle display, wooden box for decanting utensils and space for tempering wine glasses.

Our series of wine fridges:

- Vinidor | Vinidor Selection** **GrandCru | GrandCru Selection**
 Primarily for wine tempering Primarily for wine storage

The current EU energy label for electrical appliances




1. The QR code for identifying the product in EPREL (European Product Database for Energy Labelling).
2. The model identifier for manual identification of the product in the EU database EPREL, using the article number, for example.
3. The new efficiency scale from "A" to "G". However, "G" is only intended for wine coolers.
4. The total volume* of all freezer compartments.
5. The total volume* of all cold storage and refrigerator compartments.
6. The noise level is now classified into classes "A" to "D".

Liebherr appliances are typically delivered with door hinges on the right (interchangeable).


For models where the door hinge is factory-installed on the left or cannot be interchanged, the entry also indicates the models with a left hinge.

Door fronts

You can choose from the following surfaces:



Legend:
MBsddi 9558
 SmartSteel door



Our complete Liebherr product range of freestanding and fully integrated appliances with detailed product descriptions and our Liebherr specialist dealers can be found on our website – visit us at: **home.liebherr.com**

*The term 'Volume' is taken from the current Regulation (EU) 2019/2016.
 **Such as very dry or cold cellars, we recommend supporting the system with the tailor-made water box from our range of accessories.



For moments to savour.

Before you start browsing...

Take a moment to pause. Your new appliance will be your companion around the clock for many years to come. When you make such an important decision like this, it's about more than just dimensions, energy consumption, and price.

You love fresh ingredients, special moments, and quality – just like us. Our fridges and freezers are designed to make your life easier and more enjoyable.

As specialists in refrigeration and freezing, Liebherr represents the quality of German engineering' – and the biggest range of freestanding and fully integrated appliances on the market.

Discover the models and features that will make your everyday life easier and keep your food fresh for longer. You'll find many good reasons to choose a Liebherr on the next pages – and even more online.

But even better: Experience the tangible Liebherr difference for yourself in person at your nearest Liebherr specialist retail partner!

Enjoy exploring what's on offer!

Why you should choose Liebherr

History _____ 8

For over 70 years, we've been the refrigeration specialists for high-quality fridges and freezers, and we distribute them worldwide. We are at heart a family business with our roots firmly established in Germany – German engineering, based on an enduring connection with our founder.

Quality _____ 9

The quality of our products is the solid foundation for the high level of trust that customers place in the Liebherr brand. We work continuously to keep developing and optimising all our appliance components and materials.

Responsibility _____ 10

As a family-run company, we think in terms of generations, not just business cycles – We are committed to making long-term decisions that benefit people, the planet, and our business.

Features

Design _____ 21

DarkGrey _____	21
Handle options _____	22
Glass and steel look interior _____	24
Awards _____	79
Door fronts _____	3
Surfaces _____	3

Ergonomics _____ 26

Divisible glass shelf _____	24
Telescopic rails _____	25
VarioSpace _____	26
VarioSafe _____	26
VarioCool drawers _____	26
AutoDoor _____	40
OpenStage drawers _____	41
Accessories _____	78
SmartDevice _____	81

Refrigeration _____ 13

EasyFresh _____	14
BioFresh _____	15
BioFresh Professional _____	16
👉 HydroBreeze _____	16
👉 Fish & Seafood-Safe _____	16

Product group



Fridge

Freestanding _____	64
Built-in _____	20 70



Fridge-freezers

Freestanding _____	19 62
Built-in _____	20, 43 68



Side-by-side combinations

Freestanding _____	32 61
Built-in _____	46 68

(SBS concept)



Fridge-freezers with French doors

Freestanding _____	28 60
Built-in _____	42 68



XL fridge-freezers

Freestanding _____	44 62
Built-in _____	43 68

Freshness technology — 13

We were pioneers in developing the BioFresh technology in 1996, and we keep improving it year after year. With our motto 'Keep Pioneering', we continue to drive innovation so we can use our freshness technologies to significantly reduce the amount of food that goes to waste.

Energy efficiency — 18

Our appliances take top spots in the efficiency rankings, and in some cases, even outperform the highest efficiency class. This helps them protect our precious environmental resources and your wallet.

Freezing — 36

VarioTemp	36
NoFrost	37
EasyOpen	37
FrostProtect	37
Sustainable freezing	38
BluRox	39

Water and ice — 34

Water & Ice-Centre	34
EasyTwist-Ice	35
InfinitySpring	35
IceTower	35
IceMaker	35

Overviews — 56

Series	58
Freestanding appliances product range	60
Fully integrated appliances product range	68
Wine appliances product range	75

Features | Consult pages 2 and 3 for a brief explanation



Freezers

Freestanding	38 66
Fully integrated	72




Chest freezers

Freestanding	67
--------------	----



Freestanding and fully integrated under counter appliances

Freestanding	65
Under counter	46 73



Beverages	48 73
Outdoor	49 74



Wine appliances

Freestanding	50 75
Fully integrated	77
Under counter	77

German engineering – then as now.

We have been manufacturing refrigerators and freezers of the highest quality and selling them worldwide since 1954. However, at heart we are still a family business with our roots firmly established in Germany. This is where we continue to develop our long-lasting products.

German engineering – from an enduring connection with our founder, and in the knowledge that engineering expertise has been pooled here for generations.



Dr.-Ing. e. h. Hans Liebherr (1915–1993)

Pioneering entrepreneur and visionary

With an unflinching will, Hans Liebherr developed groundbreaking inventions, and with an unmistakable instinct he developed future-oriented products. On 1st April 2015, the company founder would have turned 100.




The L 319 was Liebherr's "mobile showcase" in the 1960s. Until 1968, the specially converted bus travelled around West Germany promoting the latest refrigerators and freezers from Upper Swabia.



Main factory of Liebherr-Hausgeräte in Ochsenhausen, Baden-Württemberg, Germany

Liebherr-Hausgeräte GmbH is one of 13 product segments of the Liebherr Group. The Group is one of the largest manufacturers of construction machinery in the world. Its wide range of products is recognised in international markets for their high precision and exceptional durability.

The Domestic Appliances division employs more than 6,000 staff, developing and manufacturing a wide range of high-quality fridges and freezers for the domestic and commercial markets at its main site in Ochsenhausen (Germany) and in Lienz (Austria), Marica (Bulgaria), Kluang (Malaysia), and Chhatrapati Sambhaji Nagar (India). (Last revised: 2025)



No compromises in quality, down to the last detail

Designed in Germany, tested thoroughly and guaranteed for years: the high quality and durability of our appliances can be seen in every detail. This is why we now offer a 10-year manufacturer's guarantee on selected appliances in chosen markets and provide spare parts for all models produced since 1 January 2021 – for up to 15 years, covering all functional components and stockable equipment parts.





Our path to the future

Liebherr-Hausgeräte has established a comprehensive Corporate Responsibility (CR) strategy that defines how we work – from fair working conditions and use of resources to sustainable product design. Innovations like the BluRoX insulation, renewable energy at our sites, and spare parts availability for 15 years are part of our commitment to making a lasting impact on people, the environment, and generations to come.

For this commitment, we have received the EcoVadis Silver Medal – a globally recognised assessment of corporate responsibility.



People and sustainable business

We value equality and provide safe, fair, long-term jobs. As a family business, we take responsibility with a view to the future – not just the next quarter.

Recycling

We design for recyclability by using sustainable, simplified materials and more recycled content. Increasingly, our appliances are built for disassembly, enabling resource recovery and supporting our journey towards a circular economy.



Materials


We focus on durable, safe, and lower-impact materials– including increased use of recycled steel, plastics, and bio-based foams – making recycling easier.

Usage

Appliances run 24/7, so energy efficiency and durability matter. Many of our models are among the most efficient available, with spare parts readily available. Features like BioFresh keep food fresh for longer and help reduce waste.

Production

We are always improving the efficiency and environmental performance of our production sites – increasing the use of green electricity, reducing emissions, monitoring water use, and avoiding harmful substances wherever possible.



Learn more about our corporate responsibility

To get facts, figures, and background information, visit home.liebherr.com/sustainability





Saving food with Liebherr

Each year around the world, roughly 1,052 million tonnes of food are thrown away¹. Households account for around 60 percent of this total, with each person wasting around 132 kg annually.

132 Kilograms²

The amount of food waste can be roughly broken down into the following groups²:



50%

Fresh fruit and vegetables



4%

Dairy



5%

Meat and fish



7%

Cooked and ready-made food

Food has not only emotional and financial value, but also environmental value.

Food production is responsible for³

25%

of all global greenhouse emissions and

70%

of freshwater consumption and

50%

land suitable for farming.



¹ UNEP Food Waste Index Report (2021)

² GfK (2021). For a two-person household in Germany

³ Our World in Data (2022)



Find out more about our freshness technologies here

With our carefully considered freshness technologies and digital solutions, we help you to reduce food waste in very simple ways.

For perfect food storage, alongside the ideal temperature, optimal humidity is a decisive factor. At Liebherr, we have developed innovative freshness technologies and improve them year after year. This way, food tastes genuinely fresh even after days, and loses none of its vitamins and nutrients. For each type of fresh food, we have just the right freshness technology:

Easy Fresh

Bio Fresh

0 °C

0 °C

0 °C

Bio Fresh Professional

Hydro Breeze

Fish & Seafood

0 °C

0 °C

-2 °C



Easy
Fresh

+10 Days

+8 Days

+3 Days

+10 Days

Extended storage time compared to the fridge compartment, verified by food preservation experts at UAS Münster.

Bio
Fresh

**Fruit & Vegetable
safe**



You can find out more about the shelf life of many types of food in the BioFresh storage list online.

+12 Days

+11 Days

+40 Days

+40 Days

+48 Days

Extended storage time compared to the fridge compartment, verified by food preservation experts at UAS Münster.

Freshness technologies



EasyFresh – ideal for fruit and vegetables

Unpackaged fruit and vegetables feel right at home here. Stored at the same temperature as in the fridge compartment and sealed airtight in the safe, lettuce, for example, is still crisp and fresh after seven days.



BioFresh – our all-rounder

The reliable BioFresh technology stores groceries at a temperature of just above 0°C, much cooler than in the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable safe. Meat, fish and dairy products can enjoy ideal conditions in the Meat & Dairy safe.



BioFresh Professional with HydroBreeze – refrigerate like a pro

A cold mist covers fruit and vegetables like a protective balm, ensuring crisp freshness and improving structure – the special wow effect for fruit and vegetables in the BioFresh Professional safe.



BioFresh Professional with Fish & Seafood-Safe – like freshly caught fish from the market

Particularly delicate foods like fish and seafood are best stored in icy temperatures and at low humidity. The constant temperature of -2°C in the Fish & Seafood safe is therefore ideal for keeping food tasting fresh for longer.



DuoCooling – no drying out

Our basic technology in all fridge-freezers. The two completely separate cooling circuits ensure that there is no exchange of air between the fridge and freezer compartments. The food neither dries out nor spreads odour.



NoFrost – No more defrosting

The automatic defrosting function guarantees that frozen food remains fresh. There is no longer a need to store frozen food temporarily during a manual defrost. The constant optimal freezing remains the same without any interruptions.

+16 Days

+7 Days

+8 Days

Bio
Fresh

Meat & Dairy
safe


+90 Days

Extended storage time compared to the fridge compartment, verified by food preservation experts at UAS Münster.



Efficiency without compromise

Because they run non-stop, fridges and freezers have their greatest environmental impact during daily use – through the electricity they consume. In many households, they account for around 20 percent of total energy consumption.¹



Our fridges are real all-rounders: They combine low energy consumption with quiet operation, generous storage space, and intelligent sensors that deliver optimum cooling performance.



Energy consumption

Our appliances rank among the most energy-efficient on the market – in some cases even exceeding the highest efficiency class. That saves valuable resources and reduces energy costs over the long term.



Cooling volume

From spacious drawers to the smallest design details, our appliances make the most of every litre of cooling volume – without compromising on energy efficiency.



Noise level

Kitchens are increasingly becoming part of the living area. That's why we aim to deliver not just maximum energy efficiency, but also quieter appliances.



Refrigeration

Intelligent sensors continuously adjust cooling performance to match how the appliance is being used – keeping it efficient in everyday operation and powerful when the weekly shopping arrives.

¹ Source: German Environment Agency (UBA), 2023. Based on an average household in Germany.

Another 20% more economical* than appliances in the highest energy efficiency class A: Our freestanding fridge-freezer sets new standards – even for us.

The ultra-efficient fridge-freezer in elegant BlackSteel is one of the most energy-saving appliances on the market. The features leave nothing to be desired: For example, the BioFresh safes ensure that food stays fresh for longer, and NoFrost does away with the hassle of defrosting. The appliance is also super-quiet at just 29 dB(A).



* Ultra Efficient A -20%

Ultra Silent

Bio Fresh

No Frost

Vario Temp

Smart Device




↑
202
↓

← 60 →

Energy efficiency

Our promise:
Globally unmatched
energy efficiency.



ICBa 5123 ◊ Plus series

◊ Plus series

↑
178
↓



ICBa 5123
The first fully integrated fridge-freezer in energy efficiency class A



ICNb 5123
The first Liebherr fully integrated fridge-freezer with NoFrost in energy efficiency class B

◊ Prime series



IRBbi 5150
The first fully integrated fridge for a 178-cm recess with BioFresh in energy efficiency class B



IRBbi 5151
The first fully integrated fridge for a 178-cm recess with BioFresh and a 4* freezer compartment in energy efficiency class B



ICBNbi 5153
The first fully integrated fridge-freezer with BioFresh and NoFrost in energy efficiency class B

Simple design. Simply unmissable.

Freestanding appliances
in Liebherr's new DarkGrey
colour tone

An added touch of elegance for your kitchen:
The new DarkGrey colour tone (RAL 7024)
combines modern design with stylish subtlety.
The calm aesthetic adds a warm touch to the
kitchen and blends harmoniously with materials
such as wood, stone, or concrete. The appliance
becomes an elegant eye-catcher in any tastefully
designed kitchen.

Make a statement.

The puristic design language of a Liebherr appliance catches the eye with its exceptional lines and elegant surfaces. A classic, exclusive look that allows our appliances to blend seamlessly into any modern kitchen while still standing out.



XRFsf 5245 ◊ Plus series



Recessed grip

This handle does not extend into the room. The elegant recess blends in with your kitchen's sleek, handle-free design.



Handle with opening mechanism

The door handle adapts gently to your hand movement, making it particularly easy to open.



XRCst 5295 Δ Peak series



Fits perfectly.

With InteriorFit, our freestanding appliances fit into the kitchen and save space – they do not require any ventilation gap at the side facing any walls or adjacent furniture. Only the fridge door protrudes into your kitchen. Everything else is invisible.



BlackSteel and SmartSteel interior

BlackSteel and stainless steel appliances have BlackSteel or SmartSteel interiors, creating a striking feature on the interior.



Tasteful inside and out

No matter how much you love the exterior of a Liebherr, at some point, you actually have to open it. So it's a good job that the interior is visually appealing as well.



Glass and steel look interior

The inner door also features elegant glass and real metal components. The precise machining, an eye for detail and the harmonious combination of materials, shapes and colours create an appealing overall appearance.



LightTower

This special lighting concept illuminates the interior evenly and supports the glass shelves. Flexible, space-saving, unique.



Divisible glass shelf

To quickly create space for tall containers, the front half of the glass shelf can be slid under the back half. This means you don't have to remove the whole glass shelf.

The features shown are dependent on the model.



Big interior

For all baking enthusiasts, our fully integrated appliances even provide space for a baking tray.



Drawers on telescopic rails

Easy to open and close, even when full – so that all your groceries are always in easy reach.

Our appliances with a glass and steel look interior satisfy special design aspirations: The rear wall and, depending on the model, the door panel are finished with high-quality, real metal features. For freestanding appliances, they're colour-coordinated with the SmartSteel and BlackSteel material on the exterior. This means the interior is also very eye-catching and a sight for you to enjoy each time you open the door.

Glass & Steel-look Interior

178

Freshness with zoom factor

Our ergonomic drawers are easy to use. They are therefore particularly easy to reach, for maximum clarity.



VarioSafe

This allows you to arrange smaller items neatly in the interior – at whatever height you like.



Flexibly chilled: separate drawers for all storage needs

The new VarioCool drawers can be set independently to a temperature of between 0 and +14 °C. This allows ice-cold drinks and delicate foods to be stored in separate, individually adjustable compartments.



Flexible storage space

Extra storage space – thanks to VarioSpace: In our integrated and under counter freezers and freezer compartments, individual drawers can be removed. Perfect for storing even oversized frozen food items.





One beverage store. Two options.

The practical pull-out shelf on telescopic rails in the IRDdi 5120 is equipped with two removable bottle baskets for easy transport. It can also be loaded with a whole crate of beverages to quench your thirst.

All BioFresh safes are also very easy to open when full: The telescopic rails mean the drawers will slide gently towards you. And thanks to SoftTelescopic, the safes also close almost by themselves with just a slight push.



For the best overview

Both the GlassLine drawers and the pull-out drawer in our under counter models close conveniently and safely – thanks to SoftTelescopic with a self-closing mechanism and soft closing mechanism.



The features shown are dependent on the model.

Superb, even down to the smallest detail

How would we describe our new French Door appliances? Superb, in the truest sense of the word. With maximum storage space for freshness and quality down to the finest detail, the appliances cater for your every wish.

Visually, the impressive fridge-freezers boast sophisticated design elements and features, including the MoodLight, the Water & Ice centre, and the VarioTempZone. Ample space for freshness behind the French doors – whether with EasyFresh, BioFresh or BioFresh Professional with HydroBreeze. Open the doors individually and easily thanks to our patented FlexDoorSystem. Plus, these combination appliances are available in two versions: as a French-door fridge compartment with two freezer drawers or with four French doors, one pair on the fridge and one on the freezer compartment. So 'superb' is no understatement when it comes to the new French Door appliances.





← 91 →

↑
181
↓

MBsddi 9558 ◯ Prime series

MoodLight

The indirect lighting concept aesthetically highlights the Water & Ice-Centre and the recessed grips of the freezer drawers, and can be dimmed to suit your taste.



Mood
Light

Water &
Ice
Centre

Vario
Temp
Zone

Flex
Door
System

Bio
Fresh
Professional

Hydro
Breeze

Glass &
Steel
Interior

No
Frost

Soft
System

Smart
Device



FlexDoorSystem

Quiet opening and closing: With the patented FlexDoorSystem, the French doors also open and close individually very easily and securely, and the 100% tight closure saves energy.



Water & Ice-Centre

The Water & Ice-Centre supplies cold water, ice cubes, and crushed ice 24 hours a day. Practical: The water volume of the water dispenser can be set individually for each container size.



MBbsdi 9028 ♦ Plus series

Water & Ice Centre

Bio Fresh

Vario Temp Zone

Flex Door System

Glass & Steel-look Interior

No Frost

Soft System

Smart Device



VarioTempZone

Maximum flexibility: The VarioTempZone can be set to the exact degree from -18 to -10 °C and from -2 to +5 °C, turning it into an extra cooling zone if required.

SmartSteel



BlackSteel



TerraSteel



Surface options

Whichever material you choose, one thing is certain: Your appliance will catch the eye.

Designed for exquisite kitchens and the highest aspirations

SmartSteel



XRCst 5295 Δ Peak series

BlackSteel



XRCbs 5295 Δ Peak series

↑
185
↓

←121→

The generous BioFresh Professional safes, including HydroBreeze in the top safe, plenty of space in the NoFrost freezer compartment with IceMaker, and a separate wine-tempering compartment make our side-by-side fridge-freezers an elegant freshness hub in your kitchen. And thanks to InfinitySpring in the fridge compartment, chilled water is always available on tap.

2
Zones

max. 44

No
Frost

Ice
Maker

Bio
Fresh
Professional

Hydro
Breeze

Infinity
Spring

Glass &
Steel-look
Interior



reddot winner 2025

XRCbs 5295 Δ Peak series

Specially designed for cool drinks

With Liebherr, your guests will always be able to enjoy drinks that are perfectly chilled. This is thanks to the integrated cold water source and a never-ending supply of ice. The easy way to have constant refreshment.




Direct access: the Water & Ice-Centre

In the door of our new fridge-freezers with French doors (see also page 28 – 31), the Water & Ice-Centre provides you with plenty of cold water, ice cubes, and crushed ice 24 hours a day.



Ice in an instant: EasyTwist-Ice

Quickly rustle up a supply of ice cubes – without a plumbed-in connection. Simply fill the tank with water, let it freeze and then release the ice cubes with a twist. EasyTwist-Ice is easy to clean and is a feature in most of the freestanding appliances in our Pure series. Alternatively, it can also easily be added as an accessory.



Ice-cold water on tap with no heavy lifting

With InfinitySpring, we bring a crystal-clear, cold water source right into the heart of your kitchen, so you can always stay hydrated. Making the lugging of heavy crates and water in plastic bottles a thing of the past. This relieves the strain on your back and on our environment. Simple and sustainable.



Enough ice for even the largest party: the IceTower

The IceTower in the freezers of our side-by-side combinations sets new standards by combining two large compartments – the automatic IceMaker for up to 8 kg of ice cubes and another spacious compartment – large enough to store a few family-sized pizzas upright, for example. And because we wanted to make this even more convenient, both of them glide in and out on a pull-out shelf with telescopic rails.



It's raining ice cubes: the IceMaker

Each day the IceMaker produces up to 130 ice cubes, which automatically drop into two drawers. When MaxIce is activated, it's even possible to speed up ice production if more guests than expected turn up. The IceMaker is connected to the fresh water pipe. If no plumbed-in connection is available, there is also a model with a water tank in the fridge compartment.

The features shown are dependent on the model.



CBNsda 575i ◯ Prime series



Fridge compartment
(-2 °C to +9 °C)



Cellar compartment
(+14 °C)



Freezer compartment
(-18 °C)

Vario Temp

Versatile freshness with the freezer compartment that can also refrigerate

With VarioTemp, you can accurately set the temperature of the freezer compartment in your fridge-freezer from -2 °C to +14 °C. This means, for example, you can use this space as an extra cooling zone at parties – or as a ‘cellar compartment’. Don’t need the freezer compartment? Then switch it off independently of the fridge compartment and save energy and money.

Freezing – made easy



Convenience of never having to defrost

There's no longer any need to store frozen food temporarily during a manual defrost, thanks to NoFrost technology. This is possible because the frozen food is frozen with cooled recirculated air, and the humidity in the air is also dissipated. This keeps the freezer compartment ice-free at all times so food is no longer covered in frost. The constant optimal freezing remains the same without any interruptions.




Open the door multiple times with ease: EasyOpen

Done this before? After putting all the shopping in the freezer you remember an item of food you have forgotten – and have to give the door a good pull to open it again. With your Liebherr, you don't need to do this. EasyOpen means the door can be opened multiple times, one after another, conveniently and easily.



When below zero is a big plus

No room for a freezer in the kitchen or other heated areas in your home? We have good news: with FrostProtect, all the relevant components are designed for temperatures as low as -15°C , no matter what groceries you're storing. If the ambient temperature drops below 0°C , our freezers continue working efficiently, saving as much energy and keeping your frozen food protected. This means that you can put them in unheated spaces like a garden shed or garage, giving you extra space for more important things.



The features shown are dependent on the model.

It's what's inside that counts.

At first glance, the new FNa 6635 looks like any other Liebherr freezer, but there's much more inside. Each component has been selected carefully to develop an appliance that not only offers optimum energy efficiency, but also has the lowest impact on the environment.



FNa 6635 ♦ Plus series



Inner liner and insulating foam

Both the inner liner and the insulating foam contain recycled materials and materials obtained from organic sources. These reduce the environmental impact while providing the same excellent insulation performance.

Product packaging

The environmental footprint of the packaging has also been reduced without compromising safety during transport.



Side panels and door

The door and side panels are made from 100% recycled steel, the production of which generates 80% less CO₂ emissions than the production of conventional steel.

Door seal

The TPE used for the door seal combines optimum functionality, durability and good recyclability.

For more information about the sustainability of the materials used, go to home.liebherr.com/fna6635

Sustainable freezing revolutionised – with vacuum and volcanic rock.

Our vacuum perlite technology is an innovation that will transform refrigeration and freezing. Introducing BluRoX.



BluRoX

G Made
in Germany

Our pioneering BluRoX technology features perlite, finely ground volcanic rock, in a vacuum insulation. This enables unmatched energy efficiency as well as a significant increase in the freezing volume with the same exterior dimensions. Unlike conventional insulation methods, the unique and patented BluRoX technology provides optimum thermal conductivity, which significantly reduces energy consumption and sets a new benchmark in sustainable cooling.



The first hybrid model with BluRoX in the door, as well as the first NoFrost freezer (165 cm) in energy efficiency class B.

FNB 505i ◊ Prime series




To learn more about this exciting technology and the many benefits of BluRoX, go to home.liebherr.com/blurox



One less task for you.

Our AutoDoor feature perfectly complements the handle-less kitchen, as the Liebherr appliances open automatically in response to a knock, via the SmartDevice app, or by smart speaker voice command.

Plus, the door does more than just open automatically; it makes things easier for you in every way as its settings can be adjusted to suit your habits. The opening angle and how long the door stays open before it closes automatically can be individually selected. Anybody who still prefers to open and close our fully integrated appliances by hand is still, of course, free to do so. You can recognise our fully integrated fridges and freezers with the AutoDoor function by the 'A' in the model name.



Find out more about our automatic door on selected models at: home.liebherr.com/autodoor

Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com

Transform your kitchen into a market stall.

Inspired by display cabinets in fine delicatessens, the award-winning OpenStage drawers in this fully integrated fridge showcase all groceries at a glance. We're setting new standards in ease of use and design. In the lower area, three additional BioFresh safes offer you the perfect climate for storing fruit and vegetables as well as meat, fish and dairy products.



For maximum accessibility

Your groceries are presented with maximum clarity and are within ideal reach ergonomically.

↑
178
↓

Open Stage

Light Tower

Glass & Steel-look Interior

Bio Fresh


IRBpci 5170 △ Peak series

Freshness in French door and LargeDoor format

Thanks to their generous format, these models are ideal for large families who do a big weekly shop.



Fully integrated models with French door and LargeDoor

The extra-large fully integrated combinations boast a grey inner liner and an updated visual design. And in even class E, they're now much more energy efficient.



Upgrade for the kitchen: freestanding French door

Brushed stainless steel elements on the door and trims, a grey inner liner and improved energy efficiency to class E make our freestanding French door even more attractive.





- Bio Fresh
- Light Tower
- Glass & Steel-look Interior
- No Frost
- Ice Maker
- Soft-Telescopic Rails
- Soft System
- Smart Device




Made in Germany

ICBNci 5663 ◊ Prime series

For the highest standards

We are expanding our range of fully integrated fridge-freezers. Or, should we say, we're raising it – literally. Our 194 cm-tall XL fully integrated fridge-freezers fit seamlessly into high-quality kitchen designs and impress in every way: two BioFresh safes, the highest energy efficiency in their class, and a timeless, elegant design. Discover our new XL fully integrated appliances from the Pure, Plus and Prime series – perfect for anyone with the very highest aspirations.





← 75 →

↑
201
↓

Bio
Fresh

Light
Tower

Glass &
Steel
Interior

No
Frost

Easy
Twist Ice

Soft-
Telescopic
Rails

Soft
System

Smart
Device

A
↑
G


CBNsda 775i ◊ Prime series

The highest level of energy efficiency.

The CBNsda 775i freestanding fridge-freezer combines the highest energy efficiency class A with a generous width of 75 cm. Numerous freshness technologies, such as VarioTemp, NoFrost, and the largest-ever BioFresh safe, offer the best storage conditions with unrivalled low energy consumption. Ideal for environmentally conscious families with a long shopping list.



CBNsda 775i ◊ Prime series



Got a recess? How about a kitchen island? There are lots of integration options



↑
82-88
↓



2
Zones

No
Frost

UWgbi 3682 Vinidor Selection

SUFnc 375i ◯ Prime series

Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com

They are easy to plan, simple to install and impressively equipped: The Liebherr under counter appliances are now available in both 82 to 88 cm and 86 to 92 cm heights, which means they fit perfectly under any work surface.

With many clever interior solutions, the compact fridges, freezers and wine fridges are real space-saving wonders. We are certain that with a wide range of models and equipment options, every customer will find exactly what they are looking for.

What's more, our side-by-side concept allows you to design your individual freshness centre. Combine a fridge with a freezer and/or wine fridge. The Liebherr technology prevents condensation, protecting the appliances and the kitchen furniture perfectly.




↑
86-92
↓

↑
82-88
↓


↑
86-92
↓

Easy
Fresh

URc 375i ◊ Prime series



+9 l
more cooling
volume



Drinks and a design to suit every taste

It's nice to have a choice. This applies to drinks as much as it does to the fridge. That's why the new under counter beverage fridges from Liebherr give your customers plenty of options to choose from. The range includes three new models in two series and with two different front options.

↑
86-92
↓



Beverage

Touch & Swipe Display

LED

Smart Device

UBCpr 376i ◊ Prime series

Store bottles securely and in style

The sturdy metal shelf with an elegant wooden front combines functionality with an attractive design. It provides a secure hold for bottles while adding a touch of elegance to the fridge.



Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com

A companion for your barbecue.

Our outdoor under counter appliances are the ideal solution for patios, gardens or pool areas. Their robust construction and high-quality materials are designed to withstand temperatures from -10 °C to +32 °C, guaranteeing perfect performance all year round.



Easily accessible at any time

Elegant and extremely practical: The pull-out shelf made of satin-finish glass slides smoothly on rails. One-handed operation and safety stops deliver convenience and protection during use – and the satin finish makes scratches virtually invisible.



Outdoor

Touch & Swipe Display

LED

Door Lock

Smart Device

82-88

IPX4



UORpr 366i ○ Prime series

Treasuring true taste.

Discover our wine fridges – and find out how you can not only store your collection under the perfect conditions, but also preserve the very essence of the wine.



You and your wine selection decide: 1, 2, or 3 zones.



Wine fridges with one temperature zone are specially designed for storing and ageing a large number of bottles. The conditions inside are similar to a wine cellar.

The temperature can be adjusted precisely between +5 °C and +20 °C.

For the most energy-efficient storage without any outside influences, we recommend solid-door models.

If you want to store a larger supply of wine at the ideal serving temperature in your kitchen or wherever your wine will be enjoyed, our single-zone models with a glass door are the perfect choice.

In our wine fridges with up to three independent temperature zones, red wines, white wines and champagnes can all be stored at their ideal temperature for drinking.

Each zone can be adjusted precisely between +5 °C and +20 °C.

With temperature zones of varying sizes in models with 2 and 3 zones and flexible temperature setting, these appliances are perfect for accommodating any individual wine collection.

And as fridges with a focus on temperature control are usually placed directly in the kitchen or the place where the wine will be consumed, a glass door ensures that the contents are showcased and clearly presented.



You will find useful facts about wine and our wine appliances in our Wine Special magazine or online at home.liebherr.com/wine



SommelierBoard

A real highlight in our Vinidor Selection series! There's room to show off everything you need for decanting. The high-quality shelf made of natural beechwood comes with a stainless-steel bottle presenter, a wooden box for decanting utensils and a space for tempering wine glasses for that extra-special enjoyment.



LightTower

One of the most important design elements is the lighting. In our Vinidor Selection models, the LightTower vertical lights on each side showcase the wine collection beautifully. The lighting can be activated each time the door is opened, or remain on at all times when the dimmable presentation light is set.



Vertical recessed grip

All models in the Vinidor Selection series have a recessed vertical grip extending the entire length, allowing for ergonomic and comfortable opening from any position. Models with the optically discreet grip integrate particularly harmoniously into handle-free kitchens and living-dining areas.



FlexFit wooden shelves

The removable slats of the FlexFit wooden shelves ensure they accommodate any bottle, even magnums. Thanks to the individual placement of the trims in the frame, all bottles are stored safely.



More information about wine storage and tempering and our wine fridges, including detailed model descriptions, can be found in our Wine Special magazine, which is available from your Liebherr specialist dealer or at home.liebherr.com/wine



3
Zones

Sommelier
Board

Light
Tower

Flex
Fit

Humidity
Select

Soft
System

Smart
Device



2
Zones

3
Zones

WPgbi 7483 Vinidor Selection

With two or three separate temperature zones that can be independently set to an accurate temperature of between +5 °C and +20 °C, our wine fridges can be used in the most flexible ways. This means that red wines, white wines, and champagnes can all be stored at the same time and at the ideal temperature for drinking in one single appliance that has three temperature zones. With their temperature zones of different sizes and temperature settings that offer complete flexibility, these appliances are perfect for each wine collection.



1
Zone

Humidity
Select

Smart
Device
Ready

1
Zone

WSbl 5001 GrandCru

Single-zone wine fridges are specially designed to enable a large number of bottles to be stored and to age over time, but they can also keep a larger supply of wine at the perfect temperature for drinking. For the most energy-efficient storage without any outside influences, we recommend solid-door models. Models with a glass door are also available if you want to be able to see directly inside.

Only the key equipment details are listed here. Detailed model descriptions can be found at [home.liebherr.com](https://www.home.liebherr.com)



Humidity regulation

On GrandCru models, HumiditySelect allows the humidity to be adjusted to two settings: Dehumidify or humidify. GrandCru Selection models are equipped with HumidityControl. This function allows the humidity to be set as required within the range of 50% to 80% RH*. If the value falls below 50% RH, the appliance indicates this.



For a protected view inside

To minimise the effect of harmful ultraviolet light, our glass-door models are fitted with special UV-resistant insulated glass. Depending on the model, we offer UV-Protect with double glazing or UV-Protect Plus with triple anti-UV glazing for maximum protection.



Neck-to-neck storage for maximum bottle capacity

A Liebherr wine storage fridge also makes it easier to organise a growing wine collection. To take full advantage of its capacity, the interior has been designed so that your wine bottles can be stored neck-to-neck on the wooden shelves. This means there is plenty of room even for ever-increasing wine collections. So feel free to keep collecting.



FreshAir activated charcoal filter

To ensure that your wine can mature in air of the best quality, all Liebherr wine fridges have an activated charcoal filter that reliably protects wine from all kinds of odours. This means your wine will retain its pure bouquet. To make sure that it stays that way, your Liebherr will remind you every six months to change the filter, which you can easily do yourself.

* Within home environments, Such as very dry or cold cellars, we recommend supporting the system with the tailor-made water box from our range of accessories.

Freshness in many forms, sizes, and to suit every need

If you want to know more details, you will find our extensive range of fridges, freezers, and wine fridges on the following pages.



IRBbsci 5170 Δ Peak series | EWTgb 3583 Vinidor | SIFNbsdi 5188 Δ Peak series



Use pages 2 and 3, they explain the most important features in our overview for your desired model, or so you can compare several models.

For a clear overview –
before you even view
the product range

○ Pure

◇ Plus



⬡ Prime

△ Peak

Which appliance is right for me?
This question is not always easy to answer when you are buying a new appliance. That's why we have made it even easier for you to find your way around our range of products by dividing our fridges and freezers into four series.

○ Pure series

The Pure series is our basic class: simple, clear and perfectly equipped to cover all essential requirements. Pure series appliances have been reduced to the basics, but are full to the brim with the highest Liebherr quality.



◇ Plus series

The Plus series builds on our Pure series and stands out with additional details. Plus here particularly means a plus in convenience. The appliances are not only first-class in their refrigeration and freezing capabilities, but they are also that little bit smarter. This means they help make lots of manual tasks a little easier.

⬡ Prime series

The Prime series is all about class. It makes an unmistakable mark in terms of design and material. In particular, real materials are used inside the appliances. Special lighting solutions also ensure that appliances in this series have a captivating appearance.



△ Peak series

The Peak series is our top-of-the-line series. Here, the best is combined with the best. There is no compromise. Innovative Liebherr technology combines with exceptional high-end design and convenience in a class of its own. Appliances in this series are for those who want to have it all.

Freestanding appliances



↑ 181
← 91 →

MBsddi 9558 ◊ Prime series

Key to series:

- = Pure series
- ◇ = Plus series
- ◊ = Prime series
- △ = Peak series



CBNste 8872



MBbsdi 9556



MBsddi 9058

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Vario Temp Zone	Water & Ice Centre	Ice Maker	Easy Twist Ice	Infinity Spring	Mood Light	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	----------	-----------------	--------------------	-----------	----------------	-----------------	------------	--------------



French door fridge-freezers

↑ 203 ← 91 →	CBNste 8872*	▶ E A G											
	↓ 181 ← 91 →	MBsddi 9558	◊ D A G	☁									
with 2 drawers 	MBbsdi 9556	◊ D A G	☁										
	MBbsdi 9556	◊ D A G	☁										
	MBsddi 9528	◇ D A G											
	MBbsdi 9528	◇ D A G											
	MBtsdi 9528	◇ D A G											
	MBsddi 9524	◇ D A G											
	MBsddi 9524	◇ D A G											
with 4 doors 	MBsddi 9058	◊ D A G	☁										
	MBsddi 9028	◇ D A G											
	MBbsdi 9028	◇ D A G											
	MBsddi 9024	◇ D A G											
	MBtsdi 9024	◇ D A G											
	MBbsdi 9024	◇ D A G											
	MBbsdi 9024	◇ D A G											
	Msd 9012	○ D A G											ready

LEX

*Without BluPerformance technology

Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com

Key to appliance material:

- _st SmartSteel
- _sd SmartSteel door
- _bs BlackSteel
- _bd BlackSteel door
- _ts TerraSteel
- _sf SteelFinish
- _ White

Key to handle solutions:

- ¹ Handle with opening mechanism
- ² Recessed grip



SFNsfd 5237 + SRsfd 5230
XRFsf 5230



SWNbsd 529i + SRBbsc 529i



SFNsfd 5227 + SRsfd 5220

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	Wine
------------	----------------	---------------	------------------------	-----------	------------	----------	-------------	-----------	-----------	-----------------	--------------	------

Fixed Side-by-Side sets: freezer + fridge

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	Wine
--120-- 186 186	XRFsf 5230	◇										
	SFNsfd 5237	◇	▶			■						ready
	SRsfd 5230	◇	▶		■							ready
	XRF 5230	◇										
	SFNd 5237	◇	▶			■						ready
	SRd 5230	◇	▶		■							ready

For Side-by-Side placement: wine / freezer combinations

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	Wine
--121-- --123-- 186	SWNstd 529i ¹	△	▶			■	■		■		■	■
	SWNbsd 529i ¹	△	▶			■	■		■		■	■

For Side-by-Side placement: fridges

Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	Wine
SRBstc 529i ¹	△	▶	☁			■			■	■	
SRBbsc 529i ¹	△	▶	☁			■			■	■	
SRBsdd 526i ¹	◻	▶	🐟			■				■	
SRsdc 525i ¹	◻	▶		■		■					■
SRsdd 5230 ¹	◇	▶		■							ready
SRBsfc 5220 ²	◇	▶		■							ready
SRbdd 5220 ²	◇	▶		■							ready
SRsdd 5220 ²	◇	▶		■							ready
SRsfd 5220 ²	◇	▶		■							ready
SRd 5220 ²	◇	▶		■							ready

For Side-by-Side placement: fridge-freezer

Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	Wine
SBNsdd 526i ¹	◻	▶		■		■	■		■		■

For Side-by-Side placement: freezers

Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Soft System	Ice Tower	Ice Maker	Infinity Spring	Smart Device	Wine
SFNstd 529i ¹	△	▶			■	■	■	■			■
SFNbsd 529i ¹	△	▶			■	■	■	■			■
SFNsdd 526i ¹	◻	▶			■	■	■	■			■
SFNsfd 5247 ²	◇	▶			■		■	■			ready
SFNsdd 5237 ¹	◇	▶			■						ready
SFNbdd 5227 ²	◇	▶			■						ready
SFNsdd 5227 ²	◇	▶			■						ready
SFNsfd 5227 ²	◇	▶			■						ready
SFNd 5227 ²	◇	▶			■						ready

Overview | Freestanding appliances product range

Key to series:

- = Pure series
- ◇ = Plus series
- ⊕ = Prime series
- △ = Peak series



CBNsda 775i



CBNbsa20 575i



CNsda 5723

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Vario Temp	Soft System	Ice Maker	Easy Twist Ice	Infinity Spring	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	----------	------------	-------------	-----------	----------------	-----------------	--------------

BLU Fridge-freezers with BioFresh Professional / BioFresh

202 ↕ ← 75 →	CBNbsc 778i	△										
	CBNsda 775i	⊕										
202 ↕ ← 60 →	CBNstb 579i	△										
	CBNbsa20 575i	⊕										
	CBNsda 575i	⊕										
	CBNsda 572i	◇										
	CBNbda 572i	◇										
	CBNa 572i	◇										
	CBNsdc 573i	◇										
	CBNbdc 573i	◇										
	CBNdgc 5733	◇										ready
	CBNsfc 572i	◇										
	CBNc 5723	◇										ready
	186 ↕ ← 75 →	CBNsdc 765i	⊕									
186 ↕ ← 60 →	CBNsda 5223	◇										ready
	CBNbda 5223	◇										ready
	CBNsfc 5223	◇										ready
	CBNc 5223	◇										ready

BLU Fridge-freezers with EasyFresh

202 ↕ ← 75 →	CNsdd 776i	⊕										
	CNsfa 7723	◇										ready
	CNbdd 7723	◇										ready
	CNsfd 7723	◇										ready
	CNd 7723	◇										ready
202 ↕ ← 60 →	CNsda 5723	◇										ready
	CNbda 5723	◇										ready
	CNsdb 5723	◇										ready
	CNsfc 574i	◇							water tank			
	CNbdc 573i	◇										
	CNc 5724	◇										ready

Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com



CNdgc 5703



CNbdb 5223



CUele 3331

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Smart Frost	Vario Temp	Soft System	Ice Maker	Easy Twist Ice	Infinity Spring	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	----------	-------------	------------	-------------	-----------	----------------	-----------------	--------------

BLU Fridge-freezers with EasyFresh

202 ↑ ↓	← 60 →	CNa 5713	○				■	■					ready
		CNc 5713	○				■	■					ready
		CNsfd 5704	○				■	■					ready
		CNd 5704	○				■	■					ready
		CNdgc 5703	○				■	■					ready
		CNsfd 5703	○				■	■					ready
		CNd 5703	○				■	■					ready
186 ↑ ↓	← 60 →	CNbdb 5223	◇				■	■			■		ready
		CNsdb 5223	◇				■	■			■		ready
		CNb 5213	○				■	■					ready
		CNdgc 5213	○				■	■					ready
		CNc 5213	○				■	■					ready
		CNsdc 5203	○				■	■					ready
		CNsfd 5203	○				■	■					ready
		CNd 5203	○				■	■					ready
166 ↑ ↓	← 60 →	CNc 5023	◇				■	■					ready

Fridge-freezers

181 ↑ ↓	← 55 →	CUele 3331					■						
		CUe 3331					■						
161 ↑ ↓	← 55 →	CUele 2831					■						
		CUe 2831					■						
137 ↑ ↓	← 55 →	CUele 2331					■						
		CUe 2331					■						
157 ↑ ↓	← 55 →	CTele 2931					■						
		CTe 2931					■						
140 ↑ ↓	← 55 →	CTele 2531					■						
		CTe 2531					■						
124 ↑ ↓	← 55 →	CTele 2131					■						
		CTe 2131					■						

Overview | Freestanding appliances product range

Key to series:

- = Pure series
- ◇ = Plus series
- ⬡ = Prime series
- △ = Peak series



RBbsc 528i



RBsdc 525i



RBa30 425i

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	Smart Frost	Soft System	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	-------------	-------------	--------------

BLU Fridge with BioFresh Professional / BioFresh

186 ↑ ↓	← 60 →	RBbsc 528i	△	C A G					■	■	
		RBbsb 525i	⬡	B A G		■			■	■	
		RBsdc 525i	⬡	C A G		■			■	■	
		RBsfc 5220	◇	C A G		■					ready
		RBc 5220	◇	C A G		■					ready
		RBsfd 5221	◇	D A G		■		■*			
126 ↑ ↓	← 60 →	RBa30 425i	⬡	A A G		■				■	



RDsfd 5220



Rd 5000



Rd 4600

BLU Fridge with EasyFresh

186 ↑ ↓	← 60 →	RDsfd 5220	◇	D A G		■				ready
		Rd 5220	◇	D A G		■				ready
166 ↑ ↓	← 60 →	Rd 5000	○	D A G		■				ready
146 ↑ ↓	← 60 →	Rd 4600	○	D A G		■				ready
126 ↑ ↓	← 60 →	Rd 4200	○	D A G		■				ready

Fridges

140 ↑ ↓	← 55 →	Ke 2834		E A G						
114 ↑ ↓	← 55 →	Ke 2350		E A G						

* with 4* freezer compartment

LEX



Rsdci 1620



Rdgd 1401



Rd 1200

Dimensions	Model / series	Energy rating	Easy Fresh	Smart Frost	Door Stop	Smart Device
Under counter fridges						
85 ↕ ↔ 60 ↔	Rsdci 1620	◇ C A/B	■		■	■
	Rsdci 1621	◇ C A/B	■	■*		■
	Rdi 1620	◇ D A/B	■		■	■
	Rdi 1621	◇ D A/B	■	■*		■
85 ↕ ↔ 55 ↔	Rc 1400	○ C A/B			■	
	Rc 1401	○ C A/B		■*		
	Rdgd 1400	○ D A/B			■	
	Rdgd 1401	○ D A/B		■*		
85 ↕ ↔ 50 ↔	Rd 1200	○ D A/B			■	
	Rd 1201	○ D A/B		■*		
68 ↕ ↔ 55 ↔	Re 1000	○ E A/B			■	

* with 4* freezer compartment

LEX

Overview | Freestanding appliances product range

Key to series:

- = Pure series
- ◇ = Plus series
- ⬡ = Prime series
- △ = Peak series



FNC 727i



FNa 6635



FNb 505i



Dimensions	Model / series	Energy rating	No Frost	Telescopic Rails	Easy Open	Frost Protect	Easy Twist Ice	LED	Smart Device
------------	----------------	---------------	----------	------------------	-----------	---------------	----------------	-----	--------------

Freezers with NoFrost

186 ↕ ←70→	FNC 727i	△	C	■	■	■	■	■	■
	FNC 7227	◇	C	■	■	■	■	■	ready
	FND 7227	◇	D	■	■	■	■	■	ready
166 ↕ ←70→	FNC 7026	◇	C	■	■	■	■	■	ready
146 ↕ ←70→	FNa 6635	◇	A	■	■	■	■	■	ready
	FNa 6625	◇	A	■	■	■	■	■	ready
	FNC 6625	◇	C	■	■	■	■	■	ready
186 ↕ ←60→	FNC 527i	△	C	■	■	■	■	■	■
	FND 525i	⬡	D	■	■	■	■	■	■
	FND 5237	◇	D	■	■	■	■	■	ready
	FNE 5207	○	E	■	■	■	■	■	ready
166 ↕ ←60→	FNb 505i	⬡	B	■	■	■	■	■	■
	FND 505i	⬡	D	■	■	■	■	■	■
	FND 5036	◇	D	■	■	■	■	■	ready
	FNE 5006	○	E	■	■	■	■	■	ready
146 ↕ ←60→	FNb 465i	⬡	B	■	■	■	■	■	■
	FNC 4625	◇	C	■	■	■	■	■	ready
	FND 4635	◇	D	■	■	■	■	■	ready
	FNE 4605	○	E	■	■	■	■	■	ready
126 ↕ ←60→	FNb 425i	⬡	B	■	■	■	■	■	■
	FND 4234	◇	D	■	■	■	■	■	ready
	FNE 4204	○	E	■	■	■	■	■	ready

LEX



FNsddi 1624



Fdgd 1404



Fe 1003

Dimensions	Model / series	Energy rating	No Frost	Smart Frost	Frost Protect	LED	Smart Device
------------	----------------	---------------	----------	-------------	---------------	-----	--------------

Under counter freezers

85 ↕	← 60 →	FNsddi 1624	◇		■		■	■	■
		FNdi 1624	◇		■		■	■	■
		Fci 1624	◇			■	■	■	■
85 ↕	← 55 →	FNe 1404	○		■		■	■	
		Fc 1404	○			■	■	■	
		Fdgd 1404	○			■	■	■	
		Fd 1404	○			■	■	■	
		Fe 1404	○			■	■	■	
68 ↕	← 55 →	Fe 1003	○			■	■	■	



CFd 2505



CFd 2085



CFc 1875

Dimensions	Model / series	Energy rating	Stop Frost	Super Frost	Smart Frost	Soft System	Frost Protect	LED
------------	----------------	---------------	------------	-------------	-------------	-------------	---------------	-----

Chest freezers

82 ↕	← 167 →	CFd 2505	◇		■	■	■	■	■
		CFe 2500	○		■	■	■	■	■
82 ↕	← 125 →	CFd 2085	◇		■	■	■	■	■
		CFe 2080	○		■	■	■	■	■
82 ↕	← 104 →	CFc 1875	◇		■	■	■	■	■

LEX

Side
by
Side

↑
178
↓

Fully integrated appliances

Your individual freshness centre

Combine your Liebherr fully integrated appliance with complete flexibility to suit your freshness needs. Many models can be vertically and / or horizontally combined to form an individual freshness centre, providing perfect solutions to all your storage needs.

Ask your Liebherr dealer or kitchen specialist about the Liebherr Side-by-Side concept.

SIFNdi 5188 △ Peak series | EWTdf 3553 Vinidor | IRBci 5180 △ Peak series

ⓘ Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

ⓘ For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.



ECBNe 8872



ECBNe 8870



ECBNe 7870

Dimensions	Model / series	Energy rating	Bio Fresh	No Frost	Soft System	Ice Maker
------------	----------------	---------------	-----------	----------	-------------	-----------

Integrated fridge-freezers

203 ↕ ↔ 91,5 ↔	ECBNe 8872	▶ E	■	■	■	■
	ECBNe 8870	▶ E	■	■	■	■
	ECBNe 8871	▶ E	■	■	■	■
203 ↕ ↔ 76,2 ↔	ECBNe 7870	▶ E	■	■	■	■
	ECBNe 7871	▶ E	■	■	■	■

LEX

Key to series:

- = Pure series
- ◇ = Plus series
- ⬡ = Prime series
- △ = Peak series



ICBNci 5663



ICBNci 5183



ICNbsci 5173

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	No Frost	Smart Frost	Vario Temp	Soft System	Ice Maker	Infinity Spring	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	----------	-------------	------------	-------------	-----------	-----------------	--------------

Integrated fridge-freezers with BioFresh Professional / BioFresh

194 → 56-57 →	ICBNci 5663	⬡	C			■			■	■		■
	ICBNd 5653	⬡	D			■			■	■		ready
	ICBNc 5623	◇	C			■			■			ready
	ICBNSd 5623**	◇	D			■						ready
178 → 56-57 →	ICBNci 5183	△	C				■		■	■	■	■
	ICNbsci 5173	△	C				■		■	■	■	■
	ICBNdi 5163	⬡	D			■			■	■		■
	ICBNci 5153	⬡	C			■			■	■		■
	ICBbi 5152	⬡	B			■		■		■		■
	ICBa 5123	◇	A			■		■		■		ready
	ICBNdi 5123	◇	D			■			■			■
	ICBbi 5122	◇	B			■		■		■		■

Integrated fridge-freezers with EasyFresh

194 → 56-57 →	ICNd 5603	○	D			■	■					ready
	ICNSd 5603**	○	D			■	■					ready
178 → 56-57 →	ICNbsci 5173	△	C			■	■		■	■		■
	SICNdi 5153	⬡	D			■	■		■	■		■
	ICNd 5133	◇	D			■	■		■	water tank		ready
	ICNd 5123	◇	D			■	■		■			ready
	ICNSd 5123**	◇	D			■	■					ready
	ICNe 5103	○	E			■	■					ready
	ICNSe 5103**	○	E			■	■					ready
	ICe 5103	○	E			■		■				ready
	ICSe 5103**	○	E			■		■				ready

** with sliding door instead of door-on-door assembly
You can find the full range of efficiency ratings on page 3. According to (EU) 2017/1369 6a.

Overview | Fully integrated appliances product range

▮ Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

▮ For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.



IRBPci 5170



IRBAc 5190-001



IRBbsci 5170

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	Smart Frost	Soft System	Auto Door	Infinity Spring	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	-------------	-------------	-----------	-----------------	--------------

Integrated fridges with BioFresh Professional / BioFresh

178 ↕ ←56-57→	IRBPci 5170	△	C					■			■
	IRBAc 5190-001	△	▮	C	☁			■	■	■	■
	IRBAc 5190-617	△	▮	C	☁			■	■	■	■
	IRBci 5180	△	C	☁				■		■	■
	IRBci 5170	△	C	☁				■			■
	IRBbsci 5170	△	C	☁				■			■
	IRBbi 5150	○	B					■			■
	IRBci 5150	○	C					■			■
	IRBd 5120	◇	D					■			ready
	IRBd 5121	◇	D				■*	■			ready
	IRBSd 5120**	◇	D								ready
140 ↕ ←56-57→	IRBci 4550	○	C					■			■
	IRBc 4520	◇	C					■			ready
122 ↕ ←56-57→	IRBci 4150	○	C					■			■
	IRBc 4120	◇	C					■			ready
102 ↕ ←56-57→	IRBc 4020	◇	C					■			ready

with 4 freezer compartment

LEX

Key to series:

- = Pure series
- ◇ = Plus series
- = Prime series
- △ = Peak series



IRDdi 5120



IRd 4520



DRe 4101

Dimensions	Model / series	Energy rating	Bio Fresh Professional	Bio Fresh	Easy Fresh	Smart Frost	Soft System	Auto Door	Infinity Spring	Smart Device
------------	----------------	---------------	------------------------	-----------	------------	-------------	-------------	-----------	-----------------	--------------

Integrated fridges with EasyFresh

178 ↕ -56-57-→	IRDdi 5120	◇	D			■		■		■
	IRd 5100	○	D			■				ready
	IRe 5100	○	E			■				ready
	IRe 5101	○	E			■	■*			ready
140 ↕ -56-57-→	IRd 4520	◇	D			■		■		ready
122 ↕ -56-57-→	IRc 4120	◇	C			■		■		ready
	IRc 4121	◇	C			■	■*	■		ready
	IRd 4100	○	D			■				ready
	IRd 4101	○	D			■	■*			ready
	IRSe 4100**	○	E			■				ready
	IRSe 4101**	○	E			■	■*			ready
88 ↕ -56-57-→	IRci 3950	◇	C			■		■		■
	IRc 3920	◇	C			■		■		ready

Fridges with décor panel

122 ↕ -56-57-→	DRe 4101***	○	E			■	■*			ready
88 ↕ -56-57-→	DRe 3900***	○	E			■				ready

* with 4* freezer compartment

** with sliding door instead of door-on-door assembly | *** décor panel ready
You can find the full range of efficiency ratings on page 3. According to (EU) 2017/1369 6a.

Overview | Fully integrated appliances product range

Liebherr appliances are typically delivered with door hinges on the right (interchangeable).

For models where the door hinge cannot be interchanged, the entry also indicates the models with a left hinge.



SIFNAd 5188-001



SIFNbsdi 5188



IFNci 3954

Dimensions	Model / series	Energy rating	No Frost	Smart Frost	Soft System	Ice Maker	Ice Tower	Auto Door	LED	Smart Device
Integrated freezers										
178 ↕ ← 56-57 →	SIFNAd 5188-001 △	I	D	■	■	■	■	■	■	■
	SIFNAd 5188-617 △	I	D	■	■	■	■	■	■	■
	SIFNbsdi 5188 △		D	■	■	■	■		■	■
	SIFNdi 5188 △		D	■	■	■	■		■	■
	SIFNdi 5178 △		D	■	■				■	■
	SIFNSe 5128** ◇		E	■						ready
	SIFNe 5128 ◇		E	■	■					ready
	SIFNe 5108 ○		E	■						ready
140 ↕ ← 56-57 →	SIFNdi 4556 ○		D	■	■				■	■
	SIFNdi 4155 ○		D	■	■				■	■
88 ↕ ← 56-57 →	IFNci 3954 ○		C	■	■				■	■
	SIFNci 3954 ○		C	■	■				■	■
	IFNd 3924 ◇		D	■	■					ready
72 ↕ ← 56-57 →	IFNbi 3553 ○		B	■	■				■	■
	IFNd 3503 ○		D	■						ready

LEX

Key to series:

- = Pure series
- ◇ = Plus series
- = Prime series
- △ = Peak series



SUBa30 375i

A
-30%



URDd 375i



URPd 365i

Dimensions	Model / series	Energy rating	Bio Fresh	Easy Fresh	No Frost	Smart Frost	Vario Cool Drawers	Soft System	LED	Smart Device
------------	----------------	---------------	-----------	------------	----------	-------------	--------------------	-------------	-----	--------------

Under counter fridges

86-92 ↑ ↓ ← 60 →	SUBa30 375i	⬡		■				■		■
	URPc 375i	⬡						■		■
	URc 375i	⬡		■				■		■
	URDd 375i	⬡					■	■		■
	URc 3700	○								
	URc 3701	○					■*			
82-88 ↑ ↓ ← 60 →	URPd 365i	⬡						■		■
	URd 365i	⬡		■				■		■
	URd 3600	○								
	URd 3601	○					■*			
	DURd 3600***	○								
	DURd 3601***	○					■*			

* with 4* freezer compartment



UBCpr 376i



UBCgb 3731

Dimensions	Model / series	Energy rating	Soft System	LED	Smart Device	Beverage
------------	----------------	---------------	-------------	-----	--------------	----------

Under counter beverage fridges

86-92 ↑ ↓ ← 60 →	UBCpr 376i***	⬡		■	■	■	■
	UBCgb 3731	◇			■	ready	■

LEX

** with sliding door instead of door-on-door assembly | *** décor panel ready |
 **** beverage and outdoor fridges correspond to EU regulation 2019/2018 for commercial appliances.
 You can find the full range of efficiency ratings on page 3. According to (EU) 2017/1369 6a.

Key to series:

- = Pure series
- ◇ = Plus series
- ⬡ = Prime series
- △ = Peak series



UORpr 366i



UORpr 365i

Dimensions	Model / series	Energy rating	Soft System	Door Lock	LED	Smart Device	Outdoor
------------	----------------	---------------	-------------	-----------	-----	--------------	---------

Under counter outdoor fridges

82-88 ↑ ↓ ← 60 →	UORpr 366i***	⬡		■	■	■	■
	UORpr 365i***	⬡		■	■	■	■



SUFNc 375i



SUFc 3703



SUFd 3603

Dimensions	Model / series	Energy rating	No Frost	Smart Frost	Soft System	LED	Smart Device
------------	----------------	---------------	----------	-------------	-------------	-----	--------------

Under counter freezers

86-92 ↑ ↓ ← 60 →	SUFNc 375i	⬡		■		■	■
	SUFc 3703	○			■		
82-88 ↑ ↓ ← 60 →	SUFNpc 365i	⬡		■		■	■
	SUFNd 365i	⬡		■		■	■
	SUFd 3603	○			■		
	SDUFd 3603***	○			■		

LEX

*** décor panel ready | **** beverage and outdoor fridges correspond to EU regulation 2019/2018 for commercial appliances. Only the key equipment details are listed here. Detailed model descriptions can be found at home.liebherr.com

Wine appliances



WPgbi 7473 Vinidor Selection



WPgbi 7483



WPbsi 5252



WPbsi 5052

Dimensions	Model / series	Energy rating	3 Zones	2 Zones	Glass Door	Humidity Select	UV Protect Plus	Sommelier Board	Soft System	Smart Device	
201 ↕ ↔ 70 ↔	WPgbi 7483 Vinidor Selection		■		■	■	■	■	■	■	149
	WPgbi 7473 Vinidor Selection		■		■	■	■		■	■	182
185 ↕ ↔ 60 ↔	WPgbi 5283 Vinidor Selection		■		■	■	■	■	■	■	85
	WPgbi 5273 Vinidor Selection		■		■	■	■		■	■	104
201 ↕ ↔ 70 ↔	WPgbi 7472 Vinidor Selection			■	■	■	■		■	■	204
	WPgbi 5272 Vinidor Selection			■	■	■	■		■	■	106
185 ↕ ↔ 60 ↔	WSbsi 5252 Vinidor			■		■			■	■	155
	WPbsi 5252 Vinidor			■	■	■	■		■	■	155
	WPsd 5252 Vinidor			■	■	■	■			ready	155
165 ↕ ↔ 60 ↔	WPbsi 5052 Vinidor			■	■	■	■		■	■	131
145 ↕ ↔ 60 ↔	WPsd 4652 Vinidor			■	■	■	■			ready	107

* Maximum capacity of Bordeaux bottles (0.75 l) based on: H: 300.5 mm, ø: 76.1 mm. You can find the full range of efficiency ratings on page 3. According to (EU) 2017/1369 6a.

Overview | Freestanding wine fridges product range



WSbli 7731



WPbli 5231



WSbl 5001

Dimensions	Model / series	Energy rating	1 Zone	Glass Door	Humidity Control	Humidity Select	UV Protect Plus	Smart Device	
------------	----------------	---------------	--------	------------	------------------	-----------------	-----------------	--------------	--

Freestanding wine fridges

204 ↑ ↓	← 75 →	WSbli 7731	GrandCru Selection		■		■		■	324
188 ↑ ↓	← 60 →	WPbli 5231	GrandCru Selection		■	■	■		■	229
		WSbli 5231	GrandCru Selection		■		■		■	229
168 ↑ ↓	← 60 →	WPbli 5031	GrandCru Selection		■	■	■		■	196
		WSbli 5031	GrandCru Selection		■		■		■	196
		WPbl 5001	GrandCru		■	■		■	■	ready
		WSbl 5001	GrandCru		■					ready
		WSbl 5001	GrandCru		■					ready
148 ↑ ↓	← 60 →	WPbl 4601	GrandCru		■	■		■	■	ready
		WSbl 4601	GrandCru		■					ready
128 ↑ ↓	← 60 →	WPbl 4201	GrandCru		■	■		■	■	ready
		WSbl 4201	GrandCru		■					ready



WKes 653




ZKes 453

Dimensions	Model / series	Energy rating	1 Zone	Glass Door	Humidity Control	Humidity Select	UV Protect	Cigar	
------------	----------------	---------------	--------	------------	------------------	-----------------	------------	-------	--

Freestanding compact appliances

61 ↑ ↓	← 43 →	WKes 653	GrandCru		■	■		■	■	12
		ZKes 453	Humidor			■		■	■	



Bordeaux bottle size (0.75 l)
All specifications regarding bottle capacity refer to these dimensions.



EWTgb 3583



EWTdf 2353



EWTgb 1683

Dimensions	Model / series	Energy rating	2 Zones	1 Zone	Glass Door	Humidity Select	UV Protect Plus	UV Protect	Soft System	Tip Open	Smart Device	
------------	----------------	---------------	---------	--------	------------	-----------------	-----------------	------------	-------------	----------	--------------	--

Integrated wine fridges

178	-56-57-	EWTgb 3583	Vinidor		■	■	■	■	■	■	■	83
		EWTdf 3553***	Vinidor		■	■	■	■	■	■	■	80
122	-56-57-	EWTgb 2383	Vinidor		■	■	■	■	■	■	■	51
		EWTdf 2353***	Vinidor		■	■	■	■	■	■	■	48
88	-56-57-	EWTgb 1683	Vinidor		■	■	■	■	■	■	■	33
		EWTdf 1653***	Vinidor		■	■	■	■	■	■	■	30



WKEgb 582



WKEes 553

Integrated wine fridges

45	-56-57-	WKEgb 582	GrandCru		■	■	■	■	■	■	■	18
45	-56-	WKEes 553	GrandCru		■	■	■	■	■	■	■	18



UWgbi 3782



UWpri 3672



UWgb 3632

Under counter wine fridges

86-92	-60-	UWgbi 3782	Vinidor Selection		■	■	■	■	■	■	■	38
		UWpri 3782***	Vinidor Selection		■	■	■	■	■	■	■	38
		UWpri 3762***	Vinidor Selection		■	■	■	■	■	■	■	38
		UWpri 3761***	Vinidor Selection		■	■	■	■	■	■	■	44
82-88	+60-	UWgbi 3682	Vinidor Selection		■	■	■	■	■	■	■	32
		UWpri 3672***	Vinidor Selection		■	■	■	■	■	■	■	32
		UWpri 3662***	Vinidor Selection		■	■	■	■	■	■	■	32
		UWgb 3632	Vinidor		■	■	■	■	■	■	ready	32
		UWpri 3661***	Vinidor Selection		■	■	■	■	■	■	■	44
		UWgb 3631	Vinidor		■	■	■	■	■	■	ready	44

*Maximum capacity of Bordeaux bottles (0.75 l) based on: H: 300.5 mm, ø: 76.1 mm. | *** décor panel ready
You can find the full range of efficiency ratings on page 3. According to (EU) 2017/1369 6a.

Practical accessories for every need

Discover the versatility of the Liebherr range of accessories and make your daily life that little bit easier.



VarioSafe and bottle shelf



FlexSystem



Bottle shelf



SmartDeviceBox

You can retrofit your Liebherr with a SmartDeviceBox to connect it to the internet. The SmartDeviceBox can be installed in just a few steps and will open up the whole world of digital possibilities to you.



FreshAir activated charcoal filter

Cleans the circulating air, is easy to replace, and ensures optimum air quality.



Ice cube tray with lid

Award-winning design

Our appliances continue to impress the most renowned design juries and regularly win major awards such as the German Design Award, the iF Award, and the Red Dot Award. The minimalist Liebherr design and the impressive details create a stylish space for your food.



MBsddi 9558 ◯ Prime series





Always well connected

Almost all Liebherr appliances are either factory-equipped with a network connection module or can be retrofitted with the SmartDeviceBox.

This allows you to benefit from the many possibilities that our SmartDevice app offers and from integrating your fridges, freezers, and wine fridges into your existing smart home environment. Important status and alarm notifications are sent directly to your smartphone, for example notification via the door alarm of a fridge door being left open. Our SmartDevice app has much more to offer besides: As well as simple management and remote control of your appliances, the app also helps you with tips and tricks for your Liebherr appliance. The right accessories for each appliance, access to instruction manuals and much more can also be found here.

You can download the SmartDevice app here:



Read more at:
home.liebherr.com/getsmart



Simple design. Simply unmissable.

Freestanding appliances
in Liebherr's new DarkGrey
colour tone



Fdgd 1404 ○ Pure series



home.liebherr.com

Products and their details are staged for advertising purposes. Subject to technical changes. Deviations in colour are due to printing processes.
The models shown are not available in all countries. 7904 532-00 EN-LEX. 03.26.