


---

# Waste management

---

## LIEBHERR

Material handling



# Liebherr specialist machines for waste management

---

The recycling industry is growing rapidly and is changing. In recent years, many waste disposal companies have developed from generalists to highly specialised recycling operations. This has brought with it a whole new set of challenges to be met by the machines used in the recycling industry. Liebherr acknowledges this and develops machines and equipment options for every need and application. Because we manufacture many different components ourselves, for example engines, fuel injection systems, hydraulic cylinders, etc. which have to be optimally configured for each other, Liebherr offers extremely capable, yet efficient machines. Even during the development of these components, the requirements of future applications are taken into account to ensure that Liebherr specialist machines are optimally prepared for every feasible working situation. Liebherr material

handling machines are used for a wide variety of tasks in the recycling and waste management sector. Mobile material handling machines, crawler material handlers, wheel loaders and telescopic wheel loaders, bulldozers and crawler loaders all sort, separate and load recyclables and solid waste quickly and reliably. These materials include glass, metal, wood, paper and agricultural waste, to name but a few. In addition to state-of-the-art diesel-powered material handlers, Liebherr also offers environmentally friendly and economical alternatives with electric drive.

- Material handling machines
- Wheel loaders and telescopic wheel loader
- Crawler dozers
- Crawler loaders





# Material handling machines

---



## Performance

The recycling industry is highly varied. The generation of Liebherr material handlers are adept at a wide range of tasks: feeding a conditioner or crusher, loading and unloading trucks and containers, sorting materials and waste products and piling up and moving materials of all kinds. There are many challenges and Liebherr has the right solutions. The optimal interaction between the hydraulics and electronics guarantees fast and powerful movements when handling materials and at the same time sensitive and precise work for challenging sorting tasks.

## Economy

The existing generation of material handling machines are powerful, while remaining efficient. The Group achieves this standard of efficiency by utilizing its own internal components which are highly compatible with the controlled hydraulics in the machine. Liebherr relies on state-of-the-art engine technology with intelligent machine controls that optimize the interplay of the drive components in terms of efficiency. In addition to diesel-powered machines there are a number of electric drive material handlers in the range which guarantee extremely low operating costs. They are very environmentally friendly, completely emission-free and therefore independent of statutory exhaust emission standards. For conventional machines Liebherr-Power Efficiency (LPE) enables machine operation in the area of lowest specific energy use for less consumption and greater efficiency with maximum performance.

## Reliability

Liebherr material handling machines ensure smooth operation in waste handling thanks to their sturdy and durable design. Equipment such as air filters with dust extraction, reversible fans or coarse matrix radiators have been especially developed for deployment in areas heavily contaminated with dust and also guarantee maximum reliability under these demanding conditions. Long service life along with maximum machine availability are also assured by the in-house production of all key components: diesel engine, hydraulic and electronic components, slew ring, swivel drive and steel structure, developed, tested and produced by Liebherr all at the high level of quality one would expect.

## Comfort

The Liebherr cab gives the operators the necessary space to make the best possible use of the machine's capability. Large glass panels, different types of cab elevations and rear and side area monitoring enable the operator an optimum view of the working area and the area around the machine at all times. Thanks to the low sound emissions and the lack of vibrations, the electric handling machines are particularly quiet and increase the working comfort significantly. Additionally, the Comfort driver's seat, the intuitive touchscreen colour display, and central lubrication systems for the machine and its attachments offer the necessary convenience for operators to focus on what is important – the handling capacity.

## Maintainability

The service-based machine design guarantees short servicing times, thus minimising maintenance costs. All the maintenance points are easily accessible due to the large, wide-opening service doors. The enhanced service concept places the maintenance points close to each other and reduces their number to a minimum. This means that service work can be completed even more quickly and efficiently.

# Material handling machines overview


---

## Uppercarriage

- Greater energy efficiency due to the latest engine technology with intelligent machine control
- Optimal engine output and high pump flow for fast work cycles, convincing dynamics and maximum handling performance
- Recycling package with reversible fan, air pre-filter with dust trap and external air conditioning condenser to ensure high machine availability
- Optimised servicing concept and cleverly designed maintenance access points guarantees minimum machine downtime

## Undercarriage

- Various undercarriage options available including one with a dozer blade to further increase machine versatility
- Central lubrication system manual or fully automatic for more productive working time
- Standard load holding valves fitted on all support cylinders for maximum stability in every application
- Less downtime thanks to maintenance free support cylinders





## Equipment

- High load capacities and extensive reach due to optimised kinematic properties and robust construction for greater handling performance
- Ingenious routing of hydraulic hoses optimises the oil flow and minimises power losses for maximum energy efficiency
- Pipe fracture safety valves on hoist and stick cylinders and retract stick shut-off for maximum safety during every application
- Quick coupling systems and attachments made by Liebherr for maximum machine capacity utilisation and greater handling performance



## Cab

- Joystick steering without steering column to facilitate convenient operation, greater legroom and clear view of the working area
- Less strain on the operators and workers and reduced environmental pollution due to lower noise emissions
- Optimum visibility thanks to large glass surfaces and standard rear and side area monitoring camera
- Standard proportional control with 4-way mini joystick for greater precision, high precision control and functions

# Technical data

		LH 18 Industry Litronic	LH 22 Industry Litronic
Variants		M	M/C
System performance		-	-
Reach	m	9	11
Operating weight*	kg	approx. 17,000-18,000	approx. 19,200-22,200
Engine output	kW/HP	105/143	105/143
Emission stage	Stage	V/Tier 4 Final	V/Tier 4 Final/IIIA (compliant)
Sorting grab capacity	m <sup>3</sup>	0.40-0.70	0.40-1.10
Multi-tine grab capacity	m <sup>3</sup>	0.4	0.40-0.60

		LH 24 Industry Litronic	LH 26 Industry Litronic
Variants		M	M/C
System performance		-	105 <sup>1)</sup>
Reach	m	12	13
Operating weight*	kg	approx. 22,700-23,200	approx. 24,200-27,900
Engine output	kW/HP	110/150	90 <sup>1)</sup> 115/157
Emission stage	Stage	V/Tier 4 Final	V/Tier 4 Final/IIIA (compliant)/electric
Sorting grab capacity	m <sup>3</sup>	0.50-1.10	0.50-1.10
Multi-tine grab capacity	m <sup>3</sup>	0.40-0.60	0.40-0.60

		LH 30 Industry Litronic	LH 35 Industry Litronic
Variants		M/C	M
System performance		-	-
Reach	m	14	15
Operating weight*	kg	approx. 26,500-30,200	approx. 30,700-31,900
Engine output	kW/HP	140/190	140/190
Emission stage	Stage	V/Tier 4 Final/IIIA (compliant)	V/Tier 4 Final/IIIA (compliant)
Sorting grab capacity	m <sup>3</sup>	0.75-1.15	0.75-1.15
Multi-tine grab capacity	m <sup>3</sup>	0.40-0.60	0.40-0.60

M = Mobile



C = Crawler

\* without attachment

<sup>1)</sup> only with electric

# Examples of use

---



# Wheel loaders and telescopic wheel loader

---



## Performance

A wide range of products ensures the versatile and universal use of Liebherr wheel loaders in the field of waste management. In addition to the different models, you can choose between industrial and Z-bar kinematics with the L 550 – L 566 XPower wheel loaders and the L 580 XPower. This means the right machine is always available for the specific application such as loading and compacting bulk goods in high “walking floor” containers. This increases the utilisation of the machine and thus increases productivity. The new L 507 E battery-electric wheel loader is ideal for indoor applications. This machine gives off zero emissions on-site and is extremely quiet while still maintaining its usual high working efficiency. The tried and tested stereo steering ensures a very small turning radius and a great versatility in everyday work.

## Economy

The innovative drive concepts of the Liebherr wheel loaders reduces fuel consumption by up to 30%. In addition there is minimal tyre wear and hardly any brake wear, at maximum handling capacity and efficiency, thus reducing operating costs and also protecting the environment.

## Reliability

Liebherr wheel loaders satisfy Liebherr's exacting standards in even the toughest conditions. They feature many components which are produced in-house and are therefore perfectly tailored to work in synergy. This ensures machine reliability and availability.

## Comfort

The modern, ergonomic cab design provides the operator with maximum comfort enabling them to concentrate on their work without fatigue, which once again means more safety and productivity. The Liebherr control lever allows precise and sensitive control of the machine. This ensures accurate and safe handling. The generous glass surfaces of the cab offer excellent all-round visibility thus ensuring maximum safety for people, the machine and the load.

## Maintainability

The Liebherr wheel loaders offer excellent service accessibility. All points for daily maintenance can be reached safely and conveniently. A clear benefit which saves time and money!

# Wheel loaders L 526 – L 580 XPower overview

## Maximum operator comfort for greater productivity

- Automatic central lubrication system\*
- Liebherr control lever with mini joystick\*
- Joystick steering\*
- Operator's cab without steering wheel / steering column – joystick steering only\*
- Liebherr weighing system with "Truck Payload Assist"\*
- Ride control (L 526 – L 546\* / L 550 – L 580 as standard)
- Preparation for protective ventilation and dust filtration device\*
- Stroke limit damping\*

## Highest level of performance

- Industrial lift arm linkage or Z-bar linkage (L 550 – L 566 and L 580\*)
- High Lift arms\*
- Solidlink quick hitch\*
- Programmable automatic bucket return
- Programmable automatic lift and lowering arm position
- Comprehensive range of special equipment for waste management\*
- Electronic tractive force regulation

## Robustness and quality for durable machines

- Tilt cylinder protection\*
- Lamp carrier in steel design (L 526 – L 546 as standard / L 550 – L 580\*)
- Guard for headlights\*
- Integral tyre pressure monitoring system\*
- Special tyres for waste management\*

\*optional





## Productive and safe working

- Soundproof ROPS / FOPS cab
- Windscreen guard\*
- Additional working lights, front / rear\*
- Adaptive working lighting\*
- Roof camera for front area monitoring (with Liebherr camera via Liebherr display)\*
- Skyview 360°\*
- Visualisation of the equipment position
- Liebherr key with remote control incl. Coming Home / Leaving Home function (L 550 - L 580\*)

## Short service times for greater productivity

- Radiator easy to maintain
- Fluff trap for radiator\*
- Large-mesh radiator\*
- Reversible fan drive\*
- Air pre-cleaner\*
- Turbocharger insulation (L 550 - L 580\*)
- Dust protection for alternator\*

## Productive and safe working

- Anti-slip steps and sturdy handrails
- Rear space monitoring camera via Liebherr display
- Active personnel detection at the rear\*
- Reversing obstruction detector\*
- Back-up alarm acoustic / visual\*

## Robustness and quality for durable machines

- Crash protection, rear\*
- Crash protection, rear with guard (L 526 - L 546\*)
- Ramming guard with guard (L 550 - L 580\*)
- Chassis protection\*
- Widening for mudguard\*

# Technical data

		L 507 Stereo	L 509 Stereo	L 514 Stereo
Tipping load	kg	3,240-3,750	3,400-4,430	3,770-5,750
Bucket capacity	m³	0.8-1.6	0.9-2.0	1.3-3.5
Operating weight	kg	5,550-5,835	6,390-6,875	8,860-9,985
Engine output	kW/HP	50/68	54/73	76/103
Emission stage	Stage	V	V	V

		L 518 Stereo	L 526	L 538
Tipping load	kg	3,870-6,550	5,030-8,730	6,220-9,650
Bucket capacity	m³	1.4-4.0	2.0-5.5	2.2-6.5
Operating weight	kg	9,190-10,445	13,170-14,770	14,520-16,050
Engine output	kW/HP	76/103	116/158	129/175
Emission stage	Stage	V	V	V

		L 546	L 550 XPower	L 556 XPower
Tipping load	kg	7,130-11,010	8,300-12,500	9,300-13,750
Bucket capacity	m³	2.6-7.5	2.6-9.5	2.8-10.0
Operating weight	kg	15,410-16,970	18,550-20,600	19,600-21,600
Engine output	kW/HP	138/188	163/222	183/249
Emission stage	Stage	V	V	V

		L 566 XPower	L 576 XPower	L 580 XPower
Tipping load	kg	12,100-15,900	16,250-17,600	14,800-19,500
Bucket capacity	m³	3.5-12.0	4.2-5.2	4.5-14.0
Operating weight	kg	23,900-26,900	25,650-25,800	27,650-30,100
Engine output	kW/HP	203/276	218/296	233/317
Emission stage	Stage	V	V	V

		L 509 Tele
Tipping load	kg	3,600-3,800
Bucket capacity	m³	0.9-2.0
Operating weight	kg	6,800-7,150
Max. payload, forklift	kg	2,300 <sup>1)</sup>
Max. lifting height, forklift	mm	4,800
Engine output	kW/HP	54/73
Emission stage	Stage	V

		L 507 E
Tipping load	kg	3,240-3,750
Bucket capacity	m³	0.8-1.6
Operating weight	kg	5,815-6,195
Battery	kWh	32.2/64.4
Emission stage		emission-free

<sup>1)</sup> Maximum payload on even terrain = 80% of the static tip load when articulated- in accordance with EN 474-3

# Examples of use

---



# Crawler dozers

---



## Performance

Liebherr crawler dozers are ideal for pushing, shredding, mixing, stockpiling and distributing all waste types on the landfill. At the same time, they compact the waste or do the prepwork for the compactors so that they can be used even more efficiently. In addition, dozers are used in all excavation work, such as site preparation or leveling of surfaces. The grids are specially designed for use on landfills and increase the shield volume and thus the thrust without restricting the driver's view. A range of optional equipment is available to protect and extend the life of the undercarriage and other components.

## Economy

Liebherr diesel engines offer performance and economic efficiency from the hydrostatic drive, which consumes a lower amount of fuel. The innovative cooling system enables the radiator to self-clean; this feature lowers maintenance and fuel costs for the customer.

## Reliability

Liebherr crawler dozers feature a wide range of protective guards for landfill applications. These prevent damage to the machine caused by oversized solid items and reduce the dust and dirt contamination. This prolongs the service life of the machines and prevents unnecessary downtimes.

## Comfort

Liebherr crawler dozers offer operators a spacious and comfortable workspace. This cab provides a comprehensive view of the working area and equipment. The single lever control system, allows the machine to be controlled safely and precisely at all times.

## Maintainability

Liebherr crawler dozers have minimal maintenance requirements, however; posses easily accessible service points when needed. This service feature lowers maintenance time and costs for customers.

# Crawler dozers overview

## Operational safety

- The hydraulic fans cool when required to save fuel
- A hydraulic oil thermometer monitors the oil temperature constantly
- The reversible fans automatically clear the radiator of deposits

## Protection against contamination

- A pre-filter separates particles of dirt before they reach the air filter
- The external air supply provides the alternator with clean cooling air
- Seals at critical positions keep dust and dirt away from inside the machine

## Application-specific equipment

- Waste grille extensions on the blade increase its capacity
- Counterweights provide optimum balance even with heavy duty front equipment
- Rear rippers enable work to be carried out away from the rubbish tip





## Additional safety options

- Auxiliary headlights and rotating beacons
- Turbocharger cover
- Fire extinguishers

## Damage protection

- Solid protective plates prevent damage to the containers and tanks
- Special covers protect the hydraulic cylinders
- Rear scraper plates (not shown) prevent waste material from being drawn into the chain and causing damage

## Running gear components

- Base plates with trapezoidal holes and track drive segments with recesses prevent unwanted congestion of material in the running gear
- Protective rings on the final drive protect the double slide ring seal

# Technical data

		<b>PR 736 Litronic</b>	<b>PR 736 Litronic</b>
Operating weight	kg	21,200–25,500	21,200–25,500
Blade capacity	m³	4.1–5.57	4.1–5.57
Engine output	kW / HP	160 / 217	160 / 217
Emission stage	Stage	IIIA (compliant) / Tier 3	V / Tier 4 Final



		<b>PR 746 Litronic</b>	<b>PR 746 Litronic</b>
Operating weight	kg	25,900–31,500	25,900–31,500
Blade capacity	m³	6.00–7.20	6.00–7.20
Engine output	kW / HP	190 / 258	190 / 258
Emission stage	Stage	IIIA (compliant) / Tier 3	V / Tier 4 Final

		<b>PR 756 Litronic</b>	<b>PR 756 Litronic</b>
Operating weight	kg	35,400–43,000	35,400–43,000
Blade capacity	m³	8.92–11.80	8.92–11.80
Engine output	kW / HP	260 / 353	260 / 353
Emission stage	Stage	IIIA (compliant) / Tier 3	V / Tier 4 Final

		<b>PR 766 Litronic</b>	<b>PR 766 Litronic</b>
Operating weight	kg	53,460–54,333	53,460–54,333
Blade capacity	m³	13.6	13.6
Engine output	kW / HP	310 / 422	310 / 422
Emission stage	Stage	IIIA (compliant) / Tier 3	V / Tier 4 Final

# Examples of use

---



# Crawler loaders

---



## Performance

Whether its household or natural waste – Liebherr crawler loaders prove to be all-rounders in the construction phase as well as in the operating and renovation phase. They can be used for the installation and pre-compaction of waste as well as for the application of surface layers, for material handling and for various auxiliary work. Crawler loaders with their high breaking forces are indispensable for sorting out bulky waste fractions or excavating loamy or frozen soil. Their unmatched traction on unstable ground benefits them when pushing garbage, working on embankments or recovering trucks that have got caught.

## Economy

Due to their versatility, minimal maintenance requirements and low fuel consumption, Liebherr crawler loaders are suitable as universal machines for smaller landfills or are as an integral part of the vehicle fleet at larger landfills. The bucket shape and volume, as well as the grid and cutting tool can be precisely adapted to the general conditions of quality of the waste and cover material at the landfill. As an option, the machine can also be equipped with a rear ripper. The demand-driven hydraulics and reduced engine speed in ECOmode further reduce fuel consumption.

## Reliability

Liebherr has decades of experience in the development, design and manufacture of key components such as support frames, diesel engines, hydraulic cylinders, final drives and electrics. When used on landfills, extensive protective measures against dust, particles, deposits, alkalis or acids as well as bulky or falling material are added. Thanks to sophisticated technology and innovative detail solutions, Liebherr crawler loaders offer maximum availability and service life even under the toughest operating conditions.

## Comfort

The pressurised cab with powerful air conditioning, effective sound insulation, air-suspended seat, hydraulic cab suspension and optional windshield protection offers ideal conditions for safe, relaxed and productive work. The intuitive, sensitive single lever control and unobstructed view of the work equipment allow the operator to concentrate fully on their work.

## Maintainability

The long maintenance intervals and easily accessible service points of the Liebherr crawler loaders are of particular importance in intensive continuous operation at the landfill site, ensuring that they are ready for use at all times. For the user, a dense service network means short distances, optimum planning, high availability of spare parts and fast repairs. As part of the new Liebherr Reman range, components can be economically reconditioned to the highest industrial standards.

# Crawler loaders overview

## Safety

- Polycarbonate windscreen and protective grille made from impact resistant glass for increased safety of the operator, while maintaining clear view to the front
- Container protection made from solid steel provides protection of the hydraulic tank or AdBlue tank
- Hydraulic oil thermometer as gauge on touchscreen display

## Durably designed equipment

- Heavy duty tilt cylinder guard protects against falling parts
- Lift cylinder line guard for best protection of hydraulic lines as well as greater reliability of components in exposed areas
- Attachment grille for bucket increases bucket capacity and makes it easier to shift bulky material





## Maintenance concept

- Seal between basic unit and cab prevents the accumulation of dirt in cavities and niches as well as its penetration into the cab
- Fine grids on engine compartment doors reduce the penetration of small particles into the engine compartment
- Foldable and reversible fan for easy access to the radiator. Interval and duration of the reversible fan can be individually adjusted as needed
- The new air prefilter system cleans the intake air of dust and dirt particles, dust is discharged automatically from the main filter

## Detailed drive protection solutions

- Track shoes with a dirt hole avoid deposits, which can accumulate between the bushings and track shoes. Particularly effective in combination with gutted turrass segments
- End drive protective ring as additional protection for the double mechanical seal
- Scraper plate on rear for better self-cleaning of chain running gear

# Technical data

		<b>LR 626 Litronic</b>	<b>LR 636 Litronic</b>
Operating weight	kg	16,460-19,360	21,690-23,047
Bucket capacity	m³	2.22-2.35	2.49-2.62
Engine output	kW / PS	110 / 150	135 / 184
Emission stage	Stage	V / Tier 4 Final	V / Tier 4 Final

# Examples of use

---



# Strong partner – strong service

Our services are perfect for the challenges you face every day



## Saving time – for experts who face the challenges themselves

Hand in hand to find the perfect solution. Do you want to maintain and service your machines yourself? Do you want to order the spare part you require quickly and flexibly regardless of your location and the time and be certain that you have selected the correct part?

The documentation available online and the spare parts shop in MyLiebherr enable you to access all the information you require with just a few clicks. Use our sophisticated logistics for fast deliveries of the parts you require, all in genuine quality of course. That will enable you to work efficiently. And if you're not sure what to do next, our experts are just a phone call away.



For further information, services and contact details, go to

## Transparency – your payment professionals have full details of availability, costs and much more at all times

Modular maintenance packages and Reman components to suit your company and budget. Are figures and the information they convey your strong point? Do you want to keep your current investments under review at all times and ideally be able to calculate in advance how much using the machine will cost and know all about its availability values?

Liebherr's modular CarePacks are tailored to your needs to show you in advance precisely what costs you can expect to ensure that your machine will continue to perform at its best in the future. For older machines, our Reman range delivers a smart, low cost solution for you.

## Reliability and support – for decision-makers and advance planning

You are not just interested in short term success, you want to be successful in the long term. Do you regard success not just as turnover, but also satisfied customers and helping to protect resources?

Our dense service network delivers consistency and a basis for planning, today and in the future.

If necessary, our experts are available for you 24/7. Our genuine parts and service experts able you to ensure that your machines retain their value. Our Reman range and a range of lubricants enable you to be successful at low cost whilst also protecting valuable resources.

### Some of our services for you in detail:



#### A strong partner

The safe feeling of having a strong partner by your side. Our dense service network means that our service experts are always close at hand. It is important to us that you always have a personal contact because when you need assistance, it's good to know that it's always available.



#### Reman range

The same performance and quality as a new part whilst reducing costs – that is what the replacement parts in our Reman range deliver. A wide range of components is available every day. An ideal solution, particularly for older machines, and at the same time you are helping to protect valuable resources by reusing parts.



#### Lubricants

Our portfolio of lubricants includes a series of products which enable you to actively help protect resources, including oils with longer change intervals or which are not harmful to the environment. One side-effect of these products is that they can also protect your wallet.



#### CarePacks

Our modular CarePacks can provide you with tailored packages of services at a fixed charge. That leaves you to concentrate on your work.

Liebherr Connect

# The networking of man, machine and environment

---

## Networking in the digital world of Liebherr

Thanks to intelligent machine networking, Liebherr Connect enables access to digital services and comprehensive machine and process data. When using fleet and asset management systems, Liebherr Connect forms an essential basis for any type of component or machine condition monitoring. The solution also enables efficient data exchange and opens up a wide range of possibilities for further developing the machines and adapting them to individual customer requirements.

Liebherr Connect ensures that the machine is connected to the digital world via cloud applications – in almost all of the Group's product segments: earthmoving machines, material handling machines, mining, tower cranes, mobile and crawler cranes, maritime cranes and components. To help customers and partners throughout the entire life of an application, the Group provides the assurance to use all the benefits of modern technology with Liebherr Connect. This, in turn, allows users to optimise their work processes.



Further information on Liebherr Connect  
and digital solutions can be found here:



### MyLiebherr Portal

MyLiebherr is the portal for construction machines, mining machines, mobile and crawler cranes, maritime cranes, material handling technology, gear technology and automation systems or components.


### One portal, all services

The customer portal offers comprehensive services, digital services and software solutions for efficient machine utilisation. Once registered, machines can be stored and managed, suitable spare parts can be ordered and licences can be purchased. In addition, a wide range of digital services are available for efficient machine utilisation. The range is constantly being revised and updated.



### MyLiebherr Performance


Always be well informed about the performance of your machines and attachments. MyLiebherr Performance is available for earthmoving and material handling machines in MyLiebherr. It enables plant managers in particular to recognise inefficient machine use, save fuel and reduce idle times. In combination with our extensive knowledge as a machine manufacturer, this solution can be used to reduce operating costs by means of optimisation suggestions to make machine deployment more efficient.



### MyLiebherr Maintenance

Stay up-to-date about the condition of your machines and attachments. MyLiebherr Maintenance is available for earthmoving and material handling machines in MyLiebherr. This service enables workshop managers to operate their fleet with maximum reliability. A particular advantage is that, in addition to proactive maintenance planning, specific recommendations for action are also provided. Customers benefit from the knowledge of an integrated technology group with expertise ranging from components to the entire machine. In short, MyLiebherr Maintenance helps to reduce or completely avoid unplanned machine downtime and reduce the time required for problem identification, assessment and resolution.

# The Liebherr Group



## Global and independent: more than 75 years of success

Liebherr was founded in 1949 when, with the development of the world's first mobile tower crane, Hans Liebherr laid the foundations for a family-run company which now has more than 50,000 employees and comprises over 150 companies across every continent. The holding company of the Group is Liebherr-International AG in Bulle, Switzerland, whose shareholders are exclusively members of the Liebherr family.

## Technology leadership and pioneering spirit

Liebherr is a pioneer and its forward-looking approach has seen it make important contributions to technology history over a wide variety of industries. Employees throughout the world continue to share the courage of the company founder, sharing a passion to produce innovative products and a determination to provide world-leading equipment and machinery.

## Diversified product programme

Liebherr is one of the world's biggest construction machine manufacturers and provides high-quality, user-oriented products and services. Its product range includes the product segments earthmoving, material handling, deep foundation, mining, mobile and crawler cranes, tower cranes, concrete technology, maritime cranes, aerospace and transportation systems, gear technology and automation systems, refrigerators and freezers, components and hotels.

## Customised solutions and maximum customer value

Liebherr solutions are characterised by precision, implementation and longevity. The company is committed to technological excellence and to providing customers with solutions that match their needs exactly. For Liebherr, customer focus does not end with delivery of a product but continues through a comprehensive range of back-up and support services.

[www.liebherr.com](http://www.liebherr.com)

**Liebherr-Hydraulikbagger GmbH**  
Liebherrstraße 12  
D-88457 Kirchdorf/Iller  
Tel. +49 7354 80-0  
Fax +49 7354 80-7294  
info.lhb@liebherr.com

**Liebherr-Werk Bischofshofen GmbH**  
Postfach 49  
A-5500 Bischofshofen  
Tel. +43 50809 1-0  
Fax +43 50809 11385  
info.lbh@liebherr.com

**Liebherr-Werk Telfs GmbH**  
Hans Liebherr-Straße 35  
A-6410 Telfs  
Tel. +43 50809 6-100  
Fax +43 50809 6-7772  
lwt.marketing@liebherr.com