


# D976 engine for the power generation industry

---



Designed and manufactured by Liebherr, the D976 is a benchmark combustion engine engineered for mission critical power generation applications, particularly well-suited for PRP and COP operations while also supporting standby power requirements in stationary and mobile installations, including rental fleets and data centers. Built on a robust platform and backed by Liebherr's proven engineering expertise, this 6 cylinder, 18 litre engine delivers up to 820 kW, offering outstanding flexibility across PRP and COP duty cycles, covering both constant and variable load profiles over extended running hours. Combining high engine efficiency with optimised fuel consumption and controlled emissions performance, the D976 is designed to deliver reliable and cost effective power generation across demanding PRP and COP operating profiles. Extended service intervals, simplified maintenance and the advanced LiDIA diagnostic tool maximise reliability, minimise downtime and secure long term asset value.

## System benefits for power generation packager


- Optimising package design with best in class power density and a benchmark kW per square metre footprint, enabling compact and competitive genset solutions.
- Simplifying system integration through a compact engine architecture and an industry leading power to weight ratio (kW/kg), supporting both mobile and stationary installations.
- Securing grid compliant operation across PRP and COP duty cycles with outstanding dynamic response under demanding load profiles (ISO 8528 5 G3 compliant).
- Enhancing system competitiveness through best in class engine efficiency and optimised fuel consumption, delivering an excellent euro per kW positioning in PRP and COP applications.
- Maximising long term asset value with extended service intervals, durable lifetime performance and advanced diagnostics supporting high availability.

# LIEBHERR

# Product features and technical data

## D976

Country of manufacture	Switzerland	
Configuration	6 cylinders in-line	
Aspiration	Turbocharger	
Fuel injection control system	High-Pressure Common Rail	
Bore	mm (in)	148 (5.8)
Stroke	mm (in)	174 (6.9)
Displacement	L (in <sup>3</sup> )	18 (1,098.4)
Compression ratio	16.5:1	
Coolant capacity	L (US gal)	39.5 (10.3)
Lubricant capacity	L (US gal)	97 (25.6)
Estimated dry weight	kg (lbs)	1,830 (4,034)



## Power ratings

### 50 Hz

#### Tier 0

COP			PRP			ESP		
kWm	kWe	kVA	kWm	kWe	kVA	kWm	kWe	kVA
538	511	639	645	613	766	710	667	834

#### Tier 4f / Stage V

In development
----------------

### 60 Hz

#### Tier 0

COP			PRP			ESP		
kWm	kWe	kVA	kWm	kWe	kVA	kWm	kWe	kVA
621	590	737	745	708	885	820	779	974

#### Tier 2

			820	779	974
--	--	--	-----	-----	-----

#### Tier 4f / Stage V

In development
----------------

#### Generator efficiency (typical): 95%

kWm = kiloWatt mechanical, net with fan\*; kWe = kiloWatt electrical = kWm x Generator eff.; kVA = kiloVoltAmpere calculations based on a 0.8 power factor = kWe / 0.8 1 kW = 1 hp x 1.36; 1 hp = 1 kW x 0.7355

#### Power standards

The engine performance corresponds to ISO 3046, BS 5514 and DIN 6271. The technical data applies to an engine without cooling fan and operating on a fuel with a calorific value of 42.7 MJ/kg (18360 BTU/lb) and a density of 0.84 kg/liter (7.01 lb/US gal), also where this involves a deviation from the standards. Ratings are based on ISO 8528. Engine speed governance in accordance with ISO 8528-5 G3.

## Fuel consumption

### 50 Hz g/kWh (L/h)

#### Tier 0

Load	COP	PRP	ESP
100%	182 (117)	184 (141)	186 (157)
75%	184 (88)	183 (105)	182 (115)
50%	190 (61)	187 (72)	185 (78)
25%	211 (34)	204 (39)	200 (42)

### 60 Hz g/kWh (gall/h)

#### Tier 0

Tier 0			Tier 2
COP	PRP	ESP	ESP
186 (36.3)	189 (44.3)	191 (47.2)	194 (50.0)
188 (27.5)	187 (32.9)	186 (34.4)	208 (40.2)
186 (19.1)	192 (22.5)	191 (23.6)	212 (27.3)
221 (10.8)	212 (12.4)	210 (13.0)	218 (14.1)

Tolerances on nominal specific fuel consumption declaration are valid for Diesel fuel fulfilling standard EN 590. Fuel density: 840 gr/L

## Heat rejection

### 50Hz kW (BTU/min)

#### Tier 0

Heat rejection	COP	PRP	ESP
Charge air cooler	97 (5,516)	133 (7,564)	165 (9,384)
Exhaust	362 (20,587)	470 (26,729)	494 (28,065)
Coolant	235 (13,364)	277 (15,753)	284 (16,151)

### 60Hz kW (BTU/min)

#### Tier 0

Tier 0			Tier 2
COP	PRP	ESP	ESP
133 (7,581)	177 (10,055)	193 (10,987)	208 (11,840)
467 (26,570)	555 (31,580)	584 (33,212)	632 (35,942)
225 (12,784)	243 (13,814)	247 (14,047)	261 (14,843)

## Inlet air

### 50 Hz

Tier 0			
Inlet air	COP	PRP	ESP
Combustion air inlet flow kg/h (lb/h)	2,270 (5,004)	2,782 (6,133)	2,920 (6,437)
Max. Allowable Combustion Air inlet temp, °C (°F)	60 (140)	60 (140)	60 (140)

### 60 Hz

Tier 0			Tier 2
COP	PRP	ESP	ESP
2,922 (6,441)	3,450 (7,605)	3,762 (8,293)	3,773 (8,318)
60 (140)	60 (140)	60 (140)	60 (140)

## Exhaust system

### 50Hz

Tier 0			
Exhaust system	COP	PRP	ESP
Exhaust stack gas temperature °C (°F)	496 (924)	513 (955)	493 (920)
Exhaust gas flow rate, kg/h (lb/h)	2,369 (5,222)	2,782 (6,133)	3,054 (6,732)

### 60Hz

Tier 0			Tier 2
COP	PRP	ESP	ESP
484 (903)	493 (919)	501 (933)	512 (953)
3,039 (6699)	3,592 (7,919)	3,769 (8,309)	3,939 (8,684)

# Product specifications and options

## Product specifications

Twin-scroll turbocharger

Integrated closed crankcase ventilation system (maintenance-free)

Liebherr Engine Control Unit

Liebherr high-performance injection system (2000 bar)

Hydraulic valve adjuster (maintenance free)

Hydrogenated vegetable oil (HVO) compatible

## Options

Air compressor

Cold start (-25 °C)

Remote oil filter

Coolant inlet & outlet (90° elbow)

Oil pan (flat or deep)

Remote fuel filter

Generator 24 V (140 or 180 A)

A/C compressor upon request

Flywheel housing SAE1 & SAE0

Oil level sensor

Fan drive

2x Power Take-Off

LiDIA diagnostic tool

## Rating Definition Powergen

### Ratings definition in accordance with ISO 8528 and ISO 3046

**CONTINUOUS POWER (COP)** refers to the maximum power output that a diesel engine can deliver continuously under constant load and rated speed for an unlimited number of hours per year, under standard operating conditions. This rating assumes regular maintenance and compliance with the manufacturer's specifications.


**PRIME POWER (PRP)** refers to the maximum power that a diesel engine can supply for an unlimited number of hours per year under variable load conditions. Unlike continuous power, PRP allows for load fluctuations, but the engine must not be overloaded beyond its specified limit (a 10% overload capability for governing purposes is available for this rating).

**STAND-BY POWER (ESP)** is the maximum power a diesel engine can supply during a power outage or emergency situation. It is intended for use only when the main power source fails and is limited to a maximum of 200 hours per year depending on the standard. No overload capability is permitted, and it is not designed for continuous or variable load operation.

**DATA CENTRE POWER** refers to the total electrical capacity required to operate all systems within a data center, including IT equipment, cooling infrastructure, power distribution and facility support. It must ensure continuous, reliable power delivery with redundancy and backup systems to maintain uptime.

# D976 engine for the power generation industry

---



**Want to know more ?**  
Scan to discover our full portfolio

