

Freshness technologies
Freshness technologies

Tasty for longer.

You don't compromise when you're shopping. You look for natural ingredients, the best quality and maximum freshness. Of course, anyone who values good food wants to keep it fresh for as long as possible. That is precisely why we have developed innovative freshness technologies and improve them year after year, so your food still tastes fresh after some time in the refrigerator.





EasyFresh. Ideal for fruit and vegetables.

Unpackaged fruit and vegetables feel right at home here. Stored at the same temperature as the fridge compartment and sealed airtight in the safe, lettuce, for example, is still crisp and fresh after 7 days.



BioFresh. Our all-rounder.

The reliable BioFresh technology stores groceries at a temperature just above 0 °C, much cooler than in the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable Safe. Meat, fish and dairy products can enjoy ideal conditions in the Meat & Dairy Safe.



BioFresh Professional with HydroBreeze. Refrigerate like the professionals.

A cold mist that covers fruit and vegetables like a protective balm. It ensures crisp freshness and improves structure - the special wow effect for fruit and vegetables in the BioFresh Professional Safe.



BioFresh Professional with Fish & Seafood Safe. Like freshly caught fish from the market.

Particularly delicate foods like fish and seafood are best stored in icy temperatures and at low humidity. The constant temperature of -2 $^{\circ}$ C in the Fish & Seafood Safe is therefore ideal to keep items tasting fresh for longer.



DuoCooling. No drying out.

Our basic technology in selected models. The two completely separate refrigeration circuits ensure that there is no air exchange between the fridge and freezer compartments. Groceries do not dry out or spread odour.



$\label{eq:NoFrost.Nomore defrosting.} \ensuremath{\mathsf{NoFrost}}. \ensuremath{\mathsf{No more defrosting}}.$

The automatic defrosting function guarantees that frozen foods remain fresh. There is no longer a need to store frozen food temporarily during manual defrosting. The constant optimal freezing remains the same without interruptions.



Even the smallest detail deserves the utmost attention.

We prioritise uncompromising quality – down to the tiniest screw. And we have done so from the very start. We have been manufacturing high-quality refrigerators and freezers and selling them worldwide since 1954. However, at heart we are still a family business with deep roots in Germany. It is here that we continue to develop all our products just as before. German engineering – out of loyalty to our founder and with the knowledge built up by generations of engineers.

Convenience for everybody.

Our new freestanding units are available in different series: Pure, Plus, Prime and Peak. But whatever series you opt for, every single Liebherr comes with uncompromising Liebherr quality. This is because even in the Pure series, every appliance comes with a wide range of features. One example is NoFrost – the automatic defrosting function. Another is our EasyFresh technology for storing fruit and vegetables. Then there is our DuoCooling feature. With two separate refrigerant circuits, it ensures that no air is exchanged between the fridge and freezer compartments. The stored groceries do not dry out and no odours are transferred.







Built to last.

You can experience our quality standards in the smallest of details. For example, before a door hinge is approved by us, it must pass through at least 100,000 opening cycles. This corresponds to a usage period of more than 15 years. We also test all other functional parts to ensure that they can last just as long.

And if, contrary to expectations, a small detail no longer meets your requirements, you or our premium service partners can usually correct it quickly. Because all our appliances are extremely repair-friendly. We keep all essential spare parts in stock for well over 10 years. This practice is not just sustainable, it also saves you money on minor repairs or the purchase of a new appliance.

We don't just say it. We also guarantee it.

During manufacturing we inspect all components of our refrigerators with great care and test them far more rigorously than required by law – and we do this for the last time just before they are packaged. It is only then that our appliances can relax a little. All of our manufacturing sites are certified in accordance with the international standards for quality ISO 9001, energy management ISO 50001 and environmental management ISO 14001. Therefore, nothing could be easier for us than to guarantee for at least two years that our products are free of material and manufacturing faults and are particularly easy to install.

Selected appliances have the extended guarantee promotion to 5 or 10 years - T&C's apply, and maybe subject to change or seasonal promotions. Selected fridge-freezers appliances come with a 10-year guarantee. And our core models come with a 5-year guarantee. Subject to terms, conditions and registration.

In short: one thing is certain – you will be able to enjoy your Liebherr for a long time.





6

Our path to the future.

Sustainability

People and sustainable business

Respect for human rights is of the utmost importance to us. We attach great importance to treating everyone equally and ensuring the health, safety and personal development of our employees. We also want to make a positive contribution to our communities.

Recycling

economy in the long term and actively design our products to maximise the re-use of the materials in them by making them easy to separate.

One thing unites all our product innovations: they all present a path towards greater sustainability. Taking responsibility is one of our core values. That's why we have a decades-long tradition of research and development into eco-friendly products, with the entire product lifecycle in mind.

What is more, we emphasise responsible and economical practices, including long-term financial planning and self-financing. Fairness towards other market participants, compliance with laws and internal standards and codes of conduct are an integral part of our approach.

Materials

We want to reduce the environmental impact of our business activities and are preparing recyclable products by increasing the use of renewable materials and recycled materials in our appliances and reducing the variety of materials we use. In doing so, we look at the entire product.

Product responsibility

Georgians

Use

We reduce our environmental impact by continuing to offer first-class, energy-efficient products that are extremely long-lasting and easy to repair – supported by forward-looking customer service. We also offer products and solutions that help to reduce food waste.

More on this on the following pages.

Production

We want to produce in an environmentally conscious manner by reducing the energy requirements of our plants and increasingly utilising renewable energy sources. By using water responsibly, minimising waste and avoiding pollution, we reduce our environmental impact above and beyond CO, emissions

Efficient, more efficient, Liebherr.

This year's range once again has a great many appliances with the best energy efficiency classes on the market – and that is true for all our product groups: fridges, freezers and fridge-freezers from the new generation of freestanding units.

But of course there are plenty of other details, some very minor, that make a significant difference to a Liebherr in terms of efficiency. The four energy-saving modes, for example. Like EnergySaver, which increases the standard temperature to +7 °C. Or HolidayMode, which cools only the essentials while you are on holiday. Then there is CleaningMode, which saves energy while you clean your appliance.

Quality that has an impact on the climate.

We work exclusively with long-life vacuum panels and natural refrigerants, and we will use absolutely no HFO propellants until their environmental effects are fully understood. We also bear the environment in mind during production. Mostly we install materials that can be recycled after the appliance is scrapped. We also ensure that excess plastic is consistently reused.



Performance in balance

Perfectly thought out: a powerful, complete package.

Our fridges are real all-rounders. Along with their low power consumption, they also have impressively low noise levels, plenty of space for groceries, a long service life and reliable power reserves for when it really matters. We take account of a great many factors during the development stage and can offer a perfectly balanced appliance. Or to put it another way: all good things come in fours.





Our new freestanding units occupy top positions in the efficiency rankings. In this way, they protect the precious resources of our environment and – thanks to low electricity costs – your wallet too.



We have the perfect appliance for all family sizes, lifestyles and niche heights. We make sure that we do not waste a single litre of capacity in the extra-large drawers – right down to the smallest detail, for example with the lighting solutions that have been integrated in the housing to save space.




Noise level

The boundaries between the kitchen and living areas are becoming ever more blurred in modern households. This underlines the importance of particularly quiet appliances. Our new freestanding range therefore offers a wide selection of extremely quiet appliances. In some cases, it even reaches the ultra-quiet noise level of 29 db.



High efficiency: This is how economical a Liebherr can be

You can find out how efficient our appliances are using the online tool from the EU-financed projects LABEL2020 and BELT. At this site (tool.label2020.eu) you can view and compare the electricity consumption and lots of other product data for electrical appliances. The calculator also takes account of local electricity prices and shows the costs for the entire period of use. The comparison shows that a Liebherr is worth it!




Intelligent sensor technology constantly adapts the cooling performance to current use, making our freestanding units very energy-efficient and economical in everyday use. At the same time they also have plenty of power in reserve, for example to cool down a large quantity of groceries after the weekly shop.



Performance in balance perfected: Our BluPerformance technology

What is innovative about our BluPerformance models? We have integrated all of the refrigeration technology in the appliance base. As a result, the appliances of the same size have a considerably greater net capacity. So you have noticeably more space for your food and drink. In addition, we were able to further improve energy efficiency thanks to improved ventilation and extraction in the base. And our appliances are now even quieter. We are certain that this technology will appeal not only to fans of new technology but also to those who value greater storage capacity, energy efficiency, and quiet operation.

The current EU energy label for electronic appliances



- The QR code for identifying the product in the EU's EPREL database (European Product Database for Energy Labelling).
- The model identifier for manual identification of the product in the EU's EPREL database, e.g. using the article number.
- The new A to G efficiency scale. Note: G is solely used for wine cabinets.
- The total volume * of all freezer compartments.
- 5. The total volume * of all cold storage and refrigerator compartments.
- 6. The noise level is now classified in classes A to D.

10 11

^{*} The term "volume" is defined in current Regulation (EU) 2019/2016.

Side-by-Side fridge-freezer Side-by-Side fridge-freezer



BlackSteel interior

Refine your dark kitchen with our BlackSteel interior appliances. The rear wall and inner door impress with surfaces made of black stainless steel. The anti-fingerprint finish makes this resistant to fingerprints. All trims are accentuated in BlackSteel to complete a dark appearance. A Liebherr with BlackSteel interior perfectly fits into modern dark kitchens and stands out with elegance.



BioFresh with HydroBreeze

Do you want to cool fruit and vegetables like professionals? You'll be inspired by HydroBreeze. The cold mist combined with a temperature in the safe of around 0 °C gives food that extra a boost for longer shelf life. And it creates a genuine visual wow effect. HydroBreeze is activated every 90 min. for 4 seconds and for 8 seconds when the door is opened.





12

SFNbsd 529i	
Energy efficiency class:	D A 1
Energy consumption year / 24 hrs:	199 / 0.545 kWh ¹
Total volume ² :	277 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door/side walls:	BlackSteel / BlackSteel
Exterior dimensions in cm (h/w/d):	185.5 / 59.7 / 67.5 ¹

No Frost	Super Frost	LED	Ice Tower	Soft System	Telescopic Rails	Super Silent	Touch & Swipe Display	Space Box
Vario Space	Easy Open	Smart Device						

SRBbsc 529i

Energy efficiency class:	C Â
Energy consumption year / 24 hrs:	108 / 0.295 kWh ¹
Total volume ² :	3861
Volume:	Fridge: 246.2 l / BioFresh compartment: 140.6 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door/side walls:	BlackSteel / BlackSteel
Exterior dimensions in cm (h/w/d):	185.5 / 59.7 / 67.5 ¹

Door/sid	de walls:		BlackSteel / BlackS					
Exterior dimensions in cm (h/w/d):							185.5/5	9.7 / 67.5
Bio Fresh Professional	Hydro Breeze	Super Cool	Glass & Steel Interior	Light Tower	Infinity Spring	Soft System	Soft- Telescopic Rails	Super Silent
Touch & Swipe Display	Smart Device							



Enough ice for even the largest party: the IceTower

The IceTower in our freezers sets new standards. It combines two large compartments: the automatic IceMaker for up to 8 kilograms of ice cubes, and another spacious compartment large enough to store a few family pizzas upright, for example. And because this was not convenient enough for us, both of them glide in and out on a pull-out shelf with telescopic rails. We have even included an ice scoop, so your hands stay warm.



Bottle shelf above the BioFresh Safe

Expecting guests and want to chill a few more drinks than usual? The bottle shelf above the BioFresh Safes exists for this very reason. Simply remove the glass shelf above the bottle shelf in one easy step - and you can now safely store and cool bottles of various sizes.





SFNsfd 5247 Energy efficiency class: 199 / 0.545 kWh 1 Energy consumption year / 24 hrs: Total volume 2: 277 l 36 dB(A)/C Noise output / noise class: Climate rating: SN-T (from +10 °C to +43 °C) Door / side walls: SteelFinish/silver 185.5 / 59.7 / 67.5 1 Exterior dimensions in cm (h/w/d):









and refrigeration compartments to one place after the decimal point.







You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.







2 in accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments

SRBsfc 5220

Energy efficiency class:	$\begin{bmatrix} C & A \\ f \end{bmatrix}^1$
Energy consumption year / 24 hrs:	101 / 0.276 kWh ¹
Total volume ² :	382 l
Volume:	Fridge: 288.7 l / BioFresh compartment: 93.7 l
Noise output/noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door/side walls:	SteelFinish/silver
Exterior dimensions in cm (h/w/d):	185.5 / 59.7 / 67.5 ¹



←121→

←123→

Side-by-Side fridge-freezer Side-by-Side fridge-freezer



VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



VarioSafe

Do you want a clearly arranged place for small food items such as yoghurt pots, jam jars or tubes? Your Liebherr provides this with the VarioSafe. It not only creates order, but is also highly adaptable. Simply place the two-stage height-adjustable VarioSafe in the refrigerator where it suits you best.



SRsfd 5220

Total volume 2:

Climate rating:

Door / side walls:

Energy efficiency class:

Noise output / noise class:

Energy consumption year / 24 hrs:

Exterior dimensions in cm (h/w/d):

SFNsfd 5247	
Energy efficiency class:	D A 1
Energy consumption year / 24 hrs:	199 / 0.545 kWh ¹
Total volume ² :	277 l
Noise output/noise class:	36 dB(A)/C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door/side walls:	SteelFinish/silver
Exterior dimensions in cm (h/w/d):	185.5 / 59.7 / 67.5 ¹



14



















←123→

DA

399 l

98 / 0.268 kWh 1

SteelFinish / silver

185.5 / 59.7 / 67.5 1

35 dB(A) / B, SuperSilent

SN-T (from +10 °C to +43 °C)



SpaceBox

Accommodate the "big stuff" in your Liebherr: An XL turkey or a multi-layered ice cream cake simply needs more space. Your Liebherr has the SpaceBox for exactly that purpose: At a generous height of 250 mm, it offers lots of extra space, even for large frozen goods. Helpful for you when storing food flexibly.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.





SFNsfd 5227

Energy efficiency class: 199 / 0.545 kWh 1 Energy consumption year / 24 hrs: Total volume 2: 277 l 36 dB(A)/C Noise output / noise class: Climate rating: SN-T (from +10 °C to +43 °C) Designed to operate in ambient temperatures as low as -15 °C Door/side walls: SteelFinish/silver Exterior dimensions in cm (h/w/d): 185.5 / 59.7 / 67.5 1









and refrigeration compartments to one place after the decimal point.



You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.

SRsfd 5220

Energy efficiency class:	D A T
Energy consumption year / 24 hrs:	98 / 0.268 kWh ¹
Total volume ² :	399 l
Noise output/noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door/side walls:	SteelFinish/silver
Exterior dimensions in cm (h/w/d):	185.5 / 59.7 / 67.5 ¹



2 in accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments

←123→





BioFresh drawers

Both BioFresh drawers are mounted on telescopic rails which extend effortlessly providing easy access to and a full view of your food. The lateral LED lights ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



IceMaker

The IceMaker with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated water filter ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The NoFrost technology keeps the freezer constantly frost-free.



CBNste 8872

Energy ef	ficiency class:	E
Energy co	onsumption year / 24 hrs:	328 / 0.898 kWl
Total volu	ıme¹:	522
Volume:	Fridge: 292.2 l / BioFresh compa	rtment: 70.6 l / Freezer compartment: 160
Noise out	put/noise class:	42 dB(A) / [
Climate ra	ating:	SN-T (from +10 °C to +43 °C
Door/sid	le walls:	Stainless steel / stainless stee
Exterior d	limensions in cm (h/w/d):	202.7/91/62.

Bio Cooling No Super Cool Super First Tower Light Ice Door System System

Fridge-freezer Fridge-freezers



VarioTemp

VarioTemp means you have plenty of scope when storing food in your fridge freezer. This is because you can also set the accurate temperature in the freezer compartment in a range between -2 °C and +14 °C - and therefore also use this compartment as a further cooling zone. For example, it can be used over the short term for drinks and snacks at parties – or over the long term as a cellar compartment for storing potatoes.



EasyTwist-Ice

18

Whether it's a summer day or a party: Thanks to EasyTwist-Ice, you can prepare a supply of ice cubes quickly and easily – without the need for a fixed water connection. Simply fill the tank with water, let it freeze and then release the finished ice cubes with a simple twist – and you're ready to serve cool drinks. The EasyTwist-Ice is easy to clean and ensures hygienic ice cube production at all times.





←75→



CBNsdc 765i

Energy et	orgy efficiency class:				$\left(\begin{array}{c} A \\ C \end{array} \right)^{1}$			
Energy co	onsumptio	n year/2	24 hrs:				189/0	.517 kWh 1
Total volu	ume²:							423 l
Volume:	Fridge	216.3 l/	BioFresh o	compartm	ent: 68.7	l / Freezer	comparti	ment: 138 l
Noise ou	tput/nois	e class:				34 dB	(A)/B,S	uperSilent
Climate r	ating:			SN-T (fro	m +10°C	to +43°C)		
Door/side walls:							SmartSt	eel/silver
Exterior of	dimension	s in cm (h	n/w/d):				185.5 / 7	74.7 / 67.5 ¹
Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Glass & Steel Interior	Light Tower	Easy Twist Ice
Soft System	Soft- Telescopic Rails	Super Silent	Touch & Swipe Display	Vario Space	Smart Device			



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.





←60→



CNsda 5723

Energy efficiency class:				A A	
Energy consumption year / 24 hrs:				104/0.	284 kWh ¹
Total volume ² :					371 l
Volume:	Frid	ge: 267.9	l / Freezer	compartn	nent: 103 l
Noise output / noise class:			34 dE	B(A) / B, Su	uperSilent
Climate rating:			SN-T (fr	om +10°C	to +43°C)
Door/side walls:				SmartSte	eel/silver
Exterior dimensions in cm (h/w/d):				201.5/5	9.7 / 67.5 1
Easy Duo No Super	Super	Easy	Super	Touch	Vario
Fresh Cooling Frost Cool	Frost	Twist Ice	Silent	Display	Space





Replaceable door seal

Do you think the door seal on your Liebherr needs to be replaced after a few years? This is very easy to do yourself. The replaceable door seal can be removed in a few simple steps - and the new seal is just as easy to insert. As a result, this part of the refrigerator is always spotless and hygienically clean.





CNsfd 5203

Energy efficiency class:	D
Energy consumption year / 24 hrs:	201/0.550 kWh ¹
Total volume 2:	330 l
Volume:	Fridge: 227.1 l / Freezer compartment: 103 l
Noise output/noise class:	35 dB(A)/B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door/side walls:	SteelFinish/silver
Exterior dimensions in cm (h/w/d):	185.5 / 59.7 / 67.5 ¹





















←60→



1 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used.

These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

2 in accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.





Bottle shelf

The bottle shelf is the practical and elegant answer for storing drinks. As many as five bottles can be chilled and stored neatly.




LED light

The space-saving integrated LED light ensures that the whole interior of the refrigerator is evenly and harmoniously lit. With its low energy consumption, the long-lasting LED light is an environmentally friendly solution for a perfect overview of the food in the fridge.



CUele 2831









←55→

CUe 2831

Energy efficiency class:	E Å 1
Energy consumption year / 24 hrs:	192 / 0.526 kWh ¹
Total volume 2:	265 l
Volume:	Fridge: 212.4 l / Freezer compartment: 54 l
Noise output/noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door/side walls:	white/white
Exterior dimensions in cm (h/w/d):	161.2/55/63¹



¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments

and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.

Fridge and under counter fridge



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresher for longer.



TouchControl

A gentle finger tap and you set your Liebherr to 3, 5, 7 or 9°C with TouchControl. So simple - and efficient, as the sleek button is integrated into the interior, creating more space for all your fresh goods.



EasyOpen

Thanks to the new EasyOpen technology, our freezers can be opened smoothly and easily at any time. Even without a handle. How do we do it? With the help of an innovative door gasket and the new BluPerformance technology module, we have managed to reduce the door-opening force by half. Space-saving, simple, convenient.



Freezer and under counter freezer

SmartFrost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean. Freezer drawers and glass shelves made of safety glass can be removed easily.





←60→

←55→

90 / 0.246 kWh 1

white / white

85/55/60.71

35 dB(A)/B, SuperSilent SN-T (from +10 °C to +43 °C)

125 l

Re 1400

FNd	5026
P	lus

Energy efficiency class:	DA
Energy consumption year / 24 hrs:	188 / 0.515 kWh
Total volume ² :	238
Noise output/noise class:	36 dB(A)/0
Climate rating:	SN-T (from +10 °C to +43 °C
Designed to operate in ambient temperatures as low	v as -15°C
Door/side walls:	white/white
Exterior dimensions in cm (h/w/d):	165.5 / 59.7 / 67.5













←60→



Fe 1404

Energy efficiency class:	EAT
Energy consumption year / 24 hrs:	172 / 0.471 kWh ¹
Total volume ² :	107 l
Noise output/noise class:	37 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures as lo	ow as -15°C
Door/side walls:	white/white
Exterior dimensions in cm (h/w/d):	85/55/60.7 ¹





Rsfd 5220

Energy efficiency class:	
Energy consumption year / 24 hrs:	98 / 0.268 kWh ¹
Total volume ² :	399 l
Noise output/noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door/side walls:	SteelFinish/silver
Exterior dimensions in cm (h/w/d):	185.5 / 59.7 / 67.5 ¹











Energy efficiency class:

Noise output / noise class:

Total volume 2:

Climate rating: Door/side walls:


Energy consumption year / 24 hrs:

Exterior dimensions in cm (h/w/d):















BioFresh drawers

Both BioFresh drawers are mounted on telescopic rails which extend effortlessly providing easy access to and a full view of your food. The lateral LED lights ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



LED side lighting on both sides

For a quick overview of everything in the refrigerator: thanks to the LED side lighting on both sides, your food is in view at all times. The LEDs are positioned so that your large refrigerator is also illuminated with food inside it. And the LEDs integrated flush into the side walls mean that the valuable usable area is fully maintained.



ECBNe 8872

Fixed door / Built-in appliance for integrated use

Ene	ergy effi	ciency class:	E
Ene	ergy con	sumption year / 24 hrs:	339 / 0.928 kW
Tota	al volun	ne¹:	522
Volu	ume:	Fridge: 292.2 l / BioFresh compartme	ent: 70.6 l / Freezer compartment: 160
Nois	ise outp	ut/noise class:	39 dB(A)/
Clin	mate rat	ing:	SN-T (from +10 °C to +43 °C
Ane	erture di	mensions in cm (h / w / d).	203 2-207 2 / 91 5 / min 63



Fridge-freezers for integrated use Fridge-freezers for integrated use



XL fully integrated appliances for 194-cm recess

We are expanding our range of fully integrated fridge-freezers. Or, should we say, we're raising it. Our 194-cm-high XL fully integrated fridge-freezers fit seamlessly into high-quality kitchen designs and impress in every way: two BioFresh Safes, the highest energy efficiency in their class and a timeless, elegant design.



194

ICBNci 5663

Fixed door / Built-in appliance for integrated use

Fixed door / Built-in appliance for integrated use	;
Energy efficiency class:	C A
Energy consumption year / 24 hrs:	162/0.443 kWh
Total volume 1:	276 l
Volume: Fridge: 134 l / BioFresh compart	ment: 71.2 l / Freezer compartment: 71 l
Noise output/noise class:	33 dB(A)/B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h/w/d):	194-195 / 56-57 / min. 55
	Glass &



LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



178

ICBNdi 5163

		12	
Fixed door /	Built-in	appliance	for integrated use
i ixou uooi /	Duitt III	appliance	ioi iiitogiatoa at

Energy efficiency class:							DA	
Energy c	onsumptio	n year/2	24 hrs:				208/	0.569 kWh
Total vol	ume¹:							246 l
Volume:	Fridg	je: 104.1	l/BioFres	h compar	tment: 71. 2	2 l / Freeze	r compar	tment: 71 l
Noise ou	tput/nois	e class:				34 dB	(A)/B,S	uperSilent
Climate	rating:					SN-ST (fro	m +10 °C	to +38°C)
Aperture	dimensio	ns in cm	(h/w/d):			177.2-178	3.8 / 56-5	7 / min. 55
Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Glass & Steel Interior	Light Tower	Ice Maker
Soft System	Soft- Telescopic	Super Silent	Touch & Swipe	Vario Space	Smart Device			



Transparent FrostSafe drawers

All transparent FrostSafe drawers are extra deep. They are designed so that all frozen foods, from a duck to a boxed pizza, will fit conveniently and neatly, and are easy to remove. Every drawer can be used for both freezing and storage, so there's no need to repack the food once it has been frozen.



EasyFresh


The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.





178

ICBa 5123





178

ICNSe 5103

Sliding door / Ruilt-in appliance for integrated use

Energy efficiency class:	EA
Energy consumption year / 24 hrs:	227 / 0.621 kWh
Total volume¹:	253 l
Volume:	Fridge: 183.3 l / Freezer compartment: 70 l
Noise output/noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h/w/d):	177.2-178.8 / 56-57 / min. 55






















InfinitySpring

A source of fresh, cool drinking water in your kitchen. InfinitySpring sounds like something from a fairy tale. The water dispenser enables water dispensing and provides fresh, cold water. Simply press the panel with the carafe or glass, and enjoy the water. This enables you to save on purchasing bottles of water and to live more sustainably.




Door hinge exchange, integrated freezer compartment

Switch the doors' opening direction on your 4* freezer compartment quickly and easily: The clever slide control means this can be done in seconds and without any manual skills. Simply slide the control on the 4* freezer compartment right or left - that's it, done!



IRBci 5180

Fixed door / Built-in appliance for integrated use





















178

IRBbi 5151

Fixed door / Built-in appliance for integrated use

Energy efficie	ncy class:	$\left\{\begin{array}{c} \mathbf{B} \\ \mathbf{\hat{f}} \end{array}\right\}$
Energy consur	nption year / 24 hrs:	104/0.284 kWh
Total volume 1:		276 l
Volume:	ridge: 151.3 l / BioFresh compar	tment: 98.4 l / Freezer compartment: 27 l
Noise output/	noise class:	32 dB(A) / B, SuperSilent
Climate rating		SN-T (from +10 °C to +43 °C)
Aperture dime	nsions in cm (h/w/d):	177.2-178.8 / 56-57 / min. 55



















Fridges for integrated use Fridges for integrated use



VarioBoxes

The two detachable, fridge-to-table VarioBoxes are perfect for storing ready-to-serve foods in the refrigerator. The Liebherr egg tray for 12 eggs fits perfectly in the large VarioBox. The accessories set comprises of two VarioBoxes and a robust stainless steel securing rail. VarioBoxes can be securely attached to the door interior at various levels.



SoftSystem

The stylish white SoftSystem mechanism, integrated in the door, conveniently cushions door movement to ensure extremely soft closure even when the door shelves are fully loaded. The door closes automatically from an opening angle of about 30°.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan - as powerful as it is quiet - distributes the cold air efficiently throughout the entire refrigeration compartment.







IRBbi 5150

Fixed door / Built-in appliance for integrated use

B A
80 / 0.219 kWh
296 l
Fridge: 197.7 l / BioFresh compartment: 98.4 l
29 dB(A) / A, UltraSilent
SN-T (from +10 °C to +43 °C)
177.2-178.8 / 56-57 / min. 55

































IRBd 5120

Fixed door / Built-in appliance for integrated use

rixed door / balle in appliance for integ	idica doc
Energy efficiency class:	DA
Energy consumption year / 24 hrs:	125 / 0.342 kWh
Total volume 1:	294 l
Volume:	Fridge: 195.8 l / BioFresh compartment: 98.2 l
Noise output/noise class:	33 dB(A)/B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h/w/d):	177.2-178.8 / 56-57 / min. 55











IRe 5100

Fixed door / Built-in appliance for integrated use

Energy efficiency class:	E
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume 1:	308
Noise output/noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h/w/d):	177.2-178.8 / 56-57 / min. 55



140

IRd 4520

Fixed door / Built-in appliance for integrated use

Energy efficiency class:	D Å
Energy consumption year / 24 hrs:	84 / 0.230 kWh
Total volume 1:	235 l
Noise output/noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h/w/d):	139.7-141.3 / 56-57 / min. 55











Freezer for integrated use Freezers for integrated use



IceTower

You will never run out of cold drinks at your party. The IceTower, which holds 8 kg of ice cubes, makes sure of that. The ice cube scoop and the pull-out tray on telescopic rails allow easy access to the ice cubes. An extra insert tray means you can also store less ice and make room for frozen food underneath. The adjacent drawer provides storage space for frozen goods.



Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your freezer intuitively and with ease. Simply select functions such as SuperFrost on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? Well, it then shows you the actual temperature.



VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



SIFNdi 5188 Peak

178

Fixed door / Built-in appliance for integrated use

Energy ef	ficiency o	class:					D A G	
Energy co	nsumptio	on year/	24 hrs:			190/0	.520 kWh	
Total volu	ıme¹:							213 l
Noise out	put/nois	e class:				33 dE	B(A) / B, Su	perSilent
Climate rating:						SN-T (fro	om +10°C	to +43°C)
Aperture dimensions in cm (h/w/d):						177.2-178	8.8 / 56-57	/ min. 55
No Frost	Super Frost	LED	Ice Tower	Soft System	Telescopic Rails	Super Silent	Touch & Swipe Display	Vario Space



Freezer drawers

The top drawer in the freezer is often a bit of a mystery because you just can't see what's up there. A simple tilting function on the drawer allows it to be angled downwards when opened. This gives you a complete overview all the time. It also makes it easier to add and remove frozen goods. And the pull-out stop ensures the compartment does not fall out.



LED-lighting

The LED lighting is positioned above the drawers in order to save space. It ensures the best overview of your goods, saves energy and has a long life.



SIFNe 5108

Energy efficiency class:	E A † G
Energy consumption year / 24 hrs:	237 / 0.649 kWh
Total volume 1:	213 (
Noise output/noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h/w/d):	177.2-178.8 / 56-57 / min. 55



SIFNdi 4556

Fixed door / Built-in appliance for integrated use

Energy efficiency class:	D A
Energy consumption year / 24 hrs:	173 / 0.474 kWh
Total volume¹:	156 l
Noise output/noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h/w/d):	139.7-141.3 / 56-57 / min. 55











No Super Super Touch Vario Device Frost Frost Silent Display Space Ready

SuperSilent

The boundaries between the kitchen and living areas are becoming ever more blurred in modern households. This underlines the importance of particularly quiet appliances. The URPd 365i reach the ultra-quiet level of 32dB.



SmartDevice

With the SmartDeviceBox (pre-installed in "i" models), you can adjust your appliance's settings or view status messages using your smartphone and the SmartDevice app while on the go.



Pull-out trolley

There's no better way to see food than on smooth-running telescopic rails with self-closing and soft stop mechanisms. The two fully extendable glass pull-outs ensure that everything is stored safely and is optimally accessible.



Fruit and vegetable box/multi-purpose box

Store fresh products neatly and clearly in the practical fruit and vegetable box. There's lots of space in the multi-purpose box for small refrigerated goods. Transparent, spacious and easy to clean.



Under-worktop freezer for integrated use

VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



URPd 365i

Fully extendible pull-out drawer / Under-worktop appliance for integrated use

Energy efficiency class:	D A G
Energy consumption year / 24 hrs:	74 / 0.202 kWh
Total volume 1:	124 l
Noise output/noise class:	32 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h/w/d):	82-88/60/min.56















Fixed door / Under-worktop appliance for integrated use

D A
74 / 0.202 kWh
127 (
34 dB(A) / B, SuperSilent
SN-T (from +10 °C to +43 °C)
82-88 / 60 / min. 56













SUFNd 365i

Fixed door / Under-worktop appliance for integrated use

Energy efficiency class: 150 / 0.411 kWh Energy consumption year / 24 hrs: Total volume 1:

Noise output/noise class: 34 dB(A) / B, SuperSilent Climate rating: SN-T (from +10 °C to +43 °C) Aperture dimensions in cm (h/w/d): 82-88 / 60 / min. 56



82-88



















SommelierBoard

Bring elegance to your room, with the Sommelier-Board. This refined set presents all of your wine, glasses, decanter, and utensils in a sophisticated manner. Not only does it look amazing, but it also offers practicality with the integrated storage box and dedicated working surface for wine opening and serving.



LightTower

One of the most important - and most neglected design elements is light. Cleverly used, it can do wonders for setting the right mood, just like it does in our glass door appliances. Two vertical light columns illuminate your wine bottles like the pieces of art they are, every time you open the door, or all the time. The choice is yours – just like the light intensity.





←70 →

WPgbi 7483

Vinidor Selection

Energy 6	efficiency o	class:						F A c
Energy	consumptio	n year/2	4 hrs:				144/0.	394 kWh ²
Max. Bo	rdeaux bot	tles 0.75 l:						149 1
Total vo	lume³:							561 l
Noise or	utput/nois	e class:				35 dB	(A) / B, S	uperSilent
Climate	rating:					SN-ST (fro	m +10 °C	to +38°C)
Door/s	ide walls:			В	lack insu	lated glas	s door/E	BlackSteel
Exterior	dimension	s in cm (h	/w/d):				201.3/6	9.7 / 76.4 ²
3 Zones	Temp Protect Plus	Humidity Select	Fresh Air	UV Protect Plus	Flex Fit	Sommelier Board	Vibrate Safe	Steel Interior
				Touch &				



Presentation shelf

The presentation shelf is ideal for keeping open bottles at the perfect temperature and without the risk of spills.



Wooden shelves mounted on telescopic rails

38

The Vinidor appliances are equipped with solid wooden shelves mounted on telescopic rails. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. The clip-on labelling system provides a quick and clear overview of your wine store.

Door requires furniture or s/steel frame & handle kit - Order no. 9901573



178

EWTdf 3553

Vinidor

Insulated glass door / Built-in appliance with decor panel

Energy e	efficiency c	lass:						G Å
Energy o	consumptio	n year/	24 hrs:				162/0).443 kWh
Max. Bo	rdeaux bot	tles 0.75	l:					80¹
Total vol	lume ²:							259 l
Noise ou	utput/nois	e class:				32 d	B(A) / B, St	uperSilent
Climate	rating:					SN-ST (f	rom +10°C	to +38°C)
Door:	Ins	ulated g	lass door p	orepared t	or cabine	t door or	stainless s	steel front
Aperture	e dimensio	ns in cm	(h/w/d):			177.2	-178 / 56-57	7 / min. 55
2 Zones Super Silent	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Steel Interior	LED	Soft System	Telescopic Rails



Decor options

Decor panel-ready appliances can be fitted with a kitchen front to match the kitchen plan or (as a Liebherr accessory) with a stainless steel panel and separate handle options. It can even be handle-free with the TipOpen feature.



Touch & Swipe display

Perfect enjoyment is what our Vinidor selection wine tempering fridges are all about – which is why we designed every detail to support your moment of bliss. Like the Touch & Swipe colour display that lets you select functions intuitively by tapping and swiping and makes setting temperature almost as enjoyable as savouring the wine later on.

Door requires furniture or stainless steel frame & handle kit - 9904931





82-88

UWgbi 3682

Fixed door / Under-workton annliance

Energy efficiency class:	E f
Energy consumption year / 24 hrs:	83 / 0.227 kWh
Max. Bordeaux bottles 0.75 l:	321
Total volume ²:	95 l
Noise output/noise class:	32 dB(A) / B, SuperSilent
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door:	Black insulated glass door
Aperture dimensions in cm (h/w/d):	82-88/60/min. 58









UWpri 3662 Vinidor Selection

Fixed door / Under-worktop appliance for integrated use

incu door / orider worktop appliance for integrated disc	
inergy efficiency class:	Få
nergy consumption year / 24 hrs:	104/0.284 kWh
1ax. Bordeaux bottles 0.75 l:	32 ¹
otal volume ²:	92 l
Noise output/noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door:	Insulated glass door
perture dimensions in cm (h/w/d):	82-88 / 60 / min. 58
Tomo	

Temp Protect Plus Humidity Select Air

Touch & Swipe Display Lock Devi





Liebherr After Sales & Customer Care



2-Year Guarantee

All Liebherr appliances have a full 2-year guarantee, as standard, covering parts and labour. If any part of the machine fails or a fault develops through normal use, it will be repaired free of charge (Subject to registration and guarantee terms and conditions).



This guarantee is granted free of charge for qualifying appliances. With our manufacturer's guarantee, you will not incur any costs for repair and service for 10 years.

For more information, registration and guarantee conditions, go to: home.liebherr.com/guarantee

Customer must register and install appliance as per manufacturer's instructions.

Accidental damages and consumable accessories to parts are not covered.

For further information please go to: home.liebherr.com



Customer Care

Our National Customer Care Centre can be contacted should you require instructions or service.

Please call 01 4600064 or you can email liebherr@naa.ie.

Spare Parts Direct

To order spare parts or accessories please visit our website, call 01 4600064 or email liebherr@naa.ie with the model and 9 digit service number.

The parts or accessories can be quickly despatched direct to your home.

Liebherr's Killarney Hotels Ltd.



Ard na Sidhe Country House



Hotel Dunloe Castle



The Europe Hotel & Resort

Liebherr's Killarney Hotels Ltd. owns and operates two five-star luxury hotels in Killarney, including The Europe Hotel & Resort, situated on the famous Lakes of Killarney and Hotel Dunloe Castle overlooking the Gap of Dunloe. The company also owns and manages Ard na Sidhe Country House, a delightful Victorian style manor house, which is situated on the shores of Caragh Lake just outside Killorglin. The Liebherr Group has been active in Ireland since 1958, when Liebherr (Ireland) Ltd. was founded in Killarney, Co. Kerry. Initially, this company manufactured large tower cranes. During the following decades, Liebherr's portfolio in Ireland has been significantly enlarged. Today, the Liebherr Group comprises three Irish companies operating in the sectors of maritime cranes, construction machinery and hotels, which are employing a total workforce of about 1200 people.